

Revision Date: 21-Jul-2020

Revision Number: 8

1. PRODUCT AND COMPANY IDENTIFICATION

Product Name **Product Code** Alternate Product Code **Product Class** Color **Recommended use Restrictions on use**

AQUA LOCK PLUS 100% ACRYLIC PRIMER / SEALER WHITE AQ-0400

Category 1

XA0101 SURFACE PREPARATION PRODUCT White Primers No information available

Manufacturer

Benjamin Moore & Co. 101 Paragon Drive Montvale, NJ 07645 Phone: 1-866-708-9180 www.benjaminmoore.com/INSLX

Emergency Telephone CHEMTREC (US): 800-424-9300

CHEMTREC (outside US): (703)-527-3887

2. HAZARDS IDENTIFICATION

Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin sensitization

Label elements

Warning

Hazard statements May cause an allergic skin reaction



Odor little or no odor

Precautionary Statements - Prevention

Avoid breathing dust/fume/gas/mist/vapors/spray Contaminated work clothing should not be allowed out of the workplace Wear protective gloves

Skin

IF ON SKIN: Wash with plenty of soap and water If skin irritation or rash occurs: Get medical advice/attention Wash contaminated clothing before reuse

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not applicable

Other information

No information available

3. COMPOSITION INFORMATION ON COMPONENTS

Chemical name	CAS No.	Weight-%
Nepheline syenite	37244-96-5	20 - 25
Titanium dioxide	13463-67-7	10 - 15
Zinc oxide	1314-13-2	0.5 - 1
2-Amino-2-methly-1-propanol	124-68-5	0.1 - 0.5
Sodium C14-C16 olefin sulfonate	68439-57-6	0.1 - 0.5
Carbamic acid, butyl-, 3-iodo-2-propynyl ester	55406-53-6	0.1 - 0.5

4. FIRST AID MEASURES	
General Advice	No hazards which require special first aid measures.
Eye Contact	Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.
Skin Contact	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. If skin irritation persists, call a physician. Wash clothing before reuse. Destroy contaminated articles such as shoes.
Inhalation	Move to fresh air. If symptoms persist, call a physician.
Ingestion	Clean mouth with water and afterwards drink plenty of water. Consult a physician if necessary.
Most Important Symptoms/Effects	May cause allergic skin reaction.
Notes To Physician	Treat symptomatically.
	5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local

	circumstances and the surrounding environment.	
Protective equipment and precautions for firefighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.	
Specific Hazards Arising From The Chemical	Closed containers may rupture if exposed to fire or extreme heat.	
Sensitivity to mechanical impact	No	
Sensitivity to static discharge	No	
Flash Point Data Flash point (°F) Flash Point (°C) Method	Not applicable Not applicable Not applicable	
Flammability Limits In Air		
Lower flammability limit: Upper flammability limit:	Not applicable Not applicable	
NFPA Health: 1 Flammability: 0	Instability: 0 Special: Not Applicable	
NFPA Legend		

- 0 Not Hazardous
- 1 Slightly
- 2 Moderate
- 3 High
- 4 Severe

The ratings assigned are only suggested ratings, the contractor/employer has ultimate responsibilities for NFPA ratings where this system is used.

Additional information regarding the NFPA rating system is available from the National Fire Protection Agency (NFPA) at www.nfpa.org.

	6. ACCIDENTAL RELEASE MEASURES
Personal Precautions	Avoid contact with skin, eyes and clothing. Ensure adequate ventilation.
Other Information	Prevent further leakage or spillage if safe to do so.
Environmental precautions	See Section 12 for additional Ecological Information.
Methods for Cleaning Up	Soak up with inert absorbent material. Sweep up and shovel into suitable containers for disposal.
	7. HANDLING AND STORAGE

Handling	Avoid contact with skin, eyes and clothing. Avoid breathing vapors, spray mists or sanding dust. In case of insufficient ventilation, wear suitable respiratory equipment.
Storage	Keep container tightly closed. Keep out of the reach of children.

Incompatible Materials

No information available

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Limits

Chemical name	ACGIH TLV	OSHA PEL
Titanium dioxide	TWA: 10 mg/m ³	15 mg/m³ - TWA
Zinc oxide	STEL: 10 mg/m ³ respirable particulate	5 mg/m³ - TWA
	matter	15 mg/m ³ - TWA
	TWA: 2 mg/m ³ respirable particulate	-
	matter	

Legend

ACGIH - American Conference of Governmental Industrial Hygienists Exposure Limits OSHA - Occupational Safety & Health Administration Exposure Limits N/E - Not Established

Engineering Measures	Ensure adequate ventilation, especially in confined areas.	
Personal Protective Equipment		
Eye/Face Protection	Safety glasses with side-shields.	
Skin Protection	Protective gloves and impervious clothing.	
Respiratory Protection	In case of insufficient ventilation wear suitable respiratory equipment.	
Hygiene Measures	Avoid contact with skin, eyes and clothing. Remove and wash contaminated clothing before re-use. Wash thoroughly after handling.	

9. PHYSICAL AND CHEMICAL PROPERTIES

AQ-0400 - AQUA LOCK PLUS 100% ACRYLIC PRIMER / SEALER WHITE

Flash Point (°C) Method Flammability (solid, gas) Upper flammability limit: Lower flammability limit: Autoignition Temperature (°F) Autoignition Temperature (°C) Decomposition Temperature (°C) Partition coefficient

Not applicable Not applicable Not applicable Not applicable No information available No information available No information available No information available No information available

10. STABILITY AND REACTIVITY

Reactivity	Not Applicable
Chemical Stability	Stable under normal conditions.
Conditions to avoid	Prevent from freezing.
Incompatible Materials	No materials to be especially mentioned.
Hazardous Decomposition Products	None under normal use.
Possibility of hazardous reactions	None under normal conditions of use.

11. TOXICOLOGICAL INFORMATION

Product Information		
Information on likely routes of e	exposure	
Principal Routes of Exposure	Eye contact, skin contact and inhalation.	
Acute Toxicity		
Product Information	No information available	
Symptoms related to the physical, chemical and toxicological characteristics		
Symptoms	No information available	
Delayed and immediate effects as well as chronic effects from short and long-term exposure		
Eye contact Skin contact Inhalation Ingestion Sensitization Neurological Effects Mutagenic Effects Reproductive Effects Developmental Effects	May cause slight irritation. Substance may cause slight skin irritation. Prolonged or repeated contact may dry skin and cause irritation. May cause irritation of respiratory tract. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea. May cause an allergic skin reaction No information available. No information available. No information available. No information available.	

Target organ effects	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Other adverse effects	No information available.
Aspiration Hazard	No information available

Numerical measures of toxicity

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral)	98354 mg/kg
ATEmix (inhalation-dust/mist)	457.8 mg/L

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Titanium dioxide 13463-67-7	> 10000 mg/kg (Rat)	-	-
Zinc oxide 1314-13-2	> 5000 mg/kg (Rat)	-	-
2-Amino-2-methly-1-propanol 124-68-5	= 2900 mg/kg(Rat)	> 2000 mg/kg (Rabbit)	-
Sodium C14-C16 olefin sulfonate 68439-57-6	= 2220 mg/kg (Rat)	> 740 mg/kg (Rabbit)	-
Carbamic acid, butyl-, 3-iodo-2-propynyl ester 55406-53-6	= 1470 mg/kg (Rat)	> 2000 mg/kg (Rat)	= 0.67 mg/L (Rat) 4 h = 0.63 mg/L (Rat) 4 h = 0.99 mg/L (Rat) 4 h

Chronic Toxicity

Carcinogenicity

The information below indicates whether each agency has listed any ingredient as a carcinogen:.

Chemical name	IARC	NTP	OSHA
	2B - Possible Human		Listed
Titanium dioxide	Carcinogen		

• Although IARC has classified titanium dioxide as possibly carcinogenic to humans (2B), their summary concludes: "No significant exposure to titanium dioxide is thought to occur during the use of products in which titanium dioxide is bound to other materials, such as paint."

Legend

IARC - International Agency for Research on Cancer NTP - National Toxicity Program OSHA - Occupational Safety & Health Administration

12. ECOLOGICAL INFORMATION

Ecotoxicity Effects

The environmental impact of this product has not been fully investigated.

Product Information

Acute Toxicity to Fish

No information available

Acute Toxicity to Aquatic Invertebrates

No information available

Acute Toxicity to Aquatic Plants

No information available

Persistence / Degradability

No information available.

Bioaccumulation

No information available.

Mobility in Environmental Media

No information available.

Ozone

No information available

Component Information

Acute Toxicity to Fish

<u>Titanium dioxide</u> LC50: > 1000 mg/L (Fathead Minnow - 96 hr.) <u>Carbamic acid, butyl-, 3-iodo-2-propynyl ester</u> LC50: 230 µg/L (Bluegill sunfish - 96 hr.)

Acute Toxicity to Aquatic Invertebrates

No information available

Acute Toxicity to Aquatic Plants

No information available

	13. DISPOSAL CONSIDERATIONS
Waste Disposal Method	Dispose of in accordance with federal, state, and local regulations. Local requirements may vary, consult your sanitation department or state-designated environmental protection agency for more disposal options.
	14. TRANSPORT INFORMATION
DOT	Not regulated
ICAO / IATA	Not regulated
IMDG / IMO	Not regulated
	15. REGULATORY INFORMATION

International Inventories

TSCA: United States	Yes - All components are listed or exempt.
DSL: Canada	No - Not all of the components are listed.
	One or more component is listed on NDSL.

Federal Regulations

Acute health hazard	Yes
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

None

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product contains the following HAPs:

None

US State Regulations

California Proposition 65

MARNING: Cancer and Reproductive Harm– www.P65warnings.ca.gov

State Right-to-Know

Chemical name	Massachusetts	New Jersey	Pennsylvania
Titanium dioxide	X	X	Х
Carbamic acid, butyl-,		Х	
3-iodo-2-propynyl ester			

Legend

X - Listed

16. OTHER INFORMATION

HMIS - Health: 1 Flammability: 0 Reactivity: 0 PPE: -

HMIS Legend

0 - Minimal Hazard

1 - Slight Hazard

- 2 Moderate Hazard
- 3 Serious Hazard
- 4 Severe Hazard
- * Chronic Hazard

X - Consult your supervisor or S.O.P. for "Special" handling instructions.

Note: The PPE rating has intentionally been left blank. Choose appropriate PPE that will protect employees from the hazards the material will present under the actual normal conditions of use.

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings are not required on MSDSs under 29 CFR 1910.1200, the preparer, has chosen to provide them. HMIS® ratings are to be used only in conjunction with a fully implemented HMIS® program by workers who have received appropriate HMIS® training. HMIS® is a registered trade and service mark of the NPCA. HMIS® materials may be purchased exclusively from J. J. Keller (800) 327-6868.

WARNING! If you scrape, sand, or remove old paint, you may release lead dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS, SUCH AS BRAIN DAMAGE, ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH approved respirator to control lead exposure. Clean up carefully with a HEPA vacuum and a wet mop. Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to www.epa.gov/lead.

Prepared By	Product Stewardship Department Benjamin Moore & Co. 101 Paragon Drive Montvale, NJ 07645 800-225-5554
Revision Date:	21-Jul-2020
Revision Summary	Not available

Disclaimer

The information contained herein is presented in good faith and believed to be accurate as of the effective date shown above. This information is furnished without warranty of any kind. Employers should use this information only as a supplement to other information gathered by them and must make independent determination of suitability and completeness of information from all sources to assure proper use of these materials and the safety and health of employees. Any use of this data and information must be determined by the user to be in accordance with applicable federal, provincial, and local laws and regulations.

End of Safety Data Sheet