

A1500SP1 **User's Manual**

K01-0000897-00

What is AVR?

AVR MI

PRODUCT REGISTRATION

Thank you for purchasing a CyberPower product. Please take a few minutes to register your product in Registration section at CyberPowerSystems.com/registration. Registration certifies your product's warranty, confirms your ownership in the event of a product loss or theft and entitles you to free technical support. Register your product now to receive the benefits of CyberPower ownership.

IMPORTANT SAFETY INSTRUCTIONS

(SAVE THESE INSTRUCTIONS)

This Manual Contains Important Instructions that should be followed during Installation and Maintenance of the UPS and batteries

CAUTION! To prevent the risk of fire or electric shock, install in a temperature and humidity controlled indoor area free of conductive contaminants. (Please see specifications for acceptable temperature and humidity range).

CAUTION! To reduce the risk of electric shock, do not remove the cover except to service the battery. Turn off and unplug the unit before servicing the batteries. There are no user serviceable parts inside except for the battery.

CAUTION! Hazardous live parts inside can be energized by the battery even when the AC input power is disconnected.

CAUTION! The UPS must be connected to an AC power outlet with fuse or circuit breaker protection. Do not plug into an outlet that is not grounded. If you need to de-energize this equipment, turn off and unplug the unit

CAUTION! To avoid electric shock, turn off the unit and unplug it from the AC power source before servicing the battery.

CAUTION! Not for use in a computer room as defined in the Standard for the Protection of Electronic Computer/Data Processing Equipment, ANSI/NFPA 75.

CAUTION! To reduce the risk of fire, connect only to a circuit provided with 20 amperes maximum branch circuit over current protection in accordance with the National Electric Code, ANSI/NFPA 70.

DO NOT USE FOR MEDICAL OR LIFE SUPPORT EQUIPMENT! CyberPower Systems does not sell products for life support or medical applications. DO NOT use in any circumstance that would affect the operation and safety of life support equipment, medical applications, or patient care

DO NOT USE WITH OR NEAR AQUARIUMS! To reduce the risk of fire or electric shock, do not use with or near an aquarium. Condensation from the aquarium can cause the unit to short out

DO NOT USE THE UPS ON ANY TRANSPORTATION! To reduce the risk of fire or electric shock, do not use the unit on any transportation such as airplanes or ships. The effect of shock or vibration caused during transit and the damp environment can cause the unit to short out.

INSTALLING YOUR UPS SYSTEM

INTRODUCTION

Thank you for selecting a CyberPower Systems Uninterruptible Power Supply (UPS) product. This UPS is designed to provide unsurpassed powe protection, operation and performance during the lifetime of the product.

UNPACKING

Inspect the UPS upon receipt. The box should contain the following: (a) UPS (b) User's manual (c) USB A+B type cable (d) Function Setup Guide

OVERVIEW

The A1500SP1 provides complete power protection from utility power that is not always consistent.

The A1500SP1 features 1500 Joules of surge protection. The unit ensures consistent power to your sump pump and provides long lasting battery

backup during power outages with maintenance free batteries. **AUTOMATIC VOLTAGE REGULATOR**

The A1500SP1 stabilizes inconsistent utility power voltage to consistent and safe 110/120 volts without switching to battery backup power. This help to reserve the battery for when it's needed most during a

HARDWARE INSTALLATION GUIDE


1. Your new UPS may be used immediately upon receipt. However, after receiving a new UPS, to ensure the battery's maximum charge capacity, it is recommended that you charge the battery for at least 8 hours

Your UPS is equipped with an auto-charge feature. When the UPS is plugged into an AC outlet, the battery will automatically charge whether the

- 2. Note: This UPS is designed with a safety feature to keep the system from being turned on during shipment. The first time you turn the UPS on, you will need to have it connected to AC power or it will not power up.
- 3. Elevate the UPS at least 18 inches above the floor on a stable surface like a table or shelf
- 4. Ensure the wall outlet and UPS are located near the equipment being attached for proper accessibility.
- 5. With the UPS unit turned off and unplugged, connect your sump pump into the battery power supplied outlet closest to the top of the unit. This unit will work with sump pumps up to $^{1}/_{2}$ HP in size. DO NOT plug any additional equipment into the UPS, as any additional power demands
- 6. Plug the UPS into a 2 pole, 3 wire grounded receptacle (wall outlet). Make sure the wall branch outlet is protected by a fuse or circuit breaker and does not service equipment with large electrical demands (e.g. air conditioner, copier, etc...). The warranty prohibits the use of extension cords, outlet strips, and surge strips
- 7. Press the power switch to turn the unit on. The Power On indicator light will illuminate and the unit will "beep". If an overload is detected, an audible alarm will sound and the unit will emit one long beep. To correct this, turn the UPS off and ensure that the sump pump is no large than 1/2 HP in size and that no other devices are plugged into the unit. Make sure the circuit breaker is depressed and then turn the UPS on.
- 8. To maintain optimal battery charge, leave the UPS plugged into an AC outlet at all times.
- To store the UPS for an extended period, cover it and store with the battery fully charged. While in storage, recharge the battery every three months to ensure battery life.

BASIC OPERATION

DESCRIPTION



Power Switch

Used as the master on/off switch for equipment connected to the battery power supplied outlets. (Please refer to the Function Setup Guide for more information.)

- Power On Indicator
- This LED is illuminated when the utility power is normal and the UPS outlets are providing power, free of surges and spikes. LCD module display
- The LCD display shows all the UPS information using icons and messages. For more information please review the "Definitions for Illuminated
- 4. Display/Select Button

The button can be used to select the LCD display contents including Input Voltage, and output Voltage. Short press the button to scroll down the function menu. Pressing the button for 3 seconds will keep the LCD display always on or turn the LCD display off while in AC/Utility power mode. (Please refer to the Function Setup Guide for more information.)

Mute/Enter Button

Holding the button for more than 3 seconds will silence the alarm. Short press the ENTER button to confirm the setting. After the setting has peen confirmed, the LCD screen will stop flashing. (Please refer to the Function Setup Guide for more information.)

Battery and Surge Protected Outlets

The UPS has battery powered/surge suppression outlets for connected equipment to ensure temporary uninterrupted operation of your sump pump during a power failure. (DO NOT plug any additional devices into the "Battery and Surge Protected Outlets". The power demands of these devices may overload and damage the unit.)

7. Full-Time Surge Protection Outlets

The UPS has surge suppression outlets

8. Circuit Breaker

Located on the back of the UPS, the circuit breaker serves to provide overload and fault protection.

Serial/USB Ports to PC

The USB port allows connection and communication between the USB port on the computer and the UPS unit. 10. Communication Protection Ports

Communication protection ports, bi-directional, will protect a 10/100/1000 Ethernet connection (RJ45).

11. Wiring Fault Indicator (red)

This LED indicator will illuminate to warn the user that a wiring problem exists, such as bad ground, missing ground or reversed wiring. If this is illuminated, disconnect all electrical equipment from the outlet and have an electrician verify the outlet is properly wired. The UPS will not provide

12. Coax/Cable/DSS Surge Protection

The Coax/Cable/DSS protection ports will protect any cable modem, CATV converter, or DSS receiver.

surge protection without being plugged into a grounded and properly wired wall outlet.

13. Outlets Designed for AC Adapters

The unit has two outlets spaced to allow AC power adapter blocks to be plugged into the UPS without blocking adjacent outlets

REPLACING THE BATTERY

Replacement of batteries located in an OPERATOR ACCESS AREA.

- 1. When replacing batteries, replace with the same number of the following battery: CyberPower / RB1290X2 for A1500SP1.
- CAUTION! Risk of Energy Hazard, maximum 24V 9 Ampere-hour battery for A1500SP1. Before replacing batteries, remove conductive jewelry such as chains, wrist watches, and rings. High energy conducted through these materials could cause severe burns.
- CAUTION! Do not dispose of batteries in a fire. The batteries may explode.
- CAUTION! Do not open or mutilate batteries. Released material is harmful to the skin and eyes. It may be toxic. CAUTION: A battery can present a risk of electrical shock and high short circuit current. The following precautions should be observed when

(2) Use tools with insulated handles

CAUTION - RISK OF EXPLOSION IF BATTERY IS REPLACED BY AN INCORRECT TYPE, DISPOSE OF USED BATTERIES ACCORDING TO LOCAL REGULATIONS

BATTERY REPLACEMENT PROCEDURE:

working on batteries:

- A1500SP1
- Turn off and unplug all connected equipment.
- 2. Turn the UPS off and unplug it from the AC power source.
- 3. Turn the UPS on its side.
- 4. Remove the front panel retaining screws located on the bottom of the UPS
- Slide the battery compartment cover (front panel) completely off of the unit.
- Disconnect the battery wires from the batteries.
- Remove the batteries from the compartment.
- 8. Install the replacement batteries by connecting the red wire (+) and black wire (-) to the same color connectors from both the upper and lower battery pack. Note: Only use new batteries for replacement and both batteries should be replaced at the same time to ensure maximum life
- Put the batteries back into the compartment.
- 10. Slide back the battery compartment cover and tighten the retaining screws
- Recharge the UPS for 8-16 hours to fully charge the battery.









DEFINITIONS FOR ILLUMINATED LCD INDICATORS



The LCD screen indicates a variety of UPS when the UPS is plugged into an AC outlet

INPUT voltage meter: This meter measures the AC voltage that the UPS system is receiving from the utility wall outlet. The UPS is designed, through the use of

automatic voltage regulation, to continuously correct output voltage to connected equipment to a safe 120 voltage output range. In the event of a complete power loss, severe brownout, or over-voltage, the UPS relies on its internal battery to supply consistent 110/120 output voltage. The INPUT voltage meter can be used as a diagnostic tool to identify poor-quality input power. OUTPUT voltage meter:

This meter measures, in real time, the AC voltage that the UPS system is providing to the computer, such as normal line mode, AVR mode, and battery backup mode. (Note: The OUTPUT voltage meter shows the status of the battery backup outlets.)

- This displays the run time estimate of the UPS with current battery capacity and load
- NORMAL icon: This icon appears when the UPS is working under normal conditions.
- **BATTERY** icon: During a severe brownout or blackout, this icon appears and an alarm sounds (two short beeps followed by a pause) to indicate the UPS is

operating from its internal batteries. During a prolonged brownout or blackout, the alarm will sound continuously to indicate the UPS's batteries are nearly out of power. You should save files and turn off your equipment immediately or allow the software to shut the system down AVR (Automatic Voltage Regulation) icon:

This icon appears whenever your UPS is autor

operation of your UPS, and no action is required on your part. SILENT MODE icon:

This icon appears and an alarm sounds to indicate the battery-supplied outlets are overloaded. To clear the overload, unplug some of your

OVER LOAD icon:

This icon appears whenever the UPS is in silent mode.

equipment from the battery-supplied outlets until the icon turns off and the alarm stops **FAULT icon:** This icon appears if there is a problem with the UPS, Contact CyberPower Systems at for further help and support.

E01: Charger Fault - Overcharge (Contact CyberPower Systems for support.) E02: Charger Fault - No Charge (Contact CyberPower Systems for support.)

E11: Battery Overvoltage (Contact CyberPower Systems for support.) E21: Battery Output Short Fault (Turn on the UPS again.)

E22: Battery Mode or AC/Utility Power Mode Overload Fault (Unplug at least one piece of equipment from battery outlets and turn the UPS on again.)

This meter displays the approximate charge level (in 20% increments) of the UPS's internal battery. During a blackout or severe brownout, the

UPS switches to battery power, the BATTERY icon appears, and the charge level decreases.

This meter displays the approximate output load level (in 20% increments) of the UPS battery outlets.

For more information about functions setup, please refer to the Function Setup Guide

TROUBLESHOOTING


Problem	Possible Cause	Solution
Circuit breaker button is projecting from the back of the unit.	Circuit breaker has tripped due to an overload.	Turn the UPS off and unplug at least one piece of equipment. Wait 10 seconds, reset the circuit breaker by depressing the button, and then turn the UPS on.
The UPS does not perform expected runtime.	Battery not fully charged.	Recharge the battery by leaving the UPS plugged in.
	Battery is worn out.	Contact CyberPower Systems about replacement batteries.
The UPS will not turn on.	The on/off switch is designed to prevent damage from rapidly turning it off and on.	Turn the UPS off. Wait 10 seconds and then turn the UPS on.
	The unit is not connected to an AC outlet.	The unit must be connected to a 120V 60Hz outlet.
	The battery is worn out.	Contact CyberPower Systems about replacement batteries.
	Mechanical problem.	Contact CyberPower Systems.

 ${\bf Additional\ trouble shooting\ information\ can\ be\ found\ under\ "Support"\ at\ {\bf \underline{CyberPowerSystems.com}}$

TECHNICAL SPECIFICATIONS

Serial	A1500SP1	
Model	CP1500AVRLCDa	
Capacity	1500VA / 900W	
Nominal Input Voltage	120V	
Input Frequency	60 Hz ± 3 Hz	
On-Battery Output Voltage	120Vac ± 5%	
Max. Load for UPS Outlets (5 Outlets)	1500VA / 900W	
Max. Load for Full-Time Surge Protection outlets	12 Amp (12 outlets)	
On-Battery Output Wave Form	Simulated Sine Wave	
Operating Temperature	+ 32°F to 104° F / 0° C to 40° C	
Operating Relative Humidity	0 to 90% non-condensing	
Size (W x H x D)	3.9" x 11" x 14" (100 x 280 x 355 mm)	
Net Weight	25lbs / 11.3kg	
Battery Type	CyberPower / RB1290X2	
Typical Battery Recharge Time	8 hours	
Typical Battery Life	3 to 6 years, depending on number of discharge/recharge cycles	
Recommended Battery	Sealed Maintenance Free Lead Acid Battery	
Safety Approvals	UL1778(UPS), CAN/CSA C22.2 No 107.3., FCC/DoC Class B	

SYSTEM FUNCTIONAL BLOCK DIAGRAM



FCC Compliance Statement

FCC Compliance Statement

This device complies with part 15 of the FCC rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment to an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help"

Warning: Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

Canadian Compliance Statement

CAN ICES-3 (B)/NMB-3(B)

CYBERPOWER GREENPOWER UPS™ TECHNOLOGY

Advanced Energy-Saving Patented Bypass Technology CyberPower's patented GreenPower UPS™ with Bypass Technology reduces UPS energy costs by up to

75% compared to conventional UPS models. Even when utility power is normal, conventional UPS models constantly pass power through a transformer. By contrast, under normal conditions the advanced circuitry of a GreenPower UPS™ bypasses the transformer. As a result, the power efficiency is significantly increased while decreasing waste heat, using less energy, and reducing energy costs.

When an abnormal power condition occurs, the GreenPower UPS™ automatically runs power through its



transformer to regulate voltage and provide "safe" power. Since utility power is normal over 88% of the time, the GreenPower UPS™ operates primarily in its efficient bypass mode.

The GreenPower UPS™ is also manufactured in accordance with the Restriction on Hazardous Substances (RoHS) directive making it one of the most environmentally-friendly on the market today.

Limited Warranty and Connected Equipment Guarantee

Please visit www.CyberPowerSystems.com for a copy of the Limited Warranty and Connected Equipment Guarantee.

Where Can I Get More Information?

The application of the United Nations Convention of Contracts for the International Sale of Goods is expressly excluded. CyberPower is the warrantor under this Limited Warranty.

For further information please feel free to contact CyberPower at Cyber Power Systems (USA), Inc. 4241 12th Ave E., STE 400, Shakopee, MN 55379; call us at (877) 297-6937; or submit a web ticket online at cyberpowersystems.com/support.

Cyber Power Systems (USA), Inc. encourages environmentally sound methods for disposal and recycling of its UPS products.

Please dispose and/or recycle your UPS and batteries in accordance to the local regulations of your state.