



FORCE™ QUIETCLEAN® UPRIGHT

SC5713B

MENU







CRI BRONZE SEAL OF APPROVAL



LEED QUALIFIED

The FORCE™ QuietClean® upright provides an exceptional clean certified with the CRI Bronze Seal of Approval. Featuring a sealed HEPA system with included HEPA filter to capture 99.97% of particles for cleaner emissions. FORCE™ is LEED Qualified for daytime cleaning with a sound level of 69 dBA. Includes on-board tools and stretch hose for above-the-floor cleaning.

 SEALED HEPA	 CRI BRONZE SEAL OF APPROVAL	 PERFORMANCE
quiet CLEAN 69 DBA	 LEED QUALIFIED	

SPECIFICATIONS			
MFG#	SC5713B	CLEANING WIDTH	13"
MOTOR	10 amp	CORD LENGTH	40'
CFM	135	SOUND	69 dBA
FILTRATION	Sealed HEPA	BRUSH ROLL	27809B-5
DUST CONTAINMENT	Disposable Bag	BAG	LS (63256A-10)
DUST CAPACITY	4.5 qt.	BELT	61120D-12
CLEANING TOOLS	Wand, hose, dusting brush, crevice tool	FILTER	61840-4
PACKAGING			
UPC	0 23169 11670 2	PACKAGE WEIGHT	22 lbs.
PRODUCT WEIGHT	17 lbs.	PACKAGE DIMENSIONS	29.5" x 14" x 18.75"
WARRANTY	2 Years - Parts & Labor		