








TRADITION™ UPRIGHT

SC887B

MENU

TRADITION™ upright designed with a chrome hood for added durability in the toughest environments. Lowers cost of ownership with a 2,000 hour motor, bagless dirt cup and chrome brushroll with replaceable bristle strips. Quick Kleen™ fan chamber helps diagnose and clear clogs. Designed for easy maintenance with quick-release access for emptying the dirt cup and tool-free brushroll and belt replacement.

 <p>LOW MAINTENANCE COSTS</p>	 <p>HANDY FEATURES</p>	 <p>COST OF OWNERSHIP</p>
 <p>EASY TO MAINTAIN</p>	 <p>>2,000 HOURS MOTOR LIFE</p>	

SPECIFICATIONS			
MFG#	SC887B	CLEANING WIDTH	12"
MOTOR	7 amp	CORD LENGTH	50'
CFM	145	SOUND	79 dBA
FILTRATION	n/a	BRUSH ROLL	53270
DUST CONTAINMENT	Dust Cup	BELT	52100C-12
DUST CAPACITY	1.9 qt.	CLEANING TOOLS	n/a
PACKAGING			
UPC	0 23169 10319 1	PACKAGE WEIGHT	22 lbs.
PRODUCT WEIGHT	18.4 lbs.	PACKAGE DIMENSIONS	21.5" x 15.25" x 10"
WARRANTY	2 Years - Parts & Labor		