

# WE MAKE THE CUT™



## Kett Tool PN-1020 18 Gauge Nibbler

### Features:

- 90 PSI straight handle, variable speed, 2500 rpm motor
- Replaceable punch and die
- Cuts cold-rolled mild steel up to 18 gauge and most grades of stainless steel up to 20 gauge
- Cuts intricate curves in flat or corrugated steel
- Cuts up to 60 inches per minute and achieves a cutting radius of  $\frac{5}{8}$ "
- Lightweight and easily maneuverable

### Specifications:

<b>CFM</b> 16	<b>Minimum Cutting Radius</b> $\frac{5}{8}$ "
<b>RPM</b> 0 to 2,500	<b>Cold-rolled mild steel</b> 18 gauge
<b>Power Source</b> 90 PSI compressed air	<b>Stainless Steel</b> 20 gauge
<b>Nibbler Housing</b> 1020 Aluminum	<b>Length</b> 8 inches
<b>Cutting Speed</b> 60 inches per minute	<b>Weight</b> 2.5 pounds

Kett Tool Company  
5055 Madison Road  
Cincinnati, OH 45227  
(513) 271-0333

[www.kett-tool.com](http://www.kett-tool.com)  
[info@kett-tool.com](mailto:info@kett-tool.com)

