

WE MAKE THE CUT™



Kett Tool P-500 18 Gauge Double Cut Shear

Features:

- 90 PSI pistol grip, variable speed, 2200 rpm motor
- Replaceable A-2 tool steel shear blades
- Cuts cold-rolled mild steel up to 18 gauge, most grades of stainless steel to 20 gauge
- Cuts up to 180 inches per minute
- With the 7/32" waste strip, you get a clean, burr free cut
- Lightweight and easily maneuverable - can cut a 6" radius

Specifications:

CFM 16	Minimum Cutting Radius 6 inches
RPM 0 to 2,200	Cold-rolled Mild Steel 18 gauge
Power Source 90 PSI compressed air	Stainless Steel 20 gauge
Shear Head 60-20 Steel	Length 10.5 inches
Cutting Speed 180 inches per minute	Weight 3 pounds
	Other Configurations 5.0 amp 120V Electric 90 PSI straight handle

Kett Tool Company
5055 Madison Road
Cincinnati, OH 45227
(513) 271-0333

www.kett-tool.com
info@kett-tool.com



