

SAFETY DATA SHEET

This document is not intended for general distribution.

It can be used as the basis for a general distribution document if appropriate changes are made to the identification section.

1. PRODUCT AND COMPANY IDENTIFICATION

Product Name: SPARKLE GLASS CLEANER

Product Code: 20620

SUPPLIER'S NAME: A.J. FUNK & COMPANY

ADDRESS : 1471 Timber Dr.

Elgin, IL 60123

EMERGENCY PHONE : 877-225-3865

INFORMATION PHONE : 847-741-6760

Product Use: Glass cleaner

2. HAZARDS IDENTIFICATION

CLASSIFICATION

Gas under pressure

Liquefied gas

Eye Damage/Irritation

2B



SIGNAL WORD: Warning

Hazard Statements

Contains gas under pressure; may explode if heated

Causes eye irritation

Precautionary Statements

Pressurized container – Do not pierce or burn, even after use

Wash hands thoroughly after handling

IF IN EYES: Rinse continuously with water for several minutes. Remove contact lenses if present and easy to do – continue rinsing

If eye irritation persists: Get medical advice/attention

Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F

Dispose of contents/container to comply with all local, state, and federal regulations

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Percent
WATER	7732-18-5	88.00
2-BUTOXYETHANOL	111-76-2	8.00
BUTANE	106-97-8	3.00
PROPANE	74-98-6	1.00

4. FIRST AID MEASURES

INHALATION: Remove to fresh air. Administer oxygen if needed. Apply artificial respiration if breathing has stopped. Get medical attention.

EYE CONTACT: Wash immediately with large volumes of fresh water for at least 15 minutes. Get medical attention.

SKIN CONTACT: Wipe off with a towel. Wash with soap and water. Get medical attention if irritation persists.

INGESTION: Not a likely route of exposure.

Most important symptoms/effects, acute and delayed: Repeated exposure may cause skin dryness or cracking. May cause drowsiness or dizziness.

Indication of immediate medical attention and special treatment needed: None known.

5. FIRE FIGHTING MEASURES

Suitable and unsuitable extinguishing media: Foam, Alcohol foam, CO2, Dry chemical, Water fog. Water spray may be ineffective.

Specific hazards arising from the chemical: Closed containers may explode from internal pressure build-up when exposed to extreme heat and discharge contents. Liquid content of container will not support combustion. Overexposure to decomposition products may cause a health hazard. Symptoms may not be readily apparent. Obtain medical attention. Hazardous decomposition products include carbon dioxide, carbon monoxide, and other toxic fumes.

Special equipment and precautions for fire-fighters: Water may be used to cool containers to prevent pressure build-up and explosion when exposed to extreme heat. Wear goggles and use self-contained breathing apparatus. If water is used, fog nozzles are preferred.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment, and emergency procedures: Avoid breathing vapors. Ventilate area. Remove all sources of ignition.

Methods and materials for containment and cleaning up: Clean up with absorbent material and place in closed containers for disposal.

7. HANDLING AND STORAGE

Precautions for safe handling: Do not puncture or incinerate (burn) cans. Do not stick pins, nails, or any other sharp objects into opening on top of can. Do not spray in eyes. Do not take internally. See product label for additional information.

Conditions for safe storage, including any incompatibilities: Store and use in cool, dry, well-ventilated areas. Do not store above 120 F.

8. EXPOSURE CONTROL/PERSONAL PROTECTION

Chemical Name / CAS No.	OSHA Exposure Limits	ACGIH Exposure Limits	Other Exposure Limits
WATER 7732-18-5	Not established	Not established	

2-BUTOXYETHANOL 111-76-2	PEL-TWA: 50 ppm; PEL-Ceiling: Not determined	TLV-TWA: 20 ppm; TLV-STEL: Not determined	
BUTANE 106-97-8	Not established	TWA: 1000 ppm	
PROPANE 74-98-6	Not established	TWA: 1000 ppm	

Appropriate engineering controls: Ventilation should be sufficient to prevent inhalation of any vapors. General dilution and/or local exhaust ventilation in volume to keep PEL/TLV of most hazardous ingredient below acceptable limit and lcl below stated limit.

Individual protection measures:

Respiratory protection: None under normal use. Avoid breathing vapors. In restricted areas, use approved chemical/mechanical filters designed to remove a combination of particles and vapor. In confined areas, use an approved air line respirator or hood. Self-contained breathing apparatus is required for vapor concentrations above PEL/TLV limits.

Protective gloves: None under normal use. Use solvent-resistant for prolonged or repeated contact.

Eye protection: None under normal use. However, use of safety glasses with splash guards or full face shield should be used if indicated.

Other protective clothing or equipment: None under normal use. However, use of solvent-resistant aprons or other clothing is recommended. Eye washes and safety showers in the workplace are recommended.

9. PHYSICAL AND CHEMICAL PROPERTIES

<p>Appearance: Aerosol product</p> <p>Vapor Pressure: Not determined</p> <p>Vapor Density: Heavier than air</p> <p>Density: 0.958794261</p> <p>Freezing point: Not determined</p> <p>Boiling point: N/A</p> <p>Evaporation rate: Slower than ether</p> <p>Explosive Limits: Not applicable</p> <p>Autoignition temperature: Not determined</p> <p>Viscosity: Not determined</p>	<p>Odor: Mild solvent</p> <p>Odor threshold: Not determined</p> <p>pH: Not applicable</p> <p>Melting point: Not determined</p> <p>Solubility: Not determined</p> <p>Flash point: Not determined</p> <p>Flammability: Level 1 Aerosol</p> <p>Partition coefficient (n-octanol/water): Not determined</p> <p>Decomposition temperature: Not determined</p>
---	---

10. STABILITY AND REACTIVITY

Reactivity: Not reactive under normal conditions of use.

Chemical stability: Stable under normal storage and handling conditions.

Possibility of hazardous reactions: None known.

Incompatible materials:

No data

Hazardous decomposition products:

No data

11. TOXICOLOGICAL INFORMATION

Long-term toxicological studies have not been conducted for this product.

12. ECOLOGICAL INFORMATION

Long-term ecological studies have not been conducted for this product.

13. DISPOSAL CONSIDERATIONS

Dispose of in accordance with local, state, and federal regulations. Before attempting clean up, refer to other sections of this document for hazard cautionary information.

14. TRANSPORT INFORMATION

By land: DOT Proper Shipping Name: None required per 49 CFR 173.306(i) for products that conform to the Limited Quantity provisions. Commodity shipping description: Cleaning Compound, NOI

By water: DOT & IMDG Proper Shipping Name: UN1950, Aerosols, 2.2, LTD QTY

By air: DOT & IATA Proper Shipping Name: UN1950, Aerosols, non-flammable, 2.2, LTD QTY (packing instruction Y203 applies)

15. REGULATORY INFORMATION

All ingredients are either listed on the TSCA inventory or are exempt.

16. OTHER INFORMATION

Date revised: 2015-05-15

Revision 0

Date Printed: 2015-05-21

THE INFORMATION CONTAINED HEREIN IS BASED ON DATA CONSIDERED ACCURATE. HOWEVER, NO WARRANTY IS EXPRESSED OR IMPLIED REGARDING THE ACCURACY OF THE DATA OR THE RESULTS TO BE OBTAINED FROM THE USE THEREOF. BECAUSE THE INFORMATION CONTAINED HEREIN MAY BE APPLIED UNDER CONDITIONS BEYOND OUR CONTROL, WE ASSUME NO RESPONSIBILITY FOR ITS USE.