

# WHAT IT TAKES TO PROTECT™

## Professional Lysol® Brand Disinfectant Spray

Effective against COVID-19 virus in 2 minutes<sup>2</sup>

Kills over 100 illness-causing germs<sup>3</sup>

Meets OSHA Bloodborne Pathogen Standards



1.

Disinfects  
Hard Surfaces

2.

Disinfects  
Soft Surfaces

3.

Deodorizes

## 3 Great Ways To Protect

### #1 Disinfectant Spray in the US<sup>1</sup>

- Disinfects SARS-CoV-2, the virus that causes COVID-19, in 2 minutes<sup>2</sup>
- Effective against Mycobacterium bovis BCG (TB) in 10-minute disinfection<sup>3</sup>
- Tuberculocidal, fungicidal, virucidal and bactericidal formula. Kills 99.9% of viruses and bacteria, including cold and flu viruses, MRSA, Norovirus, Rhinovirus, Poliovirus Type 1, Hepatitis A Virus, Hepatitis B Virus and HIV-1 (AIDS Virus) on hard surfaces<sup>3</sup>
- Kills 99.9% of odor-causing bacteria at the source<sup>3</sup>
- Prevents the build-up of mold for up to 7 days
- For use on hard and soft surfaces

Product	Case Pack	Item Number	Distributor Number
Crisp Linen®	19 oz./12		

Lysol® Disinfectant Spray	
Effective against COVID-19 Virus in 2 minutes <sup>2</sup>	✓
Eliminates over 100 germs <sup>3</sup>	✓
Disinfects 12 types of Cold and Flu Viruses <sup>3</sup>	✓
Kills TB in 10-minute disinfection <sup>3</sup>	✓

EPA Registration No: 777-99-675

\*\*When used as directed

<sup>1</sup>Based on Sales Data Latest 52 weeks, week end 06/06/2020  
<sup>2</sup>Lysol® Disinfectant Spray is effective against SARS-CoV-2, the virus that causes COVID-19, in 2 minutes when used as directed on hard, non-porous surfaces

<sup>3</sup>On hard, non-porous surfaces when used as directed



# WHAT IT TAKES TO PROTECT™



## Professional Lysol® Disinfectant Spray How to Use in Your Facility



**To Deodorize:**  
Spray on surfaces  
as needed.



**To Sanitize:**  
Surfaces must remain  
wet for 10 seconds  
then allow to air dry.

### HARD SURFACES

Pre-clean surfaces prior  
to use. Hold can upright  
6" to 8" from surface.  
Spray 3 to 4 seconds  
until covered  
with mist.

**To Disinfect:**  
Surfaces must remain  
wet for 3 minutes  
then allow to air dry.



**To Control and Prevent  
Mold & Mildew:**

Apply to pre-cleaned surface.  
Allow to remain wet for 3 minutes.  
Let air dry. Repeat applications  
in weekly intervals or  
when mold and mildew  
growth appears.



Rinse toys & food contact  
surfaces with potable  
water after use.



**To Spot Sanitize  
Soft Surfaces:**  
Spray until fabric is wet.  
**DO NOT SATURATE.**  
Fabric must remain  
wet for 30 seconds.  
Let air dry.



### SOFT SURFACES



**To Disinfect:**  
Spray fabric until wet.  
**DO NOT SATURATE.**  
Fabric must remain wet  
for 10 minutes. Let air dry.





# Effective Against the Following Microorganisms\*\*

Bacteria - Disinfection (hard non-porous)	Contact Time
Campylobacter jejuni	30 seconds
Acinetobacter baumannii MDR	2 minutes
Acinetobacter calcoaceticus	2 minutes
Acinetobacter haemolyticus	2 minutes
Bordetella pertussis (Whooping Cough)	2 minutes
Burkholderia cepacia	2 minutes
Citrobacter freundii	2 minutes
Corynebacterium diphtheriae	2 minutes
Corynebacterium xerosis	2 minutes
Cronobacter sakazakii << Pre-cleaned surfaces >>	2 minutes
Enterobacter aerogenes MDR	2 minutes
Enterobacter cloacae	2 minutes
Enterococcus faecalis	2 minutes
Enterococcus faecalis - Vancomycin Resistant (VRE)	2 minutes
Enterococcus faecium VRE + MDR	2 minutes
Escherichia coli	2 minutes
Escherichia coli O157:H7 (E. coli) (food poisoning)	2 minutes
Escherichia coli O104:H21	2 minutes
Escherichia coli O45:K-H-	2 minutes
Escherichia coli O111:H8	2 minutes
Escherichia coli ESBL	2 minutes
Haemophilus influenzae	2 minutes
Klebsiella oxytoca	2 minutes
Klebsiella pneumoniae	2 minutes
Klebsiella pneumoniae NDM-1 positive	2 minutes
Klebsiella pneumoniae Carbapenem resistant	2 minutes
Klebsiella pneumoniae ESBL	2 minutes
Listeria monocytogenes	2 minutes
Micrococcus luteus << Pre-cleaned surfaces >>	2 minutes
Neisseria elongata	2 minutes
Pasteurella multocida	2 minutes
Proteus mirabilis	2 minutes
Proteus vulgaris	2 minutes
Pseudomonas aeruginosa	2 minutes
Pseudomonas putida	2 minutes
Salmonella enterica (food poisoning) (skin infections)	2 minutes
Salmonella enterica serovar enteritidis	2 minutes
Salmonella enterica serovar paratyphi	2 minutes
Salmonella enterica serovar typhi	2 minutes
Salmonella enteritidis	2 minutes
Serratia marcescens	2 minutes
Shigella dysenteriae	2 minutes
Shigella flexneri	2 minutes
Shigella sonnei	2 minutes
Staphylococcus aureus (Skin infections(s))	2 minutes
Staphylococcus aureus - Methicillin resistant (HA-MRSA)	2 minutes
Staphylococcus aureus - CA-MRSA USA-300	2 minutes
Staphylococcus aureus - CA-MRSA USA-400	2 minutes
Staphylococcus epidermidis	2 minutes
Staphylococcus haemolyticus	2 minutes
Staphylococcus hominis	2 minutes

Bacteria - Disinfection (hard non-porous)	Contact Time
Staphylococcus saprophyticus	2 minutes
Streptococcus agalactiae	2 minutes
Streptococcus pneumoniae PRSP	2 minutes
Streptococcus pyogenes [Strep]	2 minutes
Streptococcus salivarius (pink eye)	2 minutes
Vibrio cholerae	2 minutes
Yersinia enterocolitica	2 minutes
Bordetella avium	3 minutes
Enterococcus faecalis - Vancomycin Resistant (VRE)	5 minutes
Acinetobacter baumannii	10 minutes
Listeria monocytogenes	10 minutes
Mycobacterium bovis BCG [Quant tuberculosis]	10 minutes
Salmonella enterica serovar paratyphi B	10 minutes

Viruses - Disinfection (hard non-porous)	Contact Time
(Avian) Influenza A Virus (H1N1) (A/Malaya/302/54) (Flu)	30 seconds
Avian Influenza A Virus (H3N2) (Flu)	30 seconds
(Avian) Influenza A Virus (H5N1) (Flu)	30 seconds
Coxsackie Type B3 Virus (Hand, Foot and Mouth Disease)	30 seconds
Cytomegalovirus	30 seconds
(Duck) Hepatitis B Virus	30 seconds
Hantavirus	30 seconds
Hepatitis C Virus (HCV) (BVDV - surrogate)	30 seconds
Herpes Simplex Virus Type 1	30 seconds
Herpes Simplex Virus Type 2	30 seconds
Human Coronavirus	30 seconds
Human Immunodeficiency Virus Type 1 [HIV-1] [AIDS Virus] (tested in the presence of 50% whole human blood)	30 seconds
Influenza A Virus (New Caledonia/20/99) (Flu)	30 seconds
Influenza B Virus (Strain B/Hong Kong/5/72) (Flu)	30 seconds
Newcastle Disease Virus	30 seconds
(Pandemic) Influenza A Virus [2009 H1N1] (Flu)	30 seconds
Respiratory Syncytial Virus (RSV) (a cause of lower respiratory infections)	30 seconds
Rhinovirus Type 39 (a leading cause of the common cold) (Sore Throat) (Upper Respiratory Tract Infections)	30 seconds
Rotavirus WA	30 seconds
SARS Coronavirus	30 seconds
(Swine) Influenza A Virus (H1N1) (Flu)	30 seconds
Vaccinia Virus	30 seconds
Echovirus Type 12	1 minute
Enterovirus Type 68	1 minute
Poliovirus Type 1	1 minute
Influenza H7N9 (wildtype A/Anhui/1/2013) (Flu)	2 minutes
SARS-CoV-2 (2019 Novel Coronavirus)	2 minutes
Adenovirus 14	3 minutes
Adenovirus 2	10 minutes
Feline Calicivirus (Norovirus) (Stomach Flu)	10 minutes
Hepatitis A Virus	10 minutes

Fungi - Disinfection (hard, non porous)	Contact Time
Trichophyton interdigitale (Athlete's Foot Fungus) (Ringworm)	2 minutes
Candida albicans	2 minutes
Candida parapsilosis	2 minutes
Aspergillus niger	3 minutes
Penicillium chrysogenum	3 minutes
Fusarium solani	10 minutes
Penicillium chrysogenum	10 minutes

Mildew Fungistat - Disinfection (hard, non porous)	Contact Time
Alternaria alternata	3 minutes
Aspergillus niger (mold & mildew)	3 minutes
Penicillium chrysogenum	3 minutes

Bacteria - Sanitization (hard, non porous)	Contact Time
Enterobacter aerogenes	10 seconds
Staphylococcus aureus (Skin infections(s))	10 seconds
Enterobacter aerogenes	30 seconds

Bacteria - Sanitization (soft surface)	Contact Time
Klebsiella pneumoniae	30 seconds
Pseudomonas aeruginosa	30 seconds
Staphylococcus aureus (Skin infections(s))	30 seconds

Bacteria - Disinfection (soft surface)	Contact Time
Salmonella enterica	9.5 minutes
Staphylococcus aureus	9.5 minutes
Pseudomonas aeruginosa	9.5 minutes

Viruses - Disinfection (soft surface)	Contact Time
Rhinovirus Type 39 (a leading cause of the common cold) (Sore Throat, Upper Respiratory)	10 minutes
Influenza A Virus (H1N1) (Strain: A/Swine/lowa/15/30)	10 minutes

Fungi - Disinfection (soft surface)	Contact Time
Trichophyton interdigitale	9.5 minutes

