

**1. IDENTIFICATION**

<b>Product Name</b>	Cream Suds® Pot & Pan Presoak & Detergent - Powder Concentrate
<b>Product Code(s)</b>	1-65
<b>Product ID:</b>	15154245_PROF_NG
<b>Product Type:</b>	Finished Product - Professional Use Only
<b>Recommended Use</b>	Dish Care
<b>Restrictions on Use</b>	Use only as directed on label.
<b>Manufacturer</b>	Procter & Gamble Professional 2 P&G Plaza Cincinnati, Ohio 45202  Procter & Gamble Inc. P.O. Box 355, Station A Toronto, ON M5W 1C5  1-800-332-7787
<b>E-mail Address</b>	pgsds.im@pg.com
<b>Emergency Telephone</b>	Transportation (24 HR) CHEMTREC - 1-800-424-9300 (U.S./ Canada) or 1-703-527-3887 Mexico toll free in country: 800-681-9531

**2. HAZARD IDENTIFICATION**

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:.

<b>Hazard Category</b>	
<b>Eye Damage / Irritation</b>	Category 2B
<b>Signal Word</b>	WARNING
<b>Hazard Statements</b>	Causes eye irritation
<b>Hazard pictograms</b>	None
<b>Precautionary Statements - Prevention</b>	Wash hands thoroughly after handling
<b>Precautionary Statements - Response</b>	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing If eye irritation persists: Get medical advice/attention IF SWALLOWED: Drink 1 or 2 glasses of water

**Precautionary Statements - Storage** None

**Precautionary Statements - Disposal** None

**Hazards not otherwise classified (HNOC)** None

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Chemical Name	Synonyms	Trade Secret	CAS-No	Weight %
Sodium carbonate	-	No	497-19-8	15 - 20
Benzenesulfonic acid, mono-C10-16-alkyl derivs., sodium salts	-	No	68081-81-2	15 - 20
Silicic acid, sodium salt	-	No	1344-09-8	10 - 15

### 4. FIRST AID MEASURES

**First aid measures for different exposure routes**

**Eye contact** Rinse with plenty of water. Get medical attention immediately if irritation persists.

**Skin contact** Rinse with plenty of water. Get medical attention if irritation develops and persists.

**Ingestion** Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur.

**Inhalation** Move to fresh air. If symptoms persist, call a physician.

**Most important symptoms/effects, acute and delayed** None under normal use conditions.

**Indication of immediate medical attention and special treatment needed, if necessary**

**Notes to Physician** Treat symptomatically.

### 5. FIRE-FIGHTING MEASURES

**Suitable extinguishing media** Dry chemical, CO<sub>2</sub>, alcohol-resistant foam or water spray.

**Unsuitable Extinguishing Media** None.

**Special hazard** None known.

**Special protective equipment for fire-fighters** As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**Specific hazards arising from the chemical** None.

## 6. ACCIDENTAL RELEASE MEASURES

### Personal precautions, protective equipment and emergency procedures

**Personal precautions** Use personal protective equipment. Do not get in eyes, on skin, or on clothing.

**Advice for emergency responders** Use personal protective equipment as required.

### Methods and materials for containment and cleaning up

**Methods for containment** Prevent dust cloud. Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up** Sweep up and shovel into suitable containers for disposal. Dispose of in accordance with local regulations.

## 7. HANDLING AND STORAGE

### Precautions for safe handling

**Advice on safe handling** Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.

### Conditions for safe storage, including any incompatibilities

**Storage Conditions** Keep containers tightly closed in a dry, cool and well-ventilated place.

**Incompatible products** None known.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control parameters

**Exposure Guidelines** No exposure limits noted for ingredient(s).

### Exposure controls

**Engineering Measures** **Distribution, Workplace and Household Settings:**  
Ensure adequate ventilation

**Product Manufacturing Plant (needed at Product-Producing Plant ONLY):**  
Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

### Personal Protective Equipment

**Eye Protection** **Distribution, Workplace and Household Settings:**  
No special protective equipment required

**Product Manufacturing Plant (needed at Product-Producing Plant ONLY):**  
Use appropriate eye protection

**Hand Protection** **Distribution, Workplace and Household Settings:**  
No special protective equipment required

**Product Manufacturing Plant (needed at Product-Producing Plant ONLY):**  
Protective gloves

**Skin and Body Protection** **Distribution, Workplace and Household Settings:**

No special protective equipment required

**Product Manufacturing Plant (needed at Product-Producing Plant ONLY):**  
Wear suitable protective clothing

**Respiratory Protection**

**Distribution, Workplace and Household Settings:**  
No special protective equipment required

**Product Manufacturing Plant (needed at Product-Producing Plant ONLY):**  
In case of insufficient ventilation wear suitable respiratory equipment

**9. PHYSICAL AND CHEMICAL PROPERTIES**

<b>Physical State @20°C</b>	solid	
<b>Appearance</b>	pink powder	
<b>Odor</b>	Baby Powder	
<b>Odor threshold</b>	No information available	
<u>Property</u>	<u>Values</u>	<u>Note</u>
<b>pH value</b>	10 - 11	(as 1% solution)
<b>Melting/freezing point</b>	No information available	
<b>Boiling point/boiling range</b>	No information available	
<b>Flash point</b>	No information available	
<b>Evaporation rate</b>	No information available	
<b>Flammability (solid, gas)</b>	No information available	
<b>Flammability Limits in Air</b>		
<b>Upper flammability limit</b>	No information available	
<b>Lower Flammability Limit</b>	No information available	
<b>Vapor pressure</b>	No information available	
<b>Vapor density</b>	No information available	
<b>Relative density</b>	0.41	
<b>Water solubility</b>	100%	
<b>Solubility in other solvents</b>	No information available	
<b>Partition coefficient: n-octanol/water</b>	No information available	
<b>Autoignition temperature</b>	No information available	.
<b>Decomposition temperature</b>	No information available	.
<b>Viscosity of Product</b>	No information available	
<b>VOC Content (%)</b>	Products comply with US state and federal regulations for VOC content in consumer products.	

**10. STABILITY AND REACTIVITY**

<b>Reactivity</b>	None under normal use conditions.
<b>Stability</b>	Stable under normal conditions.
<b>Hazardous polymerization</b>	Hazardous polymerization does not occur.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Conditions to Avoid</b>	None under normal processing.
<b>Materials to avoid</b>	None in particular.
<b>Hazardous Decomposition Products</b>	None under normal use.

**11. TOXICOLOGICAL INFORMATION**

Product Information  
Information on likely routes of exposure

Inhalation No known effect.  
 Skin contact No known effect.  
 Ingestion No known effect.  
 Eye contact Irritating to eyes.

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

Acute toxicity No known effect.  
 Skin corrosion/irritation No known effect.  
 Serious eye damage/eye irritation Irritating to eyes.  
 Skin sensitization No known effect.  
 Respiratory sensitization No known effect.  
 Germ cell mutagenicity No known effect.  
 Neurological Effects No known effect.  
 Reproductive toxicity No known effect.  
 Developmental toxicity No known effect.  
 Teratogenicity No known effect.  
 STOT - single exposure No known effect.  
 STOT - repeated exposure No known effect.  
 Target Organ Effects No known effect.  
 Aspiration hazard No known effect.  
 Carcinogenicity No known effect.

**Component Information**

Chemical Name	CAS-No	LD50 Oral	LD50 Dermal	LC50 Inhalation
Sodium carbonate	497-19-8	2800 mg/kg bw	> 2000 mg/kg bw (US EPA 16 CFR 1500.40)	-
Silicic acid, sodium salt	1344-09-8	3400 mg/kg bw (Similar to OECD 401; standard acute method; rat)	> 5000 mg/kg bw (Read across data on AgSil TM 25 Potassium silicate solution; rat)	> 2.06 mg/L air (Read across data AgSil TM 25 Potassium silicate solution; EPA OPPTS 870.1300; standard acute method; rat)

**12. ECOLOGICAL INFORMATION**

**Ecotoxicity**

The product is not expected to be hazardous to the environment.

Persistence and degradability No information available.  
 Bioaccumulative potential No information available.  
 Mobility No information available.  
 Other adverse effects No information available.

**13. DISPOSAL CONSIDERATIONS**

**Waste treatment**

Waste from Residues / Unused Products Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Disposal should be in accordance with applicable regional, national and local laws and regulations.

California Hazardous Waste Codes (non-household setting) 331

**14. TRANSPORT INFORMATION**

**DOT** Not regulated  
**IMDG** Not regulated  
**IATA** Not regulated

**15. REGULATORY INFORMATION**

**U.S. Federal Regulations**

**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

**Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)**

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of the Clean Air Act Amendments of 1990.

**Clean Water Act**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

**California Proposition 65**

This product is not subject to warning labeling under California Proposition 65.

**U.S. State Regulations (RTK)**

Chemical Name	CAS-No	Massachusetts
Sulfuric acid sodium salt (1:2)	7757-82-6	X

Chemical Name	CAS-No	Pennsylvania
Sulfuric acid sodium salt (1:2)	7757-82-6	X

**International Inventories**

**United States**

All intentionally-added components of this product(s) are listed on the US TSCA Inventory.

**Canada**

This product is in compliance with CEPA for import by P&G.

**Legend**

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**CEPA** - Canadian Environmental Protection Act

## 16. OTHER INFORMATION

### HMIS Ratings

Health hazard	-
Flammability	1
Physical hazard	0

Health hazard	1
Flammability	1
Instability	0

**Issuing Date:** 12-Feb-2015

**Revision Date:** 12-Jun-2015

### **Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of SDS**