



Safety Data Sheet

Issue Date 08-Aug-2011

Revision/Review Date: 09-Dec-2019

Version 1.1

1. IDENTIFICATION

Product Identifier

Product Name Maxim Nø Acid

Other means of Identification

Product Code 035200

Recommended Use of the Chemical and Restrictions on Use

Recommended Use Non-Acid disinfectant cleaner. For industrial use.

Details of the Supplier of the Safety Data Sheet

Midlab, Inc.
140 Private Brand Way
Athens, TN 37303

Emergency Telephone Number

Company Phone Number Phone: 1-423-337-3180
Emergency Telephone (24 hr) INFOTRAC 1-352-323-3500 (International) – Customer Number: 76773
1-800-535-5053 (North America)

2. HAZARDS IDENTIFICATION

Appearance Blue

Physical State Liquid

Odor Floral

Classification

This chemical does not meet the hazardous criteria set forth by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200). However, this Safety Data Sheet (SDS) contains valuable information critical to the safe handling and proper use of this product. This SDS should be retained and available for employees and other users of this product.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%
Water	7732-18-5	60-100
Diethylene Glycol Monobutyl Ether	112-34-5	5-10
Tetrasodium EDTA	64-02-8	1-5

**If Chemical Name/CAS No is "proprietary" and/or Weight-% is listed as a range, the specific chemical identity and/or percentage of composition has been withheld as a trade secret. **

4. FIRST-AID MEASURES

First Aid Measures

- Eye Contact** Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If eye irritation persists: Get medical advice/attention.
- Skin Contact** Wash off immediately with plenty of water for at least 15 minutes.
- Inhalation** Remove to fresh air.
- Ingestion** Clean mouth with water and drink afterwards plenty of water. If any discomfort persists, obtain medical attention.

Most Important Symptoms and Effects

Prolonged or repeated exposure can remove natural skin oils and may produce irritation.

Indication of any Immediate Medical Attention and Special Treatment Needed

Notes to Physician Treat symptomatically. May aggravate pre-existing skin disorders.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Water spray (fog). Carbon dioxide (CO2). Water. Foam.

Unsuitable Extinguishing Media

Not determined.

Specific Hazards Arising from the Chemical

None known.

Hazardous Combustion Products

Normal products of combustion.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal Precautions, Protective Equipment and Emergency Procedures

Personal Precautions Wear protective clothing as described in Section 8 of this safety data sheet.

Environmental Precautions Prevent from entering into soil, ditches, sewers, waterways and/or groundwater. See Section 12, Ecological Information. See Section 13, Disposal Considerations, for additional information. See Section 12 for additional Ecological Information.

Methods and Material for Containment and Cleaning Up

Methods for Containment Prevent from spreading or entering drains, ditches or rivers by using sand, earth, or other appropriate barriers.

Methods for Clean-Up Contain and collect with an inert absorbent and place into an appropriate container for disposal. Rinse area with clean water and dry before permitting traffic.

7. HANDLING AND STORAGE

Precautions for Safe Handling

Advice on Safe Handling Handle in accordance with good industrial hygiene and safety practice. Use personal protection recommended in Section 8. For industrial and commercial use only. Avoid contact with skin, eyes or clothing.

Conditions for Safe Storage, including any Incompatibilities

Storage Conditions Keep container tightly closed and store in a cool, dry and well-ventilated place. Protect from freezing. Keep out of the reach of children.

Incompatible Materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
None Listed			

Appropriate Engineering Controls

Engineering Controls Ensure adequate ventilation, especially in confined areas. Good general room ventilation (equivalent to outdoors) should be adequate under normal conditions. Eyewash stations. Showers.

Individual Protection Measures, such as Personal Protective Equipment

Eye/Face Protection No protective equipment is needed under normal use conditions.

Skin and Body Protection No protective equipment is needed under normal use conditions.

Respiratory Protection Under normal conditions, respirator is not normally required.

General Hygiene Considerations Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES**Information on Basic Physical and Chemical Properties**

Physical State	Liquid	Odor	Floral
Appearance	Clear	Odor Threshold	Not determined
Color	Blue		
<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>	
pH	11.5-12.0		
Melting Point/Freezing Point	0 °C / 32 °F		
Boiling Point/Boiling Range	100 °C / 212 °F		
Flash Point	Not applicable	TOC	
Evaporation Rate	Not determined		
Flammability (Solid, Gas)	Liquid-not applicable		
Upper Flammability Limits	Not applicable		
Lower Flammability Limit	Not applicable		
Vapor Pressure	Not determined		
Vapor Density	Not determined		
Specific Gravity	1.01		
Water Solubility	Completely soluble	@ 25 °C (77 °F)	
Solubility in other solvents	Not determined		
Partition Coefficient	Not determined		
Auto-ignition Temperature	Not determined		
Decomposition Temperature	Not determined		
Kinematic Viscosity	Not determined		
Dynamic Viscosity	Not determined		
Explosive Properties	Not an explosive		
Oxidizing Properties	Not determined		

10. STABILITY AND REACTIVITY**Reactivity**

Not reactive under normal conditions.

Chemical Stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to Avoid

Keep out of reach of children. Keep from freezing.

Incompatible Materials

None known based on information supplied.

Hazardous Decomposition Products

Normal products of combustion.

11. TOXICOLOGICAL INFORMATION**Information on Likely Routes of Exposure****Product Information**

Eye Contact	Avoid contact with eyes.
Skin Contact	Avoid contact with skin.
Inhalation	Avoid breathing vapors or mists.
Ingestion	Do not taste or swallow.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Diethylene Glycol Monobutyl Ether 112-34-5	= 5080 mg/kg (Rat)	-	-
Tetrasodium EDTA 64-02-8	= 10 g/kg (Rat)	-	-

Information on Physical, Chemical and Toxicological Effects

Symptoms Please see section 4 of this SDS for symptoms.

Delayed and Immediate Effects as well as Chronic Effects from Short and Long-Term Exposure

Carcinogenicity Not classifiable as a human carcinogen.

Numerical Measures of Toxicity

Not determined

12. ECOLOGICAL INFORMATION**Ecotoxicity**

The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Component Information

Chemical Name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Diethylene Glycol Monobutyl Ether 112-34-5	-	2000 mg/l (96hr) silverside minnow	-	-
Tetrasodium EDTA 64-02-8	1.01: 72 h Desmodesmus subspicatus mg/L EC50	41: 96 h Lepomis macrochirus mg/L LC50 static 59.8: 96 h Pimephales promelas mg/L LC50 static	-	610: 24 h Daphnia magna mg/L EC50

Persistence/Degradability

Not determined

Bioaccumulation

Not determined

Mobility

Not determined.

13. DISPOSAL CONSIDERATIONS

Waste Treatment Methods

- Disposal of Wastes** Disposal should be in accordance with applicable regional, national and local laws and regulations.
- Contaminated Packaging** Disposal should be in accordance with applicable regional, national and local laws and regulations.

14. TRANSPORT INFORMATION

- Note** Please see current shipping paper for most up to date shipping information, including exemptions and special circumstances.
- DOT** Not regulated
- IATA** Not regulated
- IMDG** Not regulated

15. REGULATORY INFORMATION

International Inventories

- Canada – Domestic Substances List (DSL) All ingredients are listed or exempt.
TSCA (Toxic Substances Control Act) All ingredients are listed or exempt.

Legend:

- TSCA - United States Toxic Substances Control Act Section 8(b) Inventory*
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355).

SARA 311/312 Hazard Categories

- Acute Health Hazard** Yes

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	CAS No	Weight-%	SARA 313 - Threshold Values %
Diethylene Glycol Monobutyl Ether	112-34-5	1-2	1.0

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

This product does not contain any substances regulated under applicable state right-to-know regulations

Chemical Name	State List
---------------	------------

None Listed	
-------------	--

- | | |
|---|---|
| AZ – Arizona Ambient Air Quality Guidelines | IL – Illinois Toxic Air Contaminant- Carcinogenic |
| CT – Connecticut Hazardous Air Pollutants | MA – Massachusetts Right to Know List |
| CA – California Director’s List of Hazardous Substances | MN – Minnesota Hazardous Substances List |
| CAP65 – California Prop 65 | NJ – New Jersey Right to Know List |
| FL – Florida Substances List | PA – Pennsylvania Right to Know List |
| ID – Idaho Non-Carcinogen Toxic Air Pollutants | RI – Rhode Island Hazardous Substances List |

FIFRA Label Information:

This chemical is a pesticide product registered by the United States Environmental Agency and is subject to certain labeling requirements under federal pesticide law. These requirements differ from the classification criteria and hazard information required for safety data sheets (SDS), and for workplace labels of non-pesticide chemicals. The pesticide label also includes other important information, including directions for use.

Caution
Causes moderate eye irritation.

16. OTHER INFORMATION

<u>NEPA</u>	Health Hazards Not determined	Flammability Not determined	Instability Not determined	Special Hazards Not determined
<u>HMIS</u>	Health Hazards 1	Flammability 0	Physical Hazards 0	Personal Protection Not determined

Issue Date 08-Aug-2011
Revision/Review Date: 09-Dec-2019
Revision Note Version 1.1

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

Keep Out of Reach of Children. For Industrial and Institutional Use Only.

*Denotes changes from last version.

End of Safety Data Sheet