

Safety Data Sheet

Classified in accordance 29 CFR 1910.1200

1. Product Identification

Product Information:	1000008142
Product Identifier:	CLAIRE DUST UP FLOOR DRESSING AND DUST MOP TREATMENT
Recommended Use:	Cleaner
Manufacturer/Importer/Distributor Information:	PLZ CORP 2651 WARRENVILLE RD, STE 300 DOWNERS GROVE, IL 60515 US 800-332-9000
Emergency Telephone:	866-836-8855

2. Hazard(s) identification

Classification

Flammable Aerosol, category 1
Aspiration Hazard, category 1
Skin Sensitizer, category 1

Label elements

HAZARD PICTOGRAMS



SIGNAL WORD

Danger

GHS HAZARD STATEMENTS

H222	Extremely flammable aerosol.
H304	May be fatal if swallowed and enters airways.
H317	May cause an allergic skin reaction.

GHS PRECAUTIONARY STATEMENTS

Prevention

P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.
P261	Avoid breathing dust, fumes, gas, mist, vapours, or spray.
P272	Contaminated work clothing should not be allowed out of the workplace.
P280	Wear protective gloves, protective clothing, eye protection and face protection.

Response

P301+P316	IF SWALLOWED: Get emergency medical help immediately.
-----------	---

P302+P352 IF ON SKIN: Wash with plenty of soap and water.
 P331 Do NOT induce vomiting.
 P333+P317 If skin irritation or rash occurs: Get medical help.
 P362+P364 Take off contaminated clothing and wash it before reuse.
Storage
 P405 Store locked up.
 P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/ 122°F.
Disposal
 P501 Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

Other Information
 None

3. Composition/Information on Ingredients

Mixtures

<u>Chemical Identity</u>	<u>CAS Number</u>	<u>Content in Percent (%)*</u>
Distillates (Petroleum), Hydrotreated Light	64742-47-8	50-75
White Mineral Oil	8042-47-5	10-25
Propane	74-98-6	2.5-10
Naphtha (petroleum), Heavy Alkylate	64741-65-7	2.5-10
d-Limonene	5989-27-5	0.1-1.0

** All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.*

Composition Comments: Other components are not hazardous or are below required disclosure limits.
 The exact concentration has been withheld as a trade secret.

4. First-aid Measures

SKIN CONTACT: Remove contaminated clothing and wash the skin thoroughly with soap and water after work.
EYE CONTACT: Rinse immediately with plenty of water.
INHALATION: Move to fresh air.
INGESTION: Rinse mouth.
IMPORTANT SYMPTOMS: No data available
INDICATION OF IMMEDIATE MEDICAL ATTENTION AND SPECIAL TREATMENT NEEDED: Get medical attention if symptoms occur.

5. Fire-fighting Measures

EXTINGUISHING MEDIA: Use fire-extinguishing media appropriate for surrounding materials.
UNSUITABLE EXTINGUISHING MEDIA: Do not use water jet as an extinguisher, as this will spread the fire.
UNUSUAL FIRE AND EXPLOSION HAZARDS: No data available
SPECIAL FIREFIGHTING PROCEDURES: No data available

6. Accidental Release Measures

PERSONAL PRECAUTIONS : Ventilate closed spaces before entering them. ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Keep upwind.
METHODS AND MATERIALS FOR CONTAINMENT AND CLEANUP: Stop the flow of material, if this is without risk. Absorb with sand or other inert absorbent.

ENVIRONMENTAL PRECAUTIONS: Avoid release to the environment. Prevent further leakage or spillage if safe to do so. Do not contaminate water sources or sewer. Environmental manager must be informed of all major spillages.

7. Handling and Storage

HANDLING: Keep away from sources of ignition - No smoking. Keep away from open flames, hot surfaces and sources of ignition. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use.

SAFE HANDLING ADVICE: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use.

STORAGE: Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

NFPA 30B: Aerosol Level 3

8. Exposure Controls/Personal Protection

Ingredients with Occupational Exposure Limits

<u>Chemical Name</u>	<u>TLV-TWA</u>	<u>TLV-STEL</u>	<u>PEL-TWA</u>	<u>PEL-CEILING</u>
Distillates (Petroleum), Hydrotreated Light	200 mg/m3	N.E.	N.E.	N.E.
White Mineral Oil	5 mg/m3	N.E.	5 mg/m3	N.E.
Propane	N.E.	N.E.	1000 ppm	N.E.
Naphtha (petroleum), Heavy Alkylate	N.E.	N.E.	100 ppm	N.E.
d-Limonene	N.E.	N.E.	N.E.	N.E.

Further Advice: MEL = Maximum Exposure Limit OES = Occupational Exposure Standard SUP = Supplier's Recommendation
Sk = Skin Sensitizer N.E. = Not Established

ENGINEERING CONTROLS: No data available.

Personal Protection

EYE/FACE PROTECTION: Wear goggles/face shield.

SKIN PROTECTION: No data available

RESPIRATORY PROTECTION: Seek advice from local supervisor. In case of inadequate ventilation use suitable respirator.

HYGIENIC PRACTICES: When using do not smoke. Observe good industrial hygiene practices.

9. Physical and Chemical Properties

Appearance:

Physical State:	Liquid
Form:	No data available
Color:	White
Odor:	Lemon
Odor Threshold:	No data available
pH:	No data available
Freeze Point, °C:	No data available
Boiling Point, °C:	7
Flash Point, °C:	-104
Flammability (solid, gas):	No data available
Evaporation Rate:	No data available
Combustibility:	Supports Combustion
Explosive Limits, %:	0.6 - 9.5
Vapor Pressure @20°C, PSI:	45-55
Vapor Density:	No data available
Relative Density:	0.709
Solubility in Water:	No data available
Partition Coefficient, n-octanol/water:	No data available
Auto-ignition Temperature, °C:	No data available
Decomposition temperature, °C:	No data available
Kinematic Viscosity:	No data available

10. Stability and Reactivity

REACTIVITY: No data available.

STABILITY: Material is stable under normal conditions.

POSSIBILITY OF HAZARDOUS REACTIONS: No data available.

CONDITIONS TO AVOID: Avoid heat or contamination

INCOMPATIBILITY: No data available

HAZARDOUS DECOMPOSITION PRODUCTS: No data available.

11. Toxicological Information

Information on Likely Routes of Exposure

IMPORTANT SYMPTOMS: No data available

SKIN CONTACT EFFECTS: May cause irritation on prolonged or repeated contact.

EYE CONTACT EFFECTS: May cause slight irritation with tearing.

INHALATION EFFECTS: Inhalation of high concentrations of mists may cause irritation of the nose throat and upper respiratory tract.

INGESTION EFFECTS: Ingestion may cause irritation of the mucous membranes, esophagus and stomach.

CHRONIC HAZARDS: No data available

Carcinogenicity: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible, or confirmed human carcinogen by IARC, ACGIH, NTP or OSHA.

The following values are calculated based on chapter 3.1 of the GHS document. The product itself has not been tested.

<u>ATE ORAL</u>	5,020 mg/kg
<u>ATE DERMAL</u>	2,227 mg/kg
<u>ATE INHALATION</u>	71 mg/kg

Acute Toxicity Values

The acute effects of this product have not been tested. Data on individual components are tabulated below

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
64742-47-8	Distillates (Petroleum), Hydrotreated Light	5,000 mg/kg	2,000 mg/kg	>100 mg/l
8042-47-5	White Mineral Oil	5,000 mg/kg	2,000 mg/kg	N.I.
74-98-6	Propane	5,000 mg/kg	5,000 mg/kg	100 mg/l
64741-65-7	Naphtha (petroleum), Heavy Alkylate	5,000 mg/kg	5,000 mg/kg	>5.04 mg/L Rat
5989-27-5	d-Limonene	5000 mg/kg	5000 mg/kg	100 mg/l

N.I. = No Information

Skin Corrosion & Irritation:

Product: No data available

Serious Eye Damage & Irritation:

Product: No data available

Respiratory or Skin Sensitization:

Product: No data available

Components:

d-Limonene 5989-27-5 May cause an allergic skin reaction.

STOT-Single Exposure:

Product: No data available

STOT-Repeated Exposure:

Product: No data available

Aspiration Hazard:

Product: No data available

Components:

White Mineral Oil 8042-47-5 May be fatal if swallowed and enters airways.

Naphtha (petroleum), Heavy Alkylate 64741-65-7 May be fatal if swallowed and enters airways.

Distillates (Petroleum), Hydrotreated Light 64742-47-8 May be fatal if swallowed and enters airways.

Carcinogenicity:

Product: No data available

Reproductive Toxicity:

Product: No data available

Germ Cell Mutagenicity:

Product: No data available

12. Ecological Information

ECOLOGICAL INFORMATION: No data available

PERSISTENCE: No data available

BIOACCUMULATE: No data available

MOBILITY IN SOIL: No data available

OTHER ECOLOGICAL: No data available

13. Disposal Information

DISPOSAL INFORMATION: Consult with your local, regional and federal agencies for information on proper disposal.

CONTAMINATED PACKAGING : Consult with your local, regional and federal agencies for information on proper disposal.

14. Transport Information

SPECIAL TRANSPORT PRECAUTIONS: No data available

DOT

UN Number:	UN1950
Proper Shipping Name:	AEROSOLS, FLAMMABLE
Technical Name:	N/A
Hazard Class(es)	
Class:	2.1
Subsidiary Risk	N/A
Packing Group:	N/A

IATA

UN Number:	UN1950
Proper Shipping Name:	AEROSOLS, FLAMMABLE
Technical Name:	N/A
Hazard Class(es)	
Class:	2.1
Subsidiary Risk:	N/A
Packing Group:	N/A

IMDG

UN Number:	UN1950
Proper Shipping Name:	AEROSOLS, FLAMMABLE
Technical Name:	N/A
Hazard Class(es)	
Class:	2.1
Subsidiary Risk:	N/A
Packing Group:	N/A

The classification shown in this section may be eligible for use of an exception, such as 'Limited Quantity', per the dangerous goods regulations. The shipper of this product should consult the applicable mode's regulation for the UN number displayed above to determine if any exceptions are available and may be utilized, at the shipper's discretion.

15. Regulatory Information

CHEMICAL INVENTORY STATUS:

TSCA On or in compliance with the inventory

DSL On or in compliance with the inventory

CALIFORNIA PROPOSITION 65 CARCINOGENS AND REPRODUCTIVE TOXINS:



WARNING

Warning: The following ingredients present in the product are known to the state of California to cause Cancer.

Chemical Name

CAS-No.

Myrcene

123-35-3

16. Other Information

Revision Date: 7/15/2022

Datasheet produced by: Regulatory Department

Legend

N/A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined, N.I. - No Information

TLV - Threshold Limit Values (TLVs®), as established by the American Conference of Governmental Industrial Hygienists (ACGIH®)

PEL - Permissible Exposure Limit, as established by the U.S. Occupational Safety and Health Administration (OSHA), as amended

TSCA - U.S. Toxic Substance Control Act

DSL - Canada Environmental Protection Act: Domestic Substance List

This information is provided without warranty. The information is believed to be correct. This information should be used to make an independent determination of the methods to safeguard workers and the environment.