



# Safety Data Sheet

Issue date 18-Dec-2014

Version 1

## 1. Identification of the Substance/Preparation and of the Company/Undertaking

### Product Identifier

**Product name** CHAMPION SPRAYON SPRAY SCENTS METERED AIR FRESHENER PINA COLADA  
**Chemical name** 7-8165

### Other means of identification

**Product code** FG 438-5180-5  
**Synonyms** Metered Air Freshener

### Recommended use of the chemical and restrictions on use

**Recommended Use** Room Deodorizer.  
**Uses advised against** Do not spray on varnished, painted or plastic surfaces.

### Details of the supplier of the safety data sheet

<b>Supplier Address</b>	<b>Manufacturer Address</b>
Chase Products Co.	Chase Products Co.
2727 Gardner Road	2727 Gardner Road
Broadview, IL 60155	Broadview, IL 60155
708-273-1121	708-273-1121

### Emergency Telephone Number

**Company Phone Number** 708-865-1000  
**24 Hour Emergency Phone Number** 1-800-255-3924  
**Emergency telephone** ChemTel 1-800-255-3924

## 2. Hazards Identification

### Classification

Acute toxicity - Inhalation (Gases)	Category 4
Serious eye damage/eye irritation	Category 2
Specific target organ toxicity (single exposure)	Category 3
FLAMMABLE AEROSOLS	Category 1
Gases Under Pressure	liquefied gas

### Label Elements

#### EMERGENCY OVERVIEW

**DANGER**

**hazard statements**  
HARMFUL IF INHALED  
Causes serious eye irritation  
May cause drowsiness or dizziness  
EXTREMELY FLAMMABLE AEROSOL  
Contains gas under pressure; may explode if heated



**Appearance** Clear liquid that will be aerosolized.

**Physical State** Aerosol

**Odor** Perfumed.

**Precautionary Statements - Prevention**

Avoid breathing fumes, mist, vapors or spray.  
 Use only outdoors or in a well-ventilated area  
 Wash face, hands and any exposed skin thoroughly after handling  
 Wear protective gloves, protective clothing, eye protection and face protection.  
 Keep away from heat, sparks, open flames and hot surfaces. — No smoking  
 Pressurized container: Do not pierce or burn, even after use  
 Do not spray on an open flame or other ignition source

**Precautionary Statements - Response**

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
 If eye irritation persists: Get medical advice/attention  
 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing  
 Call a POISON CENTER or doctor if you feel unwell.

**Precautionary Statements - Storage**

Store in a well-ventilated place. Keep container tightly closed  
 Store locked up  
 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F

**Precautionary Statements - Disposal**

Dispose of contents/container to an approved waste disposal plant

**Hazards not otherwise classified (HNOC)**

**Other Information**

- MAY BE HARMFUL IF SWALLOWED
- Harmful to aquatic life with long lasting effects
- Harmful to aquatic life

**3. Composition/information on Ingredients**

**Synonyms** Metered Air Freshener.  
**Chemical Family** MIXTURES.  
**Formula** 7-8165

Chemical name	CAS No	weight-%	Trade secret
Acetone	67-64-1	25-30	*
Diethylene Glycol Monoethyl Ether	111-90-0	20-25	*
N-Butane	106-97-8	15-20	*
1,1-Difluoroethane	75-37-6	10-15	*
Propane	74-98-6	5-10	*
Petroleum distillates, hydrotreated light	64742-47-8	1-5	*

\* The exact percentage (concentration) of composition has been withheld as a trade secret.

**4. First aid measures**

**FIRST AID MEASURES**

**Eye Contact** Hold eye open and rinse slowly and gently with water for 15-20 minutes. Remove contact lenses, if present, after the first 5 minutes, then continue rinsing eye. Call a poison control center or doctor for treatment advice.

**Skin contact** In case of contact, immediately flush skin with plenty of water. Wash skin with soap and water. If irritation develops, consult a physician.

**inhalation** If overcome by vapor, move person to fresh air. If person is not breathing, call 911 or an ambulance, then provide artificial respiration, preferably mouth-to-mouth, if possible. Call a poison control center or doctor for further treatment advise.

**INGESTION** Ingestion from an aerosol product is unlikely to occur. Contains petroleum distillates. Harmful if swallowed. If accidentally swallowed, do not induce vomiting, call physician immediately.

**Most important symptoms and effects, both acute and delayed**

**Symptoms** Acute: Prolonged inhalation of concentrated vapor or mist may cause headaches, dizziness and nausea. Prolonged and repeated contact with skin may cause irritation and reddening. Contact with eyes causes irritation.

**Indication of any immediate medical attention and special treatment needed**

**Note to physicians** Treat symptomatically.

**5. Fire-fighting measures**

**Suitable extinguishing media**  
Dry chemical, CO2 or water spray.

**Unsuitable extinguishing media** Caution: Use of water spray when fighting fire may be inefficient.

**Specific hazards arising from the chemical**  
This product is under pressure. Water spray may be used to cool cans in the vicinity of fire or excessive heat to prevent the explosion of the cans.

**Hazardous combustion products** Thermal decomposition may yield gases like carbon monoxide, carbon dioxide, hydrofluoric acid and carbonyl halides.

**Explosion data**  
**Sensitivity to Mechanical Impact** Contents are under pressure. Handle an extremely flammable material. Follow label directions for correct installation and placement of dispenser. Store cans in a cool, dry place away from heat and open flame.  
**Sensitivity to Static Discharge** Keep away from heat, sparks, flame, and other sources of ignition (i.e., pilot lights, electric motors and static electricity).

**Protective equipment and precautions for firefighters**  
As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**6. Accidental release measures**

**Personal precautions, protective equipment and emergency procedures**

**Personal precautions** Use with adequate general or local exhaust ventilation.

**For emergency responders** Remove all sources of ignition.

**Environmental Precautions**

**Environmental Precautions** See Section 12 for additional Ecological Information.

**Methods and material for containment and cleaning up**

**Methods for Containment** Provide adequate ventilation to area being treated. Soak up spills with chemically inert, absorbent material.

**Methods for cleaning up** Clean contaminated surface thoroughly.

**7. Handling and Storage**

**Precautions for safe handling**

**Advice on safe handling** Handle as an extremely flammable material. Follow label directions for correct installation and placement of dispenser. Store cans in a cool, dry place away from heat and open flame.

**Conditions for safe storage, including any incompatibilities**

**Storage Conditions** Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). **AEROSOL STORAGE LEVEL III (NFPA-30B).**

**Incompatible Materials** Avoid heat, open flame and contact with strong oxidizers, inorganic acids and halogens.

**8. Exposure Controls/Personal Protection**

**Control parameters**

**Exposure guidelines** See occupational exposure limits listed below.

Chemical name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Acetone 67-64-1	STEL: 750 ppm TWA: 500 ppm	TWA: 1000 ppm TWA: 2400 mg/m <sup>3</sup> (vacated) TWA: 750 ppm (vacated) TWA: 1800 mg/m <sup>3</sup> (vacated) STEL: 2400 mg/m <sup>3</sup> The acetone STEL does not apply to the cellulose acetate fiber industry. It is in effect for all other sectors (vacated) STEL: 1000 ppm	IDLH: 2500 ppm TWA: 250 ppm TWA: 590 mg/m <sup>3</sup>
N-Butane 106-97-8	STEL: 1000 ppm	(vacated) TWA: 800 ppm (vacated) TWA: 1900 mg/m <sup>3</sup>	TWA: 800 ppm TWA: 1900 mg/m <sup>3</sup>
Propane 74-98-6	TWA: 1000 ppm	TWA: 1000 ppm TWA: 1800 mg/m <sup>3</sup> (vacated) TWA: 1000 ppm (vacated) TWA: 1800 mg/m <sup>3</sup>	IDLH: 2100 ppm TWA: 1000 ppm TWA: 1800 mg/m <sup>3</sup>

**Appropriate engineering controls**

**Engineering controls** Use with adequate general or local exhaust ventilation.

**Individual protection measures, such as personal protective equipment**

**Eye/face Protection** Conventional eyeglasses to guard against splashing.

**Skin and Body Protection** Household type gloves.

**Respiratory protection** Use in a well-ventilated area ONLY. None required if used in a well-ventilated area. Follow label directions for correct use of the product..

**General hygiene considerations** Wash hands thoroughly after handling.



**Hazardous decomposition products**

Thermal decomposition may yield gases like carbon monoxide, carbon dioxide, hydrofluoric acid and carbonyl halides.

**11. Toxicological Information**

Information on likely routes of exposure

<b>Product Information</b>	This product has not been tested as whole. See below for information on ingredients.
<b>inhalation</b>	no data available.
<b>Eye Contact</b>	no data available.
<b>Skin contact</b>	no data available.
<b>INGESTION</b>	no data available.

Chemical name	Oral LD50	dermal LD50	Inhalation LC50
Acetone 67-64-1	= 5800 mg/kg ( Rat )	-	= 50100 mg/m <sup>3</sup> ( Rat ) 8 h
Diethylene Glycol Monoethyl Ether 111-90-0	= 1920 mg/kg ( Rat )	= 6 mL/kg ( Rat ) = 4200 µL/kg ( Rabbit )	> 5240 mg/m <sup>3</sup> ( Rat ) 4 h
N-Butane 106-97-8	-	-	= 658 g/m <sup>3</sup> ( Rat ) 4 h
Propane 74-98-6	-	-	= 658 mg/L ( Rat ) 4 h
Petroleum distillates, hydrotreated light 64742-47-8	> 5000 mg/kg ( Rat )	> 2000 mg/kg ( Rabbit )	> 5.2 mg/L ( Rat ) 4 h

Information on toxicological effects

**Symptoms** Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

<b>Skin corrosion/irritation</b>	May cause skin irritation and reddening after prolonged or repeated contact with skin.
<b>Serious eye damage/eye irritation</b>	Irritating to eyes.
<b>irritation</b>	May cause skin and eye irritation.
<b>corrosivity</b>	Not applicable.
<b>sensitization</b>	No information available.
<b>Germ Cell Mutagenicity</b>	No information available.
<b>carcinogenicity</b>	Not known chronic effects based on available data. None of the ingredients present in excess of 0.1% are listed as carcinogenic by NTP, IARC or OSHA.
<b>Reproductive Toxicity</b>	No information available.
<b>STOT - single exposure</b>	No information available.
<b>STOT - repeated exposure</b>	No information available.
<b>Aspiration Hazard</b>	No information available.

Numerical measures of toxicity - Product Information

<b>Unknown acute toxicity</b>	-
<b>The following values are calculated based on chapter 3.1 of the GHS document .</b>	
<b>ATEmix (oral)</b>	4755 mg/kg
<b>ATEmix (dermal)</b>	31248 mg/kg
<b>ATEmix (inhalation-gas)</b>	10804 mg/l
<b>ATEmix (inhalation-dust/mist)</b>	15 mg/l
<b>ATEmix (inhalation-vapor)</b>	78 mg/l

**12. Ecological Information**

**FG 438-5180-5 CHAMPION SPRAYON SPRAY SCENTS METERED AIR FRESHENER PINA COLADA**

This product does not contain marine pollutants.

**ecotoxicity**

43.63% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical name	Algae/aquatic plants	Fish	Toxicity to Microorganisms	Crustacea
Acetone 67-64-1		6210 - 8120: 96 h Pimephales promelas mg/L LC50 static 4.74 - 6.33: 96 h Oncorhynchus mykiss mL/L LC50 8300: 96 h Lepomis macrochirus mg/L LC50	EC50 = 14500 mg/L 15 min	10294 - 17704: 48 h Daphnia magna mg/L EC50 Static 12600 - 12700: 48 h Daphnia magna mg/L EC50
Diethylene Glycol Monoethyl Ether 111-90-0		10000: 96 h Lepomis macrochirus mg/L LC50 static 19100 - 23900: 96 h Lepomis macrochirus mg/L LC50 flow-through 11400 - 15700: 96 h Oncorhynchus mykiss mg/L LC50 flow-through 11600 - 16700: 96 h Pimephales promelas mg/L LC50 flow-through 13400: 96 h Salmo gairdneri mg/L LC50 flow-through		3940 - 4670: 48 h Daphnia magna mg/L EC50
Petroleum distillates, hydrotreated light 64742-47-8		45: 96 h Pimephales promelas mg/L LC50 flow-through 2.4: 96 h Oncorhynchus mykiss mg/L LC50 static 2.2: 96 h Lepomis macrochirus mg/L LC50 static		4720: 96 h Den-dronereides heteropoda mg/L LC50

**Persistence and degradability**

No information available.

**Bioaccumulation**

No information available.

Chemical name	Partition coefficient
Acetone 67-64-1	-0.24
Diethylene Glycol Monoethyl Ether 111-90-0	-0.8
N-Butane 106-97-8	2.89
Propane 74-98-6	2.3

**Other adverse effects**

No information available

**13. Disposal Considerations**

**Waste treatment methods**

**Disposal of wastes**

Dispose of in accordance with federal, state and local regulations.

**Contaminated packaging**

Pressurized container: Do not pierce or burn, even after use. Do not puncture or incinerate container. If empty: Place in trash or offer for recycling if available. If partly filled: Call your local solid waste agency for disposal instructions.

Chemical name	RCRA	RCRA - Basis for Listing	RCRA - D Series Wastes	RCRA - U Series Wastes
Acetone 67-64-1		Included in waste stream: F039		U002

Chemical name	California Hazardous Waste Status
Acetone 67-64-1	Ignitable

**14. Transport Information**

**DOT** Limited Quantity - Metered Air Freshener  
**UN/ID no** UN1950  
**Proper Shipping Name** Limited quantity (LQ)  
**Hazard Class** 2.1  
**Marine pollutant** This product does not contain marine pollutants.

**15. Regulatory information**

**International Inventories**

**TSCA** All ingredients of this product are listed or are excluded from listing under the U.S. Toxic Substances Control Act (TSCA) Chemical Substance Inventory.  
**DSL** All ingredients are listed or are excluded from listing on the DSL.

**Legend:**

*TSCA - United States Toxic Substances Control Act Section 8(b) Inventory*  
*DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List*

**US Federal Regulations**

**SARA 313**

This product contains the following toxic chemicals subject to the reporting requirements of Section 313 of the Emergency Planning and Community Right-to-Know Act of 1986 and 40 CFR 372. This information must be included in all SDSs that are copied and distributed for this material.

Chemical name	CAS No	weight-%	SARA 313 - Threshold Values %
Diethylene Glycol Monoethyl Ether - 111-90-0	111-90-0	20-25	1.0

**SARA 311/312 Hazard Categories**

**Acute Health Hazard** yes  
**Chronic Health Hazard** No  
**Fire Hazard** yes  
**Sudden release of pressure hazard** No  
**Reactive Hazard** No

**CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

**CERCLA**

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Acetone 67-64-1	5000 lb		RQ 5000 lb final RQ RQ 2270 kg final RQ

**US State Regulations**



**California Proposition 65**

This product does not contain any Proposition 65 chemicals

**U.S. State Right-to-Know Regulations**

Chemical name	New Jersey	Massachusetts	Pennsylvania
Acetone 67-64-1	X	X	X
Diethylene Glycol Monoethyl Ether 111-90-0	X		X
N-Butane 106-97-8	X	X	X
1,1-Difluoroethane 75-37-6	X	X	
Propane 74-98-6	X	X	X

**U.S. EPA Label information**

EPA Pesticide registration number Not applicable

**16. Other information**

<u>NFPA</u>	Health Hazards 2	Flammability 4	Instability 1	Physical and chemical properties Not applicable Personal Protection B - Eyes and hands protection
<u>HMIS</u>	Health Hazards 2	Flammability 4	Physical Hazards 1	

Prepared by Regulatory Department  
Issue date 18-Dec-2014

**Revision note**

This SDS supersedes a previous MSDS dated January 24, 2013.

**Disclaimer**

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**