



Transport Information Document

Date: August 12, 2019

3M ID Number: 61-0000-6324-0

Product Description: 3M(TM) NEUTRAL CLEANER CONCENTRATE 3H, GRAY CAP, 2 LTR SAMPLE

Transport Protective Service: PROTECTIVE SERVICE NOT REQUIRED

NMFC Item: 048580 NMFC Sub: 00 NMFC Class: 070.0

Flash Point (Closed-cup): 205°F/96°C

UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)
NOT REGULATED

UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)
NOT REGULATED

INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)
NOT REGULATED

INTERNATIONAL MARITIME ORGANIZATION (IMO)
NOT REGULATED

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit 3M.com/Transportinfo
or call 1-800-364-3577 or 651-737-6501 for assistance.



Safety Data Sheet

Copyright, 2018, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document Group:	28-7258-8	Version Number:	5.00
Issue Date:	05/22/18	Supersedes Date:	01/17/18

SECTION 1: Identification

1.1. Product identifier

3M™ Neutral Cleaner Concentrate (Product No. 3, 3M™ Chemical Management Systems)

Product Identification Numbers

ID Number	UPC	ID Number	UPC
61-0000-6324-0		61-0000-6325-7	
61-0000-6365-3		61-0000-6366-1	
61-0000-6403-2		70-0715-9194-8	00-48011-59168-6
70-0715-9195-5	00-48011-59167-9	70-0716-5816-8	000-51125-85789-5
70-0716-5855-6	00-48011-23902-1	70-0716-5856-4	00-48011-59168-6
70-0716-5857-2	00-48011-59167-9	70-0716-8340-6	00-48011-20200-1

1.2. Recommended use and restrictions on use

Recommended use

This product meets Green Seal™ Standard GS-37 based on effective performance, concentrated volume, minimized/recycled packaging, and protective limits on: VOCs and human & environmental toxicity. GreenSeal.org., Hard Surface Cleaner

1.3. Supplier's details

MANUFACTURER:	3M
DIVISION:	Commercial Solutions Division
ADDRESS:	3M Center, St. Paul, MN 55144-1000, USA
Telephone:	1-888-3M HELPS (1-888-364-3577)

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

2.1. Hazard classification

Serious Eye Damage/Irritation: Category 2A.

2.2. Label elements

Signal word

Warning

Symbols

Exclamation mark |

Pictograms**Hazard Statements**

Causes serious eye irritation.

Precautionary Statements**Prevention:**

Wear eye/face protection.
Wash thoroughly after handling.

Response:

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
If eye irritation persists: Get medical advice/attention.

7% of the mixture consists of ingredients of unknown acute oral toxicity.

7% of the mixture consists of ingredients of unknown acute dermal toxicity.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
WATER	7732-18-5	60 - 90 Trade Secret *
ETHOXYLATED C9-11 ALCOHOLS	68439-46-3	3 - 7 Trade Secret *
ALCOHOLS, C12-14, ETHOXYLATED PROPOXYLATED	68439-51-0	3 - 7 Trade Secret *
Surfactant (NJTSRN 04499600-6632)	Trade Secret*	0.5 - 1.5 Trade Secret *
Fragrance Added	Mixture	0.1 - 1.0 Trade Secret *

NJTS or NJTSRN: New Jersey Trade Secret Registry Number.

*The specific chemical identity and/or exact percentage (concentration) of this composition has been withheld as a trade secret.

SECTION 4: First aid measures**4.1. Description of first aid measures****Inhalation:**

Remove person to fresh air. If you feel unwell, get medical attention.

Skin Contact:

Wash with soap and water. If signs/symptoms develop, get medical attention.

Eye Contact:

Immediately flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. Get medical

attention.

If Swallowed:

Rinse mouth. If you feel unwell, get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable

SECTION 5: Fire-fighting measures

5.1. Suitable extinguishing media

Material will not burn. Non-combustible. Use a fire fighting agent suitable for surrounding fire.

5.2. Special hazards arising from the substance or mixture

None inherent in this product.

Hazardous Decomposition or By-Products

Substance

Carbon monoxide

Carbon dioxide

Condition

During Combustion

During Combustion

5.3. Special protective actions for fire-fighters

No special protective actions for fire-fighters are anticipated.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate area. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

6.2. Environmental precautions

Avoid release to the environment. For larger spills, cover drains and build dikes to prevent entry into sewer systems or bodies of water.

6.3. Methods and material for containment and cleaning up

Contain spill. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Remember, adding an absorbent material does not remove a physical, health, or environmental hazard. Collect as much of the spilled material as possible. Place in a closed container approved for transportation by appropriate authorities. Clean up residue with water. Seal the container. Dispose of collected material as soon as possible in accordance with applicable local/regional/national/international regulations.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid eye contact. For industrial or professional use only. This product is not intended to be used without prior dilution as specified on the product label. Grounding or safety shoes with electrostatic dissipating soles (ESD) are not required with a chemical dispensing system. Avoid breathing dust/fume/gas/mist/vapors/spray. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Avoid release to the environment. Avoid contact with oxidizing agents

(eg. chlorine, chromic acid etc.)

7.2. Conditions for safe storage including any incompatibilities

Store away from heat. Store away from oxidizing agents.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

No occupational exposure limit values exist for any of the components listed in Section 3 of this SDS.

8.2. Exposure controls

8.2.1. Engineering controls

NOTE: When used with a chemical dispensing system as directed, special ventilation is not required. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapors/spray. If ventilation is not adequate, use respiratory protection equipment.

8.2.2. Personal protective equipment (PPE)

Eye/face protection

NOTE: When used with a chemical dispensing system as directed, eye contact with the concentrate is not expected to occur. If the product is not used with a chemical dispensing system or if there is an accidental release, wear protective eye/face protection.

If product is not used with a chemical dispensing system or if there is an accidental release:

Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:

Indirect Vented Goggles

Skin/hand protection

NOTE: When used with a chemical dispensing system as directed, skin contact with the concentrate is not expected to occur. If product is not used with a chemical dispensing system or if there is an accidental release:

Select and use gloves and/or protective clothing approved to relevant local standards to prevent skin contact based on the results of an exposure assessment. Selection should be based on use factors such as exposure levels, concentration of the substance or mixture, frequency and duration, physical challenges such as temperature extremes, and other use conditions. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible gloves/protective clothing.

Note: Nitrile gloves may be worn over polymer laminate gloves to improve dexterity.

Gloves made from the following material(s) are recommended: Polymer laminate

Respiratory protection

NOTE: When used with a chemical dispensing system as directed, respiratory protection is not required.

If product is not used with a chemical dispensing system or if there is an accidental release:

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for organic vapors and particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

General Physical Form:	Liquid
Specific Physical Form:	Liquid
Odor, Color, Grade:	Bright, clear green-yellow liquid with citrus fragrance
Odor threshold	<i>No Data Available</i>
pH	6 - 7
Melting point	<i>Not Applicable</i>
Boiling Point	> 205 °F
Flash Point	205 °F [<i>Test Method:</i> Closed Cup]
Evaporation rate	Approximately 1 [<i>Ref Std:</i> WATER=1]
Flammability (solid, gas)	Not Applicable
Flammable Limits(LEL)	<i>No Data Available</i>
Flammable Limits(UEL)	<i>No Data Available</i>
Vapor Pressure	< 27 psia [<i>@ 131 °F</i>]
Vapor Density	<i>No Data Available</i>
Specific Gravity	1
Solubility in Water	Complete
Solubility- non-water	<i>No Data Available</i>
Partition coefficient: n-octanol/ water	<i>No Data Available</i>
Autoignition temperature	<i>No Data Available</i>
Decomposition temperature	<i>No Data Available</i>
Viscosity	< 100 centipoise
Volatile Organic Compounds	< 1 % weight
Percent volatile	<i>No Data Available</i>
VOC Less H2O & Exempt Solvents	< 70 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

This material may be reactive with certain agents under certain conditions - see the remaining headings in this section.

10.2. Chemical stability

Stable.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

Heat
Sparks and/or flames

10.5. Incompatible materials

Strong oxidizing agents

10.6. Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
None known.	

Refer to section 5.2 for hazardous decomposition products during combustion.

SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

11.1. Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation:

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Skin Contact:

Mild Skin Irritation: Signs/symptoms may include localized redness, swelling, itching, and dryness.

Eye Contact:

Severe Eye Irritation: Signs/symptoms may include significant redness, swelling, pain, tearing, cloudy appearance of the cornea, and impaired vision.

Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
Overall product	Dermal		No data available; calculated ATE >5,000 mg/kg
Overall product	Ingestion		No data available; calculated ATE >5,000 mg/kg
ETHOXYLATED C9-11 ALCOHOLS	Dermal	Rabbit	LD50 > 2,000 mg/kg
ETHOXYLATED C9-11 ALCOHOLS	Ingestion	Rat	LD50 1,378 mg/kg
Surfactant (NJTSRN 04499600-6632)	Dermal	Rabbit	LD50 > 2,000 mg/kg
Surfactant (NJTSRN 04499600-6632)	Ingestion	Rat	LD50 > 700 mg/kg
Fragrance Added	Inhalation-Vapor (4 hours)	Mouse	LC50 > 3.14 mg/l
Fragrance Added	Dermal	Rabbit	LD50 > 5,000 mg/kg
Fragrance Added	Ingestion	Rat	LD50 4,400 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
ETHOXYLATED C9-11 ALCOHOLS	Rabbit	Irritant
Surfactant (NJTSRN 04499600-6632)	similar health hazards	Irritant
Fragrance Added	Rabbit	Mild irritant

Serious Eye Damage/Irritation

Name	Species	Value
ETHOXYLATED C9-11 ALCOHOLS	Professional judgement	Corrosive
Surfactant (NJTSRN 04499600-6632)	Professional judgement	Corrosive
Fragrance Added	Rabbit	Mild irritant

Skin Sensitization

Name	Species	Value
ETHOXYLATED C9-11 ALCOHOLS	Guinea pig	Not classified
Fragrance Added	Mouse	Sensitizing

Respiratory Sensitization

For the component/components, either no data are currently available or the data are not sufficient for classification.

Germ Cell Mutagenicity

Name	Route	Value
ETHOXYLATED C9-11 ALCOHOLS	In Vitro	Not mutagenic
Fragrance Added	In Vitro	Not mutagenic
Fragrance Added	In vivo	Not mutagenic

Carcinogenicity

Name	Route	Species	Value
Fragrance Added	Ingestion	Rat	Some positive data exist, but the data are not sufficient for classification

Reproductive Toxicity

Reproductive and/or Developmental Effects

Name	Route	Value	Species	Test Result	Exposure Duration
ETHOXYLATED C9-11 ALCOHOLS	Dermal	Not classified for female reproduction	Rat	NOAEL 250 mg/kg/day	2 generation
ETHOXYLATED C9-11 ALCOHOLS	Dermal	Not classified for development	Rat	NOAEL 250 mg/kg/day	2 generation
ETHOXYLATED C9-11 ALCOHOLS	Dermal	Not classified for male reproduction	Rat	NOAEL 100 mg/kg/day	2 generation
Fragrance Added	Ingestion	Not classified for female reproduction	Rat	NOAEL 750 mg/kg/day	prematuring & during gestation
Fragrance Added	Ingestion	Not classified for development	Multiple animal species	NOAEL 591 mg/kg/day	during organogenesis

Target Organ(s)

Specific Target Organ Toxicity - single exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
ETHOXYLATED C9-11 ALCOHOLS	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification	Not available	NOAEL Not available	not available
Surfactant (NJTSRN 04499600-6632)	Inhalation	respiratory irritation	May cause respiratory irritation	similar health hazards	NOAEL Not available	

Fragrance Added	Ingestion	nervous system	Not classified		NOAEL Not available	
-----------------	-----------	----------------	----------------	--	---------------------	--

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
ETHOXYLATED C9-11 ALCOHOLS	Dermal	kidney and/or bladder hematopoietic system	Not classified	Rat	NOAEL 125 mg/kg/day	13 weeks
Fragrance Added	Ingestion	kidney and/or bladder	Not classified	Rat	LOAEL 75 mg/kg/day	103 weeks
Fragrance Added	Ingestion	liver	Not classified	Mouse	NOAEL 1,000 mg/kg/day	103 weeks
Fragrance Added	Ingestion	heart endocrine system bone, teeth, nails, and/or hair hematopoietic system immune system muscles nervous system respiratory system	Not classified	Rat	NOAEL 600 mg/kg/day	103 weeks

Aspiration Hazard

Name	Value
Fragrance Added	Aspiration hazard

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information

Ecotoxicological information

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

SECTION 13: Disposal considerations

13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Dispose of waste product in a permitted industrial waste facility. Empty drums/barrels/containers used for transporting and handling hazardous chemicals (chemical substances/mixtures/preparations classified as Hazardous as per applicable regulations) shall be considered, stored, treated & disposed of as hazardous wastes unless otherwise defined by applicable waste regulations. Consult with the respective regulating authorities to determine the available treatment and disposal facilities.

EPA Hazardous Waste Number (RCRA): Not regulated

SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: Regulatory information

15.1. US Federal Regulations

EPCRA 311/312 Hazard Classifications:

Physical Hazards

Not applicable

Health Hazards

Serious eye damage or eye irritation

15.2. State Regulations

15.3. Chemical Inventories

The components of this material are in compliance with the provisions of Australia National Industrial Chemical Notification and Assessment Scheme (NICNAS). Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the new substance notification requirements of CEPA.

The components of this material are in compliance with the China "Measures on Environmental Management of New Chemical Substance". Certain restrictions may apply. Contact the selling division for additional information.

The components of this material are in compliance with the provisions of Philippines RA 6969 requirements. Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the chemical notification requirements of TSCA. All required components of this product are listed on the active portion of the TSCA Inventory.

This product complies with the New Zealand Hazardous Substances and New Organisms Act (1996).

15.4. International Regulations

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: Other information

NFPA Hazard Classification

Health: 2 Flammability: 0 Instability: 0 Special Hazards: None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

HMIS Hazard Classification

Health: 2 Flammability: 0 Physical Hazard: 0 Personal Protection: X - See PPE section.

Hazardous Material Identification System (HMIS® IV) hazard ratings are designed to inform employees of chemical hazards

in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® IV ratings are to be used with a fully implemented HMIS® IV program. HMIS® is a registered mark of the American Coatings Association (ACA).

Document Group:	28-7258-8	Version Number:	5.00
Issue Date:	05/22/18	Supersedes Date:	01/17/18

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M.

3M USA SDSs are available at www.3M.com