



SAFETY DATA SHEET

Issuing Date January 5, 2015

Revision Date New

Revision Number 0

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Name Clorox® Outdoor Bleach

Other means of identification

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended use General purpose bleach for outdoor surfaces

Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Address

The Clorox Company
1221 Broadway
Oakland, CA 94612

Phone: 1-510-271-7000

Emergency telephone number

Emergency Phone Numbers

For Medical Emergencies, call: 1-800-446-1014
For Transportation Emergencies, call Chemtrec: 1-800-424-9300

2. HAZARDS IDENTIFICATION


Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200).

Skin corrosion/irritation	Category 1
Serious eye damage/eye irritation	Category 1

GHS Label elements, including precautionary statements

Emergency Overview

Signal word	Danger		
Hazard Statements	Causes severe skin burns and eye damage Causes serious eye damage		
			
Appearance	Clear, pale yellow	Physical State	Viscous liquid
			Odor Bleach

Precautionary Statements - Prevention

Do not breathe dusts or mists.

Wash face, hands and any exposed skin thoroughly after handling.

Wear protective gloves, protective clothing, face protection, and eye protection such as safety glasses.

Precautionary Statements - Response

Immediately call a poison center or doctor.

If swallowed: Rinse mouth. Do NOT induce vomiting.

If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water.

Wash contaminated clothing before reuse.

If inhaled: Remove person to fresh air and keep comfortable for breathing.

Specific treatment (see supplemental first aid instructions on this label).

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Precautionary Statements - Storage

Store locked up.

Precautionary Statements - Disposal

Dispose of contents in accordance with all applicable federal, state, and local regulations.

Hazards not otherwise classified (HNOC)

Although not expected, heart conditions or chronic respiratory problems such as asthma, chronic bronchitis, or obstructive lung disease may be aggravated by exposure to high concentrations of vapor or mist.

Unknown Toxicity

Not applicable.

Other information

Very toxic to aquatic life with long lasting effects.

Interactions with Other Chemicals

Reacts with other household chemicals such deck cleaners, wood bleaches, wood restorers, rust removers, wood or masonry finishes, toilet bowl cleaners, acids or products containing ammonia to produce hazardous gases, such as chlorine and other chlorinated compounds.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS-No	Weight %	Trade Secret
Sodium hypochlorite	7681-52-9	3 - 7	*
Sodium hydroxide	1310-73-2	0.1 - 1	*

* The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures

General Advice	Show this safety data sheet to the doctor in attendance.
Eye Contact	Flush immediately with water for at least 15 minutes. If wearing contact lenses, remove after first 5 minutes. Call a doctor or poison control center immediately.
Skin Contact	Remove contaminated clothing and wash skin thoroughly with water. If irritation persists, call a doctor.
Inhalation	Move to fresh air. If breathing is affected, call a doctor.
Ingestion	Drink a glassful of water. DO NOT induce vomiting unless told to do so by a poison control center or doctor. Call a doctor or poison control center immediately.
Protection of First-aiders	Avoid contact with skin, eyes, and clothing. Use personal protective equipment as required. Wear personal protective clothing (see section 8).

Most important symptoms and effects, both acute and delayed

Most Important Symptoms and Effects	Burning of eyes and skin.
--	---------------------------

Indication of any immediate medical attention and special treatment needed

Notes to Physician	Treat symptomatically. Use of gastric lavage or emesis is contraindicated.
---------------------------	--

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable Extinguishing Media

CAUTION: Use of water spray when fighting fire may be inefficient.

Specific Hazards Arising from the Chemical

This product causes burns to eyes, skin, and mucous membranes. Thermal decomposition can release sodium chlorate and irritating gases and vapors.

Explosion Data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions

Avoid contact with eyes, skin, and clothing. Ensure adequate ventilation. Use personal protective equipment as required. For spills of multiple products, responders should evaluate the MSDSs of the products for incompatibility with sodium hypochlorite. Breathing protection should be worn in enclosed and/or poorly-ventilated areas until hazard assessment is complete.

Other Information

Refer to protective measures listed in Sections 7 and 8.

Environmental precautions

Environmental Precautions

See Section 12 for ecological information.

Methods and material for containment and cleaning up

Methods for Containment

Prevent further leakage or spillage if safe to do so.

Methods for Cleaning Up

Absorb and containerize. Wash residual down to sanitary sewer. Contact the sanitary treatment facility in advance to assure ability to process washed-down material.

7. HANDLING AND STORAGE

Precautions for safe handling

Handling

Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes, and clothing. Do not eat, drink, or smoke when using this product.

Conditions for safe storage, including any incompatibilities

Storage

Keep containers tightly closed in a dry, cool, and well-ventilated place.

Incompatible Products

Deck cleaners, wood bleaches, wood restorers, rust removers, wood or masonry finishes, toilet bowl cleaners, acids, and products containing ammonia.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Sodium hydroxide 1310-73-2	Ceiling: 2 mg/m ³	TWA: 2 mg/m ³	IDLH: 10 mg/m ³ Ceiling: 2 mg/m ³
Sodium hypochlorite 7681-52-9	None	None	None

ACGIH TLV: American Conference of Governmental Industrial Hygienists - Threshold Limit Value. OSHA PEL: Occupational Safety and Health Administration - Permissible Exposure Limits. NIOSH IDLH: Immediately Dangerous to Life or Health.

Appropriate engineering controls

Engineering Measures Showers
 Eyewash stations
 Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/Face Protection If splashes are likely to occur: Wear safety glasses with side shields (or goggles) or face shield.

Skin and Body Protection Wear rubber or neoprene gloves and protective clothing such as long-sleeved shirt.

Respiratory Protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

Hygiene Measures Wash hands after direct contact. Do not wear product-contaminated clothing for prolonged periods. Remove and wash contaminated clothing before re-use. Do not eat, drink, or smoke when using this product.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

Physical State	Viscous liquid	Odor	Bleach
Appearance	Clear	Odor Threshold	No information available
Color	Pale yellow		

<u>Property</u>	<u>Values</u>	<u>Remarks/ Method</u>
pH	~12.9	None known
Melting/freezing point	No data available	None known
Boiling point / boiling range	No data available	None known
Flash Point	Not flammable	None known
Evaporation rate	No data available	None known
Flammability (solid, gas)	No data available	None known
Flammability Limits in Air		
Upper flammability limit	No data available	None known
Lower flammability limit	No data available	None known
Vapor pressure	No data available	None known
Vapor density	No data available	None known
Specific Gravity	~1.1	None known
Water Solubility	Soluble in water	None known
Solubility in other solvents	No data available	None known
Partition coefficient: n-octanol/water	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature	No data available	None known
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	None known
Explosive Properties	Not explosive	
Oxidizing Properties	No data available	

Other Information

Softening Point	No data available
VOC Content (%)	No data available
Particle Size	No data available
Particle Size Distribution	No data available

10. STABILITY AND REACTIVITY

Reactivity

Reacts with other household chemicals such deck cleaners, wood bleaches, wood restorers, rust removers, wood or masonry finishes, toilet bowl cleaners, acids or products containing ammonia to produce hazardous gases, such as chlorine and other chlorinated compounds.

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

None known based on information supplied.

Incompatible materials

Deck cleaners, wood bleaches, wood restorers, rust removers, wood or masonry finishes, toilet bowl cleaners, acids, and products containing ammonia.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation	Exposure to vapor or mist may irritate respiratory tract and cause coughing. Inhalation of high concentrations may cause pulmonary edema.
Eye Contact	Corrosive. May cause severe damage to eyes.
Skin Contact	May cause severe irritation to skin. Prolonged contact may cause burns to skin.
Ingestion	Ingestion may cause burns to gastrointestinal tract and respiratory tract, nausea, vomiting, and diarrhea.

Component Information

Chemical Name	LD50 Oral	LD50 Dermal	LC50 Inhalation
Sodium hypochlorite 7681-52-9	8200 mg/kg (Rat)	>10000 mg/kg (Rabbit)	-
Sodium hydroxide 1310-73-2	-	1350 mg/kg (Rabbit)	-

Information on toxicological effects

Symptoms	May cause redness and tearing of the eyes. May cause burns to eyes. May cause redness or burns to skin. Inhalation may cause coughing.
-----------------	--

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization	No information available.
Mutagenic Effects	No information available.
Carcinogenicity	The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
Sodium hypochlorite 7681-52-9	-	Group 3	-	-

IARC (International Agency for Research on Cancer)
Group 3 - Not Classifiable as to Carcinogenicity in Humans

Reproductive Toxicity	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Chronic Toxicity	Carcinogenic potential is unknown.
Target Organ Effects	Respiratory system, eyes, skin, gastrointestinal tract (GI).
Aspiration Hazard	No information available.

Numerical measures of toxicity - Product Information

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral)

40 g/kg

ATEmix (inhalation-dust/mist)

29 mg/L

12. ECOLOGICAL INFORMATION**Ecotoxicity**

Very toxic to aquatic life with long lasting effects.

Persistence and Degradability

No information available.

Bioaccumulation

No information available.

Other adverse effects

No information available.

13. DISPOSAL CONSIDERATIONS**Disposal methods**

Dispose of in accordance with all applicable federal, state, and local regulations.

Contaminated Packaging

Do not reuse empty containers. Dispose of in accordance with all applicable federal, state, and local regulations.

14. TRANSPORT INFORMATION**DOT**

NOT REGULATED.

TDG**UN-No**

UN3082

Proper Shipping Name

ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.

Hazard Class

9

Packing Group

III

Description

UN3082, ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (SODIUM HYPOCHLORITE), 9, III, MARINE POLLUTANT

ICAO**UN-No**

UN3082

Proper Shipping Name

ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.

Hazard Class

9

Packing Group

III

Description

UN3082, ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (SODIUM HYPOCHLORITE), 9, III

IATA

UN-No UN3082
Proper Shipping Name ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.
Hazard Class 9
Packing Group III
Description UN3082, ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (SODIUM HYPOCHLORITE), 9, III

IMDG/IMO

UN-No UN3082
Proper Shipping Name ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.
Hazard Class 9
Packing Group III
EmS No. F-A, S-F
Marine Pollutant Product is a marine pollutant according to the criteria set by IMDG/IMO
Description UN3082, ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (SODIUM HYPOCHLORITE), 9, III, MARINE POLLUTANT

15. REGULATORY INFORMATION

Chemical Inventories

TSCA All components of this product are either on the TSCA 8(b) Inventory or otherwise exempt from listing.
DSL/NDSL All components are on the DSL or NDSL.

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

U.S. Federal Regulations

SARA 313
 Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute Health Hazard	Yes
Chronic Health Hazard	No
Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

Clean Water Act

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Sodium hypochlorite 7681-52-9	100 lb			X
Sodium hydroxide 1310-73-2	1000 lb			X

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical Name	Hazardous Substances RQs	Extremely Hazardous Substances RQs	RQ
Sodium hypochlorite 7681-52-9	100 lb	-	RQ 100 lb final RQ RQ 45.4 kg final RQ
Sodium hydroxide 1310-73-2	1000 lb	-	RQ 1000 lb final RQ RQ 454 kg final RQ

US State Regulations**California Proposition 65**

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania	Rhode Island	Illinois
Sodium hypochlorite 7681-52-9	X	X	X	X	
Sodium hydroxide 1310-73-2	X	X	X	X	

International Regulations**Canada****WHMIS Hazard Class**

E - Corrosive material

**16. OTHER INFORMATION**

NFPA Health Hazard 3 Flammability 0 Instability 0 Physical and Chemical Hazards -

HMIS Health Hazard 3 Flammability 0 Physical Hazard 0 Personal Protection B

Prepared By Product Stewardship
23 British American Blvd.
Latham, NY 12110
1-800-572-6501

Revision Date New

Revision Note New

Reference 1114833/166110.001

General Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal, and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet