



## Safety Data Sheet

Copyright, 2014, 3M Company. All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

<b>Document Group:</b>	32-0785-9	<b>Version Number:</b>	3.01
<b>Issue Date:</b>	08/14/14	<b>Supersedes Date:</b>	12/23/13

### SECTION 1: Identification

#### 1.1. Product identifier

3M™ Glass Cleaner and Protector, Ready-To-Use

#### Product Identification Numbers

70-0715-9584-0, 70-0716-5815-0

#### 1.2. Recommended use and restrictions on use

##### Recommended use

Glass Cleaner and Protector, Hard Surface Cleaner

#### 1.3. Supplier's details

<b>MANUFACTURER:</b>	3M
<b>DIVISION:</b>	Commercial Solutions Division
<b>ADDRESS:</b>	3M Center, St. Paul, MN 55144-1000, USA
<b>Telephone:</b>	1-888-3M HELPS (1-888-364-3577)

#### 1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

### SECTION 2: Hazard identification

#### 2.1. Hazard classification

Not classified as hazardous according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

#### 2.2. Label elements

##### Signal word

Not applicable.

##### Symbols

Not applicable.

##### Pictograms

Not applicable.

#### 2.3. Hazards not otherwise classified

None.

### SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
WATER	7732-18-5	> 99 Trade Secret *
Non-ionic Surfactants (NJTSRN 04499600-6633)	Trade Secret*	< 1 Trade Secret *
ISOPROPYL ALCOHOL	67-63-0	< 1 Trade Secret *
ETHOXYLATED C9-11 ALCOHOLS	68439-46-3	< 1 Trade Secret *
SODIUM LAURYL SULFATE	151-21-3	< 1 Trade Secret *
Fragrance Added	Mixture	< 0.01 Trade Secret *

NJTS or NJTSRN: New Jersey Trade Secret Registry Number.

\*The specific chemical identity and/or exact percentage (concentration) of this composition has been withheld as a trade secret.

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

#### Inhalation:

Remove person to fresh air. If you feel unwell, get medical attention.

#### Skin Contact:

Wash with soap and water. If signs/symptoms develop, get medical attention.

#### Eye Contact:

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

#### If Swallowed:

Rinse mouth. If you feel unwell, get medical attention.

### 4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

### 4.3. Indication of any immediate medical attention and special treatment required

Not applicable

## SECTION 5: Fire-fighting measures

### 5.1. Suitable extinguishing media

Material will not burn. Non-combustible. Use a fire fighting agent suitable for surrounding fire.

### 5.2. Special hazards arising from the substance or mixture

None inherent in this product.

### 5.3. Special protective actions for fire-fighters

No special protective actions for fire-fighters are anticipated.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Ventilate the area with fresh air. Observe precautions from other sections.

### 6.2. Environmental precautions

Avoid release to the environment. For larger spills, cover drains and build dikes to prevent entry into sewer systems or bodies of water.

**6.3. Methods and material for containment and cleaning up**

Contain spill. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Remember, adding an absorbent material does not remove a physical, health, or environmental hazard. Collect as much of the spilled material as possible. Place in a closed container approved for transportation by appropriate authorities. Clean up residue with water. Seal the container. Dispose of collected material as soon as possible.

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

Keep out of reach of children. Avoid breathing mist/spray. Do not eat, drink or smoke when using this product. Wash thoroughly after handling.

**7.2. Conditions for safe storage including any incompatibilities**

No special storage requirements.

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational exposure limits**

Ingredient	C.A.S. No.	Agency	Limit type	Additional Comments
ISOPROPYL ALCOHOL	67-63-0	ACGIH	TWA:200 ppm;STEL:400 ppm	A4: Not class. as human carcin
ISOPROPYL ALCOHOL	67-63-0	OSHA	TWA:980 mg/m <sup>3</sup> (400 ppm)	

ACGIH : American Conference of Governmental Industrial Hygienists

AIHA : American Industrial Hygiene Association

CMRG : Chemical Manufacturer's Recommended Guidelines

OSHA : United States Department of Labor - Occupational Safety and Health Administration

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit

CEIL: Ceiling

**8.2. Exposure controls****8.2.1. Engineering controls**

Use in a well-ventilated area.

**8.2.2. Personal protective equipment (PPE)****Eye/face protection**

Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended: Safety Glasses with side shields

**Skin/hand protection**

No chemical protective gloves are required.

**Respiratory protection**

Under normal use conditions, airborne exposures are not expected to be significant enough to require respiratory protection.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

<b>General Physical Form:</b>	Liquid
<b>Odor, Color, Grade:</b>	Clear light blue / apple scent
<b>Odor threshold</b>	<i>No Data Available</i>

pH	6.5 - 8.5
Melting point	<i>No Data Available</i>
Boiling Point	212 °F
Flash Point	No flash point
Evaporation rate	<i>No Data Available</i>
Flammability (solid, gas)	Not Applicable
Flammable Limits(LEL)	<i>Not Applicable</i>
Flammable Limits(UEL)	<i>Not Applicable</i>
Vapor Pressure	<i>No Data Available</i>
Vapor Density	<i>No Data Available</i>
Density	<i>No Data Available</i>
Specific Gravity	1
Solubility in Water	Complete
Solubility- non-water	<i>No Data Available</i>
Partition coefficient: n-octanol/ water	<i>No Data Available</i>
Autoignition temperature	<i>No Data Available</i>
Decomposition temperature	<i>No Data Available</i>
Viscosity	5 - 10 centipoise
Volatile Organic Compounds	< 0.1 % weight
VOC Less H2O & Exempt Solvents	< 2000 g/L

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

This material is considered to be non reactive under normal use conditions.

### 10.2. Chemical stability

Stable.

### 10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

### 10.4. Conditions to avoid

None known.

### 10.5. Incompatible materials

None known.

### 10.6. Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
Carbon monoxide	Not Specified
Carbon dioxide	Not Specified

## SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

### 11.1. Information on Toxicological effects

#### Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation:

Sprayed material may cause irritation of the respiratory system. Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

**Skin Contact:**

Contact with the skin during product use is not expected to result in significant irritation.

**Eye Contact:**

Sprayed material may cause eye irritation. Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

**Ingestion:**

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

**Toxicological Data**

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

**Acute Toxicity**

Name	Route	Species	Value
Overall product	Ingestion		No data available; calculated ATE > 5,000 mg/kg
Non-ionic Surfactants (NJTSRN 04499600-6633)	Dermal	Rabbit	LD50 > 11,200 mg/kg
Non-ionic Surfactants (NJTSRN 04499600-6633)	Ingestion	Rat	LD50 3,730 mg/kg
ISOPROPYL ALCOHOL	Dermal	Rabbit	LD50 12,870 mg/kg
ISOPROPYL ALCOHOL	Inhalation-Vapor (4 hours)	Rat	LC50 72.6 mg/l
ISOPROPYL ALCOHOL	Ingestion	Rat	LD50 4,710 mg/kg
ETHOXYLATED C9-11 ALCOHOLS	Dermal	Rabbit	LD50 > 2,000 mg/kg
ETHOXYLATED C9-11 ALCOHOLS	Ingestion	Rat	LD50 1,378 mg/kg
SODIUM LAURYL SULFATE	Inhalation-Dust/Mist		LC50 > 0.975 mg/l
SODIUM LAURYL SULFATE	Dermal	Rabbit	LD50 580 mg/kg
SODIUM LAURYL SULFATE	Ingestion	Rat	LD50 1,650 mg/kg

ATE = acute toxicity estimate

**Skin Corrosion/Irritation**

Name	Species	Value
ISOPROPYL ALCOHOL	Multiple animal species	No significant irritation
ETHOXYLATED C9-11 ALCOHOLS	Rabbit	Irritant
SODIUM LAURYL SULFATE	Rabbit	Irritant

**Serious Eye Damage/Irritation**

Name	Species	Value
ISOPROPYL ALCOHOL	Rabbit	Severe irritant
ETHOXYLATED C9-11 ALCOHOLS		Corrosive
SODIUM LAURYL SULFATE	Rabbit	Corrosive

**Skin Sensitization**

Name	Species	Value
ISOPROPYL ALCOHOL	Guinea pig	Not sensitizing
ETHOXYLATED C9-11 ALCOHOLS	Guinea pig	Not sensitizing

**Respiratory Sensitization**

Name	Species	Value
------	---------	-------

**Germ Cell Mutagenicity**

Name	Route	Value
------	-------	-------

ISOPROPYL ALCOHOL	In Vitro	Not mutagenic
ISOPROPYL ALCOHOL	In vivo	Not mutagenic
ETHOXYLATED C9-11 ALCOHOLS	In Vitro	Not mutagenic

**Carcinogenicity**

Name	Route	Species	Value
ISOPROPYL ALCOHOL	Inhalation	Rat	Some positive data exist, but the data are not sufficient for classification

**Reproductive Toxicity****Reproductive and/or Developmental Effects**

Name	Route	Value	Species	Test Result	Exposure Duration
ISOPROPYL ALCOHOL	Ingestion	Some positive developmental data exist, but the data are not sufficient for classification	Rat	NOAEL 400 mg/kg/day	during organogenesis
ISOPROPYL ALCOHOL	Inhalation	Some positive developmental data exist, but the data are not sufficient for classification	Rat	LOAEL 9 mg/l	during gestation
ETHOXYLATED C9-11 ALCOHOLS	Dermal	Not toxic to female reproduction	Rat	NOAEL 250 mg/kg/day	2 generation
ETHOXYLATED C9-11 ALCOHOLS	Dermal	Not toxic to development	Rat	NOAEL 250 mg/kg/day	2 generation
ETHOXYLATED C9-11 ALCOHOLS	Dermal	Some positive male reproductive data exist, but the data are not sufficient for classification	Rat	NOAEL 100 mg/kg/day	2 generation

**Target Organ(s)****Specific Target Organ Toxicity - single exposure**

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
ISOPROPYL ALCOHOL	Inhalation	central nervous system depression	May cause drowsiness or dizziness	Human	NOAEL Not available	
ISOPROPYL ALCOHOL	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification	Human	NOAEL Not available	
ISOPROPYL ALCOHOL	Inhalation	auditory system	Some positive data exist, but the data are not sufficient for classification	Guinea pig	NOAEL 13.4 mg/l	24 hours
ISOPROPYL ALCOHOL	Ingestion	central nervous system depression	May cause drowsiness or dizziness	Human	NOAEL Not available	poisoning and/or abuse
ETHOXYLATED C9-11 ALCOHOLS	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification	Not available	NOAEL Not available	not available
SODIUM LAURYL SULFATE	Inhalation	respiratory irritation	May cause respiratory irritation	similar health hazards	NOAEL Not available	

**Specific Target Organ Toxicity - repeated exposure**

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
ISOPROPYL ALCOHOL	Inhalation	kidney and/or bladder	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 12.3 mg/l	24 months
ISOPROPYL ALCOHOL	Inhalation	nervous system	All data are negative	Rat	NOAEL 12 mg/l	13 weeks
ISOPROPYL ALCOHOL	Ingestion	kidney and/or bladder	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 400 mg/kg/day	12 weeks
ETHOXYLATED C9-11 ALCOHOLS	Dermal	kidney and/or bladder	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 125 mg/kg/day	13 weeks
ETHOXYLATED C9-11 ALCOHOLS	Dermal	hematopoietic system	All data are negative	Rat	NOAEL 125 mg/kg/day	13 weeks

#### Aspiration Hazard

Name	Value
------	-------

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

### SECTION 12: Ecological information

#### Ecotoxicological information

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

#### Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

### SECTION 13: Disposal considerations

#### 13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations. Prior to disposal, consult all applicable authorities and regulations to insure proper classification. Dispose of waste product in a permitted industrial waste facility. As a disposal alternative, incinerate in a permitted waste incineration facility. Proper destruction may require the use of additional fuel during incineration processes. Empty and clean product containers may be disposed as non-hazardous waste. Consult your specific regulations and service providers to determine available options and requirements.

EPA Hazardous Waste Number (RCRA): Not regulated

### SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

### SECTION 15: Regulatory information

#### 15.1. US Federal Regulations

Contact 3M for more information.

#### 311/312 Hazard Categories:

Fire Hazard - No    Pressure Hazard - No    Reactivity Hazard - No    Immediate Hazard - Yes    Delayed Hazard - No

#### 15.2. State Regulations

Contact 3M for more information.

#### 15.3. Chemical Inventories

The components of this product are in compliance with the chemical notification requirements of TSCA. One or more of the components in this material is not listed on the TSCA inventory, but is approved for specific commercial use(s) under a US EPA low volume exemption.

Contact 3M for more information.

#### 15.4. International Regulations

Contact 3M for more information.

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

## SECTION 16: Other information

### NFPA Hazard Classification

**Health:** 1 **Flammability:** 0 **Instability:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

### HMIS Hazard Classification

**Health:** 1 **Flammability:** 0 **Physical Hazard:** 0 **Personal Protection:** X - See PPE section.

Hazardous Material Identification System (HMIS® III) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® III ratings are to be used with a fully implemented HMIS® III program. HMIS® is a registered mark of the American Coatings Association (ACA).

<b>Document Group:</b>	32-0785-9	<b>Version Number:</b>	3.01
<b>Issue Date:</b>	08/14/14	<b>Supersedes Date:</b>	12/23/13

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application. 3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

3M USA SDSs are available at [www.3M.com](http://www.3M.com)