

Safety Data Sheet

acc. to OSHA HCS


Printing date 03/12/2015

Reviewed on 03/12/2015

1 Identification

- **Product identifier**
- **Trade name:** 808 (Red, Black, Green)
- **Application of the substance / the mixture** Stamp pad ink
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Noris-Color GmbH
Ziegelhüttener Str. 1
D-95326 KULMBACH
GERMANY
Phone: +499221/92000
Fax: +499221/920090
info@noris-color.de
- **Information department:** Laboratory/Product safety
- **Emergency telephone number:** See Manufacturer/Supplier

2 Hazard(s) identification

- **Classification of the substance or mixture**
The product is not classified according to the Globally Harmonized System (GHS).
 - **Classification according to Directive 67/548/EEC or Directive 1999/45/EC** Not applicable.
 - **Information concerning particular hazards for human and environment:**
The product does not have to be labeled due to the calculation procedure of international guidelines.
 - **Classification system:**
The classification was made according to the latest editions of international substances lists, and expanded upon from company and literature data.
 - **Label elements**
 - **Labelling according to EU guidelines:**
Observe the general safety regulations when handling chemicals.
The product is not subject to identification regulations according to directives on hazardous materials.
 - **Classification system:**
 - **NFPA ratings (scale 0 - 4)**
- 

Health = 0
Fire = 1
Reactivity = 0
- **Other hazards**
 - **Results of PBT and vPvB assessment**
 - **PBT:** Not applicable.
 - **vPvB:** Not applicable.

3 Composition/information on ingredients

- **Chemical characterization:** Mixtures
- **Description:** Mixture of the substances listed below with nonhazardous additions.

· **Dangerous components:**

| | | |
|------------|---------------------|---------|
| 56-81-5 | glycerol | 25-50% |
| 25322-68-3 | Polyethylene glycol | 10-25% |
| 57-13-6 | urea | 2.5-10% |

4 First-aid measures

- **Description of first aid measures**
- **General information:** No special measures required.

(Contd. on page 2)

Safety Data Sheet

acc. to OSHA HCS

Printing date 03/12/2015

Reviewed on 03/12/2015

Trade name: 808 (Red, Black, Green)

(Contd. of page 1)

- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:** Rinse opened eye for several minutes under running water.
- **After swallowing:**
Rinse out mouth and then drink plenty of water.
If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

7 Handling and storage

- **Handling:**
- **Precautions for safe handling** No special measures required.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**

· **Components with limit values that require monitoring at the workplace:**

56-81-5 glycerol

PEL Long-term value: 15* 5** mg/m³
mist; *total dust **respirable fraction

TLV TLV withdrawn-insufficient data human occup. exp.

(Contd. on page 3)

USA

Safety Data Sheet

acc. to OSHA HCS

Printing date 03/12/2015

Reviewed on 03/12/2015

Trade name: 808 (Red, Black, Green)

(Contd. of page 2)

25322-68-3 Polyethylene glycol

WEEL Long-term value: 10 mg/m³
(H); MW>200

57-13-6 urea

WEEL Long-term value: 10 mg/m³

· **Additional information:** The lists that were valid during the creation were used as basis.

· **Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

The usual precautionary measures for handling chemicals should be followed.

· **Breathing equipment:** Not required.

· **Protection of hands:**

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:** Goggles recommended during refilling.

9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form: Fluid

Color: According to product specification

· **Odor:** Characteristic

· **Odour threshold:** Not determined.

· **pH-value:** Not determined.

· **Change in condition**

Melting point/Melting range: Undetermined.

Boiling point/Boiling range: 100 °C (212 °F)

· **Flash point:** 101 °C (214 °F)

· **Flammability (solid, gaseous):** Not applicable.

· **Ignition temperature:** 400 °C (752 °F)

· **Decomposition temperature:** Not determined.

· **Auto igniting:** Product is not selfigniting.

· **Danger of explosion:** Product does not present an explosion hazard.

· **Explosion limits:**

Lower: 0.9 Vol %

Upper: Not determined.

· **Vapor pressure at 20 °C (68 °F):** 0.1 hPa

· **Density:** Not determined.

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 03/12/2015

Reviewed on 03/12/2015

Trade name: 808 (Red, Black, Green)

(Contd. of page 3)

| | |
|---|--|
| · Relative density | Not determined. |
| · Vapour density | Not determined. |
| · Evaporation rate | Not determined. |
| · Solubility in / Miscibility with Water: | Not miscible or difficult to mix. |
| · Partition coefficient (n-octanol/water): | Not determined. |
| · Viscosity: | |
| Dynamic: | Not determined. |
| Kinematic: | Not determined. |
| · Solvent content: | |
| Organic solvents: | 26.6 % (bis zu) |
| Water: | 43.8 % (bis zu) |
| · Solids content: | 29.6 % (bis zu) |
| · Other information | No further relevant information available. |

10 Stability and reactivity

- **Reactivity**
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
The product is not subject to classification according to internally approved calculation methods for preparations:
When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.
- **Carcinogenic categories**

- **IARC (International Agency for Research on Cancer)**

None of the ingredients is listed.

- **NTP (National Toxicology Program)**

None of the ingredients is listed.

- **OSHA-Ca (Occupational Safety & Health Administration)**

None of the ingredients is listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA HCS

Printing date 03/12/2015

Reviewed on 03/12/2015

Trade name: 808 (Red, Black, Green)

(Contd. of page 4)

- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 2 (Self-assessment): hazardous for water
Do not allow product to reach ground water, water course or sewage system.
Danger to drinking water if even small quantities leak into the ground.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:** Smaller quantities can be disposed of with household waste.
- **Waste disposal key:** Recommendation: 080111 (waste containing organic solvents)
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

- | | |
|--|-----------------|
| · UN-Number | Void |
| · DOT, ADR, ADN, IMDG, IATA | Void |
| · UN proper shipping name | Void |
| · DOT, ADR, ADN, IMDG, IATA | Void |
| · Transport hazard class(es) | Void |
| · DOT, ADR, ADN, IMDG, IATA | Void |
| · Class | Void |
| · Packing group | Void |
| · DOT, ADR, IMDG, IATA | Void |
| · Environmental hazards: | |
| · Marine pollutant: | No |
| · Special precautions for user | Not applicable. |
| · Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code | Not applicable. |
| · UN "Model Regulation": | - |

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**

| |
|--|
| · Section 355 (extremely hazardous substances): |
|--|

| |
|------------------------------------|
| None of the ingredients is listed. |
|------------------------------------|

| |
|--|
| · Section 313 (Specific toxic chemical listings): |
|--|

| |
|------------------------------------|
| None of the ingredients is listed. |
|------------------------------------|

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 03/12/2015

Reviewed on 03/12/2015

Trade name: 808 (Red, Black, Green)

(Contd. of page 5)

· **TSCA (Toxic Substances Control Act):**

| | |
|------------|---|
| 56-81-5 | glycerol |
| 25322-68-3 | Polyethylene glycol |
| 57-13-6 | urea |
| 7732-18-5 | water, distilled, conductivity or of similar purity |

· **Proposition 65**

· **Chemicals known to cause cancer:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

· **Chemicals known to cause developmental toxicity:**

None of the ingredients is listed.

· **Carcinogenic categories**

· **EPA (Environmental Protection Agency)**

| | | |
|---------|------|----|
| 57-13-6 | urea | II |
|---------|------|----|

· **TLV (Threshold Limit Value established by ACGIH)**

None of the ingredients is listed.

· **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

· **Product related hazard informations:**

Observe the general safety regulations when handling chemicals.

The product is not subject to identification regulations according to directives on hazardous materials.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Laboratory/Product safety

· **Contact:**

Noris-Color product safety department / laboratory; info@noris-color.de

Hr. Wendland

· **Date of preparation / last revision** 03/12/2015 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)