

Spitfire Professional All Purpose Power Cleaner

Version Number: 4 Preparation date: 2016-11-08

1. IDENTIFICATION

Product name: Spitfire Professional All Purpose Power Cleaner

Product Code: CBD540014, CBD540038, CBD540045

SDS #: MS0801033

Recommended use: • Cleaning product

• This product is intended to be used neat.

Uses advised against: Uses other than those identified are not recommended

Manufacturer, importer, supplier:Canadian HeadquartersUS HeadquartersSealed Air - Canada

Sealed Air 3755 Laird Road
8215 Forest Point Blvd. Mississauga, Ontario L5L 0B3
Charlotte, NC 28273-5509 Phone: 1-800-668-7171

Phone: 1-888-352-2249

SDS Internet Address: https://sds.sealedair.com

Emergency telephone number: 1-800-851-7145; 1-651-917-6133 (Int'l)

2. HAZARDS IDENTIFICATION

Classification for the undiluted product

Serious eye damage/eye irritation Category 2B

Signal Word: Warning.

Precautionary Statements

CAUSES EYE IRRITATION.

Avoid contact with eyes, skin and clothing. Wash affected areas thoroughly after handling. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. If eye irritation persists: Get medical advice or attention.

Health hazards not otherwise classified (HHNOC) - Not applicable Physical hazards not otherwise classified (PHNOC) - Not applicable

Classification for the diluted product @ RTU

This product is intended to be used neat.


Precautionary Statements

See undiluted product information above.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Classified Ingredients

Ingradient(s)	CAS#	Weight %		







Benzyl alcohol	100-51-6	1 - < 3%
Diethylene glycol monoethyl ether	111-90-0	1 - < 3%
Sodium xylene sulfonate	1300-72-7	1 - < 3%
Potassium hydroxide	1310-58-3	> 0.1 - < 1%

^{*}Exact percentages are being withheld as trade secret information

4. FIRST AID MEASURES

Undiluted Product:

Eyes: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. If eye irritation persists: Get medical advice/attention.

Skin: Rinse with plenty of water. If irritation occurs and persists, get medical attention.

Inhalation: No specific first aid measures are required.

Ingestion: Rinse mouth with water.

Most Important Symptoms/Effects: No information available.

Immediate medical attention and special treatment needed Not applicable.

Aggravated Medical Conditions: None known.

Diluted Product:

This product is intended to be used neat.

Eyes: See undiluted product information above. Skin: See undiluted product information above. Inhalation: See undiluted product information above. Ingestion: See undiluted product information above.

5. FIRE-FIGHTING MEASURES

Specific methods: No special methods required

Suitable extinguishing media: The product is not flammable. Extinguish fire using agent suitable for surrounding fire.

Specific hazards: Not applicable.

Special protective equipment for firefighters: As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Extinguishing media which must not be used for safety reasons: No information available.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions: Put on appropriate personal protective equipment (see Section 8.).

Clean-up methods - large spillage. Absorb spill with inert material (e.g. dry sand or earth), then place in **Environmental precautions** and clean-up methods:

a chemical waste container. Use a water rinse for final clean-up.

7. HANDLING AND STORAGE

Handling: Handle in accordance with good industrial hygiene and safety practice. FOR COMMERCIAL AND INDUSTRIAL USE ONLY.

Storage: Keep tightly closed in a dry, cool and well-ventilated place. KEEP OUT OF REACH OF CHILDREN.

Aerosol Level (if applicable): Not applicable

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Guidelines:

Ingredient(s)	CAS#	ACGIH	OSHA
Benzyl alcohol	100-51-6	-	-
Diethylene glycol monoethyl ether	111-90-0	-	-
Sodium xylene sulfonate	1300-72-7	-	-
Potassium hydroxide	1310-58-3	2 mg/m³ (Ceiling)	-

Undiluted Product:

Engineering measures to reduce exposure:

No special ventilation requirements. General room ventilation is adequate.

Personal Protective Equipment

Eye protection:
Hand protection:
No special requirements under normal use conditions.
No special requirements under normal use conditions.
Skin and body protection:
No special requirements under normal use conditions.
Respiratory protection:
No special requirements under normal use conditions.

Hygiene measures: Handle in accordance with good industrial hygiene and safety practice.

Diluted Product:

This product is intended to be used neat.

Personal Protective Equipment

Eye protection:

Hand protection:

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

Skin and body protection:

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

Hygiene measures:

Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State: LiquidColor: Clear, RedEvaporation Rate: No information availableOdor: Fresh Pine

Odor threshold: No information available. Boiling point/range: Not determined

Melting point/range: Not determined Decomposition temperature: Not determined

Autoignition temperature: No information available Solubility: Completely Soluble

Solubility in other solvents: No information available

Density: 8.47 | lbs/gal | 1.015 | Kg/L |

Bulk density: No information available |

Relative Density (relative to water): 1.015 |

Vapor density: No information available |

Vapor pressure: No information available.

Flash point (°F): > 200 °F > 93.4 °C

Partition coefficient (n-octanol/water): No information available

Dilution Flash Point: 200 °F 93.4 °C **Viscosity:** No information available

Elemental Phosphorus: 0.00 % by wt. VOC: 0.31 %

pH: 12.3 VOC % by wt. at use dilution 0 % *
Dilution pH: 12.3 @ RTU Flammability (Solid or Gas): Not applicable
Corrosion to metals: Not corrosive Sustained combustion: Not applicable

Explosion limits: - upper: Not determined - lower: Not determined

10. STABILITY AND REACTIVITY

Reactivity: Not Applicable Stability: Not Applicable The product is stable

Hazardous decomposition products: None reasonably foreseeable.

Materials to avoid: Do not mix with any other product or chemical unless specified in the use directions.

Conditions to avoid: No information available.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure:

Eye contact, Skin contact, Inhalation

Delayed, immediate, or chronic effects and symptoms from short and long-term exposure

Skin contact: May be mildly irritating to skin. Symptoms may include redness and/or transient discomfort.

Eye contact: Causes eye irritation. Symptoms may include discomfort, redness, and watering.

Ingestion: May be irritating to mouth, throat and stomach. Symptoms may include stomach pain and nausea.

Inhalation: May be irritating to nose, throat, and respiratory tract. Symptoms may include coughing and difficulty breathing.

Sensitization: No known effects.
Target Organs (SE): None known
Target Organs (RE): None known

Numerical measures of toxicity

^{* -} Title 17, California Code of Regulations, Division 3, Chapter 1, Subchapter 8.5, Article 2, Consumer Products, Sections 94508

ATE - Oral (mg/kg): >5000
ATE - Dermal (mg/kg): >5000
ATE - Inhalatory, mists (mg/l): >20
ATE - Inhalatory, vapors (mg/l): >50

12. ECOLOGICAL INFORMATION

Ecotoxicity: No information available.

<u>Persistence and Degradability:</u> No information available.

Bioaccumulation: No information available.

13. DISPOSAL CONSIDERATIONS

Waste from residues / unused products (undiluted product): This product, as sold, if discarded or disposed, is not a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Dispose in compliance with all Federal, state, provincial, and local laws and regulations. Waste from residues / unused products (diluted product): Not applicable.

RCRA Hazard Class (undiluted product): Not Regulated RCRA Hazard Class (diluted product): Not Regulated Contaminated Packaging: Do not re-use empty containers.

14. TRANSPORT INFORMATION

DOT/TDG/IMDG: Proper shipping descriptions can vary by pack size. Please refer to the Diversey HazMat Library, http://naextranet.diversey.com/dot/, for up to date shipping information.

DOT (Ground) Bill of Lading Description: NON REGULATED ITEM

IMDG (Ocean) Bill of Lading Description: NON REGULATED ITEM

15. REGULATORY INFORMATION

International Inventories at CAS# Level

All components of this product are listed on the following inventories: U.S.A. (TSCA), Canada (DSL/NDSL).

RIGHT TO KNOW (RTK)

Ingredient(s)	CAS#	MARTK:	NJRTK:	PARTK:	RIRTK:
Water	7732-18-5	=	=	=	-
Benzyl alcohol	100-51-6	X	=	X	-
Diethylene glycol monoethyl ether	111-90-0	-	X	-	-
Sodium xylene sulfonate	1300-72-7	=	=	=	-
Alcohol ethoxylates	68439-46-3	-	-	-	-
Potassium hydroxide	1310-58-3	X	Χ	Х	Х

CERCLA/ SARA

Ingredient(s)	CAS#	Weight %	CERCLA/SARA RQ (lbs)	Section 302 TPQ (lbs)	Section 313
Diethylene glycol monoethyl ether	111-90-0	1 - < 3%			X
Potassium hydroxide	1310-58-3	> 0.1 - < 1%	1000		

Ingredient(s)	CAA HAP	CAA ODS	CWA Priority Pollutants
Diethylene glycol monoethyl ether	X		

SARA 311/312 Hazard Categories

Immediate: X
Delayed: Fire: Reactivity: -

Sudden Release of Pressure:

Canadian Regulations

16. OTHER INFORMATION

NFPA (National Fire Protection Association)

Rating Scale: (Low Hazard) 0 - 4 (Extreme Hazard)

Health 1 Flammability 0 Instability 0

Version Number: 4

Preparation date: 2016-11-08

Reason for revision: Not applicable Prepared by: NAPRAC

Additional advice: • Contains an added fragrance, see "Odor" heading in section 9 for specific description

• This product has been classified in accordance with hazard criteria of the Controlled Products Regulations and the MSDS contains all the information required by the Controlled Products

Regulations

Notice to Reader: This document has been prepared using data from sources considered technically reliable. It does not constitute a warranty, express or implied, as to the accuracy of the information contained within. Actual conditions of use and handling are beyond seller's control. User is responsible to evaluate all available information when using product for any particular use and to comply with all Federal, State, Provincial and Local laws and regulations.