



FORCE™ UPRIGHT

SC5815D

MENU








CRI BRONZE SEAL
OF APPROVAL



LEED
QUALIFIED

The FORCE™ upright with 15" cleaning path provides an exceptional clean certified with the CRI Bronze Seal of Approval. Featuring a sealed HEPA system with included HEPA filter to capture 99.97% of particles for cleaner emissions. FORCE™ is LEED Qualified for daytime cleaning with a sound level of 69 dBA. Includes on-board tools and stretch hose for above-the-floor cleaning.

 DO NOT DISTURB 24/7	 CRI BRONZE SEAL OF APPROVAL	 SOUND
 15" WIDE AREA CLEANING	 LEED QUALIFIED	

SPECIFICATIONS			
MFG#	SC5815B	CLEANING WIDTH	15"
MOTOR	10 amp	CORD LENGTH	40'
CFM	135	SOUND	69 dBA
FILTRATION	Sealed HEPA	BRUSH ROLL	62228-3
DUST CONTAINMENT	Disposable Bag	BAG	LS (63256A-11)
DUST CAPACITY	4.5 qt.	BELT	61120D-12
CLEANING TOOLS	Wand, hose, dusting brush, crevice tool	FILTER	61840-4
PACKAGING			
UPC	0 23169 14592 4	PACKAGE WEIGHT	23 lbs.
PRODUCT WEIGHT	18 lbs.	PACKAGE DIMENSIONS	38" x 10" x 18.75"
WARRANTY	2 Years - Parts & Labor		