

Product Name MSDS Date

DCT CUTTING BOARD RESTORER

August 31, 2012

Revision No. 03

Page 1 of 6
SECTION 1

PRODUCT AND COMPANY IDENTIFICATION

PRODUCT

Product Name DCT Cutting Board Restorer

Product ID Number DCT130610
Product Description Chlorinated Cleaner

COMPANY IDENTIFICATION

Supplier Diversified Chemical Technologies, Inc.

15477 Woodrow Wilson Detroit, MI 48238 (313) 867-5444

Product Technical Information (313) 867-5444

24 Hour Emergency Phone Number (Health & Safety; Transportation) CHEMTREC - (800) 424-9300

Hazardous Ingredients

CAS Number OSHA PEL ACGIH TLV OTHER % WT

Sodium hypochlorite 7681-52-9 none established 35 – 45

HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW May cause eye irritation. Avoid contact with eyes. Wash thoroughly after handling. Harmful if swallowed.

POTENTIAL HEALTH EFFECTS

Acute Effects

Inhalation Moderate to severe irritation to respiratory tract.

Eye Moderate to severe irritation / chemical burns in full concentration. Can cause chemical burns

upon direct contact.

Skin Moderate to severe skin irritation / chemical burns in full concentration. Can cause chemical

burns upon direct contact.

Ingestion Harmful if swallowed. May cause burns to mouth, throat and stomach.

Chronic Effects Product has not been tested as a whole to determine its long-term effects.

Carcinogenicity None IARC: N/A NTP: N/A OSHA: N/A



Product Name MSDS Date Page 2 of 6 **DCT CUTTING BOARD RESTORER**

August 31, 2012

Revision No. 03

SECTION 4 FIRST AID MEASURES

INHALATION Remove to fresh air. Get prompt medical attention if necessary.

EYE CONTACT Remove contact lenses. Hold eyelids apart and flush eyes with plenty of water for at least 15

minutes. Get immediate medical attention if chemical burns exist or irritation persists.

SKIN CONTACT Remove contaminated clothing. Flush skin with plenty of water for at least 15 minutes. Get

immediate medical attention if chemical burns exist or irritation persists.

INGESTION Do not induce vomiting. Wash out mouth with water and obtain medical attention. If conscious,

milk or water to drink may be beneficial. Treat symptomatically. Get immediate medical

attention. Never give anything by mouth to an unconscious person.

SECTION 5 FIRE FIGHTING MEASURES

Flash Point None
Flash Point Method PMCC
Auto Ignition Temperature N/D

Flammable Limits: LEL - N/D UEL - N/D
Appropriate Extinguishing Media Dry Chemical, Foam, CO2

Fire Fighting Instructions Firefighters should wear self-contained breathing apparatus (SCBA) and protection for skin.

Stay away from ends of containers during a fire; containers may explode due to pressure build-up inside if heated. Do not spray water directly into storage containers due to boil over danger.

Water may be used to cool nearby containers and surfaces.

Hazardous Combustion Products Irritating fumes, toxic gases and acrid smoke. Combustion can produce a variety of

compounds including oxides of carbon; water vapor; unburned hydrocarbons; and other

unidentified organic and inorganic compounds.

SECTION 6 ACCIDENTAL RELEASE MEASURES

NOTIFICATION PROCEDURES In the event of a spill or accidental release, notify relevant authorities in accordance

with all applicable regulations. *National Response Center [Reporting – 24 HR (800) 424-8802*

GENERAL Stop leak, spill or release if you can do so without risk. Contain spill and prevent entry into sewer

drains and waterways. Retain all contaminated water for removal and treatment.

SAFETY PRECAUTIONS Use suitable protective clothing appropriate to spill size and risk of exposure. Refer to Section 8

for further details. Use extreme caution because affected area(s) may be slippery. For industrial

use only. Keep out of reach of children.

SPILL OR LEAK PROCEDURES Neutralize spilled material with weak solution of citric acid if possible. Confine spillage

and absorb spilled material with noncombustible, inert absorbent such as sand, clay, or vermiculite and place into DOT-approved containers for later disposal.



Product Name MSDS Date

DCT CUTTING BOARD RESTORER

August 31, 2012

Revision No. 03

Page 3 of 6

SECTION 7 HANDLING AND STORAGE

HANDLING Avoid contact with skin, eyes, and clothing. Wear suitable protective equipment (see Section 8).

Avoid breathing mist or vapor – use only in a well-ventilated area. Unvented containers may develop pressure – use with caution.

Wash skin thoroughly after handling.

STORAGE Store in dry conditions protected from frost and elevated temperatures.

Keep containers closed when not in use.

Store away from incompatible materials (see Section 10). Long-term storage temperatures should not exceed 120° F.

Keep away from sparks, heat and flame.

Do not store in reactive metal containers (i.e. aluminum, tin, zinc, galvanized steel or their alloys)

SECTION 8 EXPOSURE CONTROLS / PERSONAL PROTECTION

ENGINEERING CONTROLS General ventilation should be provided so that exposure to airborne contaminants are not

exceeded

PERSONAL PROTECTIVE EQUIPMENT

Respiratory Protection No protective equipment is needed under normal use conditions.

Hand Protection No protective equipment is needed under normal use conditions. In full concentration use

chemical resistant gloves when handling.

Skin Protection No protective equipment is needed under normal use conditions. In full concentration, use apron

and long sleeves to avoid contact with skin.

Eye Protection In full concentration, if contact is likely, safety glasses or goggles are recommended. If splashing is

likely, safety goggles with splash guards are recommended.

SECTION 9 PHYSICAL AND CHEMICAL PROPERTIES

AppearanceClear greenPhysical StateViscous liquidOdorChlorinepH12.8 – 13.2

Melting Point N/A

Boiling Point Decomposes on heating

Flash Point None **Evaporation Rate (water = 1)** N/AV **Vapor Pressure** N/AV **Vapor Density** N/AV Density (lb/gal) N/AV Specific Gravity (water = 1) 1.0893 Solubility Complete **Volatile Organic Compounds (%)** N/AV

Viscosity (sec) 30 -35 (concentrate, Zahn Cup, at 75F)



Product Name MSDS Date **DCT CUTTING BOARD RESTORER**

August 31, 2012

Revision No. 03

Page 4 of 6

SECTION 10 STABILITY / REACTIVITY

Chemical Stability Material is stable and unlikely to react in a hazardous manner during recommended storage

conditions and normal conditions of use.

Conditions to Avoid Heat, Open Flame, Spark, Sunlight, Ultra-Violet Light;

Reactivity / Incompatibility Reducer, other oxidizers, acids, iron, copper, ammonium compounds, organics

Hazardous Decomposition Material does not decompose at ambient temperature. Decomposes as heated.

Thermal decomposition can produce a variety of compounds, the nature of which will largely depend on the conditions bringing about decomposition. Incomplete combustion or thermal decomposition may be expected to generate such materials as: chlorine gas, particulate matter and unburned, hydrocarbons; oxides of carbon; oxides of nitrogen; water vapor; and other

unidentified organic and inorganic compounds.

Hazardous Polymerization

Will not occur.

SECTION 11 TOXICOLOGICAL INFORMATION

Product Toxicological Data

LD50 (Oral) N/D
LC50 (Inhalation) N/D
Dermal Toxicity Data (Skin) N/D
Skin and Eye Irritation Data N/D
Mutation Data N/D
Reproductive Effects Data N/D

Ingredient Toxicological Data

LD50 (Oral)

LC50 (Inhalation)

N/AV

Dermal Toxicity Data (Skin)

Skin and Eye Irritation Data

Mutation Data

N/AV

Reproductive Effects Data

N/AV

SECTION 12 ECOLOGICAL INFORMATION

Product Ecological Information N/AV

Ingredient Ecological Information N/AV

SECTION 13 DISPOSAL CONSIDERATIONS

DISPOSAL CONSIDERATIONS

Waste Disposal Neutralization/wastewater treatment is preferred method of disposal. Dispose of contaminated

water in a contained waste treatment system. Follow all applicable federal, state, local and provincial regulations. It is the end-user's responsibility to determine the regulatory status of

waste at the time of disposal.

Empty ContainersEmpty containers may still contain RCRA-regulated residuals; therefore, clean empty containers of

any residue per 40CFR261.7 guidelines and either recycle containers or dispose of in normal trash.



Product Name

DCT CUTTING BOARD RESTORER

MSDS Date

August 31, 2012

Revision No. 03

Page 5 of 6

SECTION 14 TRANSPORT INFORMATION

LAND (DOT)

DOT Proper Shipping Name Hypochlorite Solutions (contains sodium hypochlorite), 8, UN 1791, PG III, RQ

= 100 lb.

DOT Hazard Class 8
DOT Subsidiary Risk N/A
DOT ID Number UN 1791
DOT Packaging Group PG III

SEA (IMDG)

IMDG Proper Shipping Name Hypochlorite Solutions (contains sodium hypochlorite), 8, UN 1791, PG III, RQ

= 100 lb.

IMDG Hazard Class8IMDG Subsidiary RiskN/AIMDG ID NumberUN 1791IMDG Packaging GroupPG III

AIR (IATA)

IATA Proper Shipping Name Hypochlorite Solutions (contains sodium hypochlorite), 8, UN 1791, PG III, RQ

= 100 lb.

IATA Hazard Class 8
IATA Subsidiary Risk N/A
IATA ID Number UN 1791
IATA Packaging Group

Additional Information DOT Shipping Description if quantities are equal to or less than 1 gallon: Hypochlorite

Solutions (contains sodium hypochlorite), 8, UN 1791, PG III, Ltd Qty

DOT Label/Placard if quantities are equal to or less than 1 gallon: (DOT – Land Only)

none required

SECTION 15 REGULATORY INFORMATION

U.S. Federal Regulations

SARA Title III Section 311/312 Categorization (40 CFR 370)

Acute – Immediate Hazard Chronic – Delayed Hazard

SARA Title III Section 313 Categorization (40 CFR 372) This product contains a chemical(s)

subject to the reporting requirements of Section 313 of Title III of SARA: None

302 (EHS) TPQ (40 CFR 355) None 304 CERCLA RQ (302.4) None 304 EHS RQ (40 CFR 116.4) None

State Regulations

California Prop. 65 N/A

Identification of Prop. 65 Ingredient(s) N/A



Product Name

DCT CUTTING BOARD RESTORER

MSDS Date

August 31, 2012

Revision No. 03

Page 6 of 6

SECTION 15	REGULATORY INFORMATION	continued
OSHA CLASSIFICATION	DANGER	
WHMIS CLASSIFICATION	D2B (Stylized T) and E (Corrosive Material)	

This product has been classified in accordance with hazard criteria of the Controlled Products Regulations and the MSDS contains all the information required by the Controlled Products Regulations.

National Inventories

TSCA		Yes	EINECS	N/AV
CEPA	(DSL/NDSL)	Yes	ENCS	N/AV
AICS		N /AV	KECI	N/AV
IECSC		N /AV	PICCS	N/AV

SECTION 16 OTHER INFORMATION

N/D = Not Determined N/A = Not Applicable N/AV = Not Available

NFPA RATING Health (Blue): 2 Flammability (Red): 0 Reactivity (Yellow): 0

Specific Hazard(s) (White): COR/ALK

HMIS RATING Health (Blue): 2 Flammability (Red): 0 Reactivity (Yellow): 0

Personal Protective Equipment: C or D

THIS SAFETY DATA SHEET CONTAINS THE FOLLOWING REVISIONS

Revision Changes Format changes and updated MSDS to reflect conditions at use (Sections 2, 3,4,5,7, 9.10, and 13

were updated)

USER RESPONSIBILITY Each user should read and understand this information and incorporate it in individual

site safety programs in accordance with applicable hazard communication standards

and regulations.

THE INFORMATION CONTAINED HEREIN IS BASED ON DATA CONSIDERED TO BE ACCURATE. HOWEVER, NO WARRANTY IS EXPRESSED OR IMPLIED REGARDING THE ACCURACY OF THESE DATA OR THE RESULTS TO BE OBTAINED FROM THE USE THEREOF.

Prepared By: Corporate EHS Department of Diversified Chemical Technologies, Inc. and Subsidiaries