



HEALTHCARE BEYOND BURN CARE™

SAFETY DATA SHEET

This safety data sheet was created pursuant to the requirements of: US OSHA Hazard Communication Standard (29 CFR 1910.1200) and Canada WHMIS 2015 which includes the amended Hazardous Products Act (HPA) and the Hazardous Products Regulation (HPR)

Issuing Date 08-Mar-2019

Revision Date 02-Jan-2020

Revision Number 1.1

1. Identification

Product identifier

Product Name Hand Sanitizer

Other means of identification

Product Code(s) 910042.00.006

UN/ID no UN1170

Synonyms Instant Hand Sanitizer Antiseptic Gel with Vitamin E & Aloe

Recommended use of the chemical and restrictions on use

Recommended use Hand sanitizer

Restrictions on use For external use only.

Details of the supplier of the safety data sheet

Manufacturer Address
WaterJel ® Technologies
50 Broad Street
Carlstadt, NJ 07072
P: 201-507-8300

Emergency telephone number

Emergency Telephone 800-275-3433 (8:00 am-5:00 pm EST Weekdays)

2. Hazard(s) identification

Classification

Flammable liquids	Category 2
-------------------	------------

Label elements

Danger

Hazard statements

Highly flammable liquid and vapor

**Precautionary Statements - Prevention**

Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Keep container tightly closed. Ground/bond container and receiving equipment. Use explosion-proof electrical/ ventilating/ lighting/ equipment. Use only non-sparking tools. Take precautionary measures against static discharge. Wear protective gloves/eye protection/face protection.

Precautionary Statements - Response**Skin**

IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/ shower.

Fire

In case of fire: Use CO₂, dry chemical, or foam to extinguish.

Precautionary Statements - Storage

Store in a well-ventilated place. Keep cool

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant.

Other information

No information available.

3. Composition/information on ingredients

Substance

Not applicable.

Mixture**Synonyms**

Instant Hand Sanitizer Antiseptic Gel with Vitamin E & Aloe.

Chemical name	CAS No.	Weight-%	Hazardous Material Information Review Act registry number (HMIRA registry #)	Date HMIRA filed and date exemption granted (if applicable)
Ethyl alcohol	64-17-5	45-70	-	-

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. First-aid measures

Description of first aid measures**Inhalation**

Remove to fresh air.

Eye contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Do not rub affected area.

Skin contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.

Ingestion	Clean mouth with water and drink afterwards plenty of water.
Self-protection of the first aider	Remove all sources of ignition. Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination. Use personal protective equipment as required. See section 8 for more information.

Most important symptoms and effects, both acute and delayed

Symptoms	May cause redness and tearing of the eyes. May cause skin irritation in susceptible persons.
-----------------	--

Indication of any immediate medical attention and special treatment needed

Note to physicians	Treat symptomatically.
---------------------------	------------------------

5. Fire-fighting measures

Suitable Extinguishing Media	Dry chemical. Carbon dioxide (CO ₂). Water spray. Alcohol resistant foam.
Unsuitable extinguishing media	CAUTION: Use of water spray when fighting fire may be inefficient.
Specific hazards arising from the chemical	Risk of ignition. Keep product and empty container away from heat and sources of ignition. In the event of fire, cool tanks with water spray. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
Explosion data	
Sensitivity to mechanical impact	None.
Sensitivity to static discharge	Yes.
Special protective equipment for fire-fighters	Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

6. Accidental release measures**Personal precautions, protective equipment and emergency procedures**

Personal precautions	Evacuate personnel to safe areas. Use personal protective equipment as required. See section 8 for more information. Avoid contact with skin, eyes or clothing. Ensure adequate ventilation. Keep people away from and upwind of spill/leak. ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Pay attention to flashback. Take precautionary measures against static discharges. All equipment used when handling the product must be grounded. Do not touch or walk through spilled material.
Other information	Ventilate the area.

Methods and material for containment and cleaning up

Methods for containment	Stop leak if you can do it without risk. Do not touch or walk through spilled material. A vapor suppressing foam may be used to reduce vapors. Dike far ahead of spill to collect runoff water. Keep out of drains, sewers, ditches and waterways. Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal.
Methods for cleaning up	Take precautionary measures against static discharges. Dam up. Soak up with inert absorbent material. Pick up and transfer to properly labeled containers.

7. Handling and storage

Precautions for safe handling

Advice on safe handling

Use personal protection equipment. Avoid contact with skin and eyes. Avoid breathing vapors or mists. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Use grounding and bonding connection when transferring this material to prevent static discharge, fire or explosion. Use with local exhaust ventilation. Use spark-proof tools and explosion-proof equipment. Keep in an area equipped with sprinklers. Use according to package label instructions.

Conditions for safe storage, including any incompatibilities

Storage Conditions

Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). Keep in properly labeled containers. Do not store near combustible materials. Keep in an area equipped with sprinklers. Store in accordance with the particular national regulations. Store in accordance with local regulations.

8. Exposure controls/personal protection

Control parameters

Exposure Limits

Chemical name	ACGIH TLV	OSHA PEL	NIOSH	
Ethyl alcohol 64-17-5	STEL: 1000 ppm	TWA: 1000 ppm TWA: 1900 mg/m ³ (vacated) TWA: 1000 ppm (vacated) TWA: 1900 mg/m ³	IDLH: 3300 ppm TWA: 1000 ppm TWA: 1900 mg/m ³	
Chemical name	Alberta	British Columbia	Ontario	Quebec
Ethyl alcohol 64-17-5	TWA: 1000 ppm TWA: 1880 mg/m ³	STEL: 1000 ppm	STEL: 1000 ppm	TWA: 1000 ppm TWA: 1880 mg/m ³

Appropriate engineering controls

Engineering controls

Showers
Eyewash stations
Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection

Tight sealing safety goggles.

Hand protection

Wear suitable gloves. Impervious gloves.

Skin and body protection

Wear suitable protective clothing. Long sleeved clothing. Chemical resistant apron. Antistatic boots.

Respiratory protection

No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

General hygiene considerations

Do not eat, drink or smoke when using this product. Contaminated work clothing should not be allowed out of the workplace. Regular cleaning of equipment, work area and clothing is

recommended. Wash hands before breaks and immediately after handling the product.

9. Physical and chemical properties

Information on basic physical and chemical properties

Appearance	Translucent liquid
Physical state	Liquid
Color	Clear to semi-clear
Odor	Characteristic
Odor threshold	No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	6.9 - 7.3	@ 25 °C
Melting point / freezing point	No data available	None known
Boiling point / boiling range	79.4 °C / 174.9 °F	
Flash point	22.2 °C 72 °F	CC (closed cup)
Evaporation rate	No data available	None known
Flammability (solid, gas)	No data available	None known
Flammability Limit in Air		None known
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Vapor pressure	No data available	None known
Vapor density	No data available	None known
Relative density	0.87 - 0.91	@25°C
Water solubility	Soluble in water	
Solubility(ies)	No data available	None known
Partition coefficient	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature	No data available	None known
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	None known
<u>Other information</u>		
Explosive properties	No information available.	
Oxidizing properties	No information available.	
Softening point	No information available	
Molecular weight	No information available	
VOC Content (%)	No information available	
Liquid Density	No information available	
Bulk density	No information available	

10. Stability and reactivity

Reactivity	None under normal use conditions.
Chemical stability	Stable under normal conditions.
Possibility of hazardous reactions	None under normal processing.
Conditions to avoid	Heat, flames and sparks.
Incompatible materials	None known based on information supplied.
Hazardous decomposition products	None known based on information supplied.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Specific test data for the substance or mixture is not available. Vapors may be irritating to eyes, nose, throat, and lungs.
Eye contact	Specific test data for the substance or mixture is not available. May cause redness, itching, and pain.
Skin contact	Specific test data for the substance or mixture is not available. May cause irritation.
Ingestion	Specific test data for the substance or mixture is not available. May cause gastrointestinal discomfort if consumed in large amounts.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms	May cause redness and tearing of the eyes. May cause skin irritation in susceptible persons.
-----------------	--

Acute toxicity**Numerical measures of toxicity**

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral)	10,844.90 mg/kg
ATEmix (inhalation-dust/mist)	191.60 mg/l

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Ethyl alcohol	= 7060 mg/kg (Rat)	-	= 124.7 mg/L (Rat) 4 h

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation	May cause mild to moderate irritation.
Serious eye damage/eye irritation	May cause mild to moderate irritation.
Respiratory or skin sensitization	No information available.
Germ cell mutagenicity	No information available.
Carcinogenicity	Ethanol has been shown to be carcinogenic in long-term studies only when consumed as alcoholic beverage.

The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical name	ACGIH	IARC	NTP	OSHA
Ethyl alcohol 64-17-5	A3	Group 1	Known	X

Legend

ACGIH (American Conference of Governmental Industrial Hygienists)

A3 - Animal Carcinogen

IARC (International Agency for Research on Cancer)

Group 1 - Carcinogenic to Humans

NTP (National Toxicology Program)

Known - Known Carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Target organ effects	liver, Respiratory system, Eyes, Skin, Central nervous system, blood, Reproductive System.
Aspiration hazard	No information available.

12. Ecological information

Ecotoxicity

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Ethyl alcohol 64-17-5	-	LC50: 12.0 - 16.0mL/L (96h, Oncorhynchus mykiss) LC50: 13400 - 15100mg/L (96h, Pimephales promelas) LC50: >100mg/L (96h, Pimephales promelas)	-	LC50: 9268 - 14221mg/L (48h, Daphnia magna) EC50: =2mg/L (48h, Daphnia magna)

Persistence and degradability No information available.

Bioaccumulation There is no data for this product.

Component Information

Chemical name	Partition coefficient
Ethyl alcohol 64-17-5	-0.32

Mobility in soil No information available.

Mobility No information available.

Other adverse effects No information available.

13. Disposal considerations

Waste treatment methods

Waste from residues/unused products Should not be released into the environment. Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.

Contaminated packaging Empty containers pose a potential fire and explosion hazard. Do not cut, puncture or weld containers.

US EPA Waste Number D001.

California Hazardous Waste Status This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical name	California Hazardous Waste Status
Ethyl alcohol	Toxic

64-17-5

Ignitable

14. Transport information**DOT**

UN/ID no	UN1170
Proper shipping name	ETHANOL SOLUTION
Hazard class	3
Packing group	II
Special Provisions	24, IB2, T4, TP1
Description	UN1170, ETHANOL SOLUTION, 3, II
Emergency Response Guide Number	127

TDG

UN/ID no	UN1170
Proper shipping name	ETHANOL SOLUTION
Hazard class	3
Packing group	II
Special Provisions	150
Description	UN1170, ETHANOL SOLUTION, 3, II

MEX

UN/ID no	UN1170
Proper shipping name	ETHANOL SOLUTION
Hazard class	3
Special Provisions	144
Packing group	II
Description	UN1170, ETHANOL SOLUTION, 3, II

IATA

UN number	UN1170
UN proper shipping name	Ethanol solution
Transport hazard class(es)	3
Packing group	II
ERG Code	3L
Special Provisions	A180, A3, A58
Description	UN1170, Ethanol solution, 3, II

IMDG

UN number	UN1170
UN proper shipping name	ETHANOL SOLUTION
Transport hazard class(es)	3
Packing group	II
EmS-No	F-E, S-D
Special Provisions	144
Description	UN1170, ETHANOL SOLUTION, 3, II, (22.2°C C.C.)

15. Regulatory information**Safety, health and environmental regulations/legislation specific for the substance or mixture****International Regulations**

The Montreal Protocol on Substances that Deplete the Ozone Layer Not applicable

The Stockholm Convention on Persistent Organic Pollutants Not applicable

The Rotterdam Convention Not applicable

International Inventories**TSCA**

Contact supplier for inventory compliance status.

DSL/NDSL

Contact supplier for inventory compliance status.

Legend:**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List**US Federal Regulations****SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

SARA 311/312 Hazard Categories

Should this product meet EPCRA 311/312 Tier reporting criteria at 40 CFR 370, refer to Section 2 of this SDS for appropriate classifications.

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

US State Regulations**California Proposition 65**

Ethyl alcohol is only considered a Proposition 65 developmental hazard when it is ingested as an alcoholic beverage.

U.S. State Right-to-Know Regulations**US State Regulations**

Chemical name	New Jersey	Massachusetts	Pennsylvania
Ethyl alcohol 64-17-5	X	X	X
Propane-1,2-diol 57-55-6	X	-	X

U.S. EPA Label Information**EPA Pesticide Registration Number** Not applicable**16. Other information**

<u>NFPA</u>	Health hazards 1	Flammability 3	Instability 0	Physical and chemical properties -
<u>HMIS</u>	Health hazards 2	Flammability 3	Physical hazards 0	Personal protection X

Key or legend to abbreviations and acronyms used in the safety data sheet

Legend Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

TWA	TWA (time-weighted average)	STEL	STEL (Short Term Exposure Limit)
Ceiling	Maximum limit value	*	Skin designation

Key literature references and sources for data used to compile the SDS

U.S. Environmental Protection Agency ChemView Database
 European Food Safety Authority (EFSA)
 EPA (Environmental Protection Agency)
 Acute Exposure Guideline Level(s) (AEGL(s))
 U.S. Environmental Protection Agency Federal Insecticide, Fungicide, and Rodenticide Act
 U.S. Environmental Protection Agency High Production Volume Chemicals
 Food Research Journal
 Hazardous Substance Database
 International Uniform Chemical Information Database (IUCLID)
 Japan GHS Classification
 Australia National Industrial Chemicals Notification and Assessment Scheme (NICNAS)
 NIOSH (National Institute for Occupational Safety and Health)
 National Library of Medicine's ChemID Plus (NLM CIP)
 National Toxicology Program (NTP)
 New Zealand's Chemical Classification and Information Database (CCID)
 Organization for Economic Co-operation and Development Environment, Health, and Safety Publications
 Organization for Economic Co-operation and Development High Production Volume Chemicals Program
 Organization for Economic Co-operation and Development Screening Information Data Set
 World Health Organization

Issuing Date 08-Mar-2019
Revision Date 02-Jan-2020
Revision Note SDS sections updated: 14.

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet