

PURELL® FOODSERVICE SURFACE SANITIZER

Version 1.1

MSDS Number: 400000005188

Revision Date: 12/22/2015

SECTION 1. IDENTIFICATION

Product name : PURELL® FOODSERVICE SURFACE SANITIZER

Manufacturer or supplier's details

Company name of supplier : GOJO Industries, Inc.

Address : One GOJO Plaza, Suite 500
Akron, Ohio, 44311

Telephone : 1 (330) 255-6000

Emergency telephone number : 1-800-424-9300 CHEMTREC

SECTION 2. HAZARDS IDENTIFICATION**GHS Classification**

Flammable liquids : Category 3

GHS Label element

Hazard pictograms :



Signal word : Warning

Hazard statements : H226 Flammable liquid and vapour.

Precautionary statements : **Prevention:**
P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P233 Keep container tightly closed.
P240 Ground/bond container and receiving equipment.
P241 Use explosion-proof electrical/ ventilating/ lighting/ equipment.
P242 Use only non-sparking tools.
P243 Take precautionary measures against static discharge.

Response:
P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam for extinction.

Storage:
P403 + P235 Store in a well-ventilated place. Keep cool.

Disposal:
P501 Dispose of contents/ container to an approved waste disposal plant.


PURELL® FOODSERVICE SURFACE SANITIZER

Version 1.1

MSDS Number: 40000005188

Revision Date: 12/22/2015

Other hazards

None known.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**Hazardous components**

Chemical Name	CAS-No.	Concentration (%)
Ethyl Alcohol	64-17-5	>= 30 - < 50
Isopropyl Alcohol	67-63-0	>= 1 - < 5

SECTION 4. FIRST AID MEASURES

- General advice : In the case of accident or if you feel unwell, seek medical advice immediately.
When symptoms persist or in all cases of doubt seek medical advice.
- If inhaled : If inhaled, remove to fresh air.
If symptoms persist, call a physician.
- In case of skin contact : Wash with water and soap as a precaution.
Get medical attention if irritation develops and persists.
- In case of eye contact : In case of contact, immediately flush eyes with plenty of water for at least 15 minutes.
If easy to do, remove contact lens, if worn.
Seek medical advice.
- If swallowed : If swallowed, DO NOT induce vomiting.
Rinse mouth with water.
Obtain medical attention.
- Protection of first-aiders : First Aid responders should pay attention to self-protection and use the recommended protective clothing

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Water spray
Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during fire-fighting : Do not use a solid water stream as it may scatter and spread fire.
Cool closed containers exposed to fire with water spray.
Flash back possible over considerable distance.
May form explosive mixtures in air.
Exposure to decomposition products may be a hazard to health.


PURELL® FOODSERVICE SURFACE SANITIZER

Version 1.1

MSDS Number: 40000005188

Revision Date: 12/22/2015

- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
- Further information : Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
- Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
Use personal protective equipment.

SECTION 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.
Ensure adequate ventilation.
Remove all sources of ignition.
Evacuate personnel to safe areas.
Keep people away from and upwind of spill/leak.
Material can create slippery conditions.
- Environmental precautions : Discharge into the environment must be avoided.
Prevent further leakage or spillage if safe to do so.
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.
- Methods and materials for containment and cleaning up : Non-sparking tools should be used.
Soak up with inert absorbent material.
Keep in suitable, closed containers for disposal.
Clean contaminated floors and objects thoroughly while observing environmental regulations.

SECTION 7. HANDLING AND STORAGE

- Advice on safe handling : Avoid contact with eyes.
- Conditions for safe storage : No smoking.
Take measures to prevent the build up of electrostatic charge.
Keep container tightly closed in a dry and well-ventilated place.
Store in accordance with the particular national regulations.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION
Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Ethyl Alcohol	64-17-5	TWA	1,000 ppm 1,900 mg/m ³	NIOSH REL
		TWA	1,000 ppm 1,900 mg/m ³	OSHA Z-1


PURELL® FOODSERVICE SURFACE SANITIZER

Version 1.1

MSDS Number: 40000005188

Revision Date: 12/22/2015

		STEL	1,000 ppm	ACGIH
Isopropyl Alcohol	67-63-0	TWA	200 ppm	ACGIH
		STEL	400 ppm	ACGIH
		TWA	400 ppm 980 mg/m ³	NIOSH REL
		ST	500 ppm 1,225 mg/m ³	NIOSH REL
		TWA	400 ppm 980 mg/m ³	OSHA Z-1

Biological occupational exposure limits

Components	CAS-No.	Control parameters	Biological specimen	Sam-pling time	Permissible concentra-tion	Basis
Isopropyl Alcohol	67-63-0	Acetone	Urine	End of shift at end of work-week	40 mg/l	ACGIH BEI

Personal protective equipment

- Respiratory protection : No personal respiratory protective equipment normally required.
- Eye protection : No special measures necessary provided product is used correctly.
Wear face-shield and protective suit for abnormal processing problems.
- Skin and body protection : No special measures necessary provided product is used correctly.
- Protective measures : Choose body protection in relation to its type, to the concentration and amount of dangerous substances, and to the specific work-place.
Ensure that eye flushing systems and safety showers are located close to the working place.
When using do not eat, drink or smoke.
- Hygiene measures : Handle in accordance with good industrial hygiene and safety practice.
Avoid contact with eyes.
Wash hands before breaks and immediately after handling the product.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

- Appearance : liquid
- Colour : colourless
- pH : 12.6 - 12.9, (24 °C)
- Initial boiling point and boiling : 77 °C

**PURELL® FOODSERVICE SURFACE SANITIZER**

Version 1.1

MSDS Number: 400000005188

Revision Date: 12/22/2015

range

Flash point : 30.8 °C
Method: Pensky-Martens closed cup

Upper explosion limit : 19 %(V)

Lower explosion limit : 3.3 %(V)

Density : 0.952 g/cm³

Viscosity
Viscosity, dynamic : 2.6 mPa.s

SECTION 10. STABILITY AND REACTIVITY

Reactivity : Not classified as a reactivity hazard.

Possibility of hazardous reactions : Vapours may form explosive mixture with air.

Conditions to avoid : Heat, flames and sparks.

Incompatible materials : Oxidizing agents

Hazardous decomposition products : No hazardous decomposition products are known.

SECTION 11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure**

Inhalation

Skin contact

Eye contact

Acute toxicity

Not classified based on available information.

Components:**Ethyl Alcohol:**

Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg

Acute inhalation toxicity : LC50 (Rat): 124.7 mg/l
Exposure time: 4 h
Test atmosphere: vapour

Isopropyl Alcohol:

Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg

Acute inhalation toxicity : LC50 (Rat): 72.6 mg/l
Exposure time: 4 h
Test atmosphere: vapour

Acute dermal toxicity : LD50 (Rat): > 5,000 mg/kg

**PURELL® FOODSERVICE SURFACE SANITIZER**

Version 1.1

MSDS Number: 400000005188

Revision Date: 12/22/2015

Skin corrosion/irritation

Not classified based on available information.

Product:

Result: No skin irritation

Components:**Ethyl Alcohol:**

Species: Rabbit

Method: OECD Test Guideline 404

Result: No skin irritation

Isopropyl Alcohol:

Species: Rabbit

Result: No skin irritation

Serious eye damage/eye irritation

Not classified based on available information.

Respiratory or skin sensitisation

Skin sensitisation: Not classified based on available information.

Respiratory sensitisation: Not classified based on available information.

Components:**Ethyl Alcohol:**

Test Type: Local lymph node assay (LLNA)

Exposure routes: Skin contact

Species: Mouse

Result: negative

Isopropyl Alcohol:

Test Type: Buehler Test

Exposure routes: Skin contact

Species: Guinea pig

Method: OECD Test Guideline 406

Result: negative

Germ cell mutagenicity

Not classified based on available information.

Components:**Ethyl Alcohol:**Genotoxicity in vitro : Test Type: In vitro mammalian cell gene mutation test
Result: negativeGenotoxicity in vivo : Test Type: Rodent dominant lethal test (germ cell) (in vivo)
Test species: Mouse
Application Route: Ingestion
Result: negative**Isopropyl Alcohol:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)

**PURELL® FOODSERVICE SURFACE SANITIZER**

Version 1.1

MSDS Number: 400000005188

Revision Date: 12/22/2015

Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Test species: Mouse
Application Route: Intraperitoneal injection
Result: negative

Carcinogenicity

Not classified based on available information.

Components:**Isopropyl Alcohol:**

Species: Rat
Application Route: inhalation (vapour)
Exposure time: 104 weeks
Method: OECD Test Guideline 451
Result: negative

IARC No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

OSHA No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Reproductive toxicity

Not classified based on available information.

Components:**Ethyl Alcohol:**

Effects on fertility : Test Type: Two-generation reproduction toxicity study
Species: Mouse
Application Route: Ingestion
Method: OECD Test Guideline 416
Result: negative

Isopropyl Alcohol:

Effects on fertility : Test Type: Two-generation reproduction toxicity study
Species: Rat
Application Route: Ingestion
Result: negative

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: Ingestion
Result: negative

**PURELL® FOODSERVICE SURFACE SANITIZER**

Version 1.1

MSDS Number: 400000005188

Revision Date: 12/22/2015

STOT - single exposure

Not classified based on available information.

Components:**Isopropyl Alcohol:**

Assessment: May cause drowsiness or dizziness.

STOT - repeated exposure

Not classified based on available information.

Repeated dose toxicity**Components:****Ethyl Alcohol:**

Species: Rat

NOAEL: 2,400 mg/kg

Application Route: Ingestion

Exposure time: 2 y

Isopropyl Alcohol:

Species: Rat

NOAEL: 5000 ppm

Application Route: inhalation (vapour)

Exposure time: 104 w

Method: OECD Test Guideline 413

Aspiration toxicity

Not classified based on available information.

SECTION 12. ECOLOGICAL INFORMATION**Ecotoxicity****Components:****Ethyl Alcohol:**Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): > 1,000 mg/l
Exposure time: 96 hToxicity to daphnia and other : EC50 (Daphnia magna (Water flea)): > 1,000 mg/l
aquatic invertebrates Exposure time: 48 hToxicity to algae : EC50 (Chlorella vulgaris (Fresh water algae)): 275 mg/l
Exposure time: 72 h
Method: OECD Test Guideline 201Toxicity to daphnia and other : NOEC (Daphnia magna (Water flea)): 9.6 mg/l
aquatic invertebrates (Chron- Exposure time: 9 d
ic toxicity)Toxicity to bacteria : EC50 (Photobacterium phosphoreum): 32.1 mg/l
Exposure time: 0.25 h**Isopropyl Alcohol:**Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): 10,000 mg/l
Exposure time: 96 h

**PURELL® FOODSERVICE SURFACE SANITIZER**

Version 1.1

MSDS Number: 400000005188

Revision Date: 12/22/2015

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): > 10,000 mg/l
Exposure time: 24 h

Toxicity to bacteria : EC50 (Pseudomonas putida): > 1,050 mg/l
Exposure time: 16 h

Persistence and degradability**Components:****Ethyl Alcohol:**

Biodegradability : Result: Readily biodegradable.
Biodegradation: 84 %
Exposure time: 20 d

Isopropyl Alcohol:

Biodegradability : Result: rapidly degradable

Bioaccumulative potential**Components:****Ethyl Alcohol:**

Partition coefficient: n-octanol/water : log Pow: -0.35

Isopropyl Alcohol:

Partition coefficient: n-octanol/water : log Pow: 0.05

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation 40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

Remarks This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

SECTION 13. DISPOSAL CONSIDERATIONS**Disposal methods**

Waste from residues : Dispose of in accordance with local regulations.

SECTION 14. TRANSPORT INFORMATION**International Regulation**


PURELL® FOODSERVICE SURFACE SANITIZER

Version 1.1

MSDS Number: 400000005188

Revision Date: 12/22/2015

IATA-DGR

UN/ID No. : UN 1987
 Proper shipping name : Alcohols, n.o.s.
 Class : 3
 Packing group : III
 Packing instruction (cargo aircraft) : 366

IMDG-Code

UN number : UN 1987
 Proper shipping name : ALCOHOLS, N.O.S.
 Class : 3
 Packing group : III
 Labels : 3
 EmS Code : F-E, S-D
 Marine pollutant : no

National Regulations**49 CFR**

UN/ID/NA number : UN 1987
 Proper shipping name : Alcohols, n.o.s.
 Class : 3
 Packing group : III
 ERG Code : 127
 Marine pollutant : no

SECTION 15. REGULATORY INFORMATION
EPCRA - Emergency Planning and Community Right-to-Know Act**CERCLA Reportable Quantity**

Components	CAS-No.	Component RQ (lbs)	Calculated product RQ (lbs)
Potassium Hydroxide	1310-58-3	1000	*

*: Calculated RQ exceeds reasonably attainable upper limit.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Fire Hazard

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : The following components are subject to reporting levels established by SARA Title III, Section 313:

Isopropyl Alcohol 67-63-0 1.48 %

Clean Air Act

This product does not contain any hazardous air pollutants (HAP), as defined by the U.S. Clean Air Act Section 12 (40 CFR 61).


PURELL® FOODSERVICE SURFACE SANITIZER

Version 1.1

MSDS Number: 400000005188

Revision Date: 12/22/2015

This product does not contain any chemicals listed under the U.S. Clean Air Act Section 112(r) for Accidental Release Prevention (40 CFR 68.130, Subpart F).

The following chemical(s) are listed under the U.S. Clean Air Act Section 111 SOCMII Intermediate or Final VOC's (40 CFR 60.489):

Ethyl Alcohol	64-17-5	30.31 %
Isopropyl Alcohol	67-63-0	1.48 %

This product does not contain any VOC exemptions listed under the U.S. Clean Air Act Section 450.

Clean Water Act

The following Hazardous Substances are listed under the U.S. CleanWater Act, Section 311, Table 116.4A:

Potassium Hydroxide	1310-58-3	0.345 %
---------------------	-----------	---------

The following Hazardous Chemicals are listed under the U.S. CleanWater Act, Section 311, Table 117.3:

Potassium Hydroxide	1310-58-3	0.345 %
---------------------	-----------	---------

This product does not contain any toxic pollutants listed under the U.S. Clean Water Act Section 307

Massachusetts Right To Know

Ethyl Alcohol	64-17-5	30 - 50 %
Isopropyl Alcohol	67-63-0	1 - 5 %

Pennsylvania Right To Know

Water (Aqua)	7732-18-5	70 - 90 %
Ethyl Alcohol	64-17-5	30 - 50 %
Isopropyl Alcohol	67-63-0	1 - 5 %
Potassium Hydroxide	1310-58-3	0.1 - 1 %

New Jersey Right To Know

Water (Aqua)	7732-18-5	70 - 90 %
Ethyl Alcohol	64-17-5	30 - 50 %
Isopropyl Alcohol	67-63-0	1 - 5 %

California Prop 65

This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

CH INV	: On the inventory, or in compliance with the inventory
TSCA	: On TSCA Inventory
DSL	: All components of this product are on the Canadian DSL.
AICS	: On the inventory, or in compliance with the inventory
NZIoC	: On the inventory, or in compliance with the inventory
ENCS	: On the inventory, or in compliance with the inventory
ISHL	: On the inventory, or in compliance with the inventory
KECI	: On the inventory, or in compliance with the inventory

PURELL® FOODSERVICE SURFACE SANITIZER

Version 1.1

MSDS Number: 400000005188


Revision Date: 12/22/2015

PICCS : On the inventory, or in compliance with the inventory

IECSC : On the inventory, or in compliance with the inventory

Inventories

AICS (Australia), DSL (Canada), IECSC (China), REACH (European Union), ENCS (Japan), ISHL (Japan), KECI (Korea), NZIoC (New Zealand), PICCS (Philippines), TSCA (USA)

SECTION 16. OTHER INFORMATION
Further information
NFPA:

HMIS III:

HEALTH	0
FLAMMABILITY	3
PHYSICAL HAZARD	0

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

Revision Date : 12/22/2015

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.