

Version 1.0	S	DS Number: 400000005677	Revision Date: 12/13/2018
SECTION 1. IDENTIFICATION			
Product name	:	PURELL® Food Processing HE Antimicrobial Foam	EALTHY SOAP® BAK E2
Manufacturer or supplier's	deta	ails	
Company name of supplier		GOJO Industries, Inc.	
Address	:	One GOJO Plaza, Suite 500 Akron, Ohio 44311	
Telephone	:	1 (330) 255-6000	
Emergency telephone number	:	CHEMTREC 1-800-424-9300 CHEMTREC +1-703-527-3887	: Outside USA & CANADA
Recommended use of the of Recommended use	cher :	nical and restrictions on use Antibacterial Soap	
Restrictions on use	:	This is a personal care or cosm consumers and other users und foreseeable use. Cosmetics an specifically defined by regulatio exempt from the requirement of While this material is not consist contains valuable information c proper use of the product for in- as well as unusual and uninten- spills. This SDS should be retail employees and other users of t intended-use guidance, please	der normal and reasonably d consumer products, ons around the world, are f an SDS for the consumer. dered hazardous, this SDS ritical to the safe handling and dustrial workplace conditions ded exposures such as large ined and available for his product. For specific

provided on the package or instruction sheet.

SECTION 2. HAZARDS IDENTIFICATION

GHS Classification

Not a hazardous substance or mixture.

GHS label elements

Not a hazardous substance or mixture.

Other hazards

None known.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Hazardous components



Version 1.0	SDS Number: 400000005677	Revision Date: 12/13/2018
Chemical name	CAS-No.	Concentration (%)
Glycerin	56-81-5	>= 1 - < 5
Cocamidopropyl Betaine	61789-40-0	>= 1 - < 5
Benzalkonium Chloride	68391-01-5	>= 0.1 - < 1

SECTION 4. FIRST AID MEASURES

General advice	:	In the case of accident or if you feel unwell, seek medical advice immediately. When symptoms persist or in all cases of doubt seek medical advice.
If inhaled	:	If inhaled, remove to fresh air. If symptoms persist, call a physician.
In case of skin contact	:	Get medical attention if irritation develops and persists.
In case of eye contact	:	Rinse thoroughly with plenty of water, also under the eyelids. If easy to do, remove contact lens, if worn. Get medical attention if irritation develops and persists.
If swallowed	:	If swallowed, DO NOT induce vomiting. Rinse mouth with water. Obtain medical attention.
Most important symptoms and effects, both acute and delayed	:	None known.
Protection of first-aiders	:	First Aid responders should pay attention to self-protection and use the recommended protective clothing

SECTION 5. FIREFIGHTING MEASURES

Suitable extinguishing media	:	Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.
Unsuitable extinguishing media	:	None known.
Hazardous combustion products	:	Carbon oxides Nitrogen oxides (NOx)
Specific extinguishing methods	:	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. Use water spray to cool unopened containers.
Further information	:	Collect contaminated fire extinguishing water separately. This must not be discharged into drains. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.



Version 1.0	SDS Number: 400000005677	Revision Date: 12/13/2018
Special protective equipment for firefighters	: In the event of fire, wear self-co Use personal protective equipm	e 11

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures	:	Use personal protective equipment. Ensure adequate ventilation. Material can create slippery conditions.
Environmental precautions	:	Discharge into the environment must be avoided. Prevent further leakage or spillage if safe to do so. Prevent spreading over a wide area (e.g. by containment or oil barriers). Retain and dispose of contaminated wash water. Local authorities should be advised if significant spillages cannot be contained.
Methods and materials for containment and cleaning up	:	Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13). Keep in suitable, closed containers for disposal. Clean contaminated floors and objects thoroughly while observing environmental regulations.

SECTION 7. HANDLING AND STORAGE

Advice on safe handling	 For personal protection see section 8. Do not swallow. Avoid contact with eyes. Keep container closed when not in use. 	
Conditions for safe storage	 Keep in properly labelled containers. Keep containers tightly closed in a dry, cool and well- ventilated place. Store in accordance with the particular national regulations 	5.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Glycerin	56-81-5	TWA (mist, respirable fraction)	5 mg/m3	OSHA Z-1
		TWA (mist, total dust)	15 mg/m3	OSHA Z-1



Version 1.0	SDS Number: 40000005677 Revision Date: 12/13/2018
Personal protective equipn	nent
Respiratory protection	: No personal respiratory protective equipment normally required.
Eye protection	: No special protective equipment required. Wear face-shield and protective suit for abnormal processing problems.
Skin and body protection	: No special protective equipment required.
Protective measures	: Choose body protection in relation to its type, to the concentration and amount of dangerous substances, and to the specific work-place.
Hygiene measures	: Handle in accordance with good industrial hygiene and safety practice. Avoid contact with eyes.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	:	liquid
Colour	:	colourless, yellow
Odour	:	like soap
Odour Threshold	:	No data available
рН	:	5.0 - 7.0, (20 °C)
Melting point/freezing point	:	No data available
Initial boiling point and boiling range	:	99 °C
Flash point	:	> 100 °C
Evaporation rate	:	No data available
Flammability (solid, gas)	:	Not applicable
Flammability (liquids)	:	No data available
Upper explosion limit	:	No data available
Lower explosion limit	:	No data available
Vapour pressure	:	No data available
Relative vapour density	:	No data available
Density	:	1.007 g/cm3



Version 1.0	SDS Number: 400000005677	Revision Date: 12/13/2018
Solubility(ies) Water solubility	: soluble	
Partition coefficient: n- octanol/water	: Not applicable	
Auto-ignition temperature	: No data available	
Thermal decomposition	: The substance or mixture is no	t classified self-reactive.
Viscosity Viscosity, kinematic	: 75 mm2/s (20 °C)	
Explosive properties	: Not explosive	
Oxidizing properties	: The substance or mixture is no	t classified as oxidizing.

SECTION 10. STABILITY AND REACTIVITY

Reactivity	: Not classified as a reactivity hazard.
Chemical stability	: Stable under normal conditions.
Incompatible materials	: Strong oxidizing agents
Hazardous decomposition products	: No hazardous decomposition products are known.

SECTION 11. TOXICOLOGICAL INFORMATION

Information on likely routes Inhalation Eye contact Skin contact	of	exposure
Acute toxicity		
Not classified based on availa	ble	information.
Components:		
Glycerin:		DE0 (Det), $E 000 mg/kg$
Acute oral toxicity	•	LD50 (Rat): > 5,000 mg/kg
Cocamidopropyl Betaine:		
Acute oral toxicity	:	LD50 : > 5,000 mg/kg
		Method: OECD Test Guideline 401 Remarks: Based on data from similar materials
		Nomana. Dased on data nom similar materials
Acute dermal toxicity	:	LD50 (Rat): > 2,000 mg/kg
		Method: OECD Test Guideline 402 Assessment: The substance or mixture has no acute dermal
		toxicity
		Remarks: Based on data from similar materials



ntimicrobial Foam		
rsion 1.0	SDS Number: 400000005677	Revision Date: 12/13/2018
Benzalkonium Chloride: Acute oral toxicity	: LD50 (Rat): 850 mg/kg	
Acute dermal toxicity	: LD50 (Rat): 2,300 mg/kg	
Skin corrosion/irritation Not classified based on av	ailable information.	
Product:		
Assessment: Not irritating	when applied to human skin.	
<u>Components:</u>		
Glycerin: Result: No skin irritation		
Cocamidopropyl Betaine Result: Skin irritation	:	
Benzalkonium Chloride: Species: Rabbit Result: Corrosive after 3 m Remarks: Based on data f	ninutes to 1 hour of exposure rom similar materials	
Serious eye damage/eye Not classified based on av		
Components:		
Glycerin: Result: No eye irritation		
Cocamidopropyl Betaine Result: Eye irritation Remarks: Severe eye irrita		
Benzalkonium Chloride: Species: Rabbit Result: Irreversible effects Remarks: Based on data f		
Respiratory or skin sens		
	ssified based on available information. Not classified based on available inform	ation.
Components:		
Cocamidopropyl Betaine Test Type: Maximisation T Exposure routes: Skin con	est (GPMT)	

Test Type: Maximisation Test (GPMT) Exposure routes: Skin contact Species: Guinea pig Result: negative Remarks: Based on data from similar materials



Antimicrobial Foam			
Version 1.0	SDS Number: 400000005677	Revision Date: 12/13/2018	
Benzalkonium Chloride: Test Type: Buehler Test Exposure routes: Skin contac Species: Guinea pig Method: OECD Test Guidelin Result: negative Remarks: Based on data from	e 406		
Germ cell mutagenicity			
Not classified based on availa	able information.		
Components:			
Glycerin: Genotoxicity in vitro	: Test Type: In vitro mammalian c Method: OECD Test Guideline 4 Result: negative		
Cocamidopropyl Betaine:			
Genotoxicity in vitro	: Test Type: Bacterial reverse mu Method: OECD Test Guideline 4 Result: negative Remarks: Based on data from si	71	
Genotoxicity in vivo	: Test Type: Mammalian erythrocy cytogenetic assay) Test species: Mouse Application Route: Ingestion Result: negative Remarks: Based on data from si		
Benzalkonium Chloride:			
Genotoxicity in vitro	: Test Type: Bacterial reverse mu Method: OECD Test Guideline 4 Result: negative Remarks: Based on data from si	171	
Genotoxicity in vivo	: Test Type: Mammalian erythrocy cytogenetic assay) Test species: Mouse Application Route: Ingestion Method: OECD Test Guideline 4 Result: negative Remarks: Based on data from si	74	

Carcinogenicity

Not classified based on available information.

Components:

Glycerin: Species: Rat Application Route: Ingestion Exposure time: 2 Years Result: negative



sion 1.0	SDS Number: 400000005677	Revision Date: 12/13/2018
IARC	No component of this product pres equal to 0.1% is identified as proba human carcinogen by IARC.	
OSHA	No component of this product pres equal to 0.1% is identified as a car carcinogen by OSHA.	
NTP	No component of this product pres equal to 0.1% is identified as a kno by NTP.	
Reproductive toxicity Not classified based on availa	ble information.	
Components:		
Glycerin: Effects on fertility	: Test Type: Two-generation repr Species: Rat Application Route: Ingestion Result: negative	roduction toxicity study
Effects on foetal development	: Test Type: Embryo-foetal devel Species: Rabbit Application Route: Ingestion Result: negative	opment
Cocamidopropyl Betaine:		
Effects on foetal development	: Test Type: Embryo-foetal devel Species: Rat Application Route: Ingestion Method: OECD Test Guideline Result: negative	414
	Remarks: Based on data from s	similar materials
Benzalkonium Chloride:		
Effects on fertility	: Test Type: Two-generation repr Species: Rat Application Route: Ingestion Result: negative Remarks: Based on data from s	
Effects on foetal development	: Test Type: Embryo-foetal devel Species: Rat Application Route: Ingestion Result: negative Remarks: Based on data from s	

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.



Version 1.0

SDS Number: 400000005677

Revision Date: 12/13/2018

Repeated dose toxicity

Components:

Glycerin: Species: Rat NOAEL: 167 mg/m3 LOAEL: 660 mg/m3 Application Route: inhalation (dust/mist/fume) Exposure time: 13 w Symptoms: Local irritation

Cocamidopropyl Betaine:

Species: Rat NOAEL: 250 mg/kg Application Route: Ingestion Exposure time: 90 d Method: OECD Test Guideline 408 Remarks: Based on data from similar materials

Benzalkonium Chloride:

Species: Mouse NOAEL: 192 mg/kg Application Route: Ingestion Exposure time: 94 d Remarks: Based on data from similar materials

Aspiration toxicity

Not classified based on available information.

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

Components:		
Glycerin: Toxicity to fish	:	LC50 (Oncorhynchus mykiss (rainbow trout)): 54,000 mg/l Exposure time: 96 h
Toxicity to daphnia and other aquatic invertebrates	:	EC50 (Daphnia magna (Water flea)): 1,955 mg/l Exposure time: 48 h
Toxicity to bacteria	:	NOEC (Pseudomonas putida): > 10,000 mg/l Exposure time: 16 h
Cocamidopropyl Betaine: Toxicity to fish	:	LC50: > 1 - 10 mg/l Exposure time: 96 h Method: ISO 7346/2 Remarks: Based on data from similar materials
Toxicity to bacteria	:	EC50: > 100 mg/l Method: OECD Test Guideline 209 Remarks: Based on data from similar materials



sion 1.0	SDS Number: 40000005677 Revision Date: 12/1	3/2018
Benzalkonium Chloride: Toxicity to fish	: LC50 (Lepomis macrochirus (Bluegill sunfish)): 0.515 m Exposure time: 96 h Remarks: Based on data from similar materials	g/l
Toxicity to daphnia and other aquatic invertebrates	 EC50 (Daphnia magna (Water flea)): 0.016 mg/l Exposure time: 48 h Method: Directive 67/548/EEC, Annex V, C.2. Remarks: Based on data from similar materials 	
Toxicity to algae	 ErC50 (Selenastrum capricornutum (green algae)): 0.04 Exposure time: 72 h Method: OECD Test Guideline 201 Remarks: Based on data from similar materials 	19 mg/l
	EC10 (Selenastrum capricornutum (green algae)): 0.009 Exposure time: 72 h Method: OECD Test Guideline 201 Remarks: Based on data from similar materials	9 mg/l
M-Factor (Acute aquatic toxicity)	: 10	
Toxicity to fish (Chronic toxicity)	: NOEC (Pimephales promelas (fathead minnow)): 0.032: Exposure time: 34 d Remarks: Based on data from similar materials	2 mg/l
Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity)	 NOEC (Daphnia magna (Water flea)): 0.0125 mg/l Exposure time: 21 d Method: OECD Test Guideline 211 Remarks: Based on data from similar materials 	
M-Factor (Chronic aquatic toxicity)	: 1	
Persistence and degradabili	/	
Components:		
Glycerin: Biodegradability	: Result: Readily biodegradable. Biodegradation: 94 % Exposure time: 1 d	
Cocamidopropyl Betaine: Biodegradability	 Result: Readily biodegradable. Biodegradation: > 60 % Exposure time: 28 d Method: OECD Test Guideline 301 Remarks: Based on data from similar materials 	
Benzalkonium Chloride: Biodegradability	: Result: Readily biodegradable. Biodegradation: 72 % Exposure time: 28 d	



Version 1.0	SDS Number: 400000005677	Revision Date: 12/13/2018
Bioaccumulative potential		
Components:		
Glycerin: Partition coefficient: n- octanol/water	: log Pow: -1.76	
Benzalkonium Chloride: Partition coefficient: n- octanol/water	: log Pow: 2.75 Remarks: Based on data from sir	nilar materials
Mobility in soil No data available		
Other adverse effects No data available		
Product:		
Regulation	40 CFR Protection of Environmer Stratospheric Ozone - CAA Secti	,
Remarks	This product neither contains, not Class I or Class II ODS as define Section 602 (40 CFR 82, Subpt. /	d by the U.S. Clean Air Act

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods Waste from residues	: Dispose of in accordance with local regulations.
Contaminated packaging	: Dispose of as unused product. Empty containers should be taken to an approved waste handling site for recycling or disposal.

SECTION 14. TRANSPORT INFORMATION

International Regulation

IATA-DGR

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good **National Regulations**

49 CFR

Not regulated as a dangerous good

SECTION 15. REGULATORY INFORMATION



Version 1.0	SDS Number: 400000005677	Revision Date: 12/13/2018
SARA 311/312 Hazards	: No SARA Hazards	
SARA 302	: No chemicals in this material are requirements of SARA Title III, S	, , ,
SARA 313	: This material does not contain an known CAS numbers that exceed reporting levels established by Sa	the threshold (De Minimis)

Clean Air Act

This product does not contain any hazardous air pollutants (HAP), as defined by the U.S. Clean Air Act Section 12 (40 CFR 61).

This product does not contain any chemicals listed under the U.S. Clean Air Act Section 112(r) for Accidental Release Prevention (40 CFR 68.130, Subpart F).

The following chemical(s) are listed under the U.S. Clean Air Act Section 111 SOCMI Intermediate or Final VOC's (40 CFR 60.489): 2%

56-81-5 Glycerin

This product does not contain any VOC exemptions listed under the U.S. Clean Air Act Section 450.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

This product does not contain any toxic pollutants listed under the U.S. Clean Water Act Section 307

California Prop 65	This product does not require a warning label under California
	Proposition 65.

The components of this product are reported in the following inventories:

: On the inventory, or in compliance with the inventory
: On the inventory, or in compliance with the inventory
: All components of this product are on the Canadian DSL.
: On the inventory, or in compliance with the inventory
: On the inventory, or in compliance with the inventory
: On the inventory, or in compliance with the inventory
: On the inventory, or in compliance with the inventory
: On the inventory, or in compliance with the inventory
: On the inventory, or in compliance with the inventory

Inventories

AICS (Australia), DSL (Canada), IECSC (China), REACH (European Union), ENCS (Japan), ISHL (Japan), KECI (Korea), NZIOC (New Zealand), PICCS (Philippines), TCSI (Taiwan), TSCA (USA)




Version 1.0

SDS Number: 40000005677

Revision Date: 12/13/2018

SECTION 16. OTHER INFORMATION





HMIS III:



0 = not significant, 1 =Slight, 2 = Moderate, 3 = High 4 = Extreme, * = Chronic

Revision Date

: 12/13/2018

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.