

SAFETY DATA SHEET



Issuing Date: 27-Mar-2015

Revision Date: 27-Mar-2015

Version 1

1. IDENTIFICATION

Product Name Cascade Gel Automatic Dishwasher Detergent - Fresh Scent

Product ID: 99589322_RET_NG

Product Type: Finished Product - Consumer (Retail) Use Only

Recommended Use Dish Care

Restrictions on Use Use only as directed on label.

Synonyms Cascade Gel Automatic Dishwasher Detergent - Lemon Scent (99547569_RET_NG)

Manufacturer PROCTER & GAMBLE - Fabric and Home Care Division. Ivorydale Technical Centre. 5289 Spring Grove Avenue, Cincinnati, Ohio 45217-1087 USA

E-mail Address pgsds.im@pg.com

Emergency Telephone Transportation (24 HR)
CHEMTREC - 1-800-424-9300
(U.S./ Canada) or 1-703-527-3887
Mexico toll free in country: 800-681-9531

2. HAZARD IDENTIFICATION

"Consumer Products", as defined by the US Consumer Product Safety Act and which are used as intended (typical consumer duration and frequency), are exempt from the OSHA Hazard Communication Standard (29 CFR 1910.1200). This SDS is being provided as a courtesy to help assist in the safe handling and proper use of the product.

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:

Hazard Category

Skin corrosion/irritation Category 2
Eye Damage / Irritation Category 2A
Corrosive to metals Category 1

Signal Word WARNING

Hazard Statements Causes serious eye irritation
Causes skin irritation
May be corrosive to metals

Hazard pictograms



Precautionary Statements - Prevention

Wash hands thoroughly after handling
Keep only in original container

Precautionary Statements - Response

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
If eye irritation persists: Get medical advice/attention
IF SWALLOWED:
Drink 1 or 2 glasses of water
IF ON SKIN:
Rinse with plenty of water
If skin irritation occurs, get medical advice/attention
Absorb spillage to prevent material damage

Precautionary Statements - Storage

Store in corrosive resistant container

Precautionary Statements - Disposal

Dispose of contents/container in accordance with local regulation

Hazards not otherwise classified (HNOC)

None

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Chemical Name	Synonyms	Trade Secret	CAS-No	Weight %
Silicic acid, sodium salt	-	No	1344-09-8	10 - 15
Sodium carbonate	-	No	497-19-8	5 - 10
Sodium hydroxide	-	No	1310-73-2	1 - 5

4. FIRST AID MEASURES

First aid measures for different exposure routes

Eye contact

Rinse with plenty of water. Get medical attention immediately if irritation persists.

Skin contact

Rinse with plenty of water. Get medical attention if irritation develops and persists.

Ingestion

Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur.

Inhalation

Move to fresh air. If symptoms persist, call a physician.

Most important symptoms/effects, acute and delayed

None under normal use conditions.

Indication of immediate medical attention and special treatment needed, if necessary

Notes to Physician

Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media	Dry chemical, CO ₂ , alcohol-resistant foam or water spray.
Unsuitable Extinguishing Media	None.
Special hazard	None known.
Special protective equipment for fire-fighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
Specific hazards arising from the chemical	None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions	Use personal protective equipment. Do not get in eyes, on skin, or on clothing.
Advice for emergency responders	Use personal protective equipment as required.

Methods and materials for containment and cleaning up

Methods for containment	Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal.
Methods for cleaning up	Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling	Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.
--------------------------------	---

Conditions for safe storage, including any incompatibilities

Storage Conditions	Store in corrosive resistant container.
Incompatible products	None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	CAS-No	ACGIH TLV	OSHA PEL	Mexico PEL
Sodium hydroxide	1310-73-2	Ceiling: 2 mg/m ³	TWA: 2 mg/m ³ (vacated) Ceiling: 2 mg/m ³	Mexico: Ceiling 2 mg/m ³

Chemical Name	CAS-No	Alberta	Quebec	Ontario TWAEV	British Columbia
Sodium hydroxide	1310-73-2	Ceiling: 2 mg/m ³	Ceiling: 2 mg/m ³	CEV: 2 mg/m ³	Ceiling: 2 mg/m ³

No relevant exposure guidelines for other ingredients

Exposure controls

Engineering Measures

Distribution, Workplace and Household Settings:
Ensure adequate ventilation

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

Personal Protective Equipment

Eye Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Use appropriate eye protection

Hand Protection

Distribution, Workplace and Household Settings:
For sensitive skin or prolonged use, wear gloves

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Protective gloves

Skin and Body Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Wear suitable protective clothing

Respiratory Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
In case of insufficient ventilation wear suitable respiratory equipment

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State @20°C liquid
Appearance clear
Odor Scented
Odor threshold No information available

<u>Property</u>	<u>Values</u>	<u>Note</u>
pH value	11.35	(as 1% solution)
Melting/freezing point	No information available	
Boiling point/boiling range	No information available	
Flash point	> 93.3 °C / > 200 °F	Closed cup
Evaporation rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limits in Air		
Upper flammability limit	No information available	
Lower Flammability Limit	No information available	
Vapor pressure	No information available	
Vapor density	No information available	
Relative density	1.25	
Water solubility	100%	
Solubility in other solvents	No information available	

Partition coefficient: n-octanol/water No information available
 Autoignition temperature No information available
 Decomposition temperature No information available
 Viscosity of Product No information available

VOC Content (%) Products comply with US state and federal regulations for VOC content in consumer products.

10. STABILITY AND REACTIVITY

Reactivity None under normal use conditions.
Stability Stable under normal conditions.
Hazardous polymerization Hazardous polymerization does not occur.
Hazardous Reactions None under normal processing.
Conditions to Avoid None under normal processing.
Materials to avoid None in particular.
Hazardous Decomposition Products None under normal use.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Inhalation No known effect.
Skin contact Irritating to skin.
Ingestion No known effect.
Eye contact Causes serious eye irritation.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Acute toxicity No known effect.
Skin corrosion/irritation Irritating to skin.
Serious eye damage/eye irritation Causes serious eye irritation.
Skin sensitization No known effect.
Respiratory sensitization No known effect.
Germ cell mutagenicity No known effect.
Neurological Effects No known effect.
Reproductive toxicity No known effect.
Developmental toxicity No known effect.
Teratogenicity No known effect.
STOT - single exposure No known effect.
STOT - repeated exposure No known effect.
Target Organ Effects No known effect.
Aspiration hazard No known effect.
Carcinogenicity No known effect.

Component Information

Chemical Name	CAS-No	LD50 Oral	LD50 Dermal	LC50 Inhalation
Silicic acid, sodium salt	1344-09-8	3400 mg/kg bw (Similar to OECD 401; standard acute method; rat)	> 5000 mg/kg bw (Read across data on AgSil TM 25 Potassium silicate solution; rat)	> 2.06 mg/L air (Read across data AgSil TM 25 Potassium silicate solution; EPA OPPTS 870.1300; standard acute method; rat)
Sodium carbonate	497-19-8	2800 mg/kg bw (Guideline not indicated; rat)	> 2000 mg/kg bw (EPA 16 CFR 1500.40; rabbit)	-

12. ECOLOGICAL INFORMATION

Ecotoxicity

The product is not expected to be hazardous to the environment.

Persistence and degradability	No information available.
Bioaccumulative potential	No information available.
Mobility	No information available.
Other adverse effects	No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment

Waste from Residues / Unused Products	Products covered by this MSDS, in their original form, when disposed as waste, are corrosive hazardous waste, D002, according to Federal RCRA regulations (40 CFR 261). Disposal should be in accordance with local, state and federal regulations.
Contaminated packaging	Disposal should be in accordance with applicable regional, national and local laws and regulations.
California Hazardous Waste Codes (non-household setting)	331

14. TRANSPORT INFORMATION

DOT

UN no	UN3266
UN Proper shipping name	Corrosive liquid, basic, inorganic, n.o.s.
Description	UN3266, Corrosive liquid, basic, inorganic, n.o.s. (Sodium hydroxide, Sodium hypochlorite), 8, III, , Ltd. Qty.
Hazard Class	8
Packing Group	III
Emergency Response Guide Number	154

IMDG

UN Number	UN3266
UN Proper shipping name	Corrosive liquid, basic, inorganic, n.o.s.
Description	UN3266, Corrosive liquid, basic, inorganic, n.o.s. (Sodium hydroxide, Sodium hypochlorite), 8, III , Ltd. Qty.
Transport hazard class(es)	8
Packing Group	III
EmS-No	F-A, S-B

IATA

UN no	UN3266
UN Proper shipping name	Corrosive liquid, basic, inorganic, n.o.s.
Description	UN3266, Corrosive liquid, basic, inorganic, n.o.s. (Sodium hydroxide, Sodium hypochlorite), 8, III , Ltd. Qty.
Hazard Class	8
Packing Group	III
ERG Code	8L

15. REGULATORY INFORMATION

U.S. Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302):

Chemical Name	CAS-No	Hazardous Substances RQs	Extremely Hazardous Substances RQs	CERCLA/SARA 302 TPQ
Sodium hydroxide	1310-73-2	1000 lb	-	
Sodium hypochlorite	7681-52-9	100 lb	-	

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of the Clean Air Act Amendments of 1990.

Clean Water Act

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42):

Chemical Name	CAS-No	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Sodium hydroxide	1310-73-2	1000 lb	-	-	X
Sodium hypochlorite	7681-52-9	100 lb	-	-	X
Hydrozincite (Zn5(CO3)2(OH)6)	12122-17-7	-	X	-	-

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

U.S. State Regulations (RTK)

Chemical Name	CAS-No	New Jersey
Sodium hydroxide	1310-73-2	X

Chemical Name	CAS-No	Massachusetts
Sulfuric acid sodium salt (1:2)	7757-82-6	X
Sodium hydroxide	1310-73-2	X

Chemical Name	CAS-No	Pennsylvania
Sulfuric acid sodium salt (1:2)	7757-82-6	X
Sodium hydroxide	1310-73-2	X
Sodium hypochlorite	7681-52-9	X
Hydrozincite (Zn5(CO3)2(OH)6)	12122-17-7	X

Chemical Name	CAS-No	Rhode Island
Sodium hydroxide	1310-73-2	X

International Inventories

United States

All intentionally-added components of this product(s) are listed on the US TSCA Inventory.

Canada

This product is in compliance with CEPA for import by P&G.

Legend

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

CEPA - Canadian Environmental Protection Act

16. OTHER INFORMATION

Issuing Date: 27-Mar-2015

Revision Date: 27-Mar-2015

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS