

SAFETY DATA SHEET

1. Identification

Product identifier	Pacific Garden® Foam Hand Sanitizer	
Product list	Pacific Garden® Foam Hand Sanitizer, Dye Free, Fragrance Free 1000 mL SKU - 43331 Pacific Garden® Foam Hand Sanitizer, Dye Free, Fragrance Free 45 mL SKU - 48003 Pacific Garden® Automated Foam Hand Sanitizer, Fragrance Free, Dye Free 950 mL SKU- 43332 GP internal code only 6176B	
Other means of identification	None.	
Recommended use	Alcohol Hand Sanitizer	
Recommended restrictions	This product is regulated as an Over-the-Counter (OTC) drug in the US and is intended for personal care use.	
Manufacturer/Importer/Supplier/Distributor information		
Company name	Georgia-Pacific Consumer Products LP	
Address	133 Peachtree Street, NE Atlanta, GA 30303	
Telephone	Technical Information	866.435.5647
	(M)SDS Request	404.652.5119
E-mail	MSDSREQ@GAPAC.com	
Emergency phone number	Chemtrec - Emergency	800.424.9300

2. Hazard(s) identification

Physical hazards	Flammable liquids	Category 2
Health hazards	Serious eye damage/eye irritation	Category 2A
Environmental hazards	Not classified.	
OSHA defined hazards	Not classified.	

Label elements



Signal word	Danger
Hazard statement	Highly flammable liquid and vapor. Causes serious eye irritation.
Precautionary statement	
Prevention	Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Keep container tightly closed. Wear protective gloves/eye protection, if handling large quantities.
Response	In the event of large spill and subsequent exposure to the product: If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. In case of fire: Use appropriate media to extinguish.
Storage	Store in a well-ventilated place. Keep cool.
Disposal	Dispose of contents/container in accordance with local/regional/national/international regulations.
Hazard(s) not otherwise classified (HNOC)	In the event of a large spill, sparks may ignite liquid and vapor. May cause flash fire or explosion.
Supplemental information	None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
ETHYL ALCOHOL		64-17-5	62
Other components below reportable levels			38.01

The specific chemical identity and/or percentage of composition has been withheld as a trade secret.

Composition comments Percent by volume concentration of ETHYL ALCOHOL (64-17-5) is 70% (v/v).

Meets Alcohol Requirements stated in FDA Tentative Final Monograph for OTC Healthcare Antiseptic Drug Products – 21 CFR Part 333.410 (a).

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	If irritation occurs, flush skin with plenty of water. Call a physician if irritation persists.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention if irritation develops and persists.
Ingestion	Rinse mouth. Do not induce vomiting without advice from poison control center. Get medical attention if symptoms occur.
Most important symptoms/effects, acute and delayed	Causes serious eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Coughing.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically.
General information	Wash contaminated clothing before reuse.

5. Fire-fighting measures

Suitable extinguishing media	Alcohol resistant foam. Water fog. Carbon dioxide (CO ₂). Dry chemical powder, carbon dioxide, sand or earth may be used for small fires only.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	Flammable liquid - may release vapors that form flammable mixtures at or above the flash point. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	In case of fire and/or explosion do not breathe fumes. Move containers from fire area if you can do so without risk.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	Highly flammable liquid and vapor.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Wear appropriate protective equipment and clothing during clean-up. For personal protection, see section 8 of the SDS. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Local authorities should be advised if significant spillages cannot be contained.
Methods and materials for containment and cleaning up	Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Take precautionary measures against static discharge. Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Cover with plastic sheet to prevent spreading. Use a non-combustible material like vermiculite, sand or earth to soak up the product and place into a container for later disposal. Following product recovery, flush area with water. Small Spills: Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid discharge into drains, water courses or onto the ground. Use appropriate containment to avoid environmental contamination.

7. Handling and storage

Precautions for safe handling

For external use only. Keep out of the reach of children. Do not get this material in contact with eyes. Wear gloves and safety glasses or goggles if handling large quantities. Do not handle or store near an open flame, heat or other sources of ignition. When using do not smoke.

Conditions for safe storage, including any incompatibilities

Keep away from heat, sparks and open flame. Eliminate sources of ignition. Store in a cool, dry place out of direct sunlight. Store in original tightly closed container. Store in a well-ventilated place. Store away from incompatible materials (see Section 10 of the SDS). Keep in an area equipped with sprinklers.

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
ETHYL ALCOHOL (CAS 64-17-5)	PEL	1900 mg/m ³ 1000 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
ETHYL ALCOHOL (CAS 64-17-5)	STEL	1000 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
ETHYL ALCOHOL (CAS 64-17-5)	TWA	1900 mg/m ³ 1000 ppm

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

General ventilation normally adequate.

Individual protection measures, such as personal protective equipment

Eye/face protection

None necessary under normal conditions of use. Wear safety glasses or goggles if handling large quantities.

Skin protection

Hand protection

None necessary under normal conditions of use. Wear appropriate gloves if handling large quantities.

Other

None necessary under normal conditions of use. Wear appropriate gloves if handling large quantities.

Respiratory protection

Under normal conditions of use respiratory protection is not expected to be required.

Thermal hazards

Not applicable.

General hygiene considerations

When using do not smoke.

9. Physical and chemical properties

Appearance

Clear alcohol hand sanitizer.

Physical state

Liquid.

Form

Foam when dispensed.

Color

Colorless

Odor

Alcohol

Odor threshold

Not available.

pH

6 - 8

Melting point/freezing point

Not available.

Initial boiling point and boiling range

173.3 °F (78.5 °C) estimated

Flash point

62.6 °F (17.0 °C)

Evaporation rate

Not available.

Flammability (solid, gas)

Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.

Vapor pressure Not available.

Vapor density Not available.

Relative density Not available.

Solubility(ies)

Solubility (water) Complete

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature Not available.

Decomposition temperature Not available.

Viscosity Not available.

Other information

Specific gravity 0.89 - 0.9

10. Stability and reactivity

Reactivity The product is stable and non-reactive under normal conditions of use, storage and transport.

Chemical stability Material is stable under normal conditions.

Possibility of hazardous reactions Hazardous polymerization does not occur.

Conditions to avoid Avoid heat, sparks, open flames and other ignition sources. Avoid temperatures exceeding the flash point. Contact with incompatible materials.

Incompatible materials Strong oxidizing agents. Acids. Metals. Chlorine.

Hazardous decomposition products Small amounts of nitrogen oxides, carbon monoxide, carbon dioxide and hydrocarbons may be released.

11. Toxicological information

Information on likely routes of exposure

Inhalation No effects expected under normal conditions of use.

Skin contact No effects expected under normal conditions of use. Prolonged skin contact may cause temporary irritation.

Eye contact Causes serious eye irritation.

Ingestion No effects expected under normal conditions of use. May be harmful if swallowed.

Symptoms related to the physical, chemical and toxicological characteristics Causes serious eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.

Information on toxicological effects

Acute toxicity

Product	Species	Test Results
Pacific Garden® Foam Hand Sanitizer		
Acute		
Dermal		
LD50	Rabbit	2000 g/kg estimated
Inhalation		
LC50	Rat	114 mg/l, 4 Hours estimated
Oral		
LC50	Rat	9500 mg/m3, 8 hours estimated
LD50	Mouse	13380 mg/kg estimated

Components	Species	Test Results
ETHYL ALCOHOL (CAS 64-17-5)		
Acute		
Inhalation		
LC50	Rat	117 - 125 mg/l, 4 Hours
Oral		
LD50	Mouse	8300 mg/kg

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Prolonged skin contact may cause temporary irritation.
Serious eye damage/eye irritation	Causes serious eye irritation.
Respiratory or skin sensitization	
Respiratory sensitization	Not a respiratory sensitizer.
Skin sensitization	This product is not expected to cause skin sensitization.
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	Not hazardous under normal conditions of use.
	Ethanol: Chronic ingestion of ethanol in alcoholic beverages is classified by IARC as Group 1 Carcinogenic to humans.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Reproductive toxicity	Not hazardous under normal conditions of use. Chronic ingestion of ethanol can cause reproductive/developmental effects.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Not an aspiration hazard.
Chronic effects	Not hazardous under normal conditions of use. Chronic ingestion of ethanol can cause liver toxicity.

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Product	Species	Test Results
Pacific Garden® Foam Hand Sanitizer		
Aquatic		
Fish	LC50	Fish
		21599.8926 mg/l, 96 hours estimated
Components	Species	Test Results
ETHYL ALCOHOL (CAS 64-17-5)		
Aquatic		
Fish	LC50	Fathead minnow (Pimephales promelas)
		13400 - 15100 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)

ETHYL ALCOHOL -0.31

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions	This product, if discarded as supplied, is considered a hazardous waste under RCRA, D001.
Local disposal regulations	Dispose in accordance with all applicable regulations.
Hazardous waste code	D001: Waste Flammable material with a flash point <140 F
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty packaging/container can be disposed in accordance with all applicable regulations.

14. Transport information

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not established.
---	------------------

15. Regulatory information

US federal regulations	SDS prepared pursuant to the Hazard Communication Standard (29 CFR 1910.1200). This product is regulated under the US Federal Food, Drug, and Cosmetic Act.
-------------------------------	---

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories	Immediate Hazard - Yes Delayed Hazard - No Fire Hazard - Yes Pressure Hazard - No Reactivity Hazard - No
--------------------------	--

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical	Yes
--	-----

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA)	Not regulated.
---------------------------------------	----------------

US state regulations

US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)

Not listed.

US. Massachusetts RTK - Substance List

ETHYL ALCOHOL (CAS 64-17-5)

US. New Jersey Worker and Community Right-to-Know Act

ETHYL ALCOHOL (CAS 64-17-5)

US. Pennsylvania Worker and Community Right-to-Know Law

ETHYL ALCOHOL (CAS 64-17-5)

US. Rhode Island RTK

Not regulated.

US. California Proposition 65

WARNING: This product contains a chemical known to the State of California to cause cancer.

US - California Proposition 65 - CRT: Listed date/Carcinogenic substance

DIETHANOLAMINE (CAS 111-42-2)

Listed: June 22, 2012

16. Other information, including date of preparation or last revision**Issue date** June-30-2014**Revision date** April-29-2015**Version #** 02**HMIS® ratings** Health: 2
Flammability: 3
Physical hazard: 0**NFPA ratings** Health: 2
Flammability: 3
Instability: 0

Disclaimer This SDS is intended to quickly provide useful information to the user(s) of this material or product. It is not intended to serve as a comprehensive discussion of all possible risks or hazards, and it assumes a reasonable use of the product. The information contained in this SDS is believed to be accurate as of the date of preparation of this SDS and has been compiled from sources believed to be reliable. It is offered for your consideration, investigation and verification. The user or handler (or their employer) should consider the specific conditions in which this material will be used, handled, or stored and determine what specific safety or other precautions are required. Employers should ensure that their employees, agents, contractors, and customers who will use the product receive adequate warnings and safe handling procedures, including a current SDS. Product users or handlers (or their employer) who are unsure of what specific precautions are required should consult their employer, product supplier, or safety or health professionals before handling or working with this product. Please notify us immediately if you believe this SDS or other safety and health information about this product is inaccurate or incomplete.

Revision Information This document has undergone significant changes and should be reviewed in its entirety.