

Issue Date 02-May-2018

Revision/Review Date: 09-Dec-2019

Version 1.2

1. IDENTIFICATION

Product Identifier

Product Name Maxim Phoz Gel

Other means of Identification

Product Code 032200

Recommended use of the Chemical and Restrictions on Use

Recommended Use Acid bathroom cleaner. For industrial use.

Details of the Supplier of the Safety Data Sheet

Midlab, Inc.
140 Private Brand Way
Athens, TN 37303

Emergency Telephone Number

Company Phone Number Phone: 1-423-337-3180
Emergency Telephone (24 hr) INFOTRAC 1-352-323-3500 (International) – Customer Number: 76773
1-800-535-5053 (North America)

2. HAZARDS IDENTIFICATION

Appearance Pink

Physical State Liquid

Odor Cherry

Classification

Skin corrosion/irritation	Category 1 Sub-category B
Serious eye damage/eye irritation	Category 1
Corrosive to Metals	Category 1

Signal Word

Danger



Hazard Statements

Causes severe skin burns and eye damage.
May be corrosive to metals.

Precautionary Statements - Prevention

Do not breathe mist/vapors/spray.
Wash face, hands and any exposed skin thoroughly after handling.
Wear protective gloves /eye protection.
Keep only in original container.

Precautionary Statements - Response

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
If eye irritation persists: Get medical advice / attention.
IF ON SKIN (or hair): Rinse skin with water. Take off contaminated clothing and wash before reuse. If skin irritation or rash occurs: Get medical advice / attention.
IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. If experiencing respiratory symptoms: Call a POISON CENTER or doctor.
IF SWALLOWED: rinse mouth. Do NOT induce vomiting. Get immediate medical advice / attention.
IN CASE OF SPILL: Absorb spillage to prevent material damage.

Precautionary Statements - Storage

Store locked up.
Store in corrosive resistant container with a resistant inner liner.

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant.

Other Hazards

Harmful to aquatic life with long lasting effects.

Unknown Acute Toxicity

None known.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%
Water	7732-18-5	60-100
Phosphoric Acid	7664-38-2	10-30

**If Chemical Name/CAS No is "proprietary" and/or Weight-% is listed as a range, the specific chemical identity and/or percentage of composition has been withheld as a trade secret. **

4. FIRST-AID MEASURES

First Aid Measures

Eye Contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Remove and discard contact lenses. Seek immediate medical attention/advice.
Skin Contact	Wash off immediately with plenty of water for at least 15 minutes. Take off contaminated clothing. Wash contaminated clothing before reuse. Get medical attention immediately.
Inhalation	Remove to fresh air. Seek immediate medical attention/advice.
Ingestion	Rinse mouth. Drink plenty of water. Do not induce vomiting. Never give anything by mouth to an unconscious person. Call a physician or poison control center immediately.

Most Important Symptoms and Effects

Symptoms	Corrosive to eyes. Contact will cause irritation and redness to exposed areas. Prolonged contact may even cause severe skin irritation or mild burn. Chronic exposure may cause liver, kidney and/or blood disorders.
-----------------	---

Indication of Any Immediate Medical Attention and Special Treatment Needed

Notes to Physician	Treat symptomatically.
---------------------------	------------------------

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Water spray (fog). Carbon dioxide (CO₂). Dry chemical. Foam.

Unsuitable Extinguishing Media

Not determined.

Specific Hazards Arising from the Chemical

None known.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal Precautions, Protective Equipment and Emergency Procedures

Personal Precautions	Use personal protective equipment as required.
-----------------------------	--

Environmental Precautions Avoid release to the environment.

Methods and Material for Containment and Cleaning Up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for Clean-Up Collect spillage. Collect in a clean, dry waste container for disposal.

7. HANDLING AND STORAGE

Precautions for Safe Handling

Advice on Safe Handling Wash thoroughly after handling. Use personal protection recommended in Section 8. Do not breathe dust/fume/gas/mist/vapors/spray. Avoid contact with skin and eyes.

Conditions for Safe Storage, including Any Incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place. Keep locked up and out of reach of children. Keep from freezing. Keep only in original container.

Incompatible Materials Acids. Bases. Oxidizing agents. Uncontrolled contact with water.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Phosphoric Acid 7664-38-2	STEL: 3 mg/m ³ TWA: 1 mg/m ³	TWA: 1 mg/m ³ (vacated) TWA: 1 mg/m ³ (vacated) STEL: 3 mg/m ³	IDLH: 1000 mg/m ³ TWA: 1 mg/m ³ STEL: 3 mg/m ³

Appropriate Engineering Controls

Engineering Controls Ventilation systems. Eyewash stations. Showers.

Individual Protection Measures, such as Personal Protective Equipment

Eye/Face Protection Splash goggles or safety glasses.

Skin and Body Protection Rubber, Nitrile, PVC, or other chemically resistant skin protection to prevent contact.

Respiratory Protection Ensure adequate ventilation, especially in confined areas.

General Hygiene Considerations Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on Basic Physical and Chemical Properties

Physical State	Liquid	Odor	Cherry
Appearance	Clear to hazy	Odor Threshold	Not determined
Color	Pink		

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	<1	
Melting Point/Freezing Point	Not known	
Boiling Point/Boiling Range	100.5 °C / 213 °F	
Flash Point	Not applicable	
Evaporation Rate	Not determined	
Flammability (Solid, Gas)	n/a-liquid	
Upper Flammability Limits	Not determined	

Lower Flammability Limit	Not determined	
Vapor Pressure	Not determined	
Vapor Density	Not determined	
Specific Gravity	1.13	
Water Solubility	Completely soluble	@ 25 °C (77 °F)
Solubility in other solvents	Not determined	
Partition Coefficient	Not determined	
Auto-ignition Temperature	Not determined	
Decomposition Temperature	Not determined	
Kinematic Viscosity	Not determined	
Dynamic Viscosity	Not determined	
Explosive Properties	Not determined	
Oxidizing Properties	Not determined	

10. STABILITY AND REACTIVITY

Reactivity

Not reactive under normal conditions.

Chemical Stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to Avoid

Keep out of reach of children. Keep from freezing.

Incompatible Materials

Acids. Bases. Oxidizing agents. Uncontrolled contact with water.

Hazardous Decomposition Products

When exposed to fire, produces normal products of combustion.

11. TOXICOLOGICAL INFORMATION

Information on Likely Routes of Exposure

Product Information

Eye Contact	Causes severe eye damage.
Skin Contact	Causes severe skin burns.
Inhalation	Avoid breathing vapors or mists.
Ingestion	Do not taste or swallow.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Phosphoric Acid 7664-38-2	= 1530 mg/kg (Rat)	= 2730 mg/kg (Rabbit)	> 850 mg/m ³ (Rat) 1 h

Information on Physical, Chemical and Toxicological Effects

Symptoms Please see section 4 of this SDS for symptoms.

Delayed and Immediate Effects as well as Chronic Effects from Short and Long-Term Exposure

Carcinogenicity This product does not contain any carcinogens or potential carcinogens as listed by OSHA, IARC or NTP.

Numerical Measures of Toxicity

Not determined

Unknown Acute Toxicity

None known.

12. ECOLOGICAL INFORMATION**Ecotoxicity**

Harmful to aquatic life with long lasting effects.

Chemical Name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Phosphoric Acid 7664-38-2	-	3 - 3.5: 96 h Gambusia affinis mg/L LC50	-	4.6: 12 h Daphnia magna mg/L EC50

Persistence/Degradability

Not determined

Bioaccumulation

Not determined

Mobility

Not determined

Other Adverse Effects

Not determined

13. DISPOSAL CONSIDERATIONS**Waste Treatment Methods****Disposal of Wastes**

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated Packaging

Disposal should be in accordance with applicable regional, national and local laws and regulations.

California Hazardous Waste Status

Chemical Name	California Hazardous Waste Status
Phosphoric Acid 7664-38-2	Corrosive

14. TRANSPORT INFORMATION**Note**

Please see current shipping paper for most up to date shipping information, including exemptions and special circumstances.

DOT**UN/ID No**Gallon containers or larger: UN3264, Corrosive Liquid, Acidic, Inorganic, NOS (Containing Phosphoric Acid), 8, PG II
Quart bottles or smaller: Consumer Commodity ORM-D or Limited Quantity**IATA****IMDG****Marine Pollutant**

This material may meet the definition of a marine pollutant

15. REGULATORY INFORMATION**International Inventories**

Canada – Domestic Substances List (DSL)
TSCA (Toxic Substances Control Act)

All ingredients are listed or exempt.
All ingredients are listed or exempt.

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations**CERCLA**

Chemical Name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Phosphoric Acid 7664-38-2	5000 lb		RQ 5000 lb final RQ RQ 2270 kg final RQ

SARA 311/312 Hazard Categories

Acute Health Hazard Yes
Chronic Health Hazard Yes
Reactive Hazard Yes

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

CWA (Clean Water Act)

Component	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Phosphoric Acid 7664-38-2	5000 lb			X

US State Regulations**U.S. State Right-to-Know Regulations**

Chemical Name	State List
Phosphoric Acid 7664-38-2	MA, NJ, PA

AZ- Arizona Ambient Air Quality Guidelines
CT- Connecticut Hazardous Air Pollutants
CA- California Director's List of Hazardous Substances
CAP65- California Prop65
FL- Florida Substances List
ID- Idaho Non-Carcinogen Toxic Air Pollutants

IL- Illinois Toxic Air Contaminant-Carcinogenic
MA- Massachusetts Right to Know List
MN- Minnesota Hazardous Substances List
NJ- New Jersey Right to Know List
PA- Pennsylvania Right to Know List
RI- Rhode Island Hazardous Substances List

16. OTHER INFORMATION

Issue Date 01-Aug-2012
Revision/Review Date: 09-Dec-2019
Revision Note Version 1.2

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

Keep Out of Reach of Children. For Industrial and Institutional Use Only.

*Denotes changes from last version.

End of Safety Data Sheet