

SAFETY DATA SHEET



Issuing Date: 13-Nov-2019

Revision date 24-Feb-2021

Revision Number 1.01

1. IDENTIFICATION

Product Name Swiffer Wet Jet Wood

Product Identifier 90992353_RET_NG

Recommended use Floor Care.

Details of the supplier of the safety data sheet PROCTER & GAMBLE - Fabric and Home Care Division
Ivorydale Technical Centre
5289 Spring Grove Avenue
Cincinnati, Ohio 45217-1087 USA

Procter & Gamble Inc.
P.O. Box 355, Station A
Toronto, ON M5W 1C5
1-800-331-3774

E-mail Address pgsds.im@pg.com

Emergency Telephone Transportation (24 HR)
CHEMTREC - 1-800-424-9300
(U.S./ Canada) or 1-703-527-3887
Mexico toll free in country: 800-681-9531

2. HAZARD IDENTIFICATION

"Consumer Products", as defined by the US Consumer Product Safety Act and which are used as intended (typical consumer duration and frequency), are exempt from the OSHA Hazard Communication Standard (29 CFR 1910.1200). This SDS is being provided as a courtesy to help assist in the safe handling and proper use of the product.

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:.

This material is not considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Hazard statements None
Hazard pictograms None

Precautionary Statements None

Precautionary Statements - Response None

Precautionary Statements - Storage None

Precautionary Statements - Disposal None

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Additional information Actual substance concentrations fall within the ranges stated. Maximum values do not necessarily represent the values present in the formula.

4. FIRST AID MEASURES

Description of first aid measures

Eye contact Rinse with plenty of water. Get medical attention immediately if irritation persists.

Skin contact Rinse with plenty of water. Get medical attention immediately if symptoms occur.

Ingestion Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur.

Inhalation Move to fresh air. If symptoms persist, call a physician.

Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media Dry chemical, CO₂, alcohol-resistant foam or water spray. Dry chemical. Alcohol resistant foam.

Unsuitable Extinguishing Media None.

Special hazard None known.

Special protective equipment for fire-fighters As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Specific hazards arising from the chemical None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Use personal protective equipment as required. Do not get in eyes, on skin, or on clothing.

Advice for emergency responders Use personal protective equipment as required.

Environmental precautions Keep out of waterways
Do not discharge product into natural waters without pre-treatment or adequate dilution

Methods and material for containment and cleaning up

Methods for containment Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Prevent product from entering drains. Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand,

earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible products None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines No exposure limits noted for ingredient(s).

Appropriate engineering controls

Engineering Measures **Distribution, Workplace and Household Settings:**
Ensure adequate ventilation

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

Personal Protective Equipment

Eye Protection **Distribution, Workplace and Household Settings:**
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Use appropriate eye protection

Hand Protection **Distribution, Workplace and Household Settings:**
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Protective gloves

Skin and Body Protection **Distribution, Workplace and Household Settings:**
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Wear suitable protective clothing

Respiratory Protection **Distribution, Workplace and Household Settings:**
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
In case of inadequate ventilation wear respiratory protection

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state	Liquid	
Appearance	Clear colorless	
Odor	Cologne	
Odor threshold	No information available	
<u>Property</u>	<u>Values</u>	<u>Remarks</u>
pH	6.5	
Melting point / freezing point	No information available	
Initial boiling point and boiling range	99 °C / 210 °F	
Flash point	No Flash to Boiling (NFTB)	
Evaporation rate	No information available	
Flammability	No information available	
Flammability Limit in Air		
Upper flammability or explosive limits	No information available	
Lower flammability or explosive limits	No information available	
Vapor pressure	No information available	
Relative vapor density	No information available	
Relative density	No information available	
Hyphen	No information available	
Partition coefficient	No information available	
Autoignition temperature	No information available	
Decomposition temperature	No information available	
Viscosity	No information available	

10. STABILITY AND REACTIVITY

Reactivity	None under normal use conditions.
Stability	Stable under normal conditions.
Hazardous polymerization	Hazardous polymerization does not occur.
Hazardous Reactions	None under normal processing.
Conditions to Avoid	None under normal processing.
Incompatible materials	None in particular.
Hazardous decomposition products	None under normal use conditions.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Inhalation	No known effect.
Skin contact	No known effect.
Ingestion	No known effect.
Eye contact	No known effect.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Acute toxicity	No known effect.
Skin corrosion/irritation	No known effect.
Serious eye damage/eye irritation	No known effect.
Skin sensitization	No known effect.
Respiratory sensitization	No known effect.

Germ cell mutagenicity	No known effect.
Reproductive toxicity	No known effect.
Developmental toxicity	No known effect.
STOT - single exposure	No known effect.
STOT - repeated exposure	No known effect.
Aspiration hazard	No known effect.
Carcinogenicity	No known effect.

12. ECOLOGICAL INFORMATION

Ecotoxicity

The product is not expected to be hazardous to the environment.

Persistence and degradability	No information available.
Bioaccumulative potential	No information available.
Mobility	No information available.
Other adverse effects	No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Waste from Residues/Unused Products	Disposal should be in accordance with applicable regional, national and local laws and regulations.
Contaminated packaging	Disposal should be in accordance with applicable regional, national and local laws and regulations.
California Hazardous Waste Codes (non-household setting)	331

14. TRANSPORT INFORMATION

<u>DOT</u>	Not regulated
<u>IMDG</u>	Not regulated
<u>IATA</u>	Not regulated

15. REGULATORY INFORMATION

U.S. FEDERAL REGULATIONS

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of the Clean Air Act Amendments of 1990.

Clean Water Act

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

U.S. State Regulations (RTK)

This product does not contain any substances regulated by state right-to-know regulations.

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

International Inventories**United States**

All intentionally-added components of this product(s) are listed on the US TSCA Inventory

Canada

This product is in compliance with CEPA for import by P&G

Legend

United States Toxic Substances Control Act Section 8(b) Inventory (TSCA)

CEPA - Canadian Environmental Protection Act

16. OTHER INFORMATION**HMIS****NFPA**

Issuing Date: 13-Nov-2019

Revision date 24-Feb-2021

Disclaimer.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet