



Safety Data Sheet

Issue Date 02-Aug-2013

Revision/Review Date: 06-Apr-2020

Version 1.1

1. IDENTIFICATION

Product Identifier

Product Name Maxim Germicidal Cleaner

Other Means of Identification

Product Code 041000

Recommended Use of the Chemical and Restrictions on Use

Recommended Use Disinfectant cleaner. For industrial use.

Details of the Supplier of the Safety Data Sheet

Midlab, Inc.
140 Private Brand Way
Athens, TN 37303

Emergency Telephone Number

Company Phone Number Phone: 1-423-337-3180
Emergency Telephone (24 hr) INFOTRAC 1-352-323-3500 (International) – Customer Number: 76773
1-800-535-5053 (North America)

2. HAZARDS IDENTIFICATION

Appearance Yellow

Physical State Liquid

Odor Lemon

Classification

Serious Eye Damage/Eye Irritation

Category 2 Sub-category B

Signal Word

Warning

Hazard Statements

Causes eye irritation.

Precautionary Statements - Prevention

Wash face, hands and any exposed skin thoroughly after handling.

Precautionary Statements - Response

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
If eye irritation persists: Get medical advice/attention.

Precautionary Statements – Storage

Keep container tightly closed. Keep inly in original container.

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant.

Other Hazards

None known.

Unknown Acute Toxicity

None known.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%
---------------	--------	----------

No hazardous ingredients in reportable quantities are present in this product.

**If Chemical Name/CAS No is "proprietary" and/or Weight-% is listed as a range, the specific chemical identity and/or percentage of composition has been withheld as a trade secret. **

4. FIRST-AID MEASURES

First Aid Measures

Eye Contact	May cause irritation. Hold eye open and rinse slowly and gently with water for 15-20 minutes. Remove contact lenses, if present, after the first 5 minutes, then continue rinsing eyes. If irritation persists, get medical attention.
Skin Contact	May be mildly irritation. Very large exposure may be harmful. Flush immediately with plenty of water. If irritation persists, get medical attention.
Inhalation	Mists and vapors may be mildly irritating to the throat and respiratory tract. If breathing is affected, remove to fresh air. Get medical attention.
Ingestion	Harmful if swallowed. Immediately drink one cupful of water or milk. Get medical attention. Do not give anything by mouth to an unconscious person.
Aggravated Medical Conditions	Persons with pre-existing skin disorders may be more susceptible to irritating effects.

Most Important Symptoms and Effects

Symptoms	May be irritating to eyes and skin.
-----------------	-------------------------------------

Indication of Any Immediate Medical Attention and Special Treatment Needed

Notes to Physician	Treat symptomatically.
---------------------------	------------------------

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Water spray (fog). Carbon dioxide (CO2). Water. Foam.

Unsuitable Extinguishing Media

Not determined.

Specific Hazards Arising from the Chemical

Irritating and toxic gases or fumes may be released during a fire.

Hazardous Combustion Products

Combustion products are toxic.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal Precautions, Protective Equipment and Emergency Procedures

Personal Precautions	Wear protective clothing as described in Section 8 of this safety data sheet.
Environmental Precautions	Prevent from entering into soil, ditches, sewers, waterways and/or groundwater. See Section 12, Ecological Information. See Section 13, Disposal Considerations, for additional information. See Section 12 for additional Ecological Information.

Methods and Material for Containment and Cleaning Up

Methods for Containment	Prevent from spreading or entering drains, ditches or rivers by using sand, earth, or other appropriate barriers.
Methods for Clean-Up	Contain and collect with an inert absorbent and place into an appropriate container for disposal. Rinse area with clean water and dry before permitting traffic.

7. HANDLING AND STORAGE

Precautions for Safe Handling

Advice on Safe Handling

Handle in accordance with good industrial hygiene and safety practice. Use personal protection recommended in Section 8. For industrial and commercial use only. Avoid contact with skin, eyes or clothing.

Conditions for Safe Storage, Including Any Incompatibilities

Storage Conditions

Keep container tightly closed and store in a cool, dry and well-ventilated place. Protect from freezing. Keep out of the reach of children.

Incompatible Materials

None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
None reportable			

Appropriate Engineering Controls

Engineering Controls

Good general room ventilation should be adequate under normal conditions. Eyewash stations.

Individual Protection Measures, such as Personal Protective Equipment

Eye/Face Protection

Eye protection should be used when splashing may occur.

Skin and Body Protection

Wear protective gloves when handling this product.

Respiratory Protection

Under normal conditions, respirator is not normally required. Avoid breathing vapors.

General Hygiene Considerations

Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on Basic Physical and Chemical Properties

Physical State	Liquid	Odor	Lemon
Appearance	Clear liquid	Odor Threshold	Not determined
Color	Yellow		

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH (concentrate)	10.0-11.0	
Melting Point/Freezing Point	Approximately 32°F	
Boiling Point/Boiling Range	Approximately 212°F	
Flash Point	None when heated to 102°C	Cleveland Open Cup
Evaporation Rate	Not determined	
Flammability (Solid, Gas)	Liquid-not applicable	
Upper Flammability Limits	Not applicable	
Lower Flammability Limit	Not applicable	
Vapor Pressure	Not determined	
Vapor Density	Estimated to be heavier than air	
Specific Gravity	1.01	
Water Solubility	Completely soluble	
Solubility in other solvents	Not determined	
Partition Coefficient	Not determined	
Auto-ignition Temperature	Not determined	
Decomposition Temperature	Not determined	
Kinematic Viscosity	Not determined	
Dynamic Viscosity	Not determined	
Explosive Properties	Not an explosive	
Oxidizing Properties	Not determined	

10. STABILITY AND REACTIVITY

Reactivity

Not reactive under normal conditions.

Chemical Stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to Avoid

Keep out of reach of children. Keep from freezing. Keep away from heat and strong oxidizing agents.

Incompatible Materials

Strong oxidizing agents (may result in fire), reducing agents.

Hazardous Decomposition Products

Thermal decomposition may produce carbon monoxide, carbon dioxide, and toxic hydrogen chloride vapors.

11. TOXICOLOGICAL INFORMATION

Information on Likely Routes of Exposure

Product Information

Eye Contact	Avoid contact with eyes. Irritating.
Skin Contact	Avoid contact with skin. May be irritating.
Inhalation	Avoid breathing vapors or mists.
Ingestion	Do not taste or swallow.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Product as a whole	>5000mg/kg (Rat)	>2000mg/kg (Rat)	-

Information on Physical, Chemical and Toxicological Effects

Symptoms Please see section 4 of this SDS for symptoms.

Delayed and Immediate Effects as well as Chronic Effects from Short and Long-Term Exposure

Carcinogenicity This product does not contain any carcinogens or potential carcinogens as listed by OSHA, IARC or NTP.

Numerical Measures of Toxicity

Not determined

12. ECOLOGICAL INFORMATION

Ecotoxicity

Component Information

Chemical Name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Product as a whole	No data available for this product, but it is considered toxic to fish.			

Persistence/Degradability

Not expected to persist.

Bioaccumulation

Not expected to bioaccumulate.

Mobility

Not determined

Other Adverse Effects

Not determined

13. DISPOSAL CONSIDERATIONS

Waste Treatment Methods

Disposal of Wastes

Pesticide wastes are acutely hazardous. Improper disposal of excess pesticide, spray mixture or rinsate is a violation of Federal law. If these wastes cannot be disposed of by use according to label instructions, contact your State Pesticide or Environmental control agency, or the Hazardous Waste Representative at the nearest EPA Regional Office for guidance. Observe all applicable federal, state, and local regulations.

Contaminated Packaging

Remove all residue when emptying. Disposal should be in accordance with applicable regional, national and local laws and regulations.

14. TRANSPORT INFORMATION

Note

Please see current shipping paper for most up to date shipping information, including exemptions and special circumstances.

DOT

NOI Non-Hazardous

IATA

IMDG

15. REGULATORY INFORMATION

International Inventories

Canada – Domestic Substances List (DSL)
TSCA (Toxic Substances Control Act)

All ingredients are listed or exempt.
All ingredients are listed or exempt.

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

CERCLA

None Listed

SARA 311/312 Hazard Categories

Immediate Fire.

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

CWA (Clean Water Act)

None known.

US State Regulations

None known

U.S. State Right-to-Know Regulations

The following ingredients appear on various state right to know lists and/or California's Proposition 65 List:

Chemical Name	State List
None Listed	

AZ- Arizona Ambient Air Quality Guidelines
 CT- Connecticut Hazardous Air Pollutants
 CA- California Director's List of Hazardous Substances
 CAP65- California Prop65
 FL- Florida Substances List
 ID- Idaho Non-Carcinogen Toxic Air Pollutants

IL- Illinois Toxic Air Contaminant- Carcinogenic
 MA- Massachusetts Right to Know List
 MN- Minnesota Hazardous Substances List
 NJ- New Jersey Right to Know List
 PA- Pennsylvania Right to Know List
 RI- Rhode Island Hazardous Substances List

FIFRA Label Information:

This chemical is a pesticide product registered by the United States Environmental Agency and is subject to certain labeling requirements under federal pesticide law. These requirements differ from the classification criteria and hazard information required for safety data sheets (SDS), and for workplace labels of non-pesticide chemicals. The pesticide label also includes other important information, including directions for use.

Caution
 Irritating to eyes. Harmful if swallowed or absorbed through the skin.

This product is toxic to fish and freshwater aquatic invertebrates.

16. OTHER INFORMATION

<u>NFPA</u>	Health Hazards	Flammability	Instability	Special Hazards
	Not determined	Not determined	Not determined	Not determined
<u>HMIS</u>	Health Hazards	Flammability	Physical Hazards	Personal Protection
	1	0	0	Not determined

Issue Date 02-Aug-201
Revision/Review Date: 06-Apr-2020
Revision Note Version 1.1 Name update. Section 2 update.

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

Keep Out of Reach of Children. For Industrial and Institutional Use Only.

*Denotes changes from last version.

End of Safety Data Sheet