



Safety Data Sheet

Issue Date: 08-Aug-2011

Revision Date: 09-Dec-2019

Version 1.0

1. IDENTIFICATION

Product Identifier

Product Name Ultrashield 25

Other Means of Identification

Product Code 122500

Recommended Use of the Chemical and Restrictions on Use

Recommended Use High solids floor finish. For industrial use.

Details of the Supplier of the Safety Data Sheet

Midlab, Inc.
140 Private Brand Way
Athens, TN 37303

Emergency Telephone Number

Company Phone Number Phone: 1-423-337-3180
Emergency Telephone (24 hr) INFOTRAC 1-352-323-3500 (International)
1-800-535-5053 (North America)

2. HAZARDS IDENTIFICATION

Appearance White Physical State Liquid Odor Characteristic

Classification

This chemical does not meet the hazardous criteria set forth by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200). However, this Safety Data Sheet (SDS) contains valuable information critical to the safe handling and proper use of this product. This SDS should be retained and available for employees and other users of this product.

Unknown Acute Toxicity

2.48% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%
Water	7732-18-5	60-100
Proprietary Polystyrene/Acrylic Polymer Blend	Proprietary	15-40
Diethylene Glycol Monoethyl Ether	111-90-0	3-7
Tributoxyethyl Phosphate	78-51-3	1-5
Proprietary Wax Emulsion	Proprietary	1-5

4. FIRST-AID MEASURES

First Aid Measures

Eye Contact Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If eye irritation persists: Get medical advice/attention.

Skin Contact Wash off immediately with plenty of water for at least 15 minutes.

Inhalation Remove to fresh air.

Clean mouth with water and drink afterwards plenty of water. If any discomfort persists, obtain medical attention.

Most Important Symptoms and Effects

Symptoms Prolonged or repeated exposure can remove natural skin oils and may produce irritation.

Indication of Any Immediate Medical Attention and Special Treatment Needed

Notes to Physician Treat symptomatically. May aggravate pre-existing skin disorders.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Water spray (fog). Carbon dioxide (CO2). Water. Foam.

Unsuitable Extinguishing Media

Not determined.

Specific Hazards Arising from the Chemical

None known.

Hazardous Combustion Products

Normal products of combustion.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal Precautions, Protective Equipment and Emergency Procedures

Personal Precautions Wear protective clothing as described in Section 8 of this safety data sheet.

Environmental Precautions Prevent from entering into soil, ditches, sewers, waterways and/or groundwater. See Section 12, Ecological Information. See Section 13, Disposal Considerations, for additional information.

Methods and Material for Containment and Cleaning Up

Methods for Containment Prevent from spreading or entering drains, ditches or rivers by using sand, earth, or other appropriate barriers.

Methods for Clean-Up Contain and collect with an inert absorbent and place into an appropriate container for disposal. Rinse area with clean water and dry before permitting traffic.

7. HANDLING AND STORAGE

Precautions for Safe Handling

Advice on Safe Handling Handle in accordance with good industrial hygiene and safety practice. Use personal protection recommended in Section 8. For industrial and commercial use only. Avoid contact with skin, eyes or clothing.

Conditions for Safe Storage, Including Any Incompatibilities

Storage Conditions Keep container tightly closed and store in a cool, dry and well-ventilated place. Protect from freezing. Keep out of the reach of children.

Incompatible Materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines

This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

Appropriate Engineering Controls**Engineering Controls**

Ensure adequate ventilation, especially in confined areas. Good general room ventilation (equivalent to outdoors) should be adequate under normal conditions. Eyewash stations. Showers.

Individual Protection Measures, such as Personal Protective Equipment**Eye/Face Protection**

No protective equipment is needed under normal use conditions.

Skin and Body Protection

No protective equipment is needed under normal use conditions.

Respiratory Protection

Under normal conditions, respirator is not normally required.

General Hygiene Considerations Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on Basic Physical and Chemical Properties

Physical State	Liquid	Odor	Characteristic
Appearance	Opaque	Odor Threshold	Not determined
Color	White		
<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>	
pH	8.0-8.5		
Melting Point/Freezing Point	0 °C / 32 °F		
Boiling Point/Boiling Range	100 °C / 212 °F		
Flash Point	Not applicable	TOC	
Evaporation Rate	Not determined		
Flammability (Solid, Gas)	Liquid-not applicable		
Upper Flammability Limits	Not applicable		
Lower Flammability Limit	Not applicable		
Vapor Pressure	Not determined		
Vapor Density	Not determined		
Specific Gravity	1.04		
Water Solubility	Completely soluble	@ 25 °C (77 °F)	
Solubility in other solvents	Not determined		
Partition Coefficient	Not determined		
Auto-ignition Temperature	Not determined		
Decomposition Temperature	Not determined		
Kinematic Viscosity	Not determined		
Dynamic Viscosity	Not determined		
Explosive Properties	Not an explosive		
Oxidizing Properties	Not determined		

10. STABILITY AND REACTIVITY

Reactivity

Not reactive under normal conditions.

Chemical Stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Conditions to Avoid

Keep out of reach of children.

Incompatible Materials

None known based on information supplied.

Hazardous Decomposition Products

Normal products of combustion.

11. TOXICOLOGICAL INFORMATION

Information on Likely Routes of Exposure

Product Information

- Eye Contact** Avoid contact with eyes.
- Skin Contact** Avoid contact with skin.
- Inhalation** Avoid breathing vapors or mists.
- Ingestion** Do not taste or swallow.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Proprietary Polystyrene/Acrylic Polymer Blend	> 90 mL/kg (Rat)	-	-
Tributoxyethyl Phosphate 78-51-3	= 3000 mg/kg (Rat)	> 5000 mg/kg (Rabbit)	> 6.4 mg/L (Rat) 4 h
Proprietary Wax Emulsion	> 90 mL/kg (Rat)	-	-

Information on Physical, Chemical and Toxicological Effects

Symptoms Please see section 4 of this SDS for symptoms.

Delayed and Immediate Effects as well as Chronic Effects from Short and Long-Term Exposure

Carcinogenicity This product does not contain any carcinogens or potential carcinogens as listed by OSHA, IARC or NTP.

Numerical Measures of Toxicity

Not determined

Unknown Acute Toxicity 2.48% of the mixture consists of ingredient(s) of unknown toxicity.

12. ECOLOGICAL INFORMATION

Ecotoxicity

The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Component Information

Chemical Name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Tributoxyethyl Phosphate 78-51-3	-	10.4 - 12.0: 96 h Pimephales promelas mg/L LC50 flow-through	-	-

Persistence/Degradability

Bioaccumulation

Not determined

Mobility

Chemical Name	Partition Coefficient
Tributoxyethyl Phosphate 78-51-3	4.78

Other Adverse Effects

Not determined

13. DISPOSAL CONSIDERATIONS

Waste Treatment Methods

Disposal of Wastes	Disposal should be in accordance with applicable regional, national and local laws and regulations.
Contaminated Packaging	Disposal should be in accordance with applicable regional, national and local laws and regulations.

14. TRANSPORT INFORMATION

<u>Note</u>	Please see current shipping paper for most up to date shipping information, including exemptions and special circumstances.
<u>DOT</u>	Not regulated
<u>IATA</u>	Not regulated
<u>IMDG</u>	Not regulated

15. REGULATORY INFORMATION

International Inventories

Canada – Domestic Substances List (DSL)	All ingredients are listed or exempt.
TSCA (Toxic Substances Control Act)	All ingredients are listed or exempt.

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355).

SARA 311/312 Hazard Categories

Acute Health Hazard	Yes
----------------------------	-----

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

The following ingredients appear on various state right to know lists and/or California's Proposition 65 List:

Chemical Name	State List
None listed	

AZ- Arizona Ambient Air Quality Guidelines

CT- Connecticut Hazardous Air Pollutants

CA- California Director's List of Hazardous Substances

CAP65- California Prop65

FL- Florida Substances List

ID- Idaho Non-Carcinogen Toxic Air Pollutants

IL- Illinois Toxic Air Contaminant- Carcinogenic

MA- Massachusetts Right to Know List

MN- Minnesota Hazardous Substances List

NJ- New Jersey Right to Know List

PA- Pennsylvania Right to Know List

RI- Rhode Island Hazardous Substances List

16. OTHER INFORMATION

NFPA

Health Hazards

Flammability

Instability

Special Hazards

HMIS

Not determined

Not determined

Not determined

Not determined

Health Hazards

Flammability

Physical Hazards

Personal Protection

1

0

0

Not determined

Issue Date:

08-Aug-2011

Revision Date:

09-Dec-2019

Revision Note

New format Version 1.0

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

Keep Out of Reach of Children. For Industrial and Institutional Use Only.

*Denotes changes from last version.

End of Safety Data Sheet