

# SAFETY DATA SHEET

Issuing Date No data available

Revision Date 03-Dec-2014

Revision Number 1



The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

## 1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

### Product identifier

Product Name US Vial (liquid Sol Trol 125)

### Other means of identification

Synonyms None

### Recommended use of the chemical and restrictions on use

Recommended Use Filled Vial is installed in Tools for Leveling

Uses advised against No information available

### Details of the supplier of the safety data sheet

Supplier Name Johnson Level & Tool  
Supplier Address 6333 W Donges Bay Rd  
Mequon  
WI  
53092  
US  
Supplier Phone Number Phone:770-862-2603  
Contact Phone770-862-2603  
Supplier Email eronheflin@mphsales.com  
Emergency telephone number

## 2. HAZARDS IDENTIFICATION

### Classification


This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Germ cell mutagenicity	Category 1B
Aspiration toxicity	Category 1
Flammable liquids	Category 3



GHS Label elements, including precautionary statements

## Emergency Overview

<b>Signal word</b>	<b>Danger</b>	
<b>Hazard Statements</b>	May cause genetic defects May be fatal if swallowed and enters airways Flammable liquid and vapor	
		
<b>Appearance</b>	<b>Physical State</b>	<b>Odor</b>
Yellow	Liquid	Petroleum distillates

**Precautionary Statements - Prevention**

Obtain special instructions before use  
 Do not handle until all safety precautions have been read and understood  
 Use personal protective equipment as required  
 Keep away from heat/sparks/open flames/hot surfaces. - No smoking  
 Keep container tightly closed  
 Ground/bond container and receiving equipment  
 Use explosion-proof electrical/ ventilating/ lighting/ equipment  
 Use only non-sparking tools  
 Take precautionary measures against static discharge

**Precautionary Statements - Response**

IF exposed or concerned: Get medical advice/attention

**Skin**

IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower

**Ingestion**

IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician  
 Do NOT induce vomiting

**Fire**

In case of fire: Use CO<sub>2</sub>, dry chemical, or foam for extinction

**Precautionary Statements - Storage**

Store locked up  
 Store in a well-ventilated place. Keep cool

**Precautionary Statements - Disposal**

Dispose of contents/container to an approved waste disposal plant

**Hazards not otherwise classified (HNOC)**

Not applicable

**Unknown Toxicity**

0.007% of the mixture consists of ingredient(s) of unknown toxicity

**Other information**

PROLONGED OR REPEATED CONTACT MAY DRY SKIN AND CAUSE IRRITATION

**Interactions with Other Chemicals**

No information available.

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%	Trade Secret
Supplier Trade Secret	Proprietary	60 - 100	*

\*The exact percentage (concentration) of composition has been withheld as a trade secret

### 4. FIRST AID MEASURES

**First aid measures**

<b><u>General Advice</u></b>	Immediate medical attention is required. Show this safety data sheet to the doctor in attendance.
<b><u>Eye Contact</u></b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Do not rub affected area. Remove contact lenses, if present and easy to do. Continue rinsing.
<b><u>Skin Contact</u></b>	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.
<b><u>Inhalation</u></b>	Aspiration into lungs can produce severe lung damage. If breathing has stopped, give artificial respiration. Get medical attention immediately. Remove to fresh air. Avoid direct contact with skin. Use barrier to give mouth-to-mouth resuscitation. If breathing is difficult, (trained personnel should) give oxygen. Seek immediate medical attention/advice. Delayed pulmonary edema may occur.
<b><u>Ingestion</u></b>	Aspiration hazard if swallowed - can enter lungs and cause damage. Do NOT induce vomiting. If vomiting occurs spontaneously, keep head below hips to prevent aspiration. Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an unconscious person. Call a physician or poison control center immediately.
<b><u>Self-protection of the first aider</u></b>	Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination. Avoid direct contact with skin. Use barrier to give mouth-to-mouth resuscitation. Use personal protective equipment as required. Wear personal protective clothing (see section 8). Remove all sources of ignition.

**Most important symptoms and effects, both acute and delayed**

**Most Important Symptoms and Effects** Difficulty in breathing. Coughing and/ or wheezing. Dizziness.

**Indication of any immediate medical attention and special treatment needed**

**Notes to Physician** Treat symptomatically.

## 5. FIRE-FIGHTING MEASURES

**Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. Dry chemical. Carbon dioxide (CO<sub>2</sub>). Water spray. Alcohol resistant foam.

**Unsuitable extinguishing media**

CAUTION: Use of water spray when fighting fire may be inefficient.

**Specific Hazards Arising from the Chemical**

Risk of ignition. Keep product and empty container away from heat and sources of ignition. In the event of fire, cool tanks with water spray. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.

**Uniform Fire Code** Combustible Liquid: II

**Hazardous Combustion Products**

Carbon oxides.

**Explosion Data**

**Sensitivity to Mechanical Impact** No.

**Sensitivity to Static Discharge** Yes.

**Protective equipment and precautions for firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## 6. ACCIDENTAL RELEASE MEASURES

### Personal precautions, protective equipment and emergency procedures

**Personal Precautions** Ensure adequate ventilation. Use personal protective equipment as required. Evacuate personnel to safe areas. See section 8 for more information. Avoid contact with skin, eyes or clothing. Keep people away from and upwind of spill/leak. ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Pay attention to flashback. Take precautionary measures against static discharges. All equipment used when handling the product must be grounded. Do not touch or walk through spilled material.

**Other Information** Refer to protective measures listed in Sections 7 and 8. Ventilate the area.

### Environmental Precautions

**Environmental Precautions** Refer to protective measures listed in Sections 7 and 8. Prevent further leakage or spillage if safe to do so. Prevent product from entering drains.

### Methods and material for containment and cleaning up

**Methods for Containment** Prevent further leakage or spillage if safe to do so. Do not touch or walk through spilled material. A vapor suppressing foam may be used to reduce vapors. Dike far ahead of spill to collect runoff water. Keep out of drains, sewers, ditches and waterways.

**Methods for cleaning up** Take precautionary measures against static discharges. Dam up. Soak up with inert absorbent material. Pick up and transfer to properly labeled containers.

## 7. HANDLING AND STORAGE

### Precautions for safe handling

**Handling** Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Do not eat, drink or smoke when using this product. Take off contaminated clothing and wash before reuse. Use personal protection equipment. Avoid breathing vapors or mists. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Use grounding and bonding connection when transferring this material to prevent static discharge, fire or explosion. Use with local exhaust ventilation. Use spark-proof tools and explosion-proof equipment. Keep in an area equipped with sprinklers. Use according to package label instructions.

### Conditions for safe storage, including any incompatibilities

**Storage** Store locked up. Keep containers tightly closed in a dry, cool and well-ventilated place. Protect from moisture. Keep out of the reach of children. Store away from other materials. Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). Keep in properly labeled containers. Do not store near combustible materials. Keep in an area equipped with sprinklers. Store in accordance with the particular national regulations. Store in accordance with local regulations.

**Incompatible Products** None known based on information supplied.



## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control parameters

**Exposure Guidelines** This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies

### Appropriate engineering controls

**Engineering Measures** Showers  
Eyewash stations  
Ventilation systems

### Individual protection measures, such as personal protective equipment

**Eye/Face Protection** Tight sealing safety goggles.

**Skin and Body Protection** Wear protective gloves and protective clothing. Long sleeved clothing. Chemical resistant apron. Impervious gloves. Antistatic boots.

**Respiratory Protection** No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice. Do not eat, drink or smoke when using this product. Wash hands before breaks and immediately after handling the product. Contaminated work clothing should not be allowed out of the workplace. Regular cleaning of equipment, work area and clothing is recommended.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### Physical and Chemical Properties

<b>Physical State</b>	Liquid	<b>Odor</b>	Petroleum distillates
<b>Appearance</b>	Yellow	<b>Odor Threshold</b>	No information available
<b>Color</b>	No information available		

<u>Property</u>	<u>Values</u>	<u>Remarks</u>	<u>Method</u>
pH		None known	
Melting / freezing point	No data available	None known	
Boiling point / boiling range	>37 °C / 99.9 °F	None known	
Flash Point	48 C / 118 F	None known	
Evaporation Rate	No data available	None known	
Flammability (solid, gas)	No data available	None known	
Flammability Limit in Air			
Upper flammability limit	No data available		
Lower flammability limit	No data available		
Vapor pressure	No data available	None known	
Vapor density	No data available	None known	
Specific Gravity	No data available	None known	
Water Solubility	Negligible	None known	
Solubility in other solvents	No data available	None known	
Partition coefficient: n-octanol/water	No data available	None known	
Autoignition temperature	No data available	None known	

Decomposition temperature	No data available	None known
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	None known
Explosive properties	No data available	None known
Oxidizing Properties	No data available	

**Other Information**

Softening Point	No data available
VOC Content (%)	No data available
Particle Size	No data available
Particle Size Distribution	

## 10. STABILITY AND REACTIVITY

**Reactivity**

No data available.

**Chemical stability**

Stable under recommended storage conditions.

**Possibility of Hazardous Reactions**

None under normal processing.

**Hazardous Polymerization**

Hazardous polymerization does not occur.

**Conditions to avoid**

Heat, flames and sparks.

**Incompatible materials**

None known based on information supplied.

**Hazardous Decomposition Products**

Carbon oxides.

## 11. TOXICOLOGICAL INFORMATION

**Information on likely routes of exposure****Product Information**

<b>Inhalation</b>	Specific test data for the substance or mixture is not available. Aspiration into lungs can produce severe lung damage. May cause pulmonary edema. Pulmonary edema can be fatal. May cause irritation of respiratory tract.
<b>Eye Contact</b>	Specific test data for the substance or mixture is not available. May cause irritation.
<b>Skin Contact</b>	Repeated exposure may cause skin dryness or cracking.
<b>Ingestion</b>	Specific test data for the substance or mixture is not available. Potential for aspiration if swallowed. May cause lung damage if swallowed. Aspiration may cause pulmonary edema and pneumonitis. May be fatal if swallowed and enters airways.

**Component Information****Information on toxicological effects**

**Symptoms** Difficulty in breathing. Coughing and/ or wheezing. Asthma-like and/ or skin allergy-like symptoms.

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

**Sensitization** No information available.

**Mutagenic Effects** Contains a known or suspected mutagen.

**Carcinogenicity** Contains no ingredient listed as a carcinogen.

**Reproductive Toxicity** No information available.

**STOT - single exposure** No information available.

**STOT - repeated exposure** No information available.

**Chronic Toxicity** Contains a known or suspected mutagen. Possible risk of irreversible effects. Aspiration may cause pulmonary edema and pneumonitis.

**Target Organ Effects** May affect the genetic material in germ cells (sperm and eggs). Respiratory system.

**Aspiration Hazard** No information available.

**Numerical measures of toxicity Product Information**

The following values are calculated based on chapter 3.1 of the GHS document  
Not applicable

**12. ECOLOGICAL INFORMATION****Ecotoxicity**

The environmental impact of this product has not been fully investigated.

**Persistence and Degradability**

No information available.

**Bioaccumulation**

No information available

**Other adverse effects**

No information available.



### 13. DISPOSAL CONSIDERATIONS

#### Waste treatment methods

<b>Disposal methods</b>	This material, as supplied, is a hazardous waste according to federal regulations (40 CFR 261).
<b>Contaminated Packaging</b>	Dispose of contents/containers in accordance with local regulations.
<b>US EPA Waste Number</b>	D001

**California Hazardous Waste Codes** 213

This product contains one or more substances that are listed with the State of California as a hazardous waste.

### 14. TRANSPORT INFORMATION

<b><u>DOT</u></b>	NOT REGULATED (If shipped in NON BULK packaging by ground transport)
<b>Proper Shipping Name</b>	NON-REGULATED
<b>Emergency Response Guide Number</b>	128

<b><u>TDG</u></b>	
<b>UN-No.</b>	UN3295
<b>Proper Shipping Name</b>	HYDROCARBONS, LIQUID, N.O.S.
<b>Hazard Class</b>	3
<b>Packing Group</b>	III
<b>Description</b>	UN3295, HYDROCARBONS, LIQUID, N.O.S., 3, III

<b><u>MEX</u></b>	
<b>UN-No.</b>	UN3295
<b>Proper Shipping Name</b>	HYDROCARBONS, LIQUID, N.O.S.
<b>Hazard Class</b>	3
<b>Packing Group</b>	III
<b>Description</b>	UN3295, HYDROCARBONS, LIQUID, N.O.S., 3, III

<b><u>ICAO</u></b>	
<b>UN-No.</b>	UN3295
<b>Proper Shipping Name</b>	HYDROCARBONS, LIQUID, N.O.S.
<b>Hazard Class</b>	3
<b>Packing Group</b>	III
<b>Description</b>	UN3295, HYDROCARBONS, LIQUID, N.O.S., 3, III

<b><u>IATA</u></b>	
<b>UN-No.</b>	UN3295
<b>Proper Shipping Name</b>	HYDROCARBONS, LIQUID, N.O.S.
<b>Hazard Class</b>	3
<b>Packing Group</b>	III
<b>Description</b>	UN3295, HYDROCARBONS, LIQUID, N.O.S., 3, III



**IMDG/IMO**

UN-No.	UN3295
Proper Shipping Name	HYDROCARBONS, LIQUID, N.O.S.
Hazard Class	3
Packing Group	III
EmS-No.	F-E, S-D
Description	UN3295, HYDROCARBONS, LIQUID, N.O.S., 3, III, (48°C C.C.)

**RID**

UN-No.	UN3295
Proper Shipping Name	HYDROCARBONS, LIQUID, N.O.S.
Hazard Class	3
Packing Group	III
Classification code	F1
Description	UN3295, HYDROCARBONS, LIQUID, N.O.S., 3, III

**ADR**

UN-No.	UN3295
Proper Shipping Name	HYDROCARBONS, LIQUID, N.O.S.
Hazard Class	3
Packing Group	III
Classification code	F1
Description	UN3295, HYDROCARBONS, LIQUID, N.O.S., 3, III

**ADN**

UN-No.	UN3295
Proper Shipping Name	HYDROCARBONS, LIQUID, N.O.S.
Hazard Class	3
Packing Group	III
Classification code	F1
Description	UN3295, HYDROCARBONS, LIQUID, N.O.S., 3, III
Limited Quantity	5 L
Ventilation	VE01

<b>15. REGULATORY INFORMATION</b>
-----------------------------------

**International Inventories**

TSCA	Complies
DSL	All components are listed either on the DSL or NDSL.

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory  
 DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

**US Federal Regulations****SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

**SARA 311/312 Hazard Categories**

Acute Health Hazard	Yes
Chronic Health Hazard	Yes
Fire Hazard	Yes
Sudden release of pressure hazard	No
Reactive Hazard	No



**CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

**US State Regulations**

**California Proposition 65**

This product contains the following Proposition 65 chemicals.

<b>Chemical Name</b>	<b>California Proposition 65</b>
Supplier Trade Secret -	Carcinogen

**U.S. State Right-to-Know Regulations**

Chemical Name	New Jersey	Massachusetts	Pennsylvania	Rhode Island	Illinois
Supplier Trade Secret	X	X	X	X	X
Supplier Trade Secret	X	X	X	X	X

**International Regulations**

**Canada**

**WHMIS Hazard Class**

B3 - Combustible liquid

D2A - Very toxic materials



**16. OTHER INFORMATION**

<b>NFPA</b>	<b>Health Hazards 2</b>	<b>Flammability 2</b>	<b>Instability 0</b>	<b>Physical and Chemical Hazards - Personal Protection X</b>
<b>HMIS</b>	<b>Health Hazards 2*</b>	<b>Flammability 2</b>	<b>Physical Hazard 0</b>	

**Chronic Hazard Star Legend** \* = Chronic Health Hazard

**Prepared By**

Product Stewardship  
 23 British American Blvd.  
 Latham, NY 12110  
 1-800-572-6501



**Revision Date** 03-Dec-2014  
**Revision Note** No information available

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**