



# Transport Information Document

Date: May 21, 2019

3M ID Number: 70-0716-8335-6

Product Description: Scotchgard(TM) Stone Floor Protector, 3.785 Liter Bag, 2/case

Transport Protective Service: MAINTAIN TEMP ABOVE 32F (0C)

NMFC Item: 046030 NMFC Sub: 00 NMFC Class: 055.0

Flash Point (Closed-cup): No Flash Point

## UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)

NOT REGULATED

## UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)

NOT REGULATED

## INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)

NOT REGULATED

## INTERNATIONAL MARITIME ORGANIZATION (IMO)

NOT REGULATED

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit [3M.com/Transportinfo](http://3M.com/Transportinfo)  
or call 1-800-364-3577 or 651-737-6501 for assistance.



## Safety Data Sheet

Copyright,2018,3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

<b>Document Group:</b>	28-4142-7	<b>Version Number:</b>	5.02
<b>Issue Date:</b>	11/16/18	<b>Supersedes Date:</b>	07/26/18

### SECTION 1: Identification

#### 1.1. Product identifier

Scotchgard(TM) Stone Floor Protector

#### Product Identification Numbers

ID Number	UPC	ID Number	UPC
70-0715-9144-3	500-48011-59379-6	70-0715-9515-4	
70-0716-8335-6	500-48011-59379-6	70-0716-8370-3	

7000002457, 7100009939, 7100135693, 7010342469

#### 1.2. Recommended use and restrictions on use

##### Recommended use

Hard Floor Maintenance

#### 1.3. Supplier's details

<b>MANUFACTURER:</b>	3M
<b>DIVISION:</b>	Commercial Solutions Division
<b>ADDRESS:</b>	3M Center, St. Paul, MN 55144-1000, USA
<b>Telephone:</b>	1-888-3M HELPS (1-888-364-3577)

#### 1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

### SECTION 2: Hazard identification

#### 2.1. Hazard classification

Skin Corrosion/Irritation: Category 2.

Skin Sensitizer: Category 1.

Specific Target Organ Toxicity (repeated exposure): Category 2.

#### 2.2. Label elements

##### Signal word

Warning

##### Symbols

Exclamation mark | Health Hazard |

### Pictograms



### Hazard Statements

Causes skin irritation.

May cause an allergic skin reaction.

May cause damage to organs through prolonged or repeated exposure:  
respiratory system |

### Precautionary Statements

#### Prevention:

Do not breathe dust/fume/gas/mist/vapors/spray.

Wear protective gloves.

Wash thoroughly after handling.

Contaminated work clothing must not be allowed out of the workplace.

#### Response:

IF ON SKIN: Wash with plenty of soap and water.

If skin irritation or rash occurs: Get medical advice/attention.

Take off contaminated clothing and wash it before reuse.

Get medical advice/attention if you feel unwell.

#### Disposal:

Dispose of contents/container in accordance with applicable local/regional/national/international regulations.

5% of the mixture consists of ingredients of unknown acute oral toxicity.

## SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
Water	7732-18-5	60 - 90
Polymer	Trade Secret*	3 - 7
1,2-Ethanediamine, N1-[3-(trimethoxysilyl)propyl]-	1760-24-3	1 - 5 Trade Secret *
Silicic acid, lithium salt	12627-14-4	1 - 5 Trade Secret *
Silanetriol, methyl-, potassium salt	31795-24-1	0.5 - 1.5 Trade Secret *

\*The specific chemical identity and/or exact percentage (concentration) of this composition has been withheld as a trade secret.

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

#### Inhalation:

Remove person to fresh air. If you feel unwell, get medical attention.

**Skin Contact:**

Immediately wash with soap and water. Remove contaminated clothing and wash before reuse. If signs/symptoms develop, get medical attention.

**Eye Contact:**

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

**If Swallowed:**

Rinse mouth. If you feel unwell, get medical attention.

**4.2. Most important symptoms and effects, both acute and delayed**

See Section 11.1. Information on toxicological effects.

**4.3. Indication of any immediate medical attention and special treatment required**

Not applicable

**SECTION 5: Fire-fighting measures**

**5.1. Suitable extinguishing media**

Material will not burn. Use a fire fighting agent suitable for the surrounding fire. Non-combustible. Use a fire fighting agent suitable for surrounding fire.

**5.2. Special hazards arising from the substance or mixture**

None inherent in this product.

**5.3. Special protective actions for fire-fighters**

No special protective actions for fire-fighters are anticipated.

**SECTION 6: Accidental release measures**

**6.1. Personal precautions, protective equipment and emergency procedures**

Evacuate area. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

**6.2. Environmental precautions**

Avoid release to the environment. For larger spills, cover drains and build dikes to prevent entry into sewer systems or bodies of water.

**6.3. Methods and material for containment and cleaning up**

Contain spill. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Remember, adding an absorbent material does not remove a physical, health, or environmental hazard. Collect as much of the spilled material as possible. Place in a metal container approved for use in transportation by appropriate authorities. The container must be lined with polyethylene plastic or contain a plastic drum liner made of polyethylene. Clean up residue with water. Seal the container. Dispose of collected material as soon as possible in accordance with applicable local/regional/national/international regulations.

**SECTION 7: Handling and storage**

**7.1. Precautions for safe handling**

For industrial/occupational use only. Not for consumer sale or use. Keep out of reach of children. Do not breathe dust/fume/gas/mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Do not eat, drink or smoke when using this

product. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Avoid release to the environment. Wash contaminated clothing before reuse.

### 7.2. Conditions for safe storage including any incompatibilities

Store away from acids. Store away from areas where product may come into contact with food or pharmaceuticals.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Occupational exposure limits

No occupational exposure limit values exist for any of the components listed in Section 3 of this SDS.

### 8.2. Exposure controls

#### 8.2.1. Engineering controls

Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapors/spray. If ventilation is not adequate, use respiratory protection equipment.

#### 8.2.2. Personal protective equipment (PPE)

##### Eye/face protection

Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:

Safety Glasses with side shields

##### Skin/hand protection

Select and use gloves and/or protective clothing approved to relevant local standards to prevent skin contact based on the results of an exposure assessment. Selection should be based on use factors such as exposure levels, concentration of the substance or mixture, frequency and duration, physical challenges such as temperature extremes, and other use conditions. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible gloves/protective clothing. Note: Nitrile gloves may be worn over polymer laminate gloves to improve dexterity.

Gloves made from the following material(s) are recommended: Polymer laminate

If this product is used in a manner that presents a higher potential for exposure (eg. spraying, high splash potential etc.), then use of protective coveralls may be necessary. Select and use body protection to prevent contact based on the results of an exposure assessment. The following protective clothing material(s) are recommended: Apron - polymer laminate

##### Respiratory protection

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for organic vapors and particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

<b>General Physical Form:</b>	Liquid
<b>Odor, Color, Grade:</b>	White, with slight ammonia odor
<b>Odor threshold</b>	<i>No Data Available</i>

pH	11 - 12
Melting point	<i>Not Applicable</i>
Boiling Point	Approximately 212 °F
Flash Point	No flash point
Evaporation rate	<i>No Data Available</i>
Flammability (solid, gas)	Not Applicable
Flammable Limits(LEL)	<i>Not Applicable</i>
Flammable Limits(UEL)	<i>Not Applicable</i>
Vapor Pressure	17.5 mmHg [@ 20 °C]
Vapor Density	<i>No Data Available</i>
Density	Approximately 1 g/ml
Specific Gravity	Approximately 1 [Ref Std:WATER=1]
Solubility in Water	Complete
Solubility- non-water	<i>No Data Available</i>
Partition coefficient: n-octanol/ water	<i>No Data Available</i>
Autoignition temperature	<i>Not Applicable</i>
Decomposition temperature	<i>No Data Available</i>
Viscosity	<i>No Data Available</i>
Molecular weight	<i>No Data Available</i>
Volatile Organic Compounds	< 1 % weight

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

This material may be reactive with certain agents under certain conditions - see the remaining headings in this section.

### 10.2. Chemical stability

Stable.

### 10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

### 10.4. Conditions to avoid

None known.

### 10.5. Incompatible materials

Strong acids

### 10.6. Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
Carbon monoxide	Not Specified
Carbon dioxide	Not Specified

## SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

### 11.1. Information on Toxicological effects

**Signs and Symptoms of Exposure**

Based on test data and/or information on the components, this material may produce the following health effects:

**Inhalation:**

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

**Skin Contact:**

Skin Irritation: Signs/symptoms may include localized redness, swelling, itching, dryness, cracking, blistering, and pain.  
 Allergic Skin Reaction (non-photo induced): Signs/symptoms may include redness, swelling, blistering, and itching.

**Eye Contact:**

Vapors released during curing may cause eye irritation. Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

**Ingestion:**

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

**Additional Health Effects:**

**Prolonged or repeated exposure may cause target organ effects:**

Respiratory Effects: Signs/symptoms may include cough, shortness of breath, chest tightness, wheezing, increased heart rate, bluish colored skin (cyanosis), sputum production, changes in lung function tests, and/or respiratory failure.

**Toxicological Data**

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

**Acute Toxicity**

Name	Route	Species	Value
Overall product	Ingestion		No data available; calculated ATE >5,000 mg/kg
Silicic acid, lithium salt	Dermal		LD50 estimated to be 2,000 - 5,000 mg/kg
Silicic acid, lithium salt	Ingestion	Rat	LD50 > 2,000 mg/kg
1,2-Ethanediamine, N1-[3-(trimethoxysilyl)propyl]-	Dermal	Rabbit	LD50 > 2,000 mg/kg
1,2-Ethanediamine, N1-[3-(trimethoxysilyl)propyl]-	Inhalation-Dust/Mist (4 hours)	Rat	LC50 >1.49, <2.44 mg/l
1,2-Ethanediamine, N1-[3-(trimethoxysilyl)propyl]-	Ingestion	Rat	LD50 1,897 mg/kg
Silanetriol, methyl-, potassium salt	Ingestion	Rat	LD50 > 2,000 mg/kg

ATE = acute toxicity estimate

**Skin Corrosion/Irritation**

Name	Species	Value
Overall product	In vitro data	Irritant
Silicic acid, lithium salt	Rabbit	Minimal irritation
1,2-Ethanediamine, N1-[3-(trimethoxysilyl)propyl]-	Rabbit	Mild irritant
Silanetriol, methyl-, potassium salt	Professional judgement	Corrosive

**Serious Eye Damage/Irritation**

Name	Species	Value
------	---------	-------

Overall product	In vitro data	No significant irritation
Silicic acid, lithium salt	Rabbit	Corrosive
1,2-Ethanediamine, N1-[3-(trimethoxysilyl)propyl]-	Rabbit	Corrosive
Silanetriol, methyl-, potassium salt	similar health hazards	Corrosive

**Skin Sensitization**

Name	Species	Value
1,2-Ethanediamine, N1-[3-(trimethoxysilyl)propyl]-	Multiple animal species	Sensitizing

**Respiratory Sensitization**

For the component/components, either no data are currently available or the data are not sufficient for classification.

**Germ Cell Mutagenicity**

For the component/components, either no data are currently available or the data are not sufficient for classification.

**Carcinogenicity**

For the component/components, either no data are currently available or the data are not sufficient for classification.

**Reproductive Toxicity**

**Reproductive and/or Developmental Effects**

For the component/components, either no data are currently available or the data are not sufficient for classification.

**Target Organ(s)**

**Specific Target Organ Toxicity - single exposure**

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Silicic acid, lithium salt	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification	similar compounds	NOAEL Not available	

**Specific Target Organ Toxicity - repeated exposure**

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Silicic acid, lithium salt	Ingestion	nervous system   kidney and/or bladder	Some positive data exist, but the data are not sufficient for classification	similar compounds	NOAEL Not available	
1,2-Ethanediamine, N1-[3-(trimethoxysilyl)propyl]-	Inhalation	respiratory system	May cause damage to organs though prolonged or repeated exposure	Rat	NOAEL 0.015 mg/l	90 days

**Aspiration Hazard**

For the component/components, either no data are currently available or the data are not sufficient for classification.

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

**SECTION 12: Ecological information**

**Ecotoxicological information**

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.



## Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

## SECTION 13: Disposal considerations

### 13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Dispose of waste product in a permitted industrial waste facility. Empty drums/barrels/containers used for transporting and handling hazardous chemicals (chemical substances/mixtures/preparations classified as Hazardous as per applicable regulations) shall be considered, stored, treated & disposed of as hazardous wastes unless otherwise defined by applicable waste regulations. Consult with the respective regulating authorities to determine the available treatment and disposal facilities.

**EPA Hazardous Waste Number (RCRA):** Not regulated

## SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

## SECTION 15: Regulatory information

### 15.1. US Federal Regulations

#### EPCRA 311/312 Hazard Classifications:

##### Physical Hazards

Not applicable

##### Health Hazards

Respiratory or Skin Sensitization

Skin Corrosion or Irritation

Specific target organ toxicity (single or repeated exposure)

### 15.2. State Regulations

### 15.3. Chemical Inventories

The components of this material are in compliance with the provisions of Australia National Industrial Chemical Notification and Assessment Scheme (NICNAS). Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the new substance notification requirements of CEPA.

The components of this product are in compliance with the chemical notification requirements of TSCA. All required components of this product are listed on the active portion of the TSCA Inventory.

### 15.4. International Regulations

**This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.**

## SECTION 16: Other information

### NFPA Hazard Classification

**Health:** 2 **Flammability:** 0 **Instability:** 1 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

<b>Document Group:</b>	28-4142-7	<b>Version Number:</b>	5.02
<b>Issue Date:</b>	11/16/18	<b>Supersedes Date:</b>	07/26/18

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M.

**3M USA SDSs are available at [www.3M.com](http://www.3M.com)**