



### SAFETY DATA SHEET

**Preparation Date:** Dec 03, 2014  
**Supersedes Date:** Aug 18, 2014

**Version Number:** 08

#### SECTION 1 PRODUCT AND COMPANY IDENTIFICATION

##### PRODUCT IDENTIFIER

**Product Name** DCT Power-Force II  
**Product Use** Liquid Ready-to-Use  
**Product ID Number** DCT130500  
**PGP Number** 6-45

##### RECOMMENDED USE AND RESTRICTIONS ON USE

Cleaner for Stainless Steel Cooking Equipment

##### COMPANY IDENTIFICATION

**Manufacturer** Diversified Chemical Technologies, Inc.  
15477 Woodrow Wilson, Detroit, MI 48238  
(313) 867-5444

##### EMERGENCY TELEPHONE NUMBER

24 Hour Emergency Phone Number (Health & Safety; Transportation) CHEMTREC - (800) 424-9300

#### SECTION 2 HAZARDS IDENTIFICATION

##### GHS CLASSIFICATION

Product has not been tested as a whole to determine its GHS classification. Hazard categories are based on individual ingredient hazard categories. Refer Section 16 for additional GHS Phrases.

Hazard Class	Hazard Category
Acute Toxicity: Oral	4
Skin Corrosion/Irritation	1A
Serious Eye Damage/Eye Irritation	1

##### GHS LABEL ELEMENTS

###### Pictogram



###### GHS Signal Word

DANGER

##### GHS Hazard Phrases

Harmful if swallowed.  
Causes severe skin burns and eye damage.  
Causes serious eye damage.

##### GHS Precaution Phrases

Keep only in original container.  
Wash hands thoroughly after handling.  
Do not eat, drink or smoke when using this product.  
Do not breathe dust/fume/gas/mist/vapors/spray.  
Wear protective gloves/protective clothing/eye protection/face protection.  
Absorb spillage to prevent material damage.

**Product Name:** DCT Power-Force II

**Preparation Date:** Dec 03, 2014

**GHS Response Phrases**

Rinse mouth.

IF ON SKIN (or hair): Remove/take off immediately all contaminated clothing. Rinse skin with water/shower.

Wash contaminated clothing before reuse.

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

**GHS Storage and Disposal Phrases**

Store in corrosive resistant container or with a resistant inner liner.

Dispose of contents/container to ...*licensed professional waste disposal service or contact your regulatory department.*

Store locked up.

**POTENTIAL HEALTH EFFECTS (Acute and Chronic)**

**Chronic:** Product has not been tested as a whole to determine its acute and long-term effects. The product does contain ingredients that potentially may affect from repeated excessive exposures.

**Acute- Inhalation** May cause severe irritation of the upper respiratory tract with pain, burns, and inflammation.

**Acute-Skin Contact** Causes skin irritation. Prolonged or repeated skin contact may cause dermatitis. Effects may be delayed. May be harmful if absorbed through skin.

**Acute-Eye Contact** Contact with eyes may cause severe irritation, and possible eye burns.

**Acute-Ingestion** May cause irritation of the digestive tract. May be harmful if swallowed.

**SECTION 3 COMPOSITION / INFORMATION ON INGREDIENTS**

CAS Number	Ingredients*	Percentage Range
7758-29-4	Sodium phosphate, Tribasic	1 – 5
1310-58-3	Potassium hydroxide 45%	40 - 50
54549-24-5	D-Glucopyranoside, hexyl	1 – 5

\*Identity of other chemicals and/or exact percentage (concentration) has been withheld as a trade secret.

**SECTION 4 FIRST AID MEASURES**

**IN CASE OF INHALATION**

Remove from exposure and move to fresh air immediately. If breathing is difficult, give oxygen. Get medical aid. Do not use mouth-to-mouth resuscitation if victim ingested or inhaled the substance; induce artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device.

**IN CASE OF SKIN CONTACT**

Wash off with soap and plenty of water.

**IN CASE OF EYE CONTACT**

Flush eyes with plenty of water for at least 15 minutes, occasionally lifting the upper and lower eyelids. Get medical aid.

**IN CASE OF INGESTION**

Do NOT induce vomiting. If victim is conscious and alert, rinse mouth and drink 2-4 cupfuls of milk or water. Never give anything by mouth to an unconscious person. Get medical aid.

**SIGNS AND SYMPTOMS OF EXPOSURE**

To the best of our knowledge, the chemical, physical, and toxicological properties have not been investigated

**NOTE TO PHYSICIAN**

Treat symptomatically and supportively. It is advisable not to induce vomiting due to the risk of aspiration and it is not usually necessary unless a large amount has been ingested or it has been contaminated with another product.

**Product Name:** DCT Power-Force II

**Preparation Date:** Dec 03, 2014

**SECTION 5 FIRE FIGHTING MEASURES**

<b>Flash Point</b>	212 °F
<b>Flash Point Method</b>	PMCC

<b>Explosive Limits</b>	<i>LEL:</i> N/D	<i>UEL:</i> N/D
<b>Auto Ignition Point</b>	N/D	

**SUITABLE EXTINGUISHING MEDIA** Use water spray, dry chemical, carbon dioxide, or chemical foam.

**FIRE FIGHTING INSTRUCTIONS** As in any fire, wear self-contained breathing apparatus and protective clothing to prevent contact with skin and eyes. Specific Hazard(s): Emits toxic fumes under fire conditions. Vapors may be heavier than air. They can spread along the ground and collect in low or confined areas.

**FLAMMABLE PROPERTIES AND HAZARDS** No data available

**SECTION 6 ACCIDENTAL RELEASE MEASURES**

**NOTIFICATION PROCEDURES**

In the event of a spill or accidental release, notify relevant authorities in accordance with all applicable regulations. National Response Center (24-HR Reporting): (800) 424-8802.

**SAFETY PRECAUTIONS**

Use suitable protective clothing appropriate to spill size and risk of exposure. Refer to Section 8 for further details. Use extreme caution because affected area(s) may be slippery. For industrial use only. Keep out of reach of children.

**CONTAINMENT AND CLEANUP**

Avoid runoff into sanitary and storm sewers and ditches which lead to waterways. Clean up spills immediately, observing precautions. Absorb spill with inert material and place in closed containers for disposal. Ventilate area and wash spill site after material pickup is complete.

**SECTION 7 HANDLING AND STORAGE**

**PRECAUTIONS TO BE TAKEN IN HANDLING**

Avoid inhalation. Avoid contact with eyes, skin, and clothing. Avoid prolonged or repeated exposure.

**PRECAUTIONS TO BE TAKEN IN STORAGE**

Keep container closed when not in use. Store in a tightly closed container. Store in a cool, dry, well-ventilated area away from incompatible substances. Keep away from water. Corrosives area. Do not store in reactive metal containers (i.e. aluminum, tin, zinc and/or their alloys). Protect from freeze and high temperatures (>140 °F). Keep away from sparks, heat and flame.

**SECTION 8 EXPOSURE CONTROLS / PERSONAL PROTECTION**

CAS #	Ingredients	OSHA TWA	ACGIH TWA	Other Limits
N/D	N/D	N/D	N/D	N/D

**ENGINEERING CONTROLS**

The level of ventilation necessary will vary depending upon potential exposure conditions. Adequate ventilation should be provided so that exposure limits are not exceeded. If heavy misting is present, local exhaust ventilation should be considered in addition to general mechanical ventilation.

**WORK/HYGIENIC/MAINTENANCE PRACTICES**

Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing separate from home laundry and protective equipment to remove contaminants. Discard contaminated clothing and footwear that cannot be cleaned. Practice good housekeeping. Do not store work clothing and protective equipment in the same locker as personal clothing.

**Product Name:** DCT Power-Force II

**Preparation Date:** Dec 03, 2014

**PERSONAL PROTECTIVE EQUIPMENT**

Personal protective equipment selections vary based on potential exposure conditions such as applications, handling practices, concentration and ventilation. Information on the selection of protective equipment for use with this material, as provided below, is based upon intended, normal use.

**Respiratory Protection** None required under normal intended conditions of product use. However, if vapors or mists are present and if engineering controls do not maintain airborne contaminant concentrations at a level which is adequate to protect worker health, a NIOSH/MSHA approved respirator may be appropriate.

**Hand Protection** Wear appropriate protective gloves to prevent skin exposure. Glove suitability and breakthrough time will differ depending on the specific use conditions. Contact the glove manufacturer for specific advice on glove selection and breakthrough times for your use conditions. Inspect and replace worn or damaged gloves. . The types of gloves to be considered for this material include:

**Chemical resistant rubber/Neoprene.**

**Eye Protection** Safety glasses are recommended. If splashing is likely, safety goggles or safety glasses with splash shield are recommended. Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166.

**Skin and Body Protection** The types of clothing to be considered for this material include: Long-sleeved shirt and pants, at a minimum. If prolonged or repeated contact is likely, chemical-resistant clothing is recommended.

**OTHER PROTECTIVE EQUIPMENT** Provide suitable facilities for quick drenching or flushing of the eyes and body in case of contact or splash.

**SECTION 9 PHYSICAL AND CHEMICAL PROPERTIES**

<b>Appearance</b>	Colorless, viscous
<b>Physical State</b>	Clear Green
<b>Odor</b>	Mild
<b>pH</b>	14
<b>Melting Point</b>	N/A
<b>Boiling Point</b>	N/A

<b>Specific Gravity (water = 1)</b>	1.30 - 1.32
<b>Vapor Pressure</b>	N/D
<b>Viscosity</b>	N/AV
<b>Evaporation Rate (water = 1)</b>	N/D
<b>Volatile Organic Compounds (%)</b>	0.0
<b>Solubility in Water</b>	N/D

**SECTION 10 STABILITY / REACTIVITY**

**Chemical Stability** *Unstable* [ ] *Stable* [X]

**Conditions to Avoid** Reactive metals such as aluminum, tin, zinc, and alloys containing these metals

**Reactivity / Incompatibility** Strong oxidizing agents, strong acids

**Hazardous Decomposition** Material does not decompose at ambient temperature. Incomplete combustion or thermal decomposition may be expected to generate such materials as: particulate matter and unburned, hydrocarbons; oxides of carbon; oxides of potassium; water vapor; and other unidentified organic and inorganic compounds.

**Hazardous Reactions** *Will occur* [ ] *Will not occur* [X]

**SECTION 11 TOXICOLOGICAL INFORMATION**

**CARCINOGENICITY**

Product is not tested for carcinogenicity. No components of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen, except as identified below;

**IARC:** Not Listed      **ACGIH:** Not Listed      **NTP:** Not Listed

**PRODUCT TOXICOLOGICAL DATA**

Product is not tested for classification under the following categories:

**LD50 (Oral), LC50 (Inhalation), Dermal Toxicity (Skin), Skin Corrosion/Irritation, Serious Eye Damage/Irritation, Respiratory/ Skin Sensitization, Germ Cell Mutagenicity, Carcinogenicity, Reproductive Toxicity, STOT-single exposure, STOR-repeated exposure, Aspiration Hazard**

**Product Name:** DCT Power-Force II

**Preparation Date:** Dec 03, 2014

**INGREDIENT TOXICOLOGICAL DATA**

None of the ingredients above 1% concentration (0.1% for carcinogens) trigger the hazard rating or classify under the following categories, unless indicated below:

**LD50 (Oral), LC50 (Inhalation), Dermal Toxicity (Skin), Skin Corrosion/Irritation, Serious Eye Damage/Irritation, Respiratory/ Skin Sensitization, Germ Cell Mutagenicity, Carcinogenicity, Reproductive Toxicity, STOT-single exposure, STOR-repeated exposure, Aspiration Hazard**

**SECTION 12 ECOLOGICAL INFORMATION**

<b>General Ecological Information</b>	N/AV.	<b>Persistence and Degradability</b>	N/AV
<b>Bioaccumulative Potential</b>	N/AV.	<b>Mobility in Soil</b>	N/AV

**SECTION 13 DISPOSAL CONSIDERATIONS**

Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. US EPA guidelines for the classification determination are listed in 40 CFR Parts 261. Additionally, waste generators must consult state and local hazardous waste regulations to ensure complete and accurate classification.

Contact a licensed professional waste disposal service to dispose of this material. Preferred method of disposal is to dissolve or mix the material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber. Observe all federal, state, and local environmental regulations.

**Contaminated Packaging** Dispose of as unused product.  
**Empty Containers** Clean empty containers of any residue per 40CFR261.7 guidelines and either recycle containers or dispose of in normal trash.

**SECTION 14 TRANSPORT INFORMATION**

	LAND (US DOT)	MARINE (IMDG)	AIR (IATA)
<b>Proper Shipping Name</b>	Corrosive Liquid, basic, inorganic, n.o.s. (contains sodium hydroxide and potassium hydroxide)		
<b>Hazard Class</b>	8		
<b>ID Number</b>	UN3266		
<b>Packaging Group</b>	II		

**Additional Information**

**DOT Quantity Limitation:** 1 L

**DOT Label for Limited Quantities:** LQ diamond per 49CFR172.315

**SECTION 15 REGULATORY INFORMATION**

**EPA SARA (SUPERFUND AMENDMENTS AND REAUTHORIZATION ACT OF 1986) LISTS**

[302 (EHS) TPQ, 304 RQ, 313 TRI]

None of the ingredients above 1% concentration and 0.1% for carcinogens are identified in the lists, except:

7758-29-4; Sodium phosphate, Tribasic; 304 RQ - 5000 LB

1310-58-3; Potassium hydroxide; 304 RQ - 1000 LB

1310-73-2; Sodium hydroxide; 304 RQ - 1000 LB

<b>SARA TITLE III SECTION 311/312 CATEGORIZATION (40 CFR 370)</b>	Yes	No
Acute (immediate) Health Hazard	X	
Chronic (delayed) Health Hazard		X
Fire Hazard		X
Sudden Release of Pressure Hazard		X
Reactive Hazard		X

**Product Name:** DCT Power-Force II

**Preparation Date:** Dec 03, 2014

**STATE AND OTHER US EPA REGULATIONS**

California Prop. 65      N/AP

**WHMIS CLASSIFICATION (1988)**    D2B (Stylized T) and E (Corrosive Material)

*This product has been classified under WHMIS in accordance with hazard criteria of the Controlled Products Regulations and the MSDS contains all the information required by the Controlled Products Regulations.*

**NATIONAL INVENTORIES**

TSCA	Yes
CAA HAP, ODC	No
CWA NPDES	No
CEPA (DSL/NDL)	Yes
KECI	N/D

AICS	N/D
IECSC	N/D
EINECS	N/D
ENCS	N/D
PICCS	N/D

**SECTION 16**

**OTHER INFORMATION**

**ADDITIONAL GHS PHRASES**

GHS phrases provided below are in addition to the phrases available in Section 2. GHS phrases are identified in accordance with GHS regulations and are triggered for each hazard category.

*IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell.  
Specific treatment see ... on this label*

**NFPA RATING**                      Health (Blue): 3    Flammability (Red): 0    Reactivity (Yellow): 0    Specific Hazard(s) (White): COR/ALK  
**HMIS RATING**                      Health (Blue): 3    Flammability (Red): 0    Reactivity (Yellow): 0    Personal Protective Equipment: C or D

**THIS SAFETY DATA SHEET CONTAINS THE FOLLOWING REVISIONS**

Conversion from EU format MSDS to GHS format SDS; Ingredient/concentration

**USER RESPONSIBILITY**            It is the user's responsibility to determine the suitability and adopt precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of this product.

**PREPARED BY**

Corporate Environment/Health and Safety Department of Diversified Chemical Technologies, Inc. and Subsidiaries

**THE INFORMATION CONTAINED HEREIN IS BASED ON INDIVIDUAL INGREDIENT DATA CONSIDERED TO BE ACCURATE. HOWEVER, NO WARRANTY IS EXPRESSED OR IMPLIED REGARDING THE ACCURACY OF THESE DATA OR THE RESULTS TO BE OBTAINED FROM THE USE THEREOF.**