

1. IDENTIFICATION

Product Name	Dawn Professional Heavy Duty Manual Pot & Pan Detergent Concentrate
Product Identifier	C-90440437-001_PROF_NG
Product Type:	Finished Product - Professional
Recommended use	Dish Care.
Details of the supplier of the safety data sheet	Procter & Gamble Professional 1 P&G Plaza Cincinnati, Ohio 45202 Procter & Gamble Inc. P.O. Box 355, Station A Toronto, ON M5W 1C5 1-800-332-7787
E-mail Address	pgsds.im@pg.com
Emergency Telephone	Transportation (24 HR) CHEMTREC - 1-800-424-9300 (U.S./ Canada) or 1-703-527-3887 Mexico toll free in country: 800-681-9531

2. HAZARD IDENTIFICATION

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:.

<u>Hazard category</u>	
Eye Damage / Irritation	Category 2B
Flammable liquids	
Flammable liquids	Category 4
Signal word	Warning
Hazard statements	Causes eye irritation
Hazard pictograms	None
Precautionary Statements	Wash hands thoroughly after handling Keep away from heat/sparks/open flames/hot surfaces. — No smoking Keep container tightly closed
Precautionary Statements - Response	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing If eye irritation persists: Get medical advice/attention If swallowed: Drink 1 or 2 glasses of water In case of fire: Use water, CO2, dry chemical, or foam for extinction
Precautionary Statements - Storage	Store in a well-ventilated place. Keep cool
Precautionary Statements - Disposal	Dispose of contents/container to an approved waste disposal plant Dispose of

contents/containers in accordance with local regulations

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Chemical name	Synonyms	Trade Secret	CAS No	Weight-%
Sulfuric acid, mono-C10-16-alkyl esters, sodium salts	Sulfuric acid, mono-C10-16-alkyl esters, sodium salts	Yes	68585-47-7	10 - 30
Lauramine Oxide	Lauramine Oxide	Yes	70592-80-2	3 - 7
Alcohol	Ethanol	Yes	64-17-5	1 - 5
Deceth-n	Poly(oxy-1,2-ethanediyl), alpha-decyl-omega-hydr oxy-	Yes	26183-52-8	1 - 5

Additional information Actual concentrations withheld as trade secret in accordance with Canadian HPR

4. FIRST AID MEASURES

Description of first aid measures

Eye contact Rinse with plenty of water. Get medical attention immediately if irritation persists.

Skin contact Rinse with plenty of water. Call a physician if irritation develops and persists.

Ingestion Rinse mouth. Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur.

Inhalation Move to fresh air. If symptoms persist, call a physician.

Most important symptoms/effects, acute and delayed May cause eye irritation

Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media In case of fire: Use water, CO2, dry chemical, or foam for extinction.

Unsuitable Extinguishing Media Do not use a solid water stream as it may scatter and spread fire.

Special Hazard Fumes may catch fire.

Special protective equipment for fire-fighters As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Specific hazards arising from the chemical None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Use personal protective equipment as required. Do not get in eyes, on skin, or on clothing.

Advice for emergency responders Use personal protective equipment as required.

Environmental precautions Should not be released into the environment

Methods and material for containment and cleaning up

Methods for containment Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal.

Methods for cleaning up Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Keep away from open flames, hot surfaces and sources of ignition. Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place. Store in a cool/low-temperature, well-ventilated, dry place away from heat and ignition sources.

Incompatible products None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines No exposure limits noted for ingredient(s).

No relevant exposure guidelines for other ingredients

Appropriate engineering controls

Engineering Measures **Distribution, Workplace and Household Settings:**
Ensure adequate ventilation

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

Personal Protective Equipment

Eye Protection **Distribution, Workplace and Household Settings:**
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Use appropriate eye protection

Hand Protection **Distribution, Workplace and Household Settings:**
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Protective gloves

Skin and Body Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Wear suitable protective clothing

Respiratory Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
In case of inadequate ventilation wear respiratory protection

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state	Liquid	
Appearance	clear blue	
Odor	Perfumes	
Odor threshold	No information available	
<u>Property</u>	<u>Values</u>	<u>Remarks</u>
pH	9	
Melting point / freezing point	No information available	
Initial boiling point and boiling range	> 35 °C / 95 °F	
Flash point	71.5 °C / 160.7 °F	Closed cup. Product is an aqueous solution containing <=24% alcohol and >=50% water.
Evaporation rate	No information available	
Flammability	No information available	
Flammability Limit in Air		
Upper flammability or explosive limits	No information available	
Lower flammability or explosive limits	No information available	
Vapor pressure	No information available	
Relative vapor density	No information available	
Relative density	No information available	
Water solubility	No information available	
Partition coefficient	No information available	
Autoignition temperature	No information available	.
Decomposition temperature	No information available	.
Viscosity	No information available	
VOC content	.?%	

10. STABILITY AND REACTIVITY

Reactivity	None under normal use conditions.
Stability	Stable under normal conditions.
Hazardous polymerization	Hazardous polymerization does not occur.
Hazardous Reactions	None under normal processing.
Conditions to Avoid	Keep away from open flames, hot surfaces and sources of ignition.
Incompatible Materials	None in particular.

Hazardous decomposition products None under normal use conditions.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Inhalation	No known effect.
Skin contact	No known effect.
Ingestion	No known effect.
Eye contact	Irritating to eyes.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Acute toxicity	No known effect.
Skin corrosion/irritation	No known effect.
Serious eye damage/eye irritation	Irritating to eyes.
Skin sensitization	No known effect.
Respiratory sensitization	No known effect.
Germ cell mutagenicity	No known effect.
Reproductive toxicity	No known effect.
Developmental toxicity	No known effect.
STOT - single exposure	No known effect.
STOT - repeated exposure	No known effect.
Aspiration hazard	No known effect.
Carcinogenicity	No known effect.

Component Information

Chemical name	CAS No	Oral LD50	Dermal LD50	Inhalation LC50
Sulfuric acid, mono-C10-16-alkyl esters, sodium salts	68585-47-7	> 2000 mg/kg (Rat)	-	-
Lauramine Oxide	70592-80-2	1064 mg/kg (OECD 401)	> 2000 mg/kg (OECD 402)	-
Alcohol	64-17-5	10470 mg/kg bw (OECD 401)	-	116.9 - 133.8 mg/L air (OECD 403)
Deceth-n	26183-52-8	300 mg/kg	>2000 mg/kg	-

12. ECOLOGICAL INFORMATION

ecotoxicity

The product is not expected to be hazardous to the environment.

Persistence and degradability	No information available.
Bioaccumulative potential	No information available.
Mobility	No information available.
Other adverse effects	No information available.

13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from Residues/Unused Products	Disposal should be in accordance with applicable regional, national and local laws and regulations.
Contaminated packaging	Disposal should be in accordance with applicable regional, national and local laws and regulations.

California Hazardous Waste Codes 331
(non-household setting)

14. TRANSPORT INFORMATION

DOT Not regulated

IMDG Not regulated

IATA Not regulated

15. REGULATORY INFORMATION

U.S. FEDERAL REGULATIONS

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of the Clean Air Act Amendments of 1990.

Clean Water Act

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

U.S. State Regulations (RTK)

Chemical name	CAS No	New Jersey
Alcohol	64-17-5	X

Chemical name	CAS No	Massachusetts
Alcohol	64-17-5	X

Chemical name	CAS No	Pennsylvania
Alcohol	64-17-5	X

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

International Inventories

Precautionary Statements - Storage

Keep in a dry place

United States

All intentionally-added components of this product(s) are listed on the US TSCA Inventory

Canada

This product is in compliance with CEPA for import by P&G

Legend

United States Toxic Substances Control Act Section 8(b) Inventory (TSCA)

CEPA - Canadian Environmental Protection Act

16. OTHER INFORMATION

HMIS

NFPA

Issuing Date: 31-Aug-2022

Revision date 31-Aug-2022

Disclaimer.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet