

SAFETY DATA SHEET

RESOLVE® Pet Specialist Stain & Odor Remover



HEALTH • HYGIENE • HOME

1. Product and company identification

Product name : RESOLVE® Pet Specialist Stain & Odor Remover**Distributed by** : Reckitt Benckiser LLC.
Morris Corporate Center IV
399 Interpace Parkway (P.O. Box 225)
Parsippany, New Jersey 07054-0225
+1 973 404 2600**Emergency telephone number (Medical)** : 1-800-338-6167**Emergency telephone number (Transport)** : 1-800-424-9300 (U.S. & Canada) CHEMTREC
Outside U.S. and Canada (North America), call Chemtrec:703-527-3887**Website:** : <http://www.rbnainfo.com>**Product use** : Carpet Cleaners Consumer use

This SDS is designed for workplace employees, emergency personnel and for other conditions and situations where there is greater potential for large-scale or prolonged exposure, in accordance with the requirements of USDOL Occupational Safety and Health Administration.

This SDS is not applicable for consumer use of our products. For consumer use, all precautionary and first aid language is provided on the product label in accordance with the applicable government regulations, and shown in Section 15 of this SDS.

SDS # : D0159003 v2.0**Formulation #** : FF0117229 v2.0

Relevant identified uses of the substance or mixture and uses advised against

Identified uses

Carpet Cleaners Consumer use

2. Hazards identification

Classification of the substance or mixture : EYE IRRITATION - Category 2A

GHS label elements

Hazard pictograms :**Signal word** : Warning**Hazard statements** : Causes serious eye irritation.**Code #** : FF0117229
(D0159003) US**SDS #** : D0159003 v2.0**Date of issue** : 02/09/2021**1/12**

D0159003 v2.0

2. Hazards identification

Precautionary statements

- General** : Read label before use. Keep out of reach of children. If medical advice is needed, have product container or label at hand.
- Prevention** : Wear eye or face protection. Wash thoroughly after handling.
- Response** : IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice or attention.
- Storage** : Not applicable.
- Disposal** : Not applicable.
- Supplemental label elements** : None known.
- Hazards not otherwise classified** : None known.

3. Composition/information on ingredients

Substance/mixture : Mixture

Ingredient name	%	CAS number
hydrogen peroxide solution	1 - 5	7722-84-1
1-(2-butoxy-1-methylethoxy)propan-2-ol	1 - 5	29911-28-2
Sulfuric acid, mono-C12-14-alkyl esters, sodium salts	1 - 5	85586-07-8

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

4. First aid measures

Description of necessary first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 10 minutes. Get medical attention.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Get medical attention if adverse health effects persist or are severe. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.
- Skin contact** : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur. Wash clothing before reuse. Clean shoes thoroughly before reuse.
- Ingestion** : Wash out mouth with water. Remove dentures if any. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Stop if the exposed person feels sick as vomiting may be dangerous. Do not induce vomiting unless directed to do so by medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Get medical attention if adverse health effects persist or are severe. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and get medical attention immediately.

D0159003 v2.0

4. First aid measures

Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.

Most important symptoms/effects, acute and delayed

Potential acute health effects

- Eye contact** : Causes serious eye irritation.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

Over-exposure signs/symptoms

- Eye contact** : Adverse symptoms may include the following:
pain or irritation
watering
redness
- Inhalation** : No specific data.
- Skin contact** : No specific data.
- Ingestion** : No specific data.

Indication of immediate medical attention and special treatment needed, if necessary

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation.

See toxicological information (Section 11)

5. Fire-fighting measures

Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.

Specific hazards arising from the chemical : No specific fire or explosion hazard.

- Hazardous thermal decomposition products** : Decomposition products may include the following materials:
carbon dioxide
carbon monoxide

Special protective actions for fire-fighters : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

Special protective equipment for fire-fighters : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

D0159003 v2.0

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Avoid breathing vapor or mist. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment.
- For emergency responders** : If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".
- Environmental precautions** : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods and materials for containment and cleaning up

- Small spill** : Stop leak if without risk. Move containers from spill area. Dilute with water and mop up if water-soluble. Alternatively, or if water-insoluble, absorb with an inert dry material and place in an appropriate waste disposal container. Dispose of via a licensed waste disposal contractor.
- Large spill** : Stop leak if without risk. Move containers from spill area. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Dispose of via a licensed waste disposal contractor. Contaminated absorbent material may pose the same hazard as the spilled product. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

7. Handling and storage

Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8). Do not ingest. Avoid contact with eyes, skin and clothing. Avoid breathing vapor or mist. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Empty containers retain product residue and can be hazardous. Do not reuse container.
- Conditions for safe storage, including any incompatibilities** : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination. See Section 10 for incompatible materials before handling or use.

D0159003 v2.0

8. Exposure controls/personal protection

Control

Occupational exposure limits

Ingredient name	Exposure limits
hydrogen peroxide solution	<p>ACGIH TLV (United States, 3/2018). TWA: 1 ppm 8 hours. TWA: 1.4 mg/m³ 8 hours.</p> <p>OSHA PEL 1989 (United States, 3/1989). TWA: 1 ppm 8 hours. TWA: 1.4 mg/m³ 8 hours.</p> <p>NIOSH REL (United States, 10/2016). TWA: 1 ppm 10 hours. TWA: 1.4 mg/m³ 10 hours.</p> <p>OSHA PEL (United States, 5/2018). TWA: 1 ppm 8 hours. TWA: 1.4 mg/m³ 8 hours.</p>

- Appropriate engineering controls** : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.
- Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

Individual protection measures

- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: chemical splash goggles.

Skin protection

- Hand protection** : Considering the parameters specified by the glove manufacturer, check during use that the gloves are still retaining their protective properties. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. In the case of mixtures, consisting of several substances, the protection time of the gloves cannot be accurately estimated.

- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

- Respiratory protection** : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

D0159003 v2.0

9. Physical and chemical properties

Appearance

Physical state	: Liquid. [Clear.]
Color	: Colorless.
Odor	: Citrus, herbaceous odor.
Odor threshold	: Not available.
pH	: 5.3 to 5.7 [Conc. (% w/w): 100%]
Melting point	: Not available.
Boiling point	: Not available.
Flash point	: Closed cup: >93.3°C (>199.9°F)
Evaporation rate	: Not available.
Flammability (solid, gas)	: Not available.
Lower and upper explosive (flammable) limits	: Not available.
Vapor pressure	: Not available.
Vapor density	: Not available.
Relative density	: 1 to 1.04
Solubility	: Easily soluble in the following materials: cold water and hot water.
Partition coefficient: n-octanol/water	: Not available.
Auto-ignition temperature	: Not available.
Decomposition temperature	: Not available.
Viscosity	: Not available.

Aerosol product

10. Stability and reactivity

Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
Chemical stability	: The product is stable.
Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
Conditions to avoid	: No specific data.
Incompatible materials	: No specific data.
Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

11. Toxicological information

Information on toxicological effects

Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
hydrogen peroxide solution	LD50 Oral	Rat - Male, Female	805 mg/kg (70% H2O2 w/w)	-

Conclusion/Summary : Based on available data, the classification criteria are not met.

Irritation/Corrosion

D0159003 v2.0

11. Toxicological information

Product/ingredient name	Result	Species	Score	Exposure	Observation
hydrogen peroxide solution	Eyes - Severe irritant	Rabbit	-	1 milligrams	-

Conclusion/Summary

- Skin** : Based on available data, the classification criteria are not met.
Eyes : Based on Calculation Method: Causes serious eye irritation.
Respiratory : Based on available data, the classification criteria are not met.

Sensitization

Not available.

Conclusion/Summary

- Skin** : Based on available data, the classification criteria are not met.
Respiratory : Based on available data, the classification criteria are not met.

Mutagenicity

Not available.

- Conclusion/Summary** : Based on available data, the classification criteria are not met.

Carcinogenicity

Not available.

- Conclusion/Summary** : Based on available data, the classification criteria are not met.

Classification

Product/ingredient name	OSHA	IARC	NTP
hydrogen peroxide solution	-	3	-

Reproductive toxicity

Not available.

- Conclusion/Summary** : Based on available data, the classification criteria are not met.

Teratogenicity

Not available.

- Conclusion/Summary** : Based on available data, the classification criteria are not met.

Specific target organ toxicity (single exposure)

Name	Category	Route of exposure	Target organs
hydrogen peroxide solution	Category 3	-	Respiratory tract irritation

Specific target organ toxicity (repeated exposure)

Not available.

Aspiration hazard

Not available.

Information on the likely routes of exposure : Not available.

Potential acute health effects

Code # : FF0117229
(D0159003) US

SDS # : D0159003 v2.0

Date of issue : 02/09/2021

7/12

D0159003 v2.0

11. Toxicological information

- Eye contact** : Causes serious eye irritation.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

- Eye contact** : Adverse symptoms may include the following:
pain or irritation
watering
redness
- Inhalation** : No specific data.
- Skin contact** : No specific data.
- Ingestion** : No specific data.

Delayed and immediate effects and also chronic effects from short and long term exposure

Short term exposure

- Potential immediate effects** : Not available.
- Potential delayed effects** : Not available.

Long term exposure

- Potential immediate effects** : Not available.
- Potential delayed effects** : Not available.

Potential chronic health effects

Not available.

- Conclusion/Summary** : Based on available data, the classification criteria are not met.
- General** : No known significant effects or critical hazards.
- Carcinogenicity** : No known significant effects or critical hazards.
- Mutagenicity** : No known significant effects or critical hazards.
- Reproductive toxicity** : No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates

Product/ingredient name	Oral (mg/kg)	Dermal (mg/kg)	Inhalation (gases) (ppm)	Inhalation (vapors) (mg/l)	Inhalation (dusts and mists) (mg/l)
Resolve Pet Trigger Advanced	19859	N/A	N/A	455.5	N/A
hydrogen peroxide solution	805	N/A	N/A	11	N/A
Sulfuric acid, mono-C12-14-alkyl esters, sodium salts	500	N/A	N/A	N/A	N/A

D0159003 v2.0

12. Ecological information

Toxicity

Product/ingredient name	Result	Species	Exposure
hydrogen peroxide solution	Acute EC50 1.2 mg/l Marine water	Algae - Dunaliella tertiolecta - Exponential growth phase	72 hours
	Acute EC50 5.38 mg/l Fresh water	Algae - Pseudokirchneriella subcapitata	96 hours
	Acute EC50 2320 µg/l Fresh water	Daphnia - Daphnia magna - Neonate	48 hours
	Acute LC50 93 ppm Fresh water	Fish - Oncorhynchus mykiss	96 hours
	Chronic NOEC 989.7 ppm Fresh water	Fish - Oncorhynchus tshawytscha - Egg	43 days

Conclusion/Summary : Based on available data, the classification criteria are not met.

Persistence and degradability

Conclusion/Summary : Based on available data, the classification criteria are not met.

Bioaccumulative potential

Product/ingredient name	LogP _{ow}	BCF	Potential
hydrogen peroxide solution	-1.36	-	low
1-(2-butoxy-1-methylethoxy)propan-2-ol	1.523	-	low
Sulfuric acid, mono-C12-14-alkyl esters, sodium salts	-2.42	-	low

Mobility in soil

Soil/water partition coefficient (K_{oc}) : Not available.

Other adverse effects : No known significant effects or critical hazards.

13. Disposal considerations

Disposal methods : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Care should be taken when handling emptied containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

D0159003 v2.0

14. Transport information

	DOT Classification	TDG Classification	IMDG	IATA
UN number	Not regulated.	Not regulated.	Not regulated.	Not regulated.
UN proper shipping name	-	-	-	-
Transport hazard class(es)	-	-	-	-
Packing group	-	-	-	-
Environmental hazards	No.	No.	No.	No.

Additional information

Special precautions for user : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

Transport in bulk according to IMO instruments : Not available.

15. Regulatory information

U.S. Federal regulations :

Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs) : Listed

Clean Air Act Section 602 Class I Substances : Not listed

Clean Air Act Section 602 Class II Substances : Not listed

DEA List I Chemicals (Precursor Chemicals) : Not listed

DEA List II Chemicals (Essential Chemicals) : Not listed

SARA 302/304

Composition/information on ingredients

Name	%	EHS	SARA 302 TPQ		SARA 304 RQ	
			(lbs)	(gallons)	(lbs)	(gallons)
hydrogen peroxide solution	1 - 5	Yes.	1000	106.1	1000	106.1

SARA 304 RQ : 41407.9 lbs / 18799.2 kg [4868.8 gal / 18430.6 L]

SARA 311/312

Classification : EYE IRRITATION - Category 2A

Composition/information on ingredients

D0159003 v2.0

15. Regulatory information

Name	%	Classification
hydrogen peroxide solution	1 - 5	OXIDIZING LIQUIDS - Category 1 ACUTE TOXICITY (oral) - Category 4 ACUTE TOXICITY (inhalation) - Category 4 SKIN CORROSION - Category 1A SERIOUS EYE DAMAGE - Category 1 SPECIFIC TARGET ORGAN TOXICITY (SINGLE EXPOSURE) (Respiratory tract irritation) - Category 3
Sulfuric acid, mono-C12-14-alkyl esters, sodium salts	1 - 5	ACUTE TOXICITY (oral) - Category 4 SKIN IRRITATION - Category 2 SERIOUS EYE DAMAGE - Category 1

State regulations

- Massachusetts** : The following components are listed: HYDROGEN PEROXIDE
- New York** : The following components are listed: Hydrogen peroxide
- New Jersey** : The following components are listed: HYDROGEN PEROXIDE
- Pennsylvania** : The following components are listed: HYDROGEN PEROXIDE
- California Prop. 65**

This product does not require a Safe Harbor warning under California Prop. 65.

Label elements

CPSC

- Signal word** : WARNING
- Hazard statements** : MAY BE HARMFUL IF SWALLOWED. CAUSES EYE IRRITATION. MAY CAUSE SKIN IRRITATION.
- Precautionary measures** : Keep out of the reach of children. Do not swallow. Avoid contact with eyes. Avoid contact with skin and clothing. Keep container tightly closed and sealed until ready for use. Wash thoroughly after handling.

Additional information / Recommendations

- Additional information** : Short term Skin Bleaching agent. Rinse skin with water.

16. Other information

Hazardous Material Information System (U.S.A.)

Health	/	1
Flammability		0
Physical hazards		0

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings and the associated label are not required on SDSs or products leaving a facility under 29 CFR 1910.1200, the preparer may choose to provide them. HMIS® ratings are to be used with a fully implemented HMIS® program. HMIS® is a registered trademark and service mark of the American Coatings Association, Inc.

The customer is responsible for determining the PPE code for this material. For more information on HMIS® Personal Protective Equipment (PPE) codes, consult the HMIS® Implementation Manual.

National Fire Protection Association (U.S.A.)

D0159003 v2.0

16. Other information



Key to abbreviations

- : ATE = Acute Toxicity Estimate
- : BCF = Bioconcentration Factor
- : GHS = Globally Harmonized System of Classification and Labelling of Chemicals
- : IATA = International Air Transport Association
- : IBC = Intermediate Bulk Container
- : IMDG = International Maritime Dangerous Goods
- : LogPow = logarithm of the octanol/water partition coefficient
- : MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)
- : UN = United Nations

- Date of issue** : 02/09/2021
- Date of previous issue** : 10/29/2015
- Version** : 2.0
- Prepared by** : Reckitt Benckiser India Ltd
Plot No 48
Sector - 32
Institutional Area
Gurgaon, Haryana
India - 122001

▣ Indicates information that has changed from previously issued version.

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.



RB is a member of the CSPA Product Care Product Stewardship Program.