

SAFETY DATA SHEET



Issuing Date: 12-May-2022

Revision Date: 03-Oct-2022

Revision Number 5

1. IDENTIFICATION

Product Name	Tide Hygienic Clean Heavy Duty Original Scent
Product Identifier	90279087_RET_NG
Product Type:	Finished Product - Retail
Recommended use	Laundry Care.
Restrictions on use	Use only as directed on label.
Details of the supplier of the safety data sheet	PROCTER & GAMBLE - Fabric and Home Care Division Ivorydale Technical Centre 5289 Spring Grove Avenue Cincinnati, Ohio 45217-1087 USA Procter & Gamble Inc. P.O. Box 355, Station A Toronto, ON M5W 1C5 1-800-331-3774
E-mail Address	pgsds.im@pg.com
Emergency Telephone	Transportation (24 HR) CHEMTREC - 1-800-424-9300 (U.S./ Canada) or 1-703-527-3887 Mexico toll free in country: 800-681-9531

2. HAZARD IDENTIFICATION

"Consumer Products", as defined by the US Consumer Product Safety Act and which are used as intended (typical consumer duration and frequency), are exempt from the OSHA Hazard Communication Standard (29 CFR 1910.1200). This SDS is being provided as a courtesy to help assist in the safe handling and proper use of the product.

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:.

<u>Hazard category</u>	
Acute toxicity - Oral	Category 4
Eye Damage / Irritation	Category 2B
Flammable liquids	Category 4
Signal word	Warning
Hazard statements	Harmful if swallowed Causes eye irritation
Physical hazards	Combustible liquid
Hazard pictograms	



Precautionary Statements

Wash hands thoroughly after handling
Do not eat, drink or smoke when using this product
Keep away from heat/sparks/open flames/hot surfaces. — No smoking
Keep container tightly closed

Precautionary Statements - Response

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
If eye irritation persists: Get medical advice/attention
If swallowed:
Rinse with plenty of water
Drink 1 or 2 glasses of water
Call a POISON CENTER or doctor/physician if you feel unwell
In case of fire: Use water, CO₂, dry chemical, or foam for extinction

Precautionary Statements - Storage Store in a well-ventilated place. Keep cool

Precautionary Statements - Disposal None.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Chemical name	Synonyms	Trade Secret	CAS No	Weight-%
Benzenesulfonic acid, mono-C10-16-alkyl derivs., sodium salts	Benzenesulfonic acid, mono-C10-16-alkyl derivs., sodium salts	No	68081-81-2	5 - 10
MEA-C10-13 Alkyl Benzenesulfonate	Benzenesulfonic acid, mono-C10-16-alkyl derivs., compds. with ethanolamine	No	68910-32-7	5 - 10
Alcohols, C12-14, ethoxylated (EO=9)/Alcohols, C10-16, ethoxylated (EO=9)	Alcohols, C12-14, ethoxylated (EO=9)/Alcohols, C10-16, ethoxylated (EO=9)	No	68439-50-9	5 - 10
Alcohols, C12-14, ethoxylated (EO=9)/Alcohols, C10-16, ethoxylated (EO=9)	Alcohols, C12-14, ethoxylated (EO=9)/Alcohols, C10-16, ethoxylated (EO=9)	No	68002-97-1	5 - 10
Sodium Lauryl Sulfate	Sodium Lauryl Sulfate	No	68585-47-7	1 - 5
Alcohols, C14-15, ethoxylated (n=7)/Alcohols, C10-16, ethoxylated (n=7)	Alcohols, C14-15, ethoxylated (n=7)/Alcohols, C10-16, ethoxylated (n=7)	No	68951-67-7	1 - 5
Ethanol, 2-amino-, compds. with polyethylene glycol hydrogen sulfate C12-15-alkyl ethers (EO=2.5)/Ethanol, 2-amino-, compds. with polyethylene glycol	Ethanol, 2-amino-, compds. with polyethylene glycol hydrogen sulfate C12-15-alkyl ethers	No	162201-45-8	1 - 5

hydrogen sulfate C12-15-branched and linear alkyl ethers (.beta.-branching/EO=2.5)	(EO=2.5)/Ethanol, 2-amino-, compds. with polyethylene glycol hydrogen sulfate C12-15-branched and linear alkyl ethers (.beta.-branching/EO=2.5)			
Disodium tetraborate pentahydrate	Boron sodium oxide (B4Na2O7), pentahydrate	No	12179-04-3	1 - 5
Alcohol	Ethanol	No	64-17-5	1 - 5
Propylene glycol	Propylene Glycol	No	57-55-6	0.5 - 1.5
Protease	Total Protein (Subtilisin)	No	9014-01-1	0.1 - 1.0

Additional information Actual substance concentrations fall within the ranges stated. Maximum values do not necessarily represent the values present in the formula.

4. FIRST AID MEASURES

Description of first aid measures

Eye contact Rinse with plenty of water. Get medical attention immediately if irritation persists. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

Skin contact Rinse with plenty of water. Call a physician if irritation develops and persists.

Ingestion Rinse mouth. Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur. IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.

Inhalation Move to fresh air. If symptoms persist, call a physician.

Most important symptoms/effects, acute and delayed May cause eye irritation

Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Flammable properties Combustible liquid

Suitable extinguishing media In case of fire: Use water, CO2, dry chemical, or foam for extinction. Dry chemical. Alcohol resistant foam. Carbon dioxide (CO₂).

Unsuitable Extinguishing Media Do not use a solid water stream as it may scatter and spread fire.

Special Hazard combustible liquid. Fumes may catch fire.

Special protective equipment for fire-fighters As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Specific hazards arising from the chemical None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions	Use personal protective equipment as required. Do not get in eyes, on skin, or on clothing.
Advice for emergency responders	Use personal protective equipment as required.
Environmental precautions	Do not discharge product into natural waters without pre-treatment or adequate dilution

Methods and material for containment and cleaning up

Methods for containment	Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Prevent further leakage or spillage if safe to do so.
Methods for cleaning up	Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling	Keep away from open flames, hot surfaces and sources of ignition. Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.
--------------------------------	---

Conditions for safe storage, including any incompatibilities

Technical measures/Storage conditions	Keep away from open flames, hot surfaces and sources of ignition. Store away from other materials.
Storage Conditions	Store in a cool/low-temperature, well-ventilated, dry place away from heat and ignition sources. Keep containers tightly closed in a dry, cool and well-ventilated place.
Incompatible products	None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines	No exposure limits noted for ingredient(s).
----------------------------	---

No relevant exposure guidelines for other ingredients

Appropriate engineering controls

Engineering Measures	Distribution, Workplace and Household Settings: Ensure adequate ventilation Product Manufacturing Plant (needed at Product-Producing Plant ONLY): Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction Manufacturing Sites: Not relevant
-----------------------------	--

Personal Protective Equipment

Eye Protection	Distribution, Workplace and Household Settings: No special protective equipment required
-----------------------	--

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Use appropriate eye protection

Manufacturing Sites:

Wear safety glasses with side shields (or goggles)

No special protective equipment required

Hand Protection

Distribution, Workplace and Household Settings:

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Protective gloves

Skin and Body Protection

Distribution, Workplace and Household Settings:

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Wear suitable protective clothing

Respiratory Protection

Distribution, Workplace and Household Settings:

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

In case of inadequate ventilation wear respiratory protection

Hygiene Measures

Manufacturing Sites:

Wash hands thoroughly after handling

Distribution, Workplace and Household Settings:

Do not eat, drink or smoke when using this product

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state	Liquid
Appearance	blue viscous liquid
Odor	Perfumes
Odor threshold	No information available

<u>Property</u>	<u>Values</u>	<u>Remarks</u>
pH	8.3	
Melting point / freezing point	No information available	
Initial boiling point and boiling range	100 °C / 212 °F	
Flash point	78 °C / 172.4 °F	Closed cup. Product is an aqueous solution containing <=24% alcohol and >=50% water.
Evaporation rate	No information available	
Flammability	No information available	
Flammability Limit in Air		
Upper flammability or explosive limits	No information available	
Lower flammability or explosive limits	No information available	
Vapor pressure	No information available	
Relative vapor density	No information available	
Relative density	No information available	
Water solubility	No information available	
Partition coefficient	No information available	
Autoignition temperature	No information available	.
Decomposition temperature	No information available	.
Viscosity	No information available	

VOC Content (%) Products comply with US state and federal regulations for VOC content in consumer products.
VOC content .?%

10. STABILITY AND REACTIVITY

Reactivity None under normal use conditions.
Stability Stable under normal conditions.
Hazardous polymerization Hazardous polymerization does not occur.
Hazardous Reactions None under normal processing.
Conditions to Avoid Keep away from open flames, hot surfaces and sources of ignition.
Incompatible Materials None in particular.
Hazardous decomposition products None under normal use conditions.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Inhalation No known effect.
Skin contact No known effect.
Ingestion May be harmful if swallowed. Harmful if swallowed.
Eye contact Irritating to eyes. Avoid contact with eyes.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Acute toxicity May be harmful if swallowed.
Skin corrosion/irritation No known effect.
Serious eye damage/eye irritation Irritating to eyes.
Skin sensitization No known effect.
Respiratory sensitization No known effect.
Germ cell mutagenicity No known effect.
Reproductive toxicity No known effect.
Developmental toxicity No known effect.
STOT - single exposure No known effect.
STOT - repeated exposure No known effect.
Aspiration hazard No known effect.
Carcinogenicity No known effect.

Component Information

Chemical name	CAS No	Oral LD50	Dermal LD50	Inhalation LC50
Sodium Lauryl Sulfate	68585-47-7	> 2000 mg/kg (Rat)	-	-
Ethanol, 2-amino-, compds. with polyethylene glycol hydrogen sulfate C12-15-alkyl ethers (EO=2.5)/Ethanol, 2-amino-, compds. with polyethylene glycol hydrogen sulfate C12-15-branched and linear alkyl ethers (.beta.-branching/EO=2.5)	162201-45-8	> 5000 mg/kg (Rat)	-	-
Disodium tetraborate pentahydrate	12179-04-3	= 2403 mg/kg (Rat) = 2660 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	> 2 mg/m ³ (Rat) 4 h
Alcohol	64-17-5	10470 mg/kg bw (OECD 401)	-	116.9 - 133.8 mg/L air (OECD 403)
Propylene glycol	57-55-6	22000 mg/kg bw	> 2000 mg/kg bw	> 44.9 mg/L air

Protease	9014-01-1	1800 mg/kg bw (OECD 401)	-	-
----------	-----------	--------------------------	---	---

12. ECOLOGICAL INFORMATION

ecotoxicity

The product is not expected to be hazardous to the environment.

Persistence and degradability No information available.

Bioaccumulative potential No information available.

Mobility No information available.

Other adverse effects No information available.

13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from Residues/Unused Products Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Disposal should be in accordance with applicable regional, national and local laws and regulations.

California Hazardous Waste Codes (non-household setting) 331

14. TRANSPORT INFORMATION

DOT Not regulated

IMDG Not regulated

IATA Not regulated

15. REGULATORY INFORMATION

U.S. FEDERAL REGULATIONS

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of the Clean Air Act Amendments of 1990.

Clean Water Act

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

U.S. State Regulations (RTK)

Chemical name	CAS No	New Jersey
Alcohol	64-17-5	X
Propylene glycol	57-55-6	X

Chemical name	CAS No	Massachusetts
Disodium tetraborate pentahydrate	12179-04-3	X
Alcohol	64-17-5	X

Chemical name	CAS No	Pennsylvania
Alcohol	64-17-5	X
Propylene glycol	57-55-6	X

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

International Inventories

Precautionary Statements - Storage

Keep in a dry place

United States

All intentionally-added components of this product(s) are listed on the US TSCA Inventory

Canada

This product is in compliance with CEPA for import by P&G

Legend

United States Toxic Substances Control Act Section 8(b) Inventory (TSCA)

CEPA - Canadian Environmental Protection Act

16. OTHER INFORMATION

HMIS

NFPA

Issuing Date: 12-May-2022

Revision Date: 03-Oct-2022

Disclaimer.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet