

Aim for more



Superior quality that makes your work look even better


Navigator Premium Multipurpose 24lb is a superior quality paper, combining ultra brightness, opacity and an improved smooth surface. The result are sharp images with vibrant colors and excellent printing contrast.

Extra smooth surface

The microporous surface ensures faster ink drying and accurate absorption for high definition images.

24lb

8 1/2 x 11" | 11x17"



Multifunctional

Ideal for: reports, memos, color graphics, data tables and more



OPTIMAL COLOR
CONTRAST



FAST
DRYING



ACCURATE
ABSORPTION



NEWSLETTERS



MAILINGS

Designed for duplex printing

Designed with extra opacity, Navigator is perfect for double-sided and intense usage of color without show through.

Navigator paper can be used for all your documents, guaranteeing great output with any office equipment.



Premium-quality fiber

By using the best quality fiber – *Eucalyptus globulus*– Navigator guarantees optimum paper characteristics for all printing purposes. This means using a bulkier sheet, with fewer jams and better toner absorption. It's a thicker, whiter and more opaque paper, ensuring you get the best printing results.

Environment

Our commitment is to the highest environmental standards and continuous improvement in our forest management practices. Our responsible forest stewardship ensures the renewable supply of *Eucalyptus globulus* fiber and the preservation of biodiversity.

EXTRA SMOOTH, WITH MICROPOROUS SURFACE FOR FAST INK DRYING AND ACCURATE ABSORPTION, RESULTING IN HIGH DEFINITION IMAGES.



For best results use the following settings in your printer setup:
1 Select "Plain" paper type. | 2 Select "Better" printing quality. | 3 Adjust color saturation and tone for enhanced images. See your Printer Manual for further instructions.

Consistent quality:
Excellent results every day

99.99%
PAPER JAM FREE

Bs.Wgt.	Size	Item #	Brightness	Ctns/Pallet	Thickness μm	Caliper	Opacity	M-Wgt	Sheets/Ctn
24lb.	8 1/2 x 11	NMP1124	97	40	113	4.45	95	12	5,000
24lb.	11 x 17	NMP1724	97	70	113	4.45	95	24	2,500

24lb

For support information | www.navigator-usa.com



The mark of responsible forestry



EU Ecolabel: PT/011/002