

SAFETY DATA SHEET



Issuing Date: 10-May-2016

Revision Date: 10-May-2016

Version 1

1. IDENTIFICATION

Product Name Febreze Fabric Refresher Extra Strength

Product Identifier 90969771_RET_NG

Product Type: Finished Product - Consumer (Retail) Use Only

Recommended Use Fabric Refresher.

Manufacturer PROCTER & GAMBLE - Fabric and Home Care Division
Ivorydale Technical Centre
5289 Spring Grove Avenue
Cincinnati, Ohio 45217-1087 USA

Procter & Gamble Inc.
P.O. Box 355, Station A
Toronto, ON M5W 1C5
1-800-331-3774

E-mail Address pgsds.im@pg.com

Emergency Telephone Transportation (24 HR)
CHEMTREC - 1-800-424-9300
(U.S./ Canada) or 1-703-527-3887
Mexico toll free in country: 800-681-9531

2. HAZARD IDENTIFICATION

"Consumer Products", as defined by the US Consumer Product Safety Act and which are used as intended (typical consumer duration and frequency), are exempt from the OSHA Hazard Communication Standard (29 CFR 1910.1200). This SDS is being provided as a courtesy to help assist in the safe handling and proper use of the product.

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:.

Not Classified.

Hazard Statements None

Hazard pictograms None

Precautionary Statements None

Precautionary Statements - Response None

Precautionary Statements - Storage None

Precautionary Statements - Disposal None

Hazards not otherwise classified (HNOC) None

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Chemical Name	Synonyms	Trade Secret	CAS-No	Weight %
Ethanol	Ethanol	No	64-17-5	1 - 5

4. FIRST AID MEASURES

First aid measures for different exposure routes

Eye contact Rinse with plenty of water. Get medical attention immediately if irritation persists.

Skin contact Rinse with plenty of water. Get medical attention if irritation develops and persists.

Ingestion Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur.

Inhalation Move to fresh air. If symptoms persist, call a physician.

Most important symptoms/effects, acute and delayed None under normal use conditions.

Indication of immediate medical attention and special treatment needed, if necessary

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media Dry chemical, CO₂, alcohol-resistant foam or water spray. Dry chemical. Alcohol-resistant foam.

Unsuitable Extinguishing Media None.

Special hazard None known.

Special protective equipment for fire-fighters As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Specific hazards arising from the chemical None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Use personal protective equipment. Do not get in eyes, on skin, or on clothing.

Advice for emergency responders Use personal protective equipment as required.

Environmental precautions Keep out of waterways
Do not discharge product into natural waters without pre-treatment or adequate dilution

Methods and materials for containment and cleaning up

Methods for containment Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Prevent product from entering drains. Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible products None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	CAS-No	ACGIH TLV	OSHA PEL	Mexico PEL
Ethanol	64-17-5	STEL: 1000 ppm	TWA: 1000 ppm TWA: 1900 mg/m ³ (vacated) TWA: 1000 ppm (vacated) TWA: 1900 mg/m ³	Mexico: TWA 1000 ppm Mexico: TWA 1900 mg/m ³

Chemical Name	CAS-No	Alberta	Quebec	Ontario TWAEV	British Columbia
Ethanol	64-17-5	TWA: 1000 ppm TWA: 1880 mg/m ³	TWA: 1000 ppm TWA: 1880 mg/m ³	STEL: 1000 ppm	STEL: 1000 ppm

No relevant exposure guidelines for other ingredients

Exposure controls

Engineering Measures **Distribution, Workplace and Household Settings:**
Ensure adequate ventilation

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

Personal Protective Equipment

Eye Protection **Distribution, Workplace and Household Settings:**
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Use appropriate eye protection

Hand Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Protective gloves

Skin and Body Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Wear suitable protective clothing

Respiratory Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
In case of inadequate ventilation wear respiratory protection

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State @20°C

Liquid

Appearance

Clear colorless to Yellow

Odor

Perfume

Odor threshold

No information available

Property

Values

Note

pH value

5.5

Melting/freezing point

No information available

Boiling point/boiling range

95 - 100 °C / 203 - 212 °F

Flash point

No Flash to Boiling (NFTB)

Evaporation rate

0.56 - 0.72

Flammability (solid, gas)

No information available

Flammability Limits in Air

Upper flammability limit

No information available

Lower Flammability Limit

No information available

Vapor pressure

No information available

Vapor density

No information available

Relative density

0.97 - 1.03

Water solubility

No information available

Partition coefficient: n-octanol/water No information available

Autoignition temperature

No information available

Decomposition temperature

No information available

Viscosity of Product

0.1 - 10 mPa-s

VOC Content (%)

Products comply with US state and federal regulations for VOC content in consumer products.

10. STABILITY AND REACTIVITY

Reactivity

None under normal use conditions.

Stability

Stable under normal conditions.

Hazardous polymerization

Hazardous polymerization does not occur.

Hazardous Reactions

None under normal processing.

Conditions to Avoid

None under normal processing.

Materials to avoid

None in particular.

Hazardous Decomposition Products None under normal use conditions.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Inhalation	No known effect.
Skin contact	No known effect.
Ingestion	No known effect.
Eye contact	No known effect.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Acute toxicity	No known effect.
Skin corrosion/irritation	No known effect.
Serious eye damage/eye irritation	No known effect.
Skin sensitization	No known effect.
Respiratory sensitization	No known effect.
Germ cell mutagenicity	No known effect.
Neurological Effects	No known effect.
Reproductive toxicity	No known effect.
Developmental toxicity	No known effect.
Teratogenicity	No known effect.
STOT - single exposure	No known effect.
STOT - repeated exposure	No known effect.
Target Organ Effects	No known effect.
Aspiration hazard	No known effect.
Carcinogenicity	No known effect.

12. ECOLOGICAL INFORMATION

Ecotoxicity

The product is not expected to be hazardous to the environment.

Persistence and degradability	No information available.
Bioaccumulative potential	No information available.
Mobility	No information available.
Other adverse effects	No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment

Waste from Residues / Unused Products	Disposal should be in accordance with applicable regional, national and local laws and regulations.
Contaminated packaging	Disposal should be in accordance with applicable regional, national and local laws and regulations.
California Hazardous Waste Codes (non-household setting)	331

14. TRANSPORT INFORMATION

DOT Not regulated**IMDG** Not regulated**IATA** Not regulated

15. REGULATORY INFORMATION

U.S. Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302):.

Chemical Name	CAS-No	Hazardous Substances RQs	Extremely Hazardous Substances RQs	CERCLA/SARA 302 TPQ
Maleic acid	110-16-7	5000 lb	-	
Sodium hydroxide	1310-73-2	1000 lb	-	

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of the Clean Air Act Amendments of 1990.

Clean Water Act

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42):.

Chemical Name	CAS-No	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Maleic acid	110-16-7	5000 lb	-	-	X
Sodium hydroxide	1310-73-2	1000 lb	-	-	X

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

U.S. State Regulations (RTK)

Chemical Name	CAS-No	New Jersey
Ethanol	64-17-5	X

Chemical Name	CAS-No	Massachusetts
Ethanol	64-17-5	X

Chemical Name	CAS-No	Pennsylvania
Ethanol	64-17-5	X
2,2'-Oxybisethanol	111-46-6	X
Dipropylene Glycol	25265-71-8	X
Maleic acid	110-16-7	X
Ethanol	64-17-5	X

International Inventories

United States

All intentionally-added components of this product(s) are listed on the US TSCA Inventory.

Canada

This product is in compliance with CEPA for import by P&G.

Legend

United States Toxic Substances Control Act Section 8(b) Inventory (TSCA)

CEPA - Canadian Environmental Protection Act

16. OTHER INFORMATION

Issuing Date: 10-May-2016

Revision Date: 10-May-2016

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS