SAFETY DATA SHEET

Revision date: November 14, 2016



SECTION 1 : IDENTIFICATION

Black Stamp-Ever stamp

Product Identifier:

Various

Product Code(s):This product is intended for use in the manufacturing of pre-inked handstamps for the

Product Use: purpose of marking / printing on porous substrates such as paper or paper board.

Mixture

Chemical Family: Identity Group

Manufacturer's name and address: 1480 Gould Drive

Cookeville, TN, USA 35806

931-432-4000 (Monday – Friday 8:00 am – 5:00 pm Central Standard Time)

Information Telephone #:

Chemtrec 1-800-424-9300 (Within Continental U.S.)

24 Hr. Emergency Telephone #: Chemtrec 1-703-527-3887 (Outside U.S.)

SECTION 2: HAZARDS IDENTIFICATION

Classification: Acute toxicity, Oral Category 4
Serious eye damage Category 1

Serious eye damage/eye irritation Category 2A

Acute aquatic toxicity Category 1

Chronic aquatic toxicity Category 1

Reproductive toxicity Category 1B

Skin irritation Category 2

Germ cell mutagenicity Category 2

Specific target organ toxicity – Repeated exposure Category 2

Labeling: Symbols:









Signal Word: Danger

Hazard statements:	H302	Harmful if swallowed
	H315	Causes skin irritation
	H318	Causes serious eye damage
	H319	Causes serious eye irritation
	H341	Suspected of causing genetic defects
	H360	May damage fertility or the unborn child
	H373	May cause damage to organs through prolonged
		or repeated exposure
	H410	Very toxic to aquatic life with long lasting effects

Precautionary statements: P264 Wash skin thoroughly after handling.

P273 Avoid release to the environment.

P281 Wear personal protective equipment as required.
P301 + P312 IF SWALLOWED: Call a POISON
CENTER or doctor/physician if you feel

unwell.

P305+351+338 IF IN EYES: Rinse continuously with water

for several minutes. Remove contact lenses if present and easy to do – continue rinsing.

P314 Get medical advice/attention if you feel unwell.

P330 Rinse mouth

SECTION 3: COMPOSITION / INFORMATION ON INGREDIENTS

Ingredients	CAS#	Wt. %
Tricresyl Phosphate	1330-78-5	5 – 10
Di(propylene glycol) dibenzoate	27138-31-4	5 - 10
Cocamide DEA	68603-42-9	5 - 10
Diethanolamine	111-42-2	2 - 3
Benzyl benzoate	120-51-4	2 - 3
C.I. Basic Orange 2	532-82-1	0.1 - 0.5
Bis(2-Ethylhexyl) phthalate	117-81-7	< 0.2

SECTION 4: FIRST AID MEASURES

Inhalation:

Ingestion:

Immediately remove person to fresh air. If breathing has stopped, give artificial respiration. If breathing is

difficult, give oxygen by qualified medical personnel only. Seek immediate medical attention/advice. **Skin contact:**

Immediately flush with plenty of water, while removing contaminated clothing. Wash contaminated

clothing before reuse. When symptoms persist or in all cases of doubt, seek medical advice. **Eye contact:**

Flush eyes with low pressure water for at least 15 minutes while holding eyelids open. When symptoms

persist or in all cases of doubt, seek medical advice.

Seek immediate medical attention/advice. Do NOT induce vomiting. Never give anything by mouth to an

unconscious person. If vomiting occurs spontaneously, keep victim's head lowered (forward) to reduce the

risk of aspiration. Notes for physician:

Treat symptomatically.

SECTION 5: FIRE FIGHTING MEASURES

Suitable extinguishing media: Dry chemical, foam, carbon dioxide and water fog

Fire hazards/conditions of flammability: This material is not flammable.

Explosion data: Sensitivity to mechanical impact / static discharge: Not expected to be sensitive to mechanical impact or static

discharge.

.Special fire-fighting procedures/equipment:

Firefighters should wear protective equipment and self-contained breathing apparatus with full face piece operated in positive pressure mode. Move containers from fire area if safe to do so. Water spray may be useful in cooling equipment exposed to heat and flame.

Hazardous combustion products: Oxides of carbon and nitrogen, irritating fumes and smoke.

Health: 2 **NFPA Rating:** Flammability: 1 Instability: 0 Special Hazards: 0

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal precautions: All persons dealing with clean-up should wear the appropriate protective equipment. Do

not eat, drink or smoke while participating in clean up.

Environmental precautions: Ensure spilled product does not enter drains, sewers, waterways or confined spaces. For

large spills, dike the area to prevent spreading of appropriate.

Spill response/cleanup: Contain and absorb spilled liquid with non-combustible, inert absorbent material (e.g.

sand), then place absorbent material into a container for later disposal (see Section 13).

Notify the appropriate authorities as required.

Prohibited materials: None specific

Special spill response procedures: In case of a transportation accident, in the United States contact CHEMTREC at 1-800424-

9300 or International at 1-703-527-3887.

SECTION 7: HANDLING AND STORAGE

Precautions for safe handling:

Do not ingest. Avoid contact with skin, eyes and clothing. Wash thoroughly after

handling.

Conditions for safe storage:Store in a cool, dry, well-ventilated area. Store away from incompatibles, temperature

extremes and out of direct sunlight.

Incompatible materials: Strong oxidizing agents; strong reducing agents; acids

Special packaging materials: Always keep in original packaging.

SECTION 8: EXPOSURE CONTROLS AND PERSONAL PROTECTION

Components with workplace control parameters

Component	CAS No.	Value	Control Parameters	Source
Diethanolamine	111-42-4	TWA	3 ppm 15 mg/m3	USA OSHA Table Z-1 Limits for Air Contaminants – 1910.1000
		TWA	1 mg/m3	USA ACGIH Threshold Limit Values (TLV)
		TWA	3 ppm 15 mg/m3	USA NIOSH Recommended Exposure Limits
			Remarks	Liver and kidney damage Confirmed animal carcinogen with unknown relevance to humans Danger of cutaneous absorption

Component	CAS No.	Value	Control Parameters	Source
bis(2-Ethylhexyl) phthalate	117-81-7	TWA	5 mg/m3	USA ACGIH Threshold Limit Values (TLV)
			Remarks	Lower respiratory tract irritation Confirmed animal carcinogen with unknown relevance to humans
		TWA	5 mg/m3	USA NIOSH Recommended Exposure Limits
			Remarks	Potential Occupational Carcinogen See Appendix A
		ST	10 mg/m3	USA NIOSH Recommended Exposure Limits
			Remarks	Potential Occupational Carcinogen See Appendix A
		TWA	5 mg/m3	USA OSHA Table Z-1 Limits for Air Contaminants – 1910.1000
		STEL	10 mg/m3	USA OSHA Table Z-1 Limits for Air Contaminants – 1910.1000

Ventilation and engineering measures: Use general or local exhaust ventilation to maintain air concentrations below

recommended exposure limits if appropriate.

Respiratory protection: If the TLV is exceeded, a NIOSH/MSHA-approved respirator is advised. Confirmation of

which type of respirator is most suitable for the intended application should be obtained

from respiratory protection suppliers.

Skin protection: Impervious gloves must be worn when using this product if direct contact with skin is

unavoidable. Advice should be sought from glove suppliers.

Eye / face protection: Good industrial hygiene practices should be used when handling this product including

preventing eye contact and minimizing skin contact and inhalation.

Other protective equipment: As needed to prevent eye contact and minimizing skin contact and inhalation.

General hygiene considerations: Avoid breathing vapor or mist. Avoid contact with skin, eyes and clothing. Do not eat,

drink, smoke or use cosmetics while working with this product. If direct contact occurs, wash hands before eating, drinking, smoking or use of toilet facilities. Remove and wash

contaminated clothing before re-use.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Physical state: Solid

Appearance: Black flexible gel saturated with ink

Odor: Mild to negligible

Odor Threshold: N/Av Specific Gravity: 0.9

pH: Not applicable
Boiling point: >300 °F
Melting/Freezing point: Not available
Coefficient of water/oil distribution: Not available
Vapor pressure (mm Hg @ 20°C / 68°F): Not available
Vapor density (Air = 1): Heavier than air

Evaporation rate (n-Butyl acetate = 1): Slower than n-Butyl acetate

Solubility in water:NegligibleFlash Point>200 °F, TCCAuto-ignition temperatureNot applicableLower flammable limit (% by vol)Not applicableUpper flammable limit (% by vol)Not applicableFlame Projection LengthNot availableFlashback observedNot available

SECTION 10: STABILITY AND REACTIVITY

Chemical stability: Stable under the recommended storage and handling conditions prescribed.

Possibility of hazardous reactions: None are known.

Conditions to avoid: Avoid heat and open flame.

Materials to avoid and incompatibility: See Section 7 (Handling and Storage) for further details.

Hazardous decomposition products: None known; refer to hazardous combustion products in Section 5.

SECTION 11: TOXICOLOGICAL INFORMATION

Target organs: Eyes, skin

Routes of exposure: Inhalation: Not likely with intended use

Skin absorption: Not likely with intended use Skin & Eyes: Not likely with intended use Ingestion: Not likely with intended use

Toxicological data: There is no available data for the mixture itself, only for the ingredients. See below

for individual ingredient acute toxicity data.

		LD50					
Ingredient	Inhalation, rat	Oral, rat Rabbit, dermal		Intraperitoneal, rat	Intravenous, rat		
				120 mg/kg	778 mg/kg		
Tricresyl Phosphate	No data available	3,000 mg/kg	No data available				
Diethanolamine	No data available	710 mg/kg	12,200 mg/kg				
Diisononyl phthalate	> 4.4 mg/l	>10,000 mg/kg	>3,160 mg/kg				
Benzyl benzoate		1,680 mg/kg rabbit	4,000 mg/kg				
Di(propylene glycol) dibenzoate	>200 mg/l	3,914 mg/kg	>2,000 mg/kg rat				

Tricresyl phosphate: Eye damage/eye irritation: Eyes – rabbit –Mild eye irritation – 24 hours

Diethanolamine Skin corrosion/irritation: Skin – rabbit – Mild skin irritation – 24 hours

Eye damage/eye irritation: Eyes – rabbit – Severe eye irritation – 24 hours

Carcinogenic status

Carcinogenicity: Carcinogenicity – Mouse – Oral (4-phenylazophenylene-1, 3-diamine monohydrochloride)

IARC: 2B – Group 2B: Possibly carcinogenic to humans (bis(2-Ethylhexyl) phthalate)

3 - Group 3: Not classifiable as to its carcinogenicity to humans (4-phenylazophenylene-1,3-diamine

monohydrochloride)

NTP: Reasonably anticipated to be a human carcinogen (bis(2-Ethylhexyl) phthalate)

OSHA: No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential

carcinogen by OSHA.

Reproductive effects: This substance has not been evaluated as a mixture.

Teratogenicity: This substance has not been evaluated as a mixture.

Germ Cell Mutagenicity: In vitro tests showed mutagenic effects

Hisitidine reversion (Ames)

(4-phenylazophenylene-1,3-diamine monohydrochloride)

This substance has not been evaluated as a mixture.

Epidemiology: This substance has not been evaluated as a mixture.

Conditions aggravated by overexposure: This substance has not been evaluated as a mixture.

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity: No data is available on the mixture itself.

Tricresyl phosphate:	Acute toxicity to fish: Toxicity to aquatic invertebrates: Acute algae toxicity:	LC ₅₀ EC ₅₀ EC ₅₀	Rainbow trout Daphnia magna Scenedesmus pannonicus Growth inhibition	0.26 mg/l 2.3 mg/l 1.3 mg/l	96 hr 48 hr 96 hr
Diethanolamine	Toxicity to fish: Toxicity to aquatic invertebrates:	LC ₅₀ EC ₅₀	Pimephales promelas Daphnia magna	1,460 mg/l 55 mg/l	96 hr 48 hr
Diisononyl phthalate:	Toxicity to fish: semi-static test Toxicity to aquatic invertebrates: Toxicity to algae: static test	$\begin{array}{c} LC_{50} \\ EC_{50} \\ EC_{50} \end{array}$	Danio rerio Daphnia magna Desmodesmus subspicatus	> 102 mg/l > 74 mg/l >88 mg/l	96 hr 48 hr 72 hr
Di(propylene glycol) dibenzoate:	Toxicity to fish: Toxicity to aquatic invertebrates: Toxicity to algae: static test	LC ₅₀ EC ₅₀ EC ₅₀	Pimephales promelas Daphnia magna Selenastrum capricornutum 3	3.7 mg/l 19.3 mg/l 3.6 mg/l	96 hr 48 hr 72 hr
	Toxicity to bacteria:	EC_{50}	Sludge treatment	>100 mg/l	3 hr

Mobility: Diisononyl phthalate: Adsorbs on soil

No data is available on the mixture itself.

Persistence: Diisononyl phthalate: aerobic – Exposure time 28 days - 81% Readily biodegradable

No data is available on the mixture itself.

Bioaccumulation potential: No data is available on the mixture itself.

Tricresyl Phosphate Pimephales promelas (fathead minnow) – 32 d

Bioconcentration Factor (BCF): 165

Diisononyl phthalate Oncorhynchus mykiss (rainbow trout)

Bioconcentration Factor (BCF): <3 Bioaccumulations is unlikely

Other adverse environmental effects: The ecological characteristics of this mixture have not been fully investigated.

No data is available on the mixture itself, but it is expected to be very toxic to aquatic life.

SECTION 13: DISPOSAL CONSIDERATIONS

Methods of disposal:

Dispose of in accordance with federal, provincial and local hazardous waste regulations.

SECTION 14: TRANSPORT INFORMATION

This material is not UN / IATA regulated.

This material is not classified as ICAO/IATA-DGR Dangerous Goods.

This material is not classified as hazardous per the IMDG Code.

This material is not classified as hazardous per ADR.

This material is not classified as hazardous per the U.S. Department of Transportation (DOT).

SECTION 15: REGULATORY INFORMATION

Inventory Status: All listed ingredients appear on the Toxic Substances Control Act (TSCA) Inventory, EINECS/ELINCS,

AICS, and DSL.

This material is classified as hazardous under OSHA regulations (29CFR 19410.1200). See Section 2.

SARA TITLE III: Sec. 302, Extremely Hazardous Substances, 40 CFR 355:

No Extremely Hazardous Substances are present in this mixture.

SARA TITLE III: 311/312 Acute Health Hazard, Chronic Health Hazard

SARA TITLE III: 313 Diethanolamine CAS 111-42-2 Bis(2-

Ethylhexyl) phthalate CAS 117-81-7

CERCLA: No chemicals in this mixture with known CAS numbers are subject to the reporting requirements of

CERCLA.

RCRA CODE: None

Hazardous Air Pollutants (HAPS): Diethanolamine

bis(2-Ethylhexyl) phthalate

US State "Right to Know" Laws:

California Proposition 65: Vinyl chloride <0.001%

 $bis (2-Ethylhexyl)\ phthalate < 0.2\%$

Other US State "Right To Know" Lists:

The following chemicals are specifically listed by individual states: Tricresyl phosphate (PA, NJ)

Diethanolamine (MA, PA, NJ)

Diisononyl phthalate (NJ, PA)

phenylazophenylene-1,3-diamine Monohydrochloride

bis(2-Ethylhexyl) phthalate (MA, PA, NJ) 4-

(PA, NJ) Benzyl benzoate (PA, NJ)

Di(propylene glycol) dibenzoate (PA, NJ)

International Information:

Canadian Environmental Protection Act (CEPA) information: All ingredients listed appear on the Domestic Substances List (DSL).

This product is a WHMIS Controlled Product. It meets one or more of the criteria for a controlled product provided in Part IV of the Canadian Controlled Products Regulations (CPR). See Section 2.

This product has been classified according to the hazard criteria of the CPR and the MSDS contains all of the information required by the CPR.

bis(2-Ethylhexyl) phthalate is included in the Candidate List of Substances of Very High Concern (SVHC) according to Regulations (EC) No. 1907/2006 (REACH).

SECTION 16: OTHER INFORMATION

HMIS Rating: Health: * 2 Flammability: 0 Reactivity:

> * Chronic hazard 0-Minimal 1-Slight 2- Moderate 3- Serious 4- Severe

Legend: **ACGIH** American Conference of Governmental Industrial Hygienists

> **CAS** Chemical Abstract Services

Comprehensive Environmental Response, Compensation, and Liability Act of 1980 **CERCLA**

CFR Code of Federal Regulations DOT Department of Transportation **EPA Environmental Protection Agency HMIS**

Hazardous Material Identifications System

HSDB Hazardous Substances Data Bank

IARC International Agency for Research on Cancer

Inh Inhalation

MSHA Mine Safety and Health Administration **NFPA** National Fire Protection Association

NIOSH National Institute of Occupational Safety and Health

NTP National Toxicology Program

OSHA Occupational Safety and Health Administration

PEL Permissible exposure limit

RCRA Resource Conservation and Recovery Act

RTECS Registry and Toxic Effects of Chemical Substances Superfund Amendments and Reauthorization Act SARA

STEL Short Term Exposure Limit

TDG Canadian Transportation of Dangerous Goods Act and Regulations

TLV Threshold Limit Values Threshold Planning Quantity TPO Toxic Substances Control Act **TSCA TWA** Time Weighted Average

WHMIS Workplace Hazardous Materials Identification System

References:

- 1. ACGIH, Threshold Limit Values and Biological Exposure Indices
- 2. International Agency for Research on Cancer Monographs
- 3. Canadian Centre for Occupational Health and Safety, CCInfoWeb databases (Chempendium, HSDB and RTECs)
- 4. Material Safety Data Sheets for manufacturers
- 5. US EPA Title III List of Lists
- 6. California Proposition 65 List

Page 9 of 9

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.