

SAFETY DATA SHEET



Issuing Date: 20-Apr-2015

Revision Date: 20-Apr-2015

Version 1

1. IDENTIFICATION

Product Name Tide Mt Spring

Product ID: 96733930_RET_NG

Product Type: Finished Product - Consumer (Retail) Use Only

Recommended Use Laundry Care

Restrictions on Use Use only as directed on label.

Manufacturer PROCTER & GAMBLE - Fabric and Home Care Division
Ivorydale Technical Centre
5289 Spring Grove Avenue
Cincinnati, Ohio 45217-1087 USA

Procter & Gamble Inc.
P.O. Box 355, Station A
Toronto, ON M5W 1C5
1-800-331-3774

E-mail Address pgsds.im@pg.com

Emergency Telephone Transportation (24 HR)
CHEMTREC - 1-800-424-9300
(U.S./ Canada) or 1-703-527-3887
Mexico toll free in country: 800-681-9531

2. HAZARD IDENTIFICATION

"Consumer Products", as defined by the US Consumer Product Safety Act and which are used as intended (typical consumer duration and frequency), are exempt from the OSHA Hazard Communication Standard (29 CFR 1910.1200). This SDS is being provided as a courtesy to help assist in the safe handling and proper use of the product.

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:

Hazard Category

Skin corrosion/irritation Category 2
Eye Damage / Irritation Category 2A

Signal Word WARNING

Hazard Statements Causes serious eye irritation
Causes skin irritation

Hazard pictograms

**Precautionary Statements - Prevention**

Wash hands thoroughly after handling

Precautionary Statements - Response

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

If eye irritation persists: Get medical advice/attention

IF SWALLOWED:

Drink 1 or 2 glasses of water

IF ON SKIN:

Rinse with plenty of water

If skin irritation occurs, get medical advice/attention

Precautionary Statements - Storage

None

Precautionary Statements - Disposal

None

Hazards not otherwise classified (HNOC)

None

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Chemical Name	Synonyms	Trade Secret	CAS-No	Weight %
Sodium carbonate	-	No	497-19-8	30 - 35
Silicic acid, aluminum sodium salt	-	No	1344-00-9	15 - 20
Benzenesulfonic acid, mono-C10-16-alkyl derivs., sodium salts	-	No	68081-81-2	5 - 10
Carbonic acid disodium salt, compd. with hydrogen peroxide	-	No	15630-89-4	5 - 10
Silicic acid, sodium salt	-	No	1344-09-8	1 - 5
Sulfuric acid, mono-C14-18-alkyl esters, sodium salts	-	No	68081-98-1	1 - 5
Sodium 2-(nonanoyloxy)benzenesulfonate	-	No	91125-43-8	1 - 5
Heptadecanol, hydrogen sulfate, branched, sodium salt	-	No	343978-15-4	1 - 5
Poly(oxy-1,2-ethanediyl), alpha-sulfo-omega-hydroxy-, C10-16-alkyl ethers, sodium salts	-	No	68585-34-2	1 - 5
Hexadecanol, hydrogen sulfate, branched, sodium salt	-	No	343978-24-5	1 - 5
Glycine, N,N-bis[2-[bis(carboxymethyl)amino]ethyl]-, sodium salt (1:5)	-	No	140-01-2	0.1 - 1.0

4. FIRST AID MEASURES

First aid measures for different exposure routes

Eye contact	Rinse with plenty of water. Get medical attention immediately if irritation persists.
Skin contact	Rinse with plenty of water. Get medical attention if irritation develops and persists.
Ingestion	Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur.
Inhalation	Move to fresh air. If symptoms persist, call a physician.
Most important symptoms/effects, acute and delayed	None under normal use conditions.

Indication of immediate medical attention and special treatment needed, if necessary

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media	Dry chemical, CO ₂ , alcohol-resistant foam or water spray.
Unsuitable Extinguishing Media	None.
Special hazard	None known.
Special protective equipment for fire-fighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
Specific hazards arising from the chemical	None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions	Use personal protective equipment. Do not get in eyes, on skin, or on clothing.
Advice for emergency responders	Use personal protective equipment as required.

Methods and materials for containment and cleaning up

Methods for containment	Prevent dust cloud. Prevent further leakage or spillage if safe to do so.
Methods for cleaning up	Sweep up and shovel into suitable containers for disposal. Dispose of in accordance with local regulations.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.

Conditions for safe storage, including any incompatibilities

Storage Conditions	Keep containers tightly closed in a dry, cool and well-ventilated place.
Incompatible products	None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	CAS-No	ACGIH TLV	OSHA PEL	Mexico PEL
Silicic acid, aluminum sodium salt	1344-00-9	TWA: 1 mg/m ³ respirable fraction		

Chemical Name	CAS-No	Alberta	Quebec	Ontario TWAEV	British Columbia
Silicic acid, aluminum sodium salt	1344-00-9			TWA: 1 mg/m ³	TWA: 1.0 mg/m ³

No relevant exposure guidelines for other ingredients

Exposure controls

Engineering Measures

Distribution, Workplace and Household Settings:
Ensure adequate ventilation

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

Personal Protective Equipment

Eye Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Use appropriate eye protection

Hand Protection

Distribution, Workplace and Household Settings:
For sensitive skin or prolonged use, wear gloves

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Protective gloves

Skin and Body Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Wear suitable protective clothing

Respiratory Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
In case of insufficient ventilation wear suitable respiratory equipment

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State @20°C	solid
Appearance	white powder
Odor	Scented
Odor threshold	No information available

<u>Property</u>	<u>Values</u>	<u>Note</u>
pH value	10 - 11.5	
Melting/freezing point	No information available	
Boiling point/boiling range	No information available	
Flash point	No information available	
Evaporation rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limits in Air		
Upper flammability limit	No information available	
Lower Flammability Limit	No information available	
Vapor pressure	No information available	
Vapor density	No information available	
Relative density	420 -650 g/L	
Water solubility	Moderately soluble	@ 20 °C
Solubility in other solvents	No information available	
Partition coefficient: n-octanol/water	No information available	
Autoignition temperature	No information available	.
Decomposition temperature	No information available	.
Viscosity of Product	No information available	
VOC Content (%)	Products comply with US state and federal regulations for VOC content in consumer products.	

10. STABILITY AND REACTIVITY

Reactivity	None under normal use conditions.
Stability	Stable under normal conditions.
Hazardous polymerization	Hazardous polymerization does not occur.
Hazardous Reactions	None under normal processing.
Conditions to Avoid	None under normal processing.
Materials to avoid	None in particular.
Hazardous Decomposition Products	None under normal use.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Inhalation	No known effect.
Skin contact	Irritating to skin.
Ingestion	No known effect.
Eye contact	Causes serious eye irritation.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Acute toxicity	No known effect.
Skin corrosion/irritation	Irritating to skin.
Serious eye damage/eye irritation	Causes serious eye irritation.
Skin sensitization	No known effect.
Respiratory sensitization	No known effect.
Germ cell mutagenicity	No known effect.
Neurological Effects	No known effect.
Reproductive toxicity	No known effect.
Developmental toxicity	No known effect.
Teratogenicity	No known effect.
STOT - single exposure	No known effect.
STOT - repeated exposure	No known effect.

Target Organ Effects No known effect.
Aspiration hazard No known effect.
Carcinogenicity No known effect.

Component Information

Chemical Name	CAS-No	LD50 Oral	LD50 Dermal	LC50 Inhalation
Sodium carbonate	497-19-8	2800 mg/kg bw	> 2000 mg/kg bw (US EPA 16 CFR 1500.40)	-
Silicic acid, aluminum sodium salt	1344-00-9	> 10000 mg/kg bw (//OECD 401)	> 5000 mg/kg bw (//OECD 402)	> 2.08 mg/L air (//OECD 403)
Benzenesulfonic acid, mono-C10-16-alkyl derivs., sodium salts	68081-81-2	1090.00 mg/kg (rat)	-	-
Carbonic acid disodium salt, compd. with hydrogen peroxide	15630-89-4	893 mg/kg bw (U.S. EPA Office of Pesticides and Toxic Substances (1984) "Acute Exposure Oral Toxicity"; standard acute method; rat)	> 2000 mg/kg bw (EPA Guideline; standard acute method; rabbit)	-
Silicic acid, sodium salt	1344-09-8	3400 mg/kg bw (Similar to OECD 401; standard acute method; rat)	> 5000 mg/kg bw (Read across data on AgSil TM 25 Potassium silicate solution; rat)	> 2.06 mg/L air (Read across data AgSil TM 25 Potassium silicate solution; EPA OPPTS 870.1300; standard acute method; rat)
Sodium 2-(nonanoyloxy)benzenesulfonate	91125-43-8	6030.00 mg/kg (rat)	-	-
Poly(oxy-1,2-ethanediyl), alpha-sulfo-omega-hydroxy-, C10-16-alkyl ethers, sodium salts	68585-34-2	>2001 mg/kg	-	-
Glycine, N,N-bis[2-[bis(carboxymethyl)amino]ethyl]-, sodium salt (1:5)	140-01-2	> 5000 mg/kg bw (Read across data (test substance name not indicated); OECD 401; standard acute method; rat)	> 2000 mg/kg bw (OECD 402 and EU Method B.3; standard acute method; rat)	-

12. ECOLOGICAL INFORMATION**Ecotoxicity**

The product is not expected to be hazardous to the environment.

Persistence and degradability No information available.

Bioaccumulative potential No information available.

Mobility No information available.

Other adverse effects No information available.

13. DISPOSAL CONSIDERATIONS**Waste treatment**

Waste from Residues / Unused Products Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Disposal should be in accordance with applicable regional, national and local laws and regulations.

California Hazardous Waste Codes (non-household setting) 331

14. TRANSPORT INFORMATION

DOT Not regulated

IMDG Not regulated

IATA Not regulated

15. REGULATORY INFORMATION

U.S. Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302):

Chemical Name	CAS-No	Hazardous Substances RQs	Extremely Hazardous Substances RQs	CERCLA/SARA 302 TPQ
Sodium hydroxide	1310-73-2	1000 lb	-	

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of the Clean Air Act Amendments of 1990.

Clean Water Act

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42):

Chemical Name	CAS-No	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Sodium hydroxide	1310-73-2	1000 lb	-	-	X

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

U.S. State Regulations (RTK)

Chemical Name	CAS-No	Massachusetts
Sulfuric acid sodium salt (1:2)	7757-82-6	X

Chemical Name	CAS-No	Pennsylvania
Sulfuric acid sodium salt (1:2)	7757-82-6	X
Sodium hydroxide	1310-73-2	X

International Inventories

United States

All intentionally-added components of this product(s) are listed on the US TSCA Inventory.

Canada

This product is in compliance with CEPA for import by P&G.

Legend

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

CEPA - Canadian Environmental Protection Act

16. OTHER INFORMATION**Issuing Date:** 20-Apr-2015**Revision Date:** 20-Apr-2015**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS