



## 019-8000 through 019-8003

### Kernmantle Rope HLL : No Anchor

#### FEATURES :

- 2 Person HLL System
- Available in lengths from 30' to 100'
- Abrasion-resistant kernmantle rope:  
Tensile Strength: 11,261lbs
- Secure rope tensioner
- Web energy absorber with protective cover reduces impact forces
- Convenient carry and storage bag
- Anchor not included

#### PERSONAL ATTACHMENT POINT(S)

- 2 O-rings  
Minimum Breaking Strength: 5,000lbs

#### SYSTEM ATTACHMENT POINT(S)

- 2 Carabiners  
Gate Rating: 3,600lbs  
Minimum Breaking Strength: 5,000lbs

#### ITEM WEIGHT :

- Weight Varies per length



USER WEIGHT CAPACITY	
ANSI	130-310lbs (140.6kg) per person; 2 Person maximum
OSHA	420lbs (190.5kg) per person; 1 Person maximum

STANDARD COMPLIANT WITH	
ANSI	N/A
OSHA	1926.502, 1910.140, 1910.66

SIZE(S)	
019-8000	30 Feet (9.5lbs)
019-8001	60 Feet (12.5lbs)
019-8002	80 Feet (14.5lbs)
019-8003	100 Feet (16.5lbs)

COMPONENT	MATERIAL SPECIFICATION
Rope	16mm Kernmantle Rope
Rope Tensioner	YCM Plated Steel
Energy Absorber	Polyester
O-rings	Clear Zinc Plated Steel
Carabiners	YCM Plated Steel
Bag	Polyester