

SAFETY DATA SHEET



HEALTH • HYGIENE • HOME

Lysol Kills 99.9% of Bacteria Laundry Sanitizer 0% Bleach
Crisp Linen scent
Lysol Kills 99.9% of Bacteria Laundry Sanitizer 0% Bleach
Lavender scent

1. Product and company identification

- Product name** : Lysol Kills 99.9% of Bacteria Laundry Sanitizer 0% Bleach
Crisp Linen scent
Lysol Kills 99.9% of Bacteria Laundry Sanitizer 0% Bleach
Lavender scent
- Distributed by** : Reckitt Benckiser LLC.
Morris Corporate Center IV
399 Interpace Parkway (P.O. Box 225)
Parsippany, New Jersey 07054-0225
+1 973 404 2600
- Emergency telephone number (Medical)** : 1-800-338-6167
- Emergency telephone number (Transport)** : 1-800-424-9300 (U.S. & Canada) CHEMTREC
Outside U.S. and Canada (North America), call Chemtrec:703-527-3887
- Website:** : <http://www.rbnainfo.com>
- Product use** : Fabric Treatment

This SDS is designed for workplace employees, emergency personnel and for other conditions and situations where there is greater potential for large-scale or prolonged exposure, in accordance with the requirements of USDOL Occupational Safety and Health Administration.

This SDS is not applicable for consumer use of our products. For consumer use, all precautionary and first aid language is provided on the product label in accordance with the applicable government regulations, and shown in Section 15 of this SDS.

- SDS #** : D8231782 v2.0
- Formulation #:** : e0042-153 / TDS #8191218 v1.0 (Crisp Linen)
e0042-174 / TDS #8191391 v1.0 (Lavender)
- EPA ID No.** : 777-128
- UPC Code / Sizes** : 41 oz., 90 oz. HDPE bottle with CRC

2. Hazards identification

- Classification of the substance or mixture** : SERIOUS EYE DAMAGE/ EYE IRRITATION - Category 1
SKIN SENSITIZATION - Category 1

GHS label elements

D8231782 v2.0

2. Hazards identification

Hazard pictograms :



Signal word : Danger

Hazard statements : Causes serious eye damage.
May cause an allergic skin reaction.

Precautionary statements

General : Read label before use. Keep out of reach of children. If medical advice is needed, have product container or label at hand.

Prevention : Wear protective gloves. Wear eye or face protection. Avoid breathing vapor. Wash hands thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace.

Response : IF ON SKIN: Wash with plenty of soap and water. Wash contaminated clothing before reuse. If skin irritation or rash occurs: Get medical attention. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or physician.

Storage : Not applicable.

Disposal : Dispose of contents and container in accordance with all local, regional, national and international regulations.

Supplemental label elements : None known.

Hazards not otherwise classified : None known.

3. Composition/information on ingredients

Substance/mixture : Mixture

| Ingredient name | % | CAS number |
|--|---------|------------|
| Quaternary ammonium compounds, di-C8-10-alkyldimethyl, chlorides | 1 - 2.5 | 68424-95-3 |

Any concentration shown as a range is to protect confidentiality or is due to batch variation.

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

4. First aid measures

Description of necessary first aid measures

Eye contact : Get medical attention immediately. Call a poison center or physician. Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 10 minutes. Chemical burns must be treated promptly by a physician.

Inhalation : Get medical attention immediately. Call a poison center or physician. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If it is suspected that fumes are still present, the rescuer should wear an appropriate mask or self-contained breathing apparatus. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.

D8231782 v2.0

4. First aid measures

- Skin contact** : Get medical attention immediately. Call a poison center or physician. Wash with plenty of soap and water. Remove contaminated clothing and shoes. Wash contaminated clothing thoroughly with water before removing it, or wear gloves. Continue to rinse for at least 10 minutes. Chemical burns must be treated promptly by a physician. In the event of any complaints or symptoms, avoid further exposure. Wash clothing before reuse. Clean shoes thoroughly before reuse.
- Ingestion** : Get medical attention immediately. Call a poison center or physician. Wash out mouth with water. Remove dentures if any. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Stop if the exposed person feels sick as vomiting may be dangerous. Do not induce vomiting unless directed to do so by medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Chemical burns must be treated promptly by a physician. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.

Most important symptoms/effects, acute and delayed

Potential acute health effects

- Eye contact** : Causes serious eye damage.
- Inhalation** : May give off gas, vapor or dust that is very irritating or corrosive to the respiratory system.
- Skin contact** : May cause an allergic skin reaction.
- Ingestion** : May cause burns to mouth, throat and stomach.

Over-exposure signs/symptoms

- Eye contact** : Adverse symptoms may include the following:
pain
watering
redness
- Inhalation** : No specific data.
- Skin contact** : Adverse symptoms may include the following:
pain or irritation
redness
blistering may occur
- Ingestion** : Adverse symptoms may include the following:
stomach pains

Indication of immediate medical attention and special treatment needed, if necessary

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training. If it is suspected that fumes are still present, the rescuer should wear an appropriate mask or self-contained breathing apparatus. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Wash contaminated clothing thoroughly with water before removing it, or wear gloves.

See toxicological information (Section 11)

D8231782 v2.0

5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media : Use an extinguishing agent suitable for the surrounding fire.

Unsuitable extinguishing media : None known.

Specific hazards arising from the chemical : In a fire or if heated, a pressure increase will occur and the container may burst.

Hazardous thermal decomposition products : No specific data.

Special protective actions for fire-fighters : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

Special protective equipment for fire-fighters : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

For non-emergency personnel : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Do not breathe vapor or mist. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment.

For emergency responders : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

Environmental precautions : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods and materials for containment and cleaning up

Small spill : Stop leak if without risk. Move containers from spill area. Dilute with water and mop up if water-soluble. Alternatively, or if water-insoluble, absorb with an inert dry material and place in an appropriate waste disposal container. Dispose of via a licensed waste disposal contractor.

Large spill : Stop leak if without risk. Move containers from spill area. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Dispose of via a licensed waste disposal contractor. Contaminated absorbent material may pose the same hazard as the spilled product. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

D8231782 v2.0

7. Handling and storage

Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8). Persons with a history of skin sensitization problems should not be employed in any process in which this product is used. Do not get in eyes or on skin or clothing. Do not breathe vapor or mist. Do not ingest. If during normal use the material presents a respiratory hazard, use only with adequate ventilation or wear appropriate respirator. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Empty containers retain product residue and can be hazardous. Do not reuse container.
- Conditions for safe storage, including any incompatibilities** : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Store locked up. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination.

8. Exposure controls/personal protection

Control

Occupational exposure limits

Not applicable.

- Appropriate engineering controls** : If user operations generate dust, fumes, gas, vapor or mist, use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure to airborne contaminants below any recommended or statutory limits.
- Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.
- Individual protection measures**
- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.
- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: chemical splash goggles and/or face shield. If inhalation hazards exist, a full-face respirator may be required instead.
- Skin protection**
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary. Considering the parameters specified by the glove manufacturer, check during use that the gloves are still retaining their protective properties. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. In the case of mixtures, consisting of several substances, the protection time of the gloves cannot be accurately estimated.
- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

D8231782 v2.0

8. Exposure controls/personal protection

- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

9. Physical and chemical properties

Appearance

- Physical state** : Liquid. [Clear.]
- Color** : Blue.
- Odor** : Characteristic.
- Odor threshold** : Not available.
- pH** : 9.4 to 10.4 [Conc. (% w/w): 100%] [25°C]
- Melting point** : Not available.
- Boiling point** : Not available.
- Flash point** : Closed cup: >93.3°C (>199.9°F)
- Evaporation rate** : Not available.
- Flammability (solid, gas)** : Not available.
- Lower and upper explosive (flammable) limits** : Not available.
- Vapor pressure** : Not available.
- Vapor density** : Not available.
- Relative density** : 1
- Solubility** : Easily soluble in the following materials: cold water and hot water.
- Partition coefficient: n-octanol/water** : Not available.
- Auto-ignition temperature** : Not available.
- Decomposition temperature** : Not available.
- Viscosity** : Not available.

10. Stability and reactivity

- Reactivity** : No specific test data related to reactivity available for this product or its ingredients.
- Chemical stability** : The product is stable.
- Possibility of hazardous reactions** : Under normal conditions of storage and use, hazardous reactions will not occur.
- Conditions to avoid** : Keep away from extreme heat.
- Incompatible materials** : Do not mix with household chemicals.
- Hazardous decomposition products** : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

D8231782 v2.0

11. Toxicological information

Information on toxicological effects

Acute toxicity

| Product/ingredient name | Result | Species | Dose | Exposure |
|---------------------------|-----------------------|---------|--|----------|
| * Lysol Laundry Sanitizer | LC50 Inhalation Vapor | Rat | >2.13 mg/l Maximum attainable concentration | 4 hours |
| | LC50 Dermal | Rat | >5000 mg/kg | - |
| | LD50 Oral | Rat | >5000 mg/kg | - |

Conclusion/Summary : Not classified Harmful. *Information is based on toxicity test result of the product.

Irritation/Corrosion

| Product/ingredient name | Result | Species | Score | Exposure | Observation |
|---------------------------|---------------------------------------|--------------------|-----------|----------|-------------|
| * Lysol Laundry Sanitizer | Skin - Edema Eyes - Cornea opacity | Rabbit In vitro | 0.7 >5 | - - | - - |

Conclusion/Summary

Skin : Non-irritant to skin. * Information is based on toxicity test result of the product.

Eyes : Corrosive to eyes. * Information is based on toxicity test result of the product.

Sensitization

| Product/ingredient name | Route of exposure | Species | Result |
|---------------------------|-------------------|------------|-------------|
| * Lysol Laundry Sanitizer | skin | Guinea pig | Sensitizing |

Conclusion/Summary

Skin : Skin sensitizer * Information is based on toxicity test result of the product.

Mutagenicity

Not available.

Carcinogenicity

Not available.

Reproductive toxicity

Not available.

Teratogenicity

Not available.

Specific target organ toxicity (single exposure)

Not available.

Specific target organ toxicity (repeated exposure)

Not available.

Aspiration hazard

Not available.

Information on the likely routes of exposure : Not available.

Potential acute health effects

Code # : FF8191218_FF8191391 **SDS #** : D8231782 v2.0 **Date of issue** : 30/03/2016.

D8231782 v2.0

11. Toxicological information

- Eye contact** : Causes serious eye damage.
- Inhalation** : May give off gas, vapor or dust that is very irritating or corrosive to the respiratory system.
- Skin contact** : May cause an allergic skin reaction.
- Ingestion** : May cause burns to mouth, throat and stomach.

Symptoms related to the physical, chemical and toxicological characteristics

- Eye contact** : Adverse symptoms may include the following:
pain
watering
redness
- Inhalation** : No specific data.
- Skin contact** : Adverse symptoms may include the following:
pain or irritation
redness
blistering may occur
- Ingestion** : Adverse symptoms may include the following:
stomach pains

Delayed and immediate effects and also chronic effects from short and long term exposure

Short term exposure

- Potential immediate effects** : Not available.
- Potential delayed effects** : Not available.

Long term exposure

- Potential immediate effects** : Not available.
- Potential delayed effects** : Not available.

Potential chronic health effects

Not available.

- General** : Once sensitized, a severe allergic reaction may occur when subsequently exposed to very low levels.
- Carcinogenicity** : No known significant effects or critical hazards.
- Mutagenicity** : No known significant effects or critical hazards.
- Teratogenicity** : No known significant effects or critical hazards.
- Developmental effects** : No known significant effects or critical hazards.
- Fertility effects** : No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates

Not available.

D8231782 v2.0

12. Ecological information

Toxicity

| Product/ingredient name | Result | Species | Exposure |
|--|--------------------------------|---------|----------|
| Quaternary ammonium compounds, di-C8-10-alkyldimethyl, chlorides | Acute EC50 0.011 to 0.099 mg/l | Daphnia | 96 hours |

Persistence and degradability

Conclusion/Summary : The surfactant(s) contained in this preparation complies (comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

| Product/ingredient name | Aquatic half-life | Photolysis | Biodegradability |
|--|-------------------|------------|------------------|
| Quaternary ammonium compounds, di-C8-10-alkyldimethyl, chlorides | - | - | Readily |

Bioaccumulative potential

Not available.

Mobility in soil

Soil/water partition coefficient (K_{oc}) : Not available.

Other adverse effects : No known significant effects or critical hazards.

13. Disposal considerations

Disposal methods : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Care should be taken when handling emptied containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

14. Transport information

Not a DOT controlled material (United States). Not a TDG-controlled material. This preparation is not classified as dangerous according to international transport regulations (ADR/RID, IMDG or ICAO/IATA).

D8231782 v2.0

15. Regulatory information

U.S. Federal regulations : **TSCA 4(a) proposed test rules:** Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides
TSCA 8(a) CDR Exempt/Partial exemption: Not determined
United States inventory (TSCA 8b): All components are listed or exempted.

Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs) : Not listed

Clean Air Act Section 602 Class I Substances : Not listed

Clean Air Act Section 602 Class II Substances : Not listed

DEA List I Chemicals (Precursor Chemicals) : Not listed

DEA List II Chemicals (Essential Chemicals) : Not listed

SARA 302/304

Composition/information on ingredients

No products were found.

SARA 304 RQ : Not applicable.

SARA 311/312

Classification : Immediate (acute) health hazard

Composition/information on ingredients

| Name | % | Fire hazard | Sudden release of pressure | Reactive | Immediate (acute) health hazard | Delayed (chronic) health hazard |
|--|---------|-------------|----------------------------|----------|---------------------------------|---------------------------------|
| Quaternary ammonium compounds, di-C8-10-alkyldimethyl, chlorides | 1 - 2.5 | No. | No. | No. | Yes. | No. |

State regulations

Massachusetts : None of the components are listed.

New York : None of the components are listed.

New Jersey : The following components are listed: ETHYL ALCOHOL; ALCOHOL

Pennsylvania : The following components are listed: DENATURED ALCOHOL

Canada

WHMIS (Canada) : Class D-1B: Material causing immediate and serious toxic effects (Toxic).
Class D-2B: Material causing other toxic effects (Toxic).

Canadian lists

Canadian NPRI : None of the components are listed.

CEPA Toxic substances : None of the components are listed.

Canada inventory : All components are listed or exempted.

D8231782 v2.0

15. Regulatory information

Label elements

- Signal word:** : Danger
- Hazard statements** : Corrosive Causes irreversible eye damage
- Precautionary measures** : Do not get in eyes, on skin, or on clothing.
Wear protective eyewear (goggles, face shield or safety glasses). Wash thoroughly with soap and water after handling and before eating, drinking, chewing gum, using tobacco or using the toilet. Remove contaminated clothing and wash it before reuse.
- Skin sensitizer:** : Prolonged or frequently repeated skin contact may cause allergic reactions in some individuals

16. Other information

Hazardous Material Information System (U.S.A.) :

| | |
|---------------------|---|
| Health | 3 |
| Flammability | 0 |
| Physical hazards | 0 |
| Personal protection | B |

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings are not required on MSDSs under 29 CFR 1910.1200, the preparer may choose to provide them. HMIS® ratings are to be used with a fully implemented HMIS® program. HMIS® is a registered mark of the National Paint & Coatings Association (NPCA). HMIS® materials may be purchased exclusively from J. J. Keller (800) 327-6868.

The customer is responsible for determining the PPE code for this material.

National Fire Protection Association (U.S.A.) :



Reprinted with permission from NFPA 704-2001, Identification of the Hazards of Materials for Emergency Response Copyright ©1997, National Fire Protection Association, Quincy, MA 02269. This reprinted material is not the complete and official position of the National Fire Protection Association, on the referenced subject which is represented only by the standard in its entirety.

Copyright ©2001, National Fire Protection Association, Quincy, MA 02269. This warning system is intended to be interpreted and applied only by properly trained individuals to identify fire, health and reactivity hazards of chemicals. The user is referred to certain limited number of chemicals with recommended classifications in NFPA 49 and NFPA 325, which would be used as a guideline only. Whether the chemicals are classified by NFPA or not, anyone using the 704 systems to classify chemicals does so at their own risk.

- Key to abbreviations** :
- ATE = Acute Toxicity Estimate
 - BCF = Bioconcentration Factor
 - GHS = Globally Harmonized System of Classification and Labelling of Chemicals
 - IATA = International Air Transport Association
 - IBC = Intermediate Bulk Container
 - IMDG = International Maritime Dangerous Goods
 - LogPow = logarithm of the octanol/water partition coefficient
 - MARPOL 73/78 = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)

D8231782 v2.0

16. Other information

UN = United Nations

Date of issue : 30/03/2016.
Date of previous issue : 06/08/2015.
Version : 2
Prepared by : Reckitt Benckiser LLC.
Product Safety Department
1 Philips Parkway
Montvale, New Jersey 07646-1810 USA.
FAX: 201-476-7770

Revision comments : Update to product name. Revision on section 2 & 15 classifications. Revision on section 14 classification.

☑ Indicates information that has changed from previously issued version.

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.



RB is a member of the CSPA Product Care Product Stewardship Program.