

SAFETY DATA SHEET

LYSOL® Disinfecting Wipes - Brand New Day



HEALTH • HYGIENE • HOME

1. Product and company identification

Product name : LYSOL® Disinfecting Wipes - Brand New Day

Distributed by : Reckitt Benckiser LLC.
Morris Corporate Center IV
399 Interpace Parkway (P.O. Box 225)
Parsippany, New Jersey 07054-0225
+1 973 404 2600

Reckitt Benckiser (Canada) Inc.
1680 Tech Avenue, Unit #2
Mississauga, Ontario L4W 5S9
CANADA
Telephone: +1 905 283 7000

Emergency telephone number (Medical) : 1-800-338-6167

Emergency telephone number (Transport) : 1-800-424-9300 (U.S. & Canada) CHEMTREC
Outside U.S. and Canada (North America), call Chemtrec:703-527-3887

Website: : <http://www.rbnainfo.com>

Product use : Surface Disinfectant.
Wipes Concentration

This SDS is designed for workplace employees, emergency personnel and for other conditions and situations where there is greater potential for large-scale or prolonged exposure, in accordance with the requirements of USDOL Occupational Safety and Health Administration.

This SDS is not applicable for consumer use of our products. For consumer use, all precautionary and first aid language is provided on the product label in accordance with the applicable government regulations, and shown in Section 15 of this SDS.

SDS # : D8272491 v1.0

Formulation #: : 8269969 v1.0 Brighter Horizon (Coconut)
8269973 v1.0 Brand New Day (Tropical)

EPA ID No. : 777-114

DIN # : 02359014

D8272491 v1.0

2. Hazards identification

Classification of the substance or mixture : Not classified

GHS label elements

Hazard pictograms : Not applicable.
Signal word : No signal word.
Hazard statements : No known significant effects or critical hazards.

Precautionary statements

General : Not applicable.
Prevention : Not applicable.
Response : Not applicable.
Storage : Not applicable.
Disposal : Not applicable.
Supplemental label elements : None known.
Hazards not otherwise classified : None known.

3. Composition/information on ingredients

Substance/mixture : Mixture

Ingredient name	%	CAS number
Ethyl alcohol	1 - 2.5	64-17-5

Any concentration shown as a range is to protect confidentiality or is due to batch variation.

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

4. First aid measures

Description of necessary first aid measures

Eye contact : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.

Inhalation : Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur.

Skin contact : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur.

Ingestion : Wash out mouth with water. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.

Most important symptoms/effects, acute and delayed

Potential acute health effects

Eye contact : May cause eye irritation upon direct contact with eyes.
Inhalation : No known significant effects or critical hazards.

Code # : PM8269969_PM8269973 (D8272491)_NA **SDS #** : D8272491 v1.0 **Date of issue** : 23/06/2016.

2/12

D8272491 v1.0

4. First aid measures

Skin contact : No known significant effects or critical hazards.

Ingestion : No known significant effects or critical hazards.

Over-exposure signs/symptoms

Eye contact : No specific data.

Inhalation : No specific data.

Skin contact : No specific data.

Ingestion : No specific data.

Indication of immediate medical attention and special treatment needed, if necessary

Notes to physician : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.

Specific treatments : No specific treatment.

Protection of first-aiders : No action shall be taken involving any personal risk or without suitable training.

See toxicological information (Section 11)

5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media : Use an extinguishing agent suitable for the surrounding fire.

Unsuitable extinguishing media : None known.

Specific hazards arising from the chemical : In a fire or if heated, a pressure increase will occur and the container may burst.

Hazardous thermal decomposition products : Decomposition products may include the following materials:
carbon dioxide
carbon monoxide

Special protective actions for fire-fighters : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

Special protective equipment for fire-fighters : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

For non-emergency personnel : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Put on appropriate personal protective equipment.

For emergency responders : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

D8272491 v1.0

6. Accidental release measures

Environmental precautions : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods and materials for containment and cleaning up

Small spill : Stop leak if without risk. Move containers from spill area. Dilute with water and mop up if water-soluble. Alternatively, or if water-insoluble, absorb with an inert dry material and place in an appropriate waste disposal container. Dispose of via a licensed waste disposal contractor.

Large spill : Stop leak if without risk. Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Dispose of via a licensed waste disposal contractor. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

7. Handling and storage

Precautions for safe handling

Protective measures : Put on appropriate personal protective equipment (see Section 8).

Conditions for safe storage, including any incompatibilities : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination.

8. Exposure controls/personal protection

Control

Occupational exposure limits

Ingredient name	Exposure limits
Ethyl alcohol	<p>ACGIH TLV (United States, 4/2014). STEL: 1000 ppm 15 minutes.</p> <p>OSHA PEL 1989 (United States, 3/1989). TWA: 1000 ppm 8 hours. TWA: 1900 mg/m³ 8 hours.</p> <p>NIOSH REL (United States, 10/2013). TWA: 1000 ppm 10 hours. TWA: 1900 mg/m³ 10 hours.</p> <p>OSHA PEL (United States, 2/2013). TWA: 1000 ppm 8 hours. TWA: 1900 mg/m³ 8 hours.</p>

Appropriate engineering controls : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

Environmental exposure controls : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

D8272491 v1.0

8. Exposure controls/personal protection

Individual protection measures

- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.
- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields.
- Skin protection**
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.
- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

9. Physical and chemical properties

Appearance

- Physical state** : Liquid.
- Color** : Clear.
- Odor** : Characteristic.
- Odor threshold** : Not available.
- pH** : 10.5 [liquid preparations]
- Melting point** : Not available.
- Boiling point** : Not available.
- Flash point** : Closed cup: >93.3°C (>199.9°F) liquid preparations
- Evaporation rate** : Not available.
- Flammability (solid, gas)** : Not available.
- Lower and upper explosive (flammable) limits** : Not available.
- Vapor pressure** : Not available.
- Vapor density** : Not available.
- Relative density** : 0.985 [liquid preparations]
- Solubility** : Not available.
- Partition coefficient: n-octanol/water** : Not available.
- Auto-ignition temperature** : Not available.

D8272491 v1.0

9. Physical and chemical properties

Decomposition temperature : Not available.

Viscosity : Not available.

10. Stability and reactivity

Reactivity : No specific test data related to reactivity available for this product or its ingredients.

Chemical stability : The product is stable.

Possibility of hazardous reactions : Under normal conditions of storage and use, hazardous reactions will not occur.

Conditions to avoid : No specific data.

Incompatible materials : Do not use with other products.

Hazardous decomposition products : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

11. Toxicological information

Information on toxicological effects

Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
Ethyl alcohol *Lysol Brand II Kills 99.9% of Viruses & Bacteria**Disinfecting Wipes Brand New Day scent	LC50 Inhalation Vapor	Rat	124700 mg/m ³	4 hours
	LD50 Oral	Rat	7 g/kg	-
	LC50 Inhalation Vapor	Rat	>2.04 mg/l	24 hours
	LD50 Dermal	Rat	>5000 mg/kg	-
	LD50 Oral	Rat	>5000 mg/kg	-

Conclusion/Summary : Not classified * Information is based on toxicity test result of the concentrate of a similar product.

Irritation/Corrosion

Product/ingredient name	Result	Species	Score	Exposure	Observation
Ethyl alcohol *Lysol Brand II Kills 99.9% of Viruses & Bacteria**Disinfecting Wipes Brand New Day scent	Eyes - Moderate irritant	Rabbit	-	0.066666667 minutes	-
	Eyes - Mild irritant	Rabbit	-	100 milligrams	-
	Eyes - Moderate irritant	Rabbit	-	24 hours 500 milligrams	-
	Eyes - Severe irritant	Rabbit	-	100 microliters	-
	Skin - Mild irritant	Rabbit	-	500 milligrams	-
	Skin - Moderate irritant	Rabbit	-	400 milligrams	-
	Skin - Slight irritant	Rabbit	1.5	24 hours 20 milligrams	-
Eyes - Cornea opacity	Rabbit	0	-	-	

Conclusion/Summary

D8272491 v1.0

11. Toxicological information

Skin : Non-irritant to skin. * Information is based on toxicity test result of the concentrate of a similar product.

Eyes : Non-irritating to the eyes. * Information is based on toxicity test result of the concentrate of a similar product.

Sensitization

Product/ingredient name	Route of exposure	Species	Result
*Lysol Brand II Kills 99.9% of Viruses & Bacteria**Disinfecting Wipes Brand New Day scent	skin	Guinea pig	Not sensitizing

Conclusion/Summary

Skin : Non-sensitizer to skin. * Information is based on toxicity test result of the concentrate of a similar product.

Mutagenicity

Not available.

Carcinogenicity

Not available.

Classification

Product/ingredient name	OSHA	IARC	NTP
Ethyl alcohol	-	1	-

Reproductive toxicity

Not available.

Teratogenicity

Not available.

Specific target organ toxicity (single exposure)

Not available.

Specific target organ toxicity (repeated exposure)

Not available.

Aspiration hazard

Not available.

Information on the likely routes of exposure : Not available.

Potential acute health effects

Eye contact : May cause eye irritation upon direct contact with eyes.

Inhalation : No known significant effects or critical hazards.

Skin contact : No known significant effects or critical hazards.

Ingestion : No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

D8272491 v1.0

11. Toxicological information

- Eye contact** : No specific data.
- Inhalation** : No specific data.
- Skin contact** : No specific data.
- Ingestion** : No specific data.

Delayed and immediate effects and also chronic effects from short and long term exposure

Short term exposure

- Potential immediate effects** : Not available.
- Potential delayed effects** : Not available.

Long term exposure

- Potential immediate effects** : Not available.
- Potential delayed effects** : Not available.

Potential chronic health effects

Not available.

- General** : No known significant effects or critical hazards.
- Carcinogenicity** : No known significant effects or critical hazards.
- Mutagenicity** : No known significant effects or critical hazards.
- Teratogenicity** : No known significant effects or critical hazards.
- Developmental effects** : No known significant effects or critical hazards.
- Fertility effects** : No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates

Not available.

12. Ecological information

Toxicity

Product/ingredient name	Result	Species	Exposure
Ethyl alcohol	Acute EC50 17.921 mg/l Marine water	Algae - Ulva pertusa	96 hours
	Acute EC50 2000 µg/l Fresh water	Daphnia - Daphnia magna	48 hours
	Acute LC50 25500 µg/l Marine water	Crustaceans - Artemia franciscana - Larvae	48 hours
	Acute LC50 42000 µg/l Fresh water	Fish - Oncorhynchus mykiss	4 days
	Chronic NOEC 4.995 mg/l Marine water	Algae - Ulva pertusa	96 hours
	Chronic NOEC 0.375 ul/L Fresh water	Fish - Gambusia holbrooki - Larvae	12 weeks

Persistence and degradability

Not available.

D8272491 v1.0

12. Ecological information

Bioaccumulative potential

Product/ingredient name	LogP _{ow}	BCF	Potential
Ethyl alcohol	-0.35	-	low

Mobility in soil

Soil/water partition coefficient (K_{oc}) : Not available.

Other adverse effects : No known significant effects or critical hazards.

13. Disposal considerations

Disposal methods : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

14. Transport information

Not a DOT controlled material (United States). Not a TDG-controlled material. This preparation is not classified as dangerous according to international transport regulations (ADR/RID, IMDG or ICAO/IATA).

15. Regulatory information

U.S. Federal regulations : **TSCA 4(a) proposed test rules:** Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides
TSCA 8(a) PAIR: 2-methylpropan-2-ol; 2-(4-tert-butylbenzyl)propionaldehyde; dimethylcyclohex-3-ene-1-carbaldehyde; isopentyl acetate; 3-p-cumenyl-2-methylpropionaldehyde; benzaldehyde; anisaldehyde; α-hexylcinnamaldehyde; piperonal; 1,1'-oxydipropan-2-ol; 2-benzylideneheptanal
TSCA 8(a) CDR Exempt/Partial exemption: Not determined
United States inventory (TSCA 8b): All components are listed or exempted.
Clean Water Act (CWA) 311: isopentyl acetate

Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs) : Not listed

Clean Air Act Section 602 Class I Substances : Not listed

Clean Air Act Section 602 Class II Substances : Not listed

DEA List I Chemicals (Precursor Chemicals) : Not listed

D8272491 v1.0

15. Regulatory information

DEA List II Chemicals (Essential Chemicals) : Not listed

SARA 302/304

Composition/information on ingredients

No products were found.

SARA 304 RQ : Not applicable.

SARA 311/312

Classification : Not applicable.

Composition/information on ingredients

Name	%	Fire hazard	Sudden release of pressure	Reactive	Immediate (acute) health hazard	Delayed (chronic) health hazard
Ethyl alcohol	1 - 2.5	Yes.	No.	No.	Yes.	No.

State regulations

- Massachusetts** : The following components are listed: ETHYL ALCOHOL
- New York** : None of the components are listed.
- New Jersey** : The following components are listed: ETHYL ALCOHOL; ALCOHOL
- Pennsylvania** : The following components are listed: DENATURED ALCOHOL

Canada

- WHMIS (Canada)** : Not controlled under WHMIS (Canada).
- Canadian lists
- Canadian NPRI** : The following components are listed: Ethanol
- CEPA Toxic substances** : None of the components are listed.
- Canada inventory** : At least one component is not listed in DSL but all such components are listed in NDSL.

Label elements

- Signal word:** : CAUTION
- Hazard statements** : May cause eye irritation.
- Precautionary measures** : Avoid contact with eyes.
Wash hands after use.

16. Other information

Hazardous Material Information System (U.S.A.) :

Health	1
Flammability	0
Physical hazards	0
Personal protection	B

D8272491 v1.0

16. Other information

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings are not required on MSDSs under 29 CFR 1910.1200, the preparer may choose to provide them. HMIS® ratings are to be used with a fully implemented HMIS® program. HMIS® is a registered mark of the National Paint & Coatings Association (NPCA). HMIS® materials may be purchased exclusively from J. J. Keller (800) 327-6868.

The customer is responsible for determining the PPE code for this material.

National Fire Protection Association (U.S.A.) :



Reprinted with permission from NFPA 704-2001, Identification of the Hazards of Materials for Emergency Response Copyright ©1997, National Fire Protection Association, Quincy, MA 02269. This reprinted material is not the complete and official position of the National Fire Protection Association, on the referenced subject which is represented only by the standard in its entirety.

Copyright ©2001, National Fire Protection Association, Quincy, MA 02269. This warning system is intended to be interpreted and applied only by properly trained individuals to identify fire, health and reactivity hazards of chemicals. The user is referred to certain limited number of chemicals with recommended classifications in NFPA 49 and NFPA 325, which would be used as a guideline only. Whether the chemicals are classified by NFPA or not, anyone using the 704 systems to classify chemicals does so at their own risk.

Key to abbreviations :

- ATE = Acute Toxicity Estimate
- BCF = Bioconcentration Factor
- GHS = Globally Harmonized System of Classification and Labelling of Chemicals
- IATA = International Air Transport Association
- IBC = Intermediate Bulk Container
- IMDG = International Maritime Dangerous Goods
- LogPow = logarithm of the octanol/water partition coefficient
- MARPOL 73/78 = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)
- UN = United Nations

Date of issue : 23/06/2016.
Date of previous issue : No previous validation
Version : 1
Prepared by : Reckitt Benckiser LLC.
 Product Safety Department
 1 Philips Parkway
 Montvale, New Jersey 07646-1810 USA.
 FAX: 201-476-7770

Indicates information that has changed from previously issued version.

Notice to reader

D8272491 v1.0

16. Other information

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.



RB is a member of the CSPA Product Care Product Stewardship Program.