



021-4072

10K Swivel Anchor & Concrete Wedge Bolt

FEATURES :

- 180° / 360° rotating connection point
- 5/8" expansion bolt with sleeve (concrete)
- Engineered for superior durability
- Installs quickly as a temporary or permanent anchor point
- Used vertically or horizontally
- Minimum breaking strength : 10,000lbs

FALL ARREST POINT(S) :

- 1 D-ring

ITEM WEIGHT :

- 2.1lbs (.95kg)



USER WEIGHT CAPACITY	
ANSI	130-310lbs (140.6kg)
OSHA	420lbs (190.5kg)

STANDARD COMPLIANT WITH	
ANSI	A10.32, Z359.18-2017 Type A
OSHA	1926.502, 1910.66

Replacement Part # (s)	
021-4073	10K Replacement Concrete Wedge Bolt

COMPONENT	MATERIAL SPECIFICATION
Anchor	High strength plated steel
Bolt	Zinc plated steel