

A07758 TM CLEAN & FRESH 12pk 12n6.6

Version 1.2

Revision Date 12/12/2016

Print Date 02/15/2017

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : A07758 TM CLEAN & FRESH 12pk 12n6.6

Material number : 00000000001042771

Manufacturer or supplier's details

Company : Zep Inc.

Address : 1310 Seaboard Industrial Blvd., NW
Atlanta, GA 30318

Telephone : 404-352-1680

Emergency telephone numbers**For SDS Information** : Compliance Services 1-877-428-9937**For a Medical Emergency** : 877-541-2016 Toll Free - All Calls Recorded**For a Transportation Emergency** : CHEMTREC: 800-424-9300 - All Calls Recorded.
In the District of Columbia 202-483-7616**Recommended use of the chemical and restrictions on use**

Recommended use : Air Care

SECTION 2. HAZARDS IDENTIFICATION**Emergency Overview**

Appearance	Aerosol containing a liquefied gas
Colour	colourless
Odour	characteristic

GHS Classification

Flammable aerosols : Category 1
 Gases under pressure : Liquefied gas
 Eye irritation : Category 2A
 Skin sensitisation : Category 1
 Specific target organ toxicity - single exposure : Category 3 (Central nervous system)

GHS label elements

Hazard pictograms :



Signal word : Danger

Hazard statements : H222 Extremely flammable aerosol.
 H280 Contains gas under pressure; may explode if heated.
 H317 May cause an allergic skin reaction.
 H319 Causes serious eye irritation.
 H336 May cause drowsiness or dizziness.

A07758 TM CLEAN & FRESH 12pk 12n6.6

Version 1.2

Revision Date 12/12/2016

Print Date 02/15/2017

Precautionary statements : **Prevention:**
 P210 Keep away from heat/sparks/open flames/hot surfaces. No smoking.
 P211 Do not spray on an open flame or other ignition source.
 P251 Pressurized container: Do not pierce or burn, even after use.
 P261 Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.
 P264 Wash skin thoroughly after handling.
 P271 Use only outdoors or in a well-ventilated area.
 P272 Contaminated work clothing should not be allowed out of the workplace.
 P280 Wear protective gloves/ eye protection/ face protection.

Response:
 P302 + P352 IF ON SKIN: Wash with plenty of soap and water.
 P304 + P340 + P312 IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER/doctor if you feel unwell.
 P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P333 + P313 If skin irritation or rash occurs: Get medical advice/ attention.
 P337 + P313 If eye irritation persists: Get medical advice/ attention.
 P363 Wash contaminated clothing before reuse.

Storage:
 P403 + P233 Store in a well-ventilated place. Keep container tightly closed.
 P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.

Disposal:
 Dispose of contents/container in accordance with local regulation.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical name	CAS-No.	Concentration [%]
acetone	67-64-1	>= 50 - < 70
propane	74-98-6	>= 20 - < 30
benzyl salicylate	118-58-1	>= 0.1 - < 1
Oils, sweet orange (terpenes and terpenoids)	68647-72-3	>= 0.1 - < 1
citronellol	106-22-9	>= 0.1 - < 1

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

General advice : Show this safety data sheet to the doctor in attendance.

If inhaled : If breathed in, move person into fresh air.
 If not breathing, give artificial respiration.
 If breathing is difficult, give oxygen.

A07758 TM CLEAN & FRESH 12pk 12n6.6

Version 1.2

Revision Date 12/12/2016

Print Date 02/15/2017

- In case of skin contact : Wash off immediately with plenty of water for at least 15 minutes.
Call a physician if irritation persists.
- In case of eye contact : Immediately flush eye(s) with plenty of water.
Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
- If swallowed : Never give anything by mouth to an unconscious person.
If victim is fully conscious, give a cupful of water.
Obtain medical attention.
DO NOT induce vomiting unless directed to do so by a physician or poison control center.
- Most important symptoms and effects, both acute and delayed : Effects are immediate and delayed.
Symptoms may include irritation, redness, pain, and rash.
Symptoms may include central nervous system depression, resulting in headache, nausea and/or dizziness.
Causes serious eye irritation.
May cause drowsiness or dizziness.
Review section 2 of SDS to see all potential hazards.
- Notes to physician : Treat symptomatically. Symptoms may be delayed.
-

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Foam
Carbon dioxide (CO₂)
Water spray
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during firefighting : Do not allow run-off from fire fighting to enter drains or water courses.
- Hazardous combustion products : Carbon dioxide (CO₂)
Carbon monoxide
Smoke
Nitrogen oxides (NO_x)
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
- Further information : Use a water spray to cool fully closed containers.
- Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary.
-

SECTION 6. ACCIDENTAL RELEASE MEASURES

A07758 TM CLEAN & FRESH 12pk 12n6.6

Version 1.2

Revision Date 12/12/2016

Print Date 02/15/2017

- Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.
Remove all sources of ignition.
Evacuate personnel to safe areas.
Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas.
- Environmental precautions : Prevent product from entering drains.
Prevent further leakage or spillage if safe to do so.
If the product contaminates rivers and lakes or drains inform respective authorities.
- Methods and materials for containment and cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Sweep up and shovel into suitable containers for disposal.

SECTION 7. HANDLING AND STORAGE

- Advice on safe handling : Keep away from fire (No Smoking).
Avoid contact with skin and eyes.
Handle and open container with care.
Smoking, eating and drinking should be prohibited in the application area.
Always replace cap after use.
Use only with adequate ventilation.
Do not breathe vapours or spray mist.
- Conditions for safe storage : BEWARE: Aerosol is pressurized. Keep away from direct sun exposure and temperatures over 50 °C. Do not open by force or throw into fire even after use. Do not spray on flames or red-hot objects.
No smoking.
Observe label precautions.
Keep in a dry, cool and well-ventilated place.
Electrical installations / working materials must comply with the technological safety standards.
- Materials to avoid : Keep away from oxidizing agents and strongly acid or alkaline materials.
- Storage temperature : < 48 °C

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION
Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
acetone	67-64-1	TWA	250 ppm	ACGIH
		STEL	500 ppm	ACGIH
		TWA	250 ppm 590 mg/m ³	NIOSH REL
		TWA	1,000 ppm	OSHA Z-1

A07758 TM CLEAN & FRESH 12pk 12n6.6

Version 1.2

Revision Date 12/12/2016

Print Date 02/15/2017

			2,400 mg/m ³	
		TWA	750 ppm 1,800 mg/m ³	OSHA P0
		STEL	1,000 ppm 2,400 mg/m ³	OSHA P0
		STEL	750 ppm 1,780 mg/m ³	CAL PEL
		C	3,000 ppm	CAL PEL
		PEL	500 ppm 1,200 mg/m ³	CAL PEL
propane	74-98-6	TWA	1,000 ppm	ACGIH
		TWA	1,000 ppm 1,800 mg/m ³	NIOSH REL
		TWA	1,000 ppm 1,800 mg/m ³	OSHA Z-1
		TWA	1,000 ppm 1,800 mg/m ³	OSHA P0
		PEL	1,000 ppm 1,800 mg/m ³	CAL PEL

Hazardous components without workplace control parameters

Biological occupational exposure limits

Component	CAS-No.	Control parameters	Biological specimen	Sampling time	Permissible concentration	Basis
2-PROPANONE	67-64-1	Acetone	Urine	End of shift (As soon as possible after exposure ceases)	25 mg/l	ACGIH BEI

Engineering measures : effective ventilation in all processing areas**Personal protective equipment**

Respiratory protection : Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.

Hand protection
Remarks : The suitability for a specific workplace should be discussed with the producers of the protective gloves.Eye protection : Wear face-shield and protective suit for abnormal processing problems.
Ensure that eyewash stations and safety showers are close to the workstation location.
Safety glassesSkin and body protection : Impervious clothing
Choose body protection according to the amount and concentration of the dangerous substance at the work place.

Hygiene measures : Handle in accordance with good industrial hygiene and safety practice.

A07758 TM CLEAN & FRESH 12pk 12n6.6

Version 1.2

Revision Date 12/12/2016

Print Date 02/15/2017

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	: Aerosol containing a liquefied gas
Colour	: colourless
Odour	: characteristic
Odour Threshold	: No data available
pH	: Not applicable
Melting point/freezing point	: No data available
Boiling point	: No data available
Flash point	: Not applicable
Evaporation rate	: not determined
Flammability (solid, gas)	: Extremely flammable aerosol.
Upper explosion limit	: No data available
Lower explosion limit	: No data available
Vapour pressure	: 5,515.8 hPa (21 °C)
Relative vapour density	: No data available
Density	: No data available
Solubility(ies)	
Water solubility	: partly soluble
Solubility in other solvents	: not determined
Partition coefficient: n-octanol/water	: No data available
Auto-ignition temperature	: not determined
Thermal decomposition	: No data available
Viscosity	
Viscosity, kinematic	: No data available
Heat of combustion	: 37.30 kJ/g

SECTION 10. STABILITY AND REACTIVITY

Reactivity	: Stable
Chemical stability	: Stable under normal conditions. No decomposition if stored and applied as directed.

A07758 TM CLEAN & FRESH 12pk 12n6.6

Version 1.2

Revision Date 12/12/2016

Print Date 02/15/2017

Possibility of hazardous reactions	: Vapours may form explosive mixture with air. No decomposition if stored and applied as directed.
Conditions to avoid	: Heat, flames and sparks. Extremes of temperature and direct sunlight.
Incompatible materials	: Oxidizing agents Alkali metals Acids
Hazardous decomposition products	: Carbon oxides

SECTION 11. TOXICOLOGICAL INFORMATION**Potential Health Effects**

Aggravated Medical Condition	: None known.
Symptoms of Overexposure	: Effects are immediate and delayed. Symptoms may include irritation, redness, pain, and rash. Symptoms may include central nervous system depression, resulting in headache, nausea and/or dizziness.

Carcinogenicity:

IARC	No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Acute toxicity**Components:****acetone:**

Acute oral toxicity	: LD50 Rat: 5,800 mg/kg
Acute inhalation toxicity	: LC50 Rat: 132 mg/l Exposure time: 3 h LC50 Rat: 50.1 mg/l
Acute dermal toxicity	: LD50 Guinea pig: > 7,426 mg/kg LD50 Rabbit: > 7,426 mg/kg

A07758 TM CLEAN & FRESH 12pk 12n6.6

Version 1.2

Revision Date 12/12/2016

Print Date 02/15/2017

propane:

Acute inhalation toxicity : LC50 Mouse: 1,237 mg/l
Exposure time: 2 h

LC50 Rat: 658 mg/l
Exposure time: 4 h

LC50 Rat: 1,355 mg/l

benzyl salicylate:

Acute oral toxicity : LD50 Oral Rat: 2,227 mg/kg

Skin corrosion/irritation

Product:

Remarks: May cause skin irritation and/or dermatitis.

Serious eye damage/eye irritation

Product:

Remarks: Irritating to eyes.

Respiratory or skin sensitisation

Product:

Remarks: Causes sensitisation.

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

acetone:

propane:

benzyl salicylate:

Oils, sweet orange (terpenes and terpenoids):

citronellol:

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

Further information

A07758 TM CLEAN & FRESH 12pk 12n6.6

Version 1.2

Revision Date 12/12/2016

Print Date 02/15/2017

Product:

Remarks: Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting., Concentrations substantially above the TLV value may cause narcotic effects., Solvents may degrease the skin.

SECTION 12. ECOLOGICAL INFORMATION**Ecotoxicity**

No data available

Persistence and degradability

No data available

Bioaccumulative potential**Product:**

Partition coefficient: n-octanol/water : Remarks: No data available

Components:**citronellol :**

Partition coefficient: n-octanol/water : Pow: 3.6

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation

40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

Remarks

This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information

: No data available

SECTION 13. DISPOSAL CONSIDERATIONS**Disposal methods**

Waste from residues

: Dispose of in accordance with local regulations.
The product should not be allowed to enter drains, water courses or the soil.
Do not contaminate ponds, waterways or ditches with

A07758 TM CLEAN & FRESH 12pk 12n6.6

Version 1.2

Revision Date 12/12/2016

Print Date 02/15/2017

chemical or used container.

Contaminated packaging : Empty remaining contents.
 Dispose of as unused product.
 Do not re-use empty containers.
 Do not burn, or use a cutting torch on, the empty drum.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
 ORM-D, CONSUMER COMMODITY

Transportation Regulation: IMDG (Vessel):
 UN1950, AEROSOLS, 2.1, - Limited quantity

Transportation Regulation: IATA (Cargo Air):
 UN1950, Aerosols, flammable, 2.1, - Limited quantity

Transportation Regulation: IATA (Passenger Air):
 UN1950, Aerosols, flammable, 2.1, - Limited quantity

Transportation Regulation: TDG (Canada):
 UN1950, AEROSOLS, 2.1, - Limited quantity

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SECTION 15. REGULATORY INFORMATION

TSCA list : No substances are subject to a Significant New Use Rule.
 No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act**CERCLA Reportable Quantity**

Components	CAS-No.	Component RQ (lbs)	Calculated product RQ (lbs)
acetone	67-64-1	5000	*

*: Calculated RQ exceeds reasonably attainable upper limit.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Fire Hazard
 Sudden Release of Pressure Hazard

A07758 TM CLEAN & FRESH 12pk 12n6.6

Version 1.2

Revision Date 12/12/2016

Print Date 02/15/2017

Acute Health Hazard

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop 65 This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

TSCA On TSCA Inventory
DSL This product contains one or more components that are listed on the Canadian NDSL. All other components are on the Canadian DSL.

For information on the country notification status for other regions please contact the manufacturer's regulatory group.


Inventory Acronym and Validity Area Legend:

TSCA (USA), DSL (Canada), NDSL (Canada)

SECTION 16. OTHER INFORMATION

Further information

NFPA:



HMIS III:

HEALTH	1
FLAMMABILITY	3
PHYSICAL HAZARD	2

0 = not significant, 1 = Slight,
 2 = Moderate, 3 = High
 4 = Extreme, * = Chronic

OSHA - GHS Label Information:

Hazard pictograms



Signal word

Hazard statements

: **Danger:**
 : Extremely flammable aerosol. Contains gas under pressure; may explode if heated.
 : May cause an allergic skin reaction. Causes serious eye irritation. May cause

A07758 TM CLEAN & FRESH 12pk 12n6.6

Version 1.2

Revision Date 12/12/2016

Print Date 02/15/2017

Precautionary statements : draw sickness or dizziness.

Prevention: Keep away from heat/sparks/open flames/hot surfaces. No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray. Wash skin thoroughly after handling. Use only outdoors or in a well-ventilated area. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves/ eye protection/ face protection.

Response: IF ON SKIN: Wash with plenty of soap and water. IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER/doctor if you feel unwell. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation or rash occurs: Get medical advice/attention. If eye irritation persists: Get medical advice/attention. Wash contaminated clothing before reuse.

Storage: Store in a well-ventilated place. Keep container tightly closed. Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.

Disposal: Dispose of contents/container in accordance with local regulation.

Version:	1.2
Revision Date:	12/12/2016
Print Date:	02/15/2017

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®, Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®, Rexodan®, Mykal™, and a number of private labeled brands.