



022-11029

10' Tech Tripod Basic

FEATURES :

- Lightweight aluminum construction
- Quick setup with easy height and diameter adjustment using detent pins
- Multiple stance configurations to allow for a variety of work zones, including an over-an-edge scenario
- 7 Individual 5,000 lb. anchor points in the head unit including a centered 360° captive eye
- Multi-surface steel feet with rubber pads
- Safety chain and quick link
- Convenient and durable storage/travel bag
- Minimum Breaking Strength: 5,000 lbs. (2268 kg)
- Maximum Material Capacity: 620 lbs. (281 kg)
- System Capacity: 620 lbs. (281 kg)

FALL ARREST POINT(S) :

- 360° Captive Eye
- (6) 5,000 lb. Anchor Points in Head Unit

ITEM WEIGHT :

- **64.3 lbs. (29.2 kg)**



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-141 kg)
OSHA	Up to 420 lbs. (191 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.18-2017 Type T, Z359.4-2013, Z117.1-2022
OSHA	1926.502, 1910.140

COMPATIBLE COMPONENTS	
019-11010	Universal Tripod Bracket
019-11017	Tripod Replacement Chain
022-11031	Perimeter Warning Line
022-11030	Tripod Step
020-11025	Aluminum Pulley

COMPONENT	MATERIAL SPECIFICATION
Tripod Base/Legs	Aluminum
Head Unit	Aluminum
Captive Eye	Stainless Steel
Feet	Powder coated steel, rubber
Fasteners	Zinc plated steel
Detent Pins	Nylon/Stainless steel