

**BZ7360 Z FRESH BREEZE R01601 12QT/CS**

Version 1.0

Revision Date 10/10/2014

Print Date 06/01/2015

**SECTION 1. PRODUCT AND COMPANY IDENTIFICATION**

Material name : BZ7360 Z FRESH BREEZE R01601 12QT/CS

Material number : 00000000001041417

**Manufacturer or supplier's details**

Company : Zep Inc.

Address : 1310 Seaboard Industrial Blvd., NW  
Atlanta, GA 30318

Telephone : 404-352-1680

**Emergency telephone numbers****For SDS Information** : Compliance Services 1-877-428-9937**For a Medical Emergency** : 877-541-2016 Toll Free - All Calls Recorded**For a Transportation  
Emergency** : CHEMTREC: 800-424-9300 - All Calls Recorded.  
In the District of Columbia 202-483-7616**SECTION 2. HAZARDS IDENTIFICATION****Emergency Overview**

Appearance	liquid
Colour	clear, colourless
Odour	pleasant

**GHS Classification**Flammable liquids : Category 3  
Skin irritation : Category 2  
Eye irritation : Category 2A**GHS Label element**

Hazard pictograms :



Signal word : Warning

Hazard statements : H226 Flammable liquid and vapour.  
H315 Causes skin irritation.  
H319 Causes serious eye irritation.Precautionary statements : **Prevention:**  
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
P233 Keep container tightly closed.  
P240 Ground/bond container and receiving equipment.  
P241 Use explosion-proof electrical/ ventilating/ lighting/ equipment.

**BZ7360 Z FRESH BREEZE R01601 12QT/CS**

Version 1.0

Revision Date 10/10/2014

Print Date 06/01/2015

P242 Use only non-sparking tools.

P243 Take precautionary measures against static discharge.

P264 Wash skin thoroughly after handling.

P280 Wear protective gloves/ eye protection/ face protection.

**Response:**

P303 + P361 + P353 IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P332 + P313 If skin irritation occurs: Get medical advice/ attention.

P337 + P313 If eye irritation persists: Get medical advice/ attention.

P362 Take off contaminated clothing and wash before reuse.

P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam for extinction.

**Storage:**

P403 + P235 Store in a well-ventilated place. Keep cool.

**Disposal:**

P501 Dispose of contents/container in accordance with local regulation.

**Potential Health Effects****Carcinogenicity:****IARC**

No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

**ACGIH**

Confirmed animal carcinogen with unknown relevance to humans

ethanol

64-17-5

**OSHA**

No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

**NTP**

No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Substance / Mixture : Mixture

**Hazardous components**

Chemical Name	CAS-No.	Concentration [%]
Alcohol Ethoxylates	66455-15-0	>= 5 - < 10
ethanol	64-17-5	>= 1 - < 5
allyl 3-cyclohexylpropionate	2705-87-5	>= 1 - < 5

**SECTION 4. FIRST AID MEASURES**

**BZ7360 Z FRESH BREEZE R01601 12QT/CS**

Version 1.0

Revision Date 10/10/2014

Print Date 06/01/2015

- |                         |   |
|-------------------------|---|
| General advice          | : Move out of dangerous area.<br>Show this safety data sheet to the doctor in attendance.<br>Do not leave the victim unattended.  |
| If inhaled              | : If unconscious place in recovery position and seek medical advice.<br>If symptoms persist, call a physician.  |
| In case of skin contact | : If skin irritation persists, call a physician.<br>If on skin, rinse well with water.<br>If on clothes, remove clothes.  |
| In case of eye contact  | : Immediately flush eye(s) with plenty of water.<br>Remove contact lenses.<br>Protect unharmed eye.<br>Keep eye wide open while rinsing.<br>If eye irritation persists, consult a specialist. |
| If swallowed            | : Keep respiratory tract clear.<br>Do not give milk or alcoholic beverages.<br>Never give anything by mouth to an unconscious person.<br>If symptoms persist, call a physician.               |

---

**SECTION 5. FIREFIGHTING MEASURES**

- |   |   |
|---|---|
| Suitable extinguishing media                  | : Alcohol-resistant foam<br>Carbon dioxide (CO <sub>2</sub> )<br>Dry chemical   |
| Unsuitable extinguishing media                | : High volume water jet   |
| Hazardous combustion products                 | : Carbon dioxide (CO <sub>2</sub> )<br>Carbon monoxide<br>Smoke   |
| Specific extinguishing methods                | : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.   |
| Further information                           | : Collect contaminated fire extinguishing water separately. This must not be discharged into drains.<br>Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.<br>For safety reasons in case of fire, cans should be stored separately in closed containments.<br>Use a water spray to cool fully closed containers. |
| Special protective equipment for firefighters | : Wear self-contained breathing apparatus for firefighting if necessary.  |

---

**SECTION 6. ACCIDENTAL RELEASE MEASURES**

- |   |  |
|---|--|
| Personal precautions, protective equipment and emergency procedures | : Use personal protective equipment.<br>Remove all sources of ignition.<br>Evacuate personnel to safe areas.<br>Beware of vapours accumulating to form explosive |
|---|--|

**BZ7360 Z FRESH BREEZE R01601 12QT/CS**

Version 1.0

Revision Date 10/10/2014

Print Date 06/01/2015

concentrations. Vapours can accumulate in low areas.

- Environmental precautions : Prevent product from entering drains.  
Prevent further leakage or spillage if safe to do so.  
If the product contaminates rivers and lakes or drains inform respective authorities.
- Methods and materials for containment and cleaning up : Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

**SECTION 7. HANDLING AND STORAGE**

- Advice on safe handling : Avoid formation of aerosol.  
Do not breathe vapours/dust.  
Avoid contact with skin and eyes.  
For personal protection see section 8.  
Smoking, eating and drinking should be prohibited in the application area.  
Take precautionary measures against static discharges.  
Provide sufficient air exchange and/or exhaust in work rooms.  
Open drum carefully as content may be under pressure.  
Dispose of rinse water in accordance with local and national regulations.
- Conditions for safe storage : No smoking.  
Keep container tightly closed in a dry and well-ventilated place.  
Containers which are opened must be carefully resealed and kept upright to prevent leakage.  
Observe label precautions.  
Electrical installations / working materials must comply with the technological safety standards.
- Materials to avoid : Keep away from oxidising agents and strongly acid or alkaline materials.

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**
**Components with workplace control parameters**

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
ethanol	64-17-5	TWA	1,000 ppm	ACGIH
		TWA	1,000 ppm 1,900 mg/m <sup>3</sup>	NIOSH REL
		TWA	1,000 ppm 1,900 mg/m <sup>3</sup>	OSHA Z-1
		TWA	1,000 ppm 1,900 mg/m <sup>3</sup>	OSHA P0

**BZ7360 Z FRESH BREEZE R01601 12QT/CS**

Version 1.0

Revision Date 10/10/2014

Print Date 06/01/2015

**Personal protective equipment**

Hand protection Remarks	: The suitability for a specific workplace should be discussed with the producers of the protective gloves.
Eye protection	: Eye wash bottle with pure water Tightly fitting safety goggles Wear face-shield and protective suit for abnormal processing problems.
Skin and body protection	: impervious clothing Choose body protection according to the amount and concentration of the dangerous substance at the work place.
Hygiene measures	: When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

Appearance	: liquid
Colour	: clear, colourless
Odour	: pleasant
Odour Threshold	: no data available
pH	: 5 - 7
Melting point/freezing point	: no data available
Boiling point	: 87.8 °C
Flash point	: 47.77 °C Method: closed cup
Evaporation rate	: 1
Upper explosion limit	: no data available
Lower explosion limit	: no data available
Vapour pressure	: no data available
Relative vapour density	: no data available
Density	: 0.991 g/cm <sup>3</sup>
Solubility(ies)	
Water solubility	: soluble in cold water, soluble in hot water
Partition coefficient: n-octanol/water	: no data available
Auto-ignition temperature	: not determined

**BZ7360 Z FRESH BREEZE R01601 12QT/CS**

Version 1.0

Revision Date 10/10/2014

Print Date 06/01/2015

Thermal decomposition : no data available

Viscosity

Viscosity, kinematic : 5 mm<sup>2</sup>/s (20 °C)

---

**SECTION 10. STABILITY AND REACTIVITY**

Chemical stability : Stable under normal conditions.

Possibility of hazardous reactions : Vapours may form explosive mixture with air.  
No decomposition if stored and applied as directed.

Conditions to avoid : Heat, flames and sparks.

Incompatible materials : Oxidizing agents

Hazardous decomposition products : Carbon oxides

---

**SECTION 11. TOXICOLOGICAL INFORMATION****Acute toxicity****Product:**Acute oral toxicity : Acute toxicity estimate : > 5,000 mg/kg  
Method: Calculation methodAcute dermal toxicity : Acute toxicity estimate : > 5,000 mg/kg  
Method: Calculation method**Components:****allyl 3-cyclohexylpropionate:**

Acute oral toxicity : LD50 Oral rat: 585 mg/kg

**Skin corrosion/irritation****Product:**

Remarks: May cause skin irritation in susceptible persons.

**Serious eye damage/eye irritation****Product:**

Remarks: Moderate eye irritation

**Respiratory or skin sensitisation**

**BZ7360 Z FRESH BREEZE R01601 12QT/CS**

Version 1.0

Revision Date 10/10/2014

Print Date 06/01/2015

no data available

**Germ cell mutagenicity**

no data available

**Carcinogenicity**

no data available

**Reproductive toxicity**

no data available

**Alcohol Ethoxylates:**

**ethanol:**

**allyl 3-cyclohexylpropionate:**

**STOT - single exposure**

no data available

**STOT - repeated exposure**

no data available

**Aspiration toxicity**

no data available

**Further information**

**Product:**

Remarks: Solvents may degrease the skin.

---

**SECTION 12. ECOLOGICAL INFORMATION**

**Ecotoxicity**

no data available

**Persistence and degradability**

no data available

**Bioaccumulative potential**

**Product:**

Partition coefficient: n-octanol/water : Remarks: no data available

**Mobility in soil**

no data available

**Other adverse effects**

no data available

**Product:**

Regulation 40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

**BZ7360 Z FRESH BREEZE R01601 12QT/CS**

Version 1.0

Revision Date 10/10/2014

Print Date 06/01/2015

Remarks : This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information : no data available

**SECTION 13. DISPOSAL CONSIDERATIONS****Disposal methods**

Waste from residues : Dispose of in accordance with local regulations.  
Do not dispose of waste into sewer.  
Do not contaminate ponds, waterways or ditches with chemical or used container.

Contaminated packaging : Empty remaining contents.  
Dispose of as unused product.  
Do not re-use empty containers.  
Do not burn, or use a cutting torch on, the empty drum.

**SECTION 14. TRANSPORT INFORMATION****International regulation****IATA-DGR**

UN/ID No. : 1993  
Proper shipping name : Flammable liquid, n.o.s.  
(ETHANOL)  
Class : 3  
Packing group : III  
Labels : 3  
Packing instruction (cargo aircraft) : 366  
Packing instruction (passenger aircraft) : 355

**IMDG-Code**

UN number : 1993  
Proper shipping name : FLAMMABLE LIQUID, N.O.S.  
(ETHANOL)  
Class : 3  
Packing group : III  
Labels : 3  
EmS Code : F-E, S-E  
Marine pollutant : no



**BZ7360 Z FRESH BREEZE R01601 12QT/CS**

Version 1.0

Revision Date 10/10/2014

Print Date 06/01/2015

**Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code**

Not applicable for product as supplied.

**National Regulations****49 CFR**

UN/ID/NA number : 1993  
Proper shipping name : Flammable liquids, n.o.s.  
(ETHANOL)  
Class : 3  
Packing group : III  
Labels : 3  
ERG Code : 128  
Marine pollutant : no

**Special precautions for user**

not applicable

---

**SECTION 15. REGULATORY INFORMATION****EPCRA - Emergency Planning and Community Right-to-Know Act****CERCLA Reportable Quantity**

This material does not contain any components with a CERCLA RQ.

**SARA 304 Extremely Hazardous Substances Reportable Quantity**

This material does not contain any components with a section 304 EHS RQ.

**SARA 311/312 Hazards** : Fire Hazard  
Acute Health Hazard

**SARA 302** : SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

**SARA 313** : SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

**California Prop 65** This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

**The components of this product are reported in the following inventories:**

**TSCA** On TSCA Inventory  
**DSL** All components of this product are on the Canadian DSL.  
**AICS** Not in compliance with the inventory

**BZ7360 Z FRESH BREEZE R01601 12QT/CS**

Version 1.0

Revision Date 10/10/2014

Print Date 06/01/2015

**NZIoC** Not in compliance with the inventory  
**PICCS** Not in compliance with the inventory  
**IECSC** Not in compliance with the inventory


**Inventory Acronym and Validity Area Legend:**

AICS (Australia), DSL (Canada), IECSC (China), REACH (European Union), ENCS (Japan), ISHL (Japan), KECI (Korea), NZIoC (New Zealand), PICCS (Philippines), TSCA (USA)

**SECTION 16. OTHER INFORMATION**

**Further information**

**NFPA:**



**HMIS III:**

<b>HEALTH</b>	<b>2</b>
<b>FLAMMABILITY</b>	<b>2</b>
<b>PHYSICAL HAZARD</b>	<b>0</b>

0 = not significant, 1 =Slight,  
 2 = Moderate, 3 = High  
 4 = Extreme, \* = Chronic

**OSHA GHS Label Information:**

Hazard pictograms :



Signal word :

**Warning:**

Hazard statements :

Flammable liquid and vapour. Causes skin irritation. Causes serious eye irritation.

Precautionary statements :

**Prevention:** Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Keep container tightly closed. Ground/bond container and receiving equipment. Use explosion-proof electrical/ ventilating/ lighting/ equipment. Use only non-sparking tools. Take precautionary measures against static discharge. Wash skin thoroughly after handling. Wear protective gloves/ eye protection/ face protection.

**Response:** IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation occurs: Get medical advice/ attention. If eye irritation persists: Get medical advice/ attention. Take off contaminated clothing and wash before reuse. In case of fire: Use dry sand, dry chemical or alcohol-resistant foam for extinction.

**Storage:** Store in a well-ventilated place. Keep cool.

**Disposal:** Dispose of contents/container in accordance with local regulation.

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations

**BZ7360 Z FRESH BREEZE R01601 12QT/CS**

Version 1.0

Revision Date 10/10/2014

Print Date 06/01/2015

to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®, Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®, Rexodan®, Mykal™, and a number of private labeled brands.