



019-11015

120' 3-Way System, Universal Mount

FEATURES :

- Serves as the support element, provides fall protection and facilitates rescue or evacuation if necessary
- Storable handle, max operation force: 30 lbs.
- 6:1 gear ratio
- Carrying handle
- Universal mounting bracket
- Universal Tripod Bracket (019-11010) is required for installation (not included)
- All components are Z359.12 compliant

MINIMUM BREAKING STRENGTH:

- 3,600 lbs. (16 kN)

FALL ARREST POINT(S) :

- 1 snap hook

ITEM WEIGHT :

- 44.3 lbs. (20.1 kg)



Class
1
Anchor at or above dorsal D-ring

USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-140.6 kg)
OSHA	Up to 420 lbs. (190.5 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.14-2021, Z359.4-2013
OSHA	1926.502, 1910.66, 1910.140

ANSI CLASS 1 (ABOVE D-RING)	
Max. arrest force	≤ 1,800 lbs. (816.5 kg)
Avg. arrest force	≤ 1,350 lbs. (612.4 kg)
Max. arrest distance	≤ 42 in. (107 cm)
Actual arrest distance	28 in. (71 cm)
Max. free fall distance	24 in. (61 cm)
Min. required fall clearance	7 ft. 4 in. (2.2 m)
For full clearance requirements, see user instructions	

MATERIAL SPECIFICATION	
Housing	Aluminum
Handle	Steel with plastic grip
Mounting bracket	Steel
Cable	3/16" galvanized steel
Load indicating swivel snap hook	YCM steel