

QUA-016, rev.: 00

OUTDOOR EXTENSION CORD WITH RUGGED SAFETY SEAL LOCK



| | |
|---|--|
| ELECTRICAL AND STRUCTURAL CHARACTERISTICS. | Cord / Cable: - Type: SJTW 14AWG X 3C (14 AWG=2,08 mm ² 3 conductors), 300 V, 105 °C - Length: 25 ft. (7.62 m) |
| | Plug: NEMA 5-15P (2 P + Ground Polarized) Socket: NEMA 5-15R (2 P + Ground Polarized) Current: 15 A Voltage: 125 V AC Maximum Power: 1875W Insulated for 300V cable |
| MATERIALS | Base: ABS/PC Waterproof Cover: PP Contacts: Brass Cord Insulation jacket: Thermoplastic |
| DEGREE OF PROTECTION | IP67 (IEC 60529) NEMA 4X |
| IMPACT RESISTANCE | IK07 (IEC 62262) |
| GLOW WIRE TEST | Live parts supports 750 °C Other parts 650 °C |
| BALL PRESSURE TEST | Live parts supports 125 °C |
| APPLIED STANDARD | UL STD. 817 CSA Std. C22.2 NO.21 |
| DIMENSIONS | Power Shell: 9.05" x 2.16" (22.99 cm x 5.49 cm) |
| WEIGHT | 3 lb (1.36 kg) |
| DIELECTRIC STRENGTH | 1250Vac |
| INSULATION RESISTANCE | >100Mohms |

