

BZ7475 GEN PURPS RTU CLNR R17901 12QT/CS

Version 1.1

Revision Date 12/17/2014

Print Date 06/01/2015

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : BZ7475 GEN PURPS RTU CLNR R17901 12QT/CS

Material number : 00000000001041437

Manufacturer or supplier's details

Company : Zep Inc.

Address : 1310 Seaboard Industrial Blvd., NW
Atlanta, GA 30318

Telephone : 404-352-1680

Emergency telephone numbers
For SDS Information : Compliance Services 1-877-428-9937

For a Medical Emergency : 877-541-2016 Toll Free - All Calls Recorded

For a Transportation Emergency : CHEMTREC: 800-424-9300 - All Calls Recorded.
In the District of Columbia 202-483-7616

SECTION 2. HAZARDS IDENTIFICATION
Emergency Overview

Appearance	liquid
Colour	green
Odour	characteristic

GHS Classification

Skin corrosion : Category 1A

Serious eye damage : Category 1

GHS Label element

Hazard pictograms :



Signal word : Danger

Hazard statements : H314 Causes severe skin burns and eye damage.

Precautionary statements : **Prevention:**
P264 Wash skin thoroughly after handling.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

Response:
P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
P303 + P361 + P353 IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower.

BZ7475 GEN PURPS RTU CLNR R17901 12QT/CS

Version 1.1

Revision Date 12/17/2014

Print Date 06/01/2015

P304 + P340 + P310 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Immediately call a POISON CENTER or doctor/ physician.
 P305 + P351 + P338 + P310 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or doctor/ physician.
 P363 Wash contaminated clothing before reuse.

Storage:

P405 Store locked up.

Disposal:

P501 Dispose of contents/container in accordance with local regulation.

Potential Health Effects**Carcinogenicity:****IARC**

No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

ACGIH

Confirmed animal carcinogen with unknown relevance to humans

OSHA

2-butoxyethanol

111-76-2

No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP

No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

No hazardous ingredients

SECTION 4. FIRST AID MEASURES

General advice : Move out of dangerous area.
 Consult a physician.
 Show this safety data sheet to the doctor in attendance.
 Do not leave the victim unattended.

If inhaled : If unconscious place in recovery position and seek medical advice.
 If symptoms persist, call a physician.

In case of skin contact : Immediate medical treatment is necessary as untreated wounds from corrosion of the skin heal slowly and with difficulty.
 If on skin, rinse well with water.
 If on clothes, remove clothes.

BZ7475 GEN PURPS RTU CLNR R17901 12QT/CS

Version 1.1

Revision Date 12/17/2014

Print Date 06/01/2015

- In case of eye contact : Small amounts splashed into eyes can cause irreversible tissue damage and blindness.
In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
Continue rinsing eyes during transport to hospital.
Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
- If swallowed : Keep respiratory tract clear.
Do NOT induce vomiting.
Do not give milk or alcoholic beverages.
Never give anything by mouth to an unconscious person.
If symptoms persist, call a physician.
Take victim immediately to hospital.

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Dry chemical
Fire blanket
Foam
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during firefighting : Do not allow run-off from fire fighting to enter drains or water courses.
- Hazardous combustion products : No hazardous combustion products are known
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
- Further information : Collect contaminated fire extinguishing water separately. This must not be discharged into drains.
Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
- Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.
- Environmental precautions : Prevent product from entering drains.
Prevent further leakage or spillage if safe to do so.
If the product contaminates rivers and lakes or drains inform respective authorities.
- Methods and materials for : Neutralise with acid.

BZ7475 GEN PURPS RTU CLNR R17901 12QT/CS

Version 1.1

Revision Date 12/17/2014

Print Date 06/01/2015

containment and cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal.

SECTION 7. HANDLING AND STORAGE

Advice on safe handling : Do not breathe vapours/dust.
Avoid contact with skin and eyes.
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
To avoid spills during handling keep bottle on a metal tray.
Dispose of rinse water in accordance with local and national regulations.

Conditions for safe storage : Keep container tightly closed in a dry and well-ventilated place.
Observe label precautions.
Electrical installations / working materials must comply with the technological safety standards.

Materials to avoid : Oxidizing agents
Do not store near acids.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION
Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
2-butoxyethanol	111-76-2	TWA	20 ppm	ACGIH
		TWA	5 ppm 24 mg/m ³	NIOSH REL
		TWA	50 ppm 240 mg/m ³	OSHA Z-1
		TWA	25 ppm 120 mg/m ³	OSHA P0

Personal protective equipment

Respiratory protection : No personal respiratory protective equipment normally required.

Hand protection
Remarks : The suitability for a specific workplace should be discussed with the producers of the protective gloves.

Eye protection : Eye wash bottle with pure water
Tightly fitting safety goggles
Wear face-shield and protective suit for abnormal processing

BZ7475 GEN PURPS RTU CLNR R17901 12QT/CS

Version 1.1

Revision Date 12/17/2014

Print Date 06/01/2015

problems.

- Skin and body protection : impervious clothing
Choose body protection according to the amount and concentration of the dangerous substance at the work place.
- Hygiene measures : When using do not eat or drink.
When using do not smoke.
Wash hands before breaks and at the end of workday.
-

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

- Appearance : liquid
- Colour : green
- Odour : characteristic
- Odour Threshold : no data available
- pH : 11.5 - 12.5
- Melting point/freezing point : no data available
- Boiling point : 100 °C
- Flash point :
not applicable
- Evaporation rate : 1
- Upper explosion limit : no data available
- Lower explosion limit : no data available
- Vapour pressure : no data available
- Relative vapour density : no data available
- Density : 1.01 g/cm³
- Solubility(ies)
- Water solubility : soluble in cold water, soluble in hot water
- Partition coefficient: n-octanol/water : no data available
- Auto-ignition temperature : not determined
- Thermal decomposition : no data available
- Viscosity
- Viscosity, kinematic : no data available
-

SECTION 10. STABILITY AND REACTIVITY

- Reactivity : Stable
-

BZ7475 GEN PURPS RTU CLNR R17901 12QT/CS

Version 1.1

Revision Date 12/17/2014

Print Date 06/01/2015

Chemical stability	: Stable under normal conditions.
Possibility of hazardous reactions	: No decomposition if stored and applied as directed.
Conditions to avoid	: no data available
Incompatible materials	: Acids Strong oxidizing agents
Hazardous decomposition products	: Carbon dioxide (CO ₂)

SECTION 11. TOXICOLOGICAL INFORMATION**Acute toxicity****Product:**

Acute oral toxicity : Acute toxicity estimate : > 5,000 mg/kg
Method: Calculation method

Skin corrosion/irritation**Product:**

Remarks: Extremely corrosive and destructive to tissue.

Serious eye damage/eye irritation**Product:**

Remarks: May cause irreversible eye damage.

Respiratory or skin sensitisation

no data available

Germ cell mutagenicity

no data available

Carcinogenicity

no data available

Reproductive toxicity

no data available

STOT - single exposure

no data available

STOT - repeated exposure

no data available

Aspiration toxicity

no data available

Further information

BZ7475 GEN PURPS RTU CLNR R17901 12QT/CS

Version 1.1

Revision Date 12/17/2014

Print Date 06/01/2015

Product:

Remarks: no data available

SECTION 12. ECOLOGICAL INFORMATION**Ecotoxicity**

no data available

Persistence and degradability

no data available

Bioaccumulative potential**Product:**Partition coefficient: n-
octanol/water : Remarks: no data available**Mobility in soil**

no data available

Other adverse effects

no data available

Product:Regulation 40 CFR Protection of Environment; Part 82 Protection of
Stratospheric Ozone - CAA Section 602 Class I
SubstancesRemarks This product neither contains, nor was manufactured
with a Class I or Class II ODS as defined by the U.S.
Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A
+ B).Additional ecological : no data available
information

SECTION 13. DISPOSAL CONSIDERATIONS**Disposal methods**Waste from residues : Do not dispose of waste into sewer.
Do not contaminate ponds, waterways or ditches with
chemical or used container.
Dispose of in accordance with local regulations.Contaminated packaging : Empty remaining contents.
Dispose of as unused product.
Do not re-use empty containers.

BZ7475 GEN PURPS RTU CLNR R17901 12QT/CS

Version 1.1

Revision Date 12/17/2014

Print Date 06/01/2015

SECTION 14. TRANSPORT INFORMATION
International regulation
UNRTDG

Not regulated as a dangerous good

IATA-DGR

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable for product as supplied.

National Regulations
49 CFR

Not regulated as a dangerous good

Special precautions for user

not applicable

SECTION 15. REGULATORY INFORMATION
EPCRA - Emergency Planning and Community Right-to-Know Act
CERCLA Reportable Quantity

Components	CAS-No.	Component RQ (lbs)	Calculated product RQ (lbs)
sodium hydroxide	1310-73-2	1000	*

*: Calculated RQ exceeds reasonably attainable upper limit.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Acute Health Hazard

SARA 302 : SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop 65 : This product does not contain any chemicals known to State of

BZ7475 GEN PURPS RTU CLNR R17901 12QT/CS

Version 1.1

Revision Date 12/17/2014

Print Date 06/01/2015

California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

- TSCA** On TSCA Inventory
- DSL** This product contains one or several components that are not on the Canadian DSL nor NDSL.
- AICS** Not in compliance with the inventory
- NZIoC** Not in compliance with the inventory
- PICCS** Not in compliance with the inventory
- IECSC** Not in compliance with the inventory


Inventory Acronym and Validity Area Legend:

AICS (Australia), DSL (Canada), IECSC (China), REACH (European Union), ENCS (Japan), ISHL (Japan), KECI (Korea), NZIoC (New Zealand), PICCS (Philippines), TSCA (USA)

SECTION 16. OTHER INFORMATION

Further information

NFPA:



HMIS III:

HEALTH	3
FLAMMABILITY	0
PHYSICAL HAZARD	0

0 = not significant, 1 =Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA GHS Label Information:

Hazard pictograms :



Signal word : **Danger:**
Hazard statements : Causes severe skin burns and eye damage.
Precautionary statements :

Prevention: Wash skin thoroughly after handling. Wear protective gloves/ protective clothing/ eye protection/ face protection.
Response: IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Immediately call a POISON CENTER or doctor/ physician. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or doctor/ physician. Wash contaminated clothing before reuse.
Storage: Store locked up.
Disposal: Dispose of contents/container in accordance with local regulation.

BZ7475 GEN PURPS RTU CLNR R17901 12QT/CS

Version 1.1

Revision Date 12/17/2014

Print Date 06/01/2015

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®, Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®, Rexodan®, Mykal™, and a number of private labeled brands.