

**ZEP CHERRY BOMB HC\_4CS 48OZ**

Version 5.1

Revision Date 02/27/2018

Print Date 12/10/2021

**SECTION 1. PRODUCT AND COMPANY IDENTIFICATION**

Material name : ZEP CHERRY BOMB HC\_4CS 48OZ

Material number : ZUCBHC484

**Manufacturer or supplier's details**

Company : Zep Inc.

Address : 350 Joe Frank Harris Parkway, SE  
Emerson, GA 30137

Telephone : 404-352-1680

**Emergency telephone numbers**
**For SDS Information** : Compliance Services 1-877-428-9937

**For a Medical Emergency** : 877-541-2016 Toll Free - All Calls Recorded

**For a Transportation Emergency** : CHEMTREC: 800-424-9300 - All Calls Recorded.  
In the District of Columbia 202-483-7616

**Recommended use of the chemical and restrictions on use**

Recommended use : Hand Care

**SECTION 2. HAZARDS IDENTIFICATION**
**Emergency Overview**

Appearance	viscous, liquid
Colour	red
Odour	like fruit

**GHS Classification**

Not a hazardous substance or mixture.

**GHS label elements**

Not a hazardous substance or mixture.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Substance / Mixture : Mixture

**Hazardous components**

Chemical name	CAS-No.	Concentration [%]
Distillates (petroleum), hydrotreated light	64742-47-8	>= 20 - < 30
4-Nonylphenol branched, ethoxylated	127087-87-0	>= 10 - < 20
2-aminoethanol Tallate	68440-25-5	>= 1 - < 5
White mineral oil (petroleum)	8042-47-5	>= 1 - < 5
Solvent naphtha (petroleum), heavy aliph.	64742-96-7	>= 1 - < 5
Poly(oxy-1,2-ethanediyl), .alpha.-hydro.-omega.-	25322-68-3	>= 1 - < 5

**ZEP CHERRY BOMB HC\_4CS 48OZ**

Version 5.1

Revision Date 02/27/2018

Print Date 12/10/2021

hydroxy-Ethane-1,2-diol, ethoxylated	
--------------------------------------	--

The exact percentages of disclosed substances are withheld as trade secrets.

**SECTION 4. FIRST AID MEASURES**

- |   |  |
|---|--|
| General advice  | : Move out of dangerous area.<br>Show this safety data sheet to the doctor in attendance.<br>Do not leave the victim unattended.   |
| If inhaled  | : If unconscious, place in recovery position and seek medical advice.<br>If symptoms persist, call a physician.  |
| In case of skin contact                                     | : This product is formulated for use on skin but should always be immediately washed off with plenty of water. Discontinue use if irritation and redness develop. If conditions persist for more than 72 hours, consult a physician. |
| In case of eye contact                                      | : Rinse immediately with plenty of water for at least 15 minutes.<br>Remove contact lenses.<br>Protect unharmed eye.<br>Keep eye wide open while rinsing.<br>If eye irritation persists, consult a specialist.                       |
| If swallowed  | : Keep respiratory tract clear.<br>DO NOT induce vomiting unless directed to do so by a physician or poison control center.<br>Never give anything by mouth to an unconscious person.<br>If symptoms persist, call a physician.      |
| Most important symptoms and effects, both acute and delayed | : Effects may be delayed, symptoms may include minor eye or skin irritation.<br>Overexposure may cause mild eye or skin irritation.  |
| Notes to physician  | : Treat symptomatically. Symptoms may be delayed.  |

**SECTION 5. FIREFIGHTING MEASURES**

- |                                      |  |
|--------------------------------------|--|
| Suitable extinguishing media         | : Alcohol-resistant foam<br>Carbon dioxide (CO <sub>2</sub> )<br>Dry chemical<br>Water spray jet |
| Unsuitable extinguishing media       | : High volume water jet  |
| Specific hazards during firefighting | : Do not allow run-off from fire fighting to enter drains or water courses.                      |
| Hazardous combustion products        | : Carbon dioxide (CO <sub>2</sub> )<br>Carbon monoxide<br>Smoke                                  |
| Specific extinguishing               | : Use extinguishing measures that are appropriate to local                                       |

**ZEP CHERRY BOMB HC\_4CS 48OZ**

Version 5.1

Revision Date 02/27/2018

Print Date 12/10/2021

methods	circumstances and the surrounding environment.
Further information	: Collect contaminated fire extinguishing water separately. This must not be discharged into drains. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
Special protective equipment for firefighters	: Wear self-contained breathing apparatus for firefighting if necessary.

**SECTION 6. ACCIDENTAL RELEASE MEASURES**

Personal precautions, protective equipment and emergency procedures	: Material can create slippery conditions. Use non-slip safety shoes in areas where spills or leaks can occur. Refer to protective measures listed in sections 7 and 8.
Environmental precautions	: Prevent product from entering drains. Prevent further leakage or spillage if safe to do so. If the product contaminates rivers and lakes or drains inform respective authorities.
Methods and materials for containment and cleaning up	: Wipe up with absorbent material (e.g. cloth, fleece). Keep in suitable, closed containers for disposal.

**SECTION 7. HANDLING AND STORAGE**

Advice on safe handling	: Avoid contact with eyes. For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area. Dispose of rinse water in accordance with local and national regulations.
Conditions for safe storage	: Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage.
Materials to avoid	: Oxidizing agents

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**
**Components with workplace control parameters**

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Distillates (petroleum), hydrotreated light	64742-47-8	TWA	500 ppm 2,000 mg/m <sup>3</sup>	OSHA Z-1
		TWA	400 ppm	OSHA P0

**ZEP CHERRY BOMB HC\_4CS 48OZ**

Version 5.1

Revision Date 02/27/2018

Print Date 12/10/2021

			1,600 mg/m3	
		TWA (Mist)	5 mg/m3	OSHA Z-1
		TWA (Mist)	5 mg/m3	OSHA P0
		TWA (Mist)	5 mg/m3	NIOSH REL
		ST (Mist)	10 mg/m3	NIOSH REL
		PEL (particulate)	5 mg/m3	CAL PEL
White mineral oil (petroleum)	8042-47-5	TWA (Mist)	5 mg/m3	
		STEL (Mist)	10 mg/m3	
		TWA (Mist)	5 mg/m3	OSHA Z-1
		TWA (Inhalable fraction)	5 mg/m3	ACGIH
		TWA (Mist)	5 mg/m3	OSHA P0
		TWA (Mist)	5 mg/m3	NIOSH REL
		ST (Mist)	10 mg/m3	NIOSH REL
		PEL (particulate)	5 mg/m3	CAL PEL
Poly(oxy-1,2-ethanediyl), .alpha.-hydro-.omega.- hydroxy-Ethane-1,2-diol, ethoxylated	25322-68-3	TWA (aerosol)	10 mg/m3	US WEEL
			10 mg/m3	US WEEL

**Engineering measures** : effective ventilation in all processing areas

**Personal protective equipment**

Respiratory protection : No personal respiratory protective equipment normally required.

Hand protection

Remarks

: No special protection is required.

Eye protection

: Eye protection is not required while washing with this product. In the workplace, the use of safety glasses is recommended to avoid eye exposure during the handling of containers or during spill clean-up.

Skin and body protection

: No special protection is required.

Hygiene measures

: When using do not eat or drink.  
When using do not smoke.  
Wash hands before breaks and at the end of workday.

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

Appearance : viscous, liquid

Colour : red

Odour : like fruit

**ZEP CHERRY BOMB HC\_4CS 48OZ**

Version 5.1

Revision Date 02/27/2018

Print Date 12/10/2021

Odour Threshold	: No data available
pH	: 7 - 8
Melting point/freezing point	: No data available
Boiling point	: No data available
Flash point	: > 93.3 °C Method: TCC
Evaporation rate	: No data available
Upper explosion limit	: No data available
Lower explosion limit	: No data available
Vapour pressure	: No data available
Relative vapour density	: No data available
Density	: 0.96 g/cm <sup>3</sup>
Solubility(ies)	
Water solubility	: slightly soluble
Solubility in other solvents	: not determined
Partition coefficient: n-octanol/water	: No data available
Auto-ignition temperature	: not determined
Thermal decomposition	: No data available
Viscosity	
Viscosity, kinematic	: > 25 mm <sup>2</sup> /s (40 °C)

---

**SECTION 10. STABILITY AND REACTIVITY**

Reactivity	: Stable
Chemical stability	: Stable under normal conditions.
Possibility of hazardous reactions	: No decomposition if stored and applied as directed.
Conditions to avoid	: No data available
Incompatible materials	: Oxidizing agents
Hazardous decomposition products	: Carbon oxides

---

**SECTION 11. TOXICOLOGICAL INFORMATION****Potential Health Effects**

**ZEP CHERRY BOMB HC\_4CS 48OZ**

Version 5.1

Revision Date 02/27/2018

Print Date 12/10/2021

Aggravated Medical Condition : None known.  
Symptoms of Overexposure : Effects may be delayed, symptoms may include minor eye or skin irritation.

**Carcinogenicity:**

**IARC** No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.  
**ACGIH** No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.  
**OSHA** No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.  
**NTP** No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

**Acute toxicity****Product:**

Acute oral toxicity : Acute toxicity estimate : > 5,000 mg/kg  
Method: Calculation method  
Acute dermal toxicity : Acute toxicity estimate : > 5,000 mg/kg  
Method: Calculation method

**Components:****Distillates (petroleum), hydrotreated light:**

Acute oral toxicity : LD50 Rat: > 5,000 mg/kg  
Acute inhalation toxicity : LC50 Rat: > 4.6 mg/l  
Exposure time: 6 h  
Acute dermal toxicity : LD50 Rat: > 2,000 mg/kg

**4-Nonylphenol branched, ethoxylated:**

Acute oral toxicity : LD50 Oral Rat: 16,000 mg/kg  
Acute dermal toxicity : LD50 Rabbit: 2,573 mg/kg

**Skin corrosion/irritation****Product:**

Result: No skin irritation

**Serious eye damage/eye irritation****Product:**

**ZEP CHERRY BOMB HC\_4CS 48OZ**

Version 5.1

Revision Date 02/27/2018

Print Date 12/10/2021

Result: No eye irritation

**Respiratory or skin sensitisation**

No data available

**Germ cell mutagenicity**

No data available

**Carcinogenicity**

No data available

**Reproductive toxicity**

No data available

**STOT - single exposure**

No data available

**STOT - repeated exposure**

No data available

**Aspiration toxicity**

No data available

**Further information****Product:**

Remarks: No data available

**Components:****Distillates (petroleum), hydrotreated light:**

Remarks: No data available

---

**SECTION 12. ECOLOGICAL INFORMATION****Ecotoxicity**

No data available

**Persistence and degradability**

No data available

**Bioaccumulative potential****Product:**Partition coefficient: n- : Remarks: No data available  
octanol/water**Mobility in soil**

No data available

**Other adverse effects**

**ZEP CHERRY BOMB HC\_4CS 48OZ**

Version 5.1

Revision Date 02/27/2018

Print Date 12/10/2021

No data available

**Product:**

Regulation 40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

Remarks This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information : No data available

**Components:****Distillates (petroleum), hydrotreated light :**

Additional ecological information : No data available

---

**SECTION 13. DISPOSAL CONSIDERATIONS****Disposal methods**

Waste from residues : The product should not be allowed to enter drains, water courses or the soil.  
Do not contaminate ponds, waterways or ditches with chemical or used container.  
Dispose of in accordance with local regulations.

Contaminated packaging : Empty remaining contents.  
Dispose of as unused product.  
Do not re-use empty containers.

---

**SECTION 14. TRANSPORT INFORMATION**

Transportation Regulation: 49 CFR (USA): NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL
--

Transportation Regulation: IMDG (Vessel): NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL
---

Transportation Regulation: IATA (Cargo Air): NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL
--

Transportation Regulation: IATA (Passenger Air): NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL
--

Transportation Regulation: TDG (Canada):
--



**ZEP CHERRY BOMB HC\_4CS 48OZ**

Version 5.1

Revision Date 02/27/2018

Print Date 12/10/2021

NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL
--

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

---

**SECTION 15. REGULATORY INFORMATION**

**TSCA list** : No substances are subject to a Significant New Use Rule.

No substances are subject to TSCA 12(b) export notification requirements.

**EPCRA - Emergency Planning and Community Right-to-Know Act****CERCLA Reportable Quantity**

This material does not contain any components with a CERCLA RQ.

**SARA 304 Extremely Hazardous Substances Reportable Quantity**

This material does not contain any components with a section 304 EHS RQ.

**SARA 311/312 Hazards** : No SARA Hazards

**SARA 302** : The following components are subject to reporting levels established by SARA Title III, Section 302:

Pumice	1332-09-8	2.59 %
--------	-----------	--------

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

**SARA 313** : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

**California Prop. 65**

This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

**The components of this product are reported in the following inventories:**

**TSCA** : On TSCA Inventory  
**DSL** : All components of this product are on the Canadian DSL

For information on the country notification status for other regions please contact the manufacturer's regulatory group.

**ZEP CHERRY BOMB HC\_4CS 48OZ**


Version 5.1

Revision Date 02/27/2018

Print Date 12/10/2021

**Inventory Acronym and Validity Area Legend:**

TSCA (USA), DSL (Canada), NDSL (Canada)

**SECTION 16. OTHER INFORMATION****Further information****NFPA:****HMIS III:**

<b>HEALTH</b>	<b>0</b>
<b>FLAMMABILITY</b>	<b>1</b>
<b>PHYSICAL HAZARD</b>	<b>0</b>

0 = not significant, 1 = Slight,  
 2 = Moderate, 3 = High  
 4 = Extreme, \* = Chronic

**OSHA - GHS Label Information:**

Not a hazardous substance or mixture.

Version:	5.1
Revision Date:	02/27/2018
Print Date:	12/10/2021

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®, Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®, Rexodan®, Mykal™, and a number of private labeled brands.