

CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Version 3.0

Revision Date 07/17/2018

Print Date 05/07/2019

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Material number : ZUCIT128

Manufacturer or supplier's details

Company : Zep Inc.

Address : 350 Joe Frank Harris Parkway, SE
Emerson, GA 30137

Telephone : 404-352-1680

Emergency telephone numbers**For SDS Information** : Compliance Services 1-877-428-9937**For a Medical Emergency** : 877-541-2016 Toll Free - All Calls Recorded**For a Transportation** : CHEMTREC: 800-424-9300 - All Calls Recorded.**Emergency** : In the District of Columbia 202-483-7616**Recommended use of the chemical and restrictions on use**

Recommended use : Cleaner

Note: This product is labeled as a consumer product in accordance with the United States Consumer Product Safety Commission regulations. The warnings presented below in this Safety Data Sheet (SDS) comply with the 2012 OSHA Hazard Communication Standard (GHS - Globally Harmonized System of Classification and Labeling). The requirements for the labeling and warnings of consumer products may differ from those required for GHS based hazard communication.

SECTION 2. HAZARDS IDENTIFICATION**Emergency Overview**

Appearance	liquid
Colour	orange
Odour	characteristic

GHS Classification

Flammable liquids : Category 4
 Eye irritation : Category 2A
 Skin sensitisation : Category 1

GHS label elements

Hazard pictograms :



Signal word : Warning

Hazard statements : H227 Combustible liquid.
 H317 May cause an allergic skin reaction.

CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Version 3.0

Revision Date 07/17/2018

Print Date 05/07/2019

H319 Causes serious eye irritation.

Precautionary statements

: **Prevention:**

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P261 Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.

P264 Wash skin thoroughly after handling.

P272 Contaminated work clothing should not be allowed out of the workplace.

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

Response:

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P333 + P313 If skin irritation or rash occurs: Get medical advice/ attention.

P337 + P313 If eye irritation persists: Get medical advice/ attention.

P362 + P364 Take off contaminated clothing and wash it before reuse.

P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish.

Storage:

P403 + P235 Store in a well-ventilated place. Keep cool.

Disposal:

P501 Dispose of contents/container in accordance with local regulation.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical name	CAS-No.	Concentration [%]
Alcohols, C9-11, ethoxylated	68439-46-3	>= 1 - < 5
Citrus, ext.	94266-47-4	>= 1 - < 5

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

General advice

: Move out of dangerous area.
Show this safety data sheet to the doctor in attendance.
Do not leave the victim unattended.
Get medical attention.

If inhaled

: If unconscious, place in recovery position and seek medical advice.
If symptoms persist, call a physician.

CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Version 3.0

Revision Date 07/17/2018

Print Date 05/07/2019

- In case of skin contact : Wash off immediately with plenty of water for at least 15 minutes.
Remove contaminated clothing and shoes.
Wash contaminated clothing before reuse.
If skin irritation persists, call a physician.
- In case of eye contact : Continue rinsing eyes during transport to hospital.
Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.
- If swallowed : Keep respiratory tract clear.
DO NOT induce vomiting unless directed to do so by a physician or poison control center.
Never give anything by mouth to an unconscious person.
If symptoms persist, call a physician.
Do not give milk or alcoholic beverages.
- Most important symptoms and effects, both acute and delayed : Effects are immediate and delayed.
Symptoms may include irritation, redness, pain, and rash.
Effects are dependent on exposure (dose, concentration, contact time).
May cause an allergic skin reaction.
Causes serious eye irritation.
Review section 2 of SDS to see all potential hazards.
- Notes to physician : Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during firefighting : Do not allow run-off from fire fighting to enter drains or water courses.
- Hazardous combustion products : Carbon dioxide (CO₂)
Carbon monoxide
Smoke
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
- Further information : Collect contaminated fire extinguishing water separately. This must not be discharged into drains.
Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
Standard procedure for chemical fires.

CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Version 3.0

Revision Date 07/17/2018

Print Date 05/07/2019

Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.

Environmental precautions : Prevent product from entering drains. Prevent further leakage or spillage if safe to do so. If the product contaminates rivers and lakes or drains inform respective authorities.

Methods and materials for containment and cleaning up : Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13). Keep in suitable, closed containers for disposal.

SECTION 7. HANDLING AND STORAGE

Advice on safe handling : Do not breathe vapours or spray mist. Avoid contact with skin and eyes. For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area. Take precautionary measures against static discharges. Provide sufficient air exchange and/or exhaust in work rooms. Dispose of rinse water in accordance with local and national regulations. Persons susceptible to skin sensitisation problems or asthma, allergies, chronic or recurrent respiratory disease should not be employed in any process in which this mixture is being used.

Conditions for safe storage : Keep in a well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage. Observe label precautions. Keep away from sources of ignition - No smoking. Electrical installations / working materials must comply with the technological safety standards.

Materials to avoid : Do not store near acids. Oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Components with workplace control parameters**

Contains no substances with occupational exposure limit values.

CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Version 3.0

Revision Date 07/17/2018

Print Date 05/07/2019

Engineering measures : effective ventilation in all processing areas

Personal protective equipment

Respiratory protection : Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.

Hand protection

Material : Protective gloves

Remarks : The suitability for a specific workplace should be discussed with the producers of the protective gloves.

Eye protection

: Access to clean water to rinse eyes must be available, options include: eye wash stations or showers, or eye wash bottles with pure water.
Tightly fitting safety goggles
Wear face-shield and protective suit for abnormal processing problems.

Skin and body protection

: Impervious clothing
Choose body protection according to the amount and concentration of the dangerous substance at the work place.

Hygiene measures

: When using do not eat or drink.
When using do not smoke.
Wash hands before breaks and at the end of workday.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : liquid

Colour : orange

Odour : characteristic

Odour Threshold : No data available

pH : 11 - 12

Melting point/freezing point : No data available

Boiling point : 100 °C

Flash point : 67.7 °C
Method: TCC

Evaporation rate : No data available

Upper explosion limit : No data available

Lower explosion limit : No data available

Vapour pressure : No data available

Relative vapour density : No data available

CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Version 3.0

Revision Date 07/17/2018

Print Date 05/07/2019

Density	: 1.003 g/cm ³
Solubility(ies)	
Water solubility	: soluble
Solubility in other solvents	: not determined
Partition coefficient: n-octanol/water	: No data available
Auto-ignition temperature	: not determined
Thermal decomposition	: No data available
Viscosity	
Viscosity, kinematic	: No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity	: Stable
Chemical stability	: Stable under normal conditions.
Possibility of hazardous reactions	: Vapours may form explosive mixture with air. No decomposition if stored and applied as directed.
Conditions to avoid	: Heat, flames and sparks.
Incompatible materials	: Oxidizing agents
Hazardous decomposition products	: Carbon monoxide, carbon dioxide and unburned hydrocarbons (smoke).

SECTION 11. TOXICOLOGICAL INFORMATION**Potential Health Effects**

Aggravated Medical Condition	: None known.
Symptoms of Overexposure	: Effects are immediate and delayed. Symptoms may include irritation, redness, pain, and rash. Effects are dependent on exposure (dose, concentration, contact time).

Carcinogenicity:**IARC**

No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

ACGIH

No component of this product present at levels greater than or

CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Version 3.0

Revision Date 07/17/2018

Print Date 05/07/2019

OSHA

equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.

NTP

No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Acute toxicity**Product:**

Acute oral toxicity : Acute toxicity estimate : > 5,000 mg/kg
Method: Calculation method

Components:**Alcohols, C9-11, ethoxylated:**

Acute oral toxicity : LD50 Oral Rat: 1,400 mg/kg

Skin corrosion/irritation**Product:**

Remarks: May irritate skin.

Serious eye damage/eye irritation**Product:**

Remarks: Irritating to eyes.

Respiratory or skin sensitisation**Product:**

Remarks: Causes sensitisation.

Assessment: Moderate skin irritation

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Version 3.0

Revision Date 07/17/2018

Print Date 05/07/2019

No data available

Further information**Product:**

Remarks: No data available

SECTION 12. ECOLOGICAL INFORMATION**Ecotoxicity****Components:****Citrus, ext. :**

Toxicity to fish : LC50 (Fish): 0.1 - 1.0 mg/l
Remarks: Information taken from reference works and the literature.

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): 0.1 - 1.0 mg/l
Remarks: Information taken from reference works and the literature.

Persistence and degradability**Components:****Citrus, ext. :**

Biodegradability : Remarks: Readily biodegradable
Information taken from reference works and the literature.

Bioaccumulative potential**Product:**

Partition coefficient: n-octanol/water : Remarks: No data available

Components:**Citrus, ext. :**

Bioaccumulation : Bioconcentration factor (BCF): < 2,000
Remarks: Information taken from reference works and the literature.

Mobility in soil

No data available

Other adverse effects**Product:**

Regulation 40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Version 3.0

Revision Date 07/17/2018

Print Date 05/07/2019

Remarks : This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information : Not applicable

Components:**Citrus, ext. :**

Results of PBT and vPvB assessment : This substance is not considered to be persistent, bioaccumulating and toxic (PBT)., Remarks: Information taken from reference works and the literature.

SECTION 13. DISPOSAL CONSIDERATIONS**Disposal methods**

Waste from residues : The product should not be allowed to enter drains, water courses or the soil.
Do not contaminate ponds, waterways or ditches with chemical or used container.
Dispose of in accordance with local regulations.

Contaminated packaging : Empty remaining contents.
Dispose of as unused product.
Do not re-use empty containers.
Do not burn, or use a cutting torch on, the empty drum.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IMDG (Vessel):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Cargo Air):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Passenger Air):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: TDG (Canada):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Version 3.0

Revision Date 07/17/2018

Print Date 05/07/2019

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SECTION 15. REGULATORY INFORMATION

TSCA list : No substances are subject to a Significant New Use Rule.

No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act
CERCLA Reportable Quantity

Components	CAS-No.	Component RQ (lbs)	Calculated product RQ (lbs)
sodium hydroxide	1310-73-2	1000	*

*: Calculated RQ exceeds reasonably attainable upper limit.

CERCLA Reportable Quantity

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Flammable (gases, aerosols, liquids, or solids)
Respiratory or skin sensitisation
Serious eye damage or eye irritation

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop. 65

This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

DSL All components of this product are on the Canadian DSL
TSCA On TSCA Inventory

CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Version 3.0


Revision Date 07/17/2018

Print Date 05/07/2019

For information on the country notification status for other regions please contact the manufacturer's regulatory group.

Inventory Acronym and Validity Area Legend:

TSCA (USA), DSL (Canada), NDSL (Canada)

SECTION 16. OTHER INFORMATION
Further information
NFPA:

HMIS III:

HEALTH	3
FLAMMABILITY	2
PHYSICAL HAZARD	0

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA - GHS Label Information:

Hazard pictograms



Signal word

: **Warning:**

Hazard statements

: Combustible liquid. May cause an allergic skin reaction. Causes serious eye irritation.

Precautionary statements

:

Prevention: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray. Wash skin thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves/ protective clothing/ eye protection/ face protection.

Response: IF ON SKIN: Wash with plenty of soap and water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation or rash occurs: Get medical advice/ attention. If eye irritation persists: Get medical advice/ attention. Take off contaminated clothing and wash it before reuse. In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish.

Storage: Store in a well-ventilated place. Keep cool.

Disposal: Dispose of contents/container in accordance with local regulation.

Version:	3.0
Revision Date:	07/17/2018
Print Date:	05/07/2019

CONCENTRTD HVY-DTY CIT DEG & CLNR 128 OZ

Version 3.0

Revision Date 07/17/2018

Print Date 05/07/2019

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®, Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®, Rexodan®, Mykal™, and a number of private labeled brands.